

Law Enforcement Safety

Made for the Mission.

3M's safety and communications solutions for law enforcement help to serve your challenging safety needs for SWAT, Firearms Training, Department of Corrections, Evidence Response Team, and Explosive Ordnance Disposal applications.



Tactical
Communication
Headsets



Electronic
Earplugs



Earmuffs



Earplugs



Protective
Eyewear



Half Face
Respirators



Full Face
Respirators



Powered Air
Purifying
Respirators
(PAPRs)



SCBA

Support that goes beyond.

3M is more than just high-quality, reliable products. Thanks to our long-standing and active involvement in the law enforcement industry for many decades, our product specialists can support your team's technical, regulatory, application, and training needs.



Training & Education



Innovative Technology



Regulatory Knowledge



Global Safety Provider



Mission First.

For over 75 years, 3M has been delivering innovative protective solutions to law enforcement personnel, committed to helping increase effectiveness and safety in dangerous, high-risk environments.

Mission Ready.

Fueled by proprietary technologies and innovative designs, 3M's holistic solutions help address unique requirements across various law enforcement applications.

Mission Effective.

3M's personal protective solutions are designed and perfected to help improve survivability, communications, and safety in multi-threat operations.



SWAT

The multi-faceted and high-risk nature of SWAT operations requires proper resources, training, and equipment. 3M is proud to support law enforcement professionals with protective equipment that helps them stay safe and focused.

3M™ PELTOR™ ComTac™ VII Headset (TMAS)



3M™ PELTOR™ ComTac™ VIII Headset

The trusted and proven standard for communications and hearing protection worldwide.

- Environmental listening, featuring 3M Mission Audio Profiles (MAP), helps maintain auditory situational awareness.
- Soundscaping to help with radio communication speech intelligibility.
- Earplug mode to help maintain auditory situational awareness when used in combination with earplugs.



3M™ PELTOR™ Tactical Modular Audio System (TMAS)

The 3M™ PELTOR™ communication system helps effectively communicate in dynamic noise environments.

- Near Field Magnetic Induction (NFI) allows for wireless transmission of audio to headsets and/or earpieces.
- 3M Natural Interaction Behavior (NIB) technology enables intra-team communication in high-noise environments.
- Includes features of 3M™ PELTOR™ ComTac™ VIII Headset.



3M™ Scott™ ProPak SCBA + Promask PP

A firefighting-rated CBRN certified SCBA ensemble for challenging environments. Select ProPak-f or height-adjustable ProPak-fx with Promask PP.

- ProPak is EN 137 Type-2 certified.
- Promask PP is EN 136 Class 3 certified.
- ProPak with Promask is an AS/NZS 1716:2012 certified ensemble.
- ProPak-f/fx + Promask PP is BS 8468-1:2020 CBRN certified.



3M™ Scott™ M95 & M98 Civil Defense Respirators

Designed for civil defense, law enforcement and public order applications.

- 3M™ M95 & M98 are EN 136 Class 3 certified.
- Tested against CWA's (CBRN) and riot control agents.
- EN 148-1 DIN40 filter connection.
- Built-in hydration port
- CBRN and riot control canisters available.
- M98 features speech diaphragm and panoramic visor.



3M™ SecureFit™ Protective Eyewear 500 Series

Contemporary safety glasses featuring a streamlined lens shape.

- 3M™ Pressure Diffusion Temple Technology provides comfortable pressure equalization.
- Anti-Fog/Anti-Scratch Coating helps minimize lens fogging.

Firearms Training

3M's broad portfolio of personal protective equipment can help minimize life-threatening injuries or fatal accidents during demanding law enforcement training, including firearm drills, fieldwork, crowd control, self-defense, arrest tactics, and more.

3M™ PELTOR™ ComTac™ VIII Headset



3M™ PELTOR™ ProTac Shooter Headset

Helps protect against hazardous, impulse, and nuisance noise.

- Professional-quality hearing protection.
- Environmental microphones for level-dependent hearing protection and ambient listening.



3M™ PELTOR™ Tactical Earplug TEP-200

Compact in-ear hearing protection.

- Rechargeable electronic earplugs help reduce loud noise while amplifying low-level sounds.
- Integrated with level-dependent technology that helps provide situational awareness.



3M™ PELTOR™ ComTac™ VII Headset

The trusted and proven standard for communications and hearing protection worldwide.

- 3M Natural Interaction Behavior (NIB) technology enables intra-team communication in high-noise environments.
- The System Control Unit (SCU-300) can be remotely operated via the Remote Control Unit (RCU-300), both included.
- Earplug mode to help maintain auditory situational awareness when used in combination with earplugs.



3M™ PELTOR™ ComTac™ VIII Hearing Defender

Protects hearing and promotes auditory situational awareness and communications in challenging environments.

- Advanced listening mode featuring Mission Audio Profiles (MAP) to maximise audibility based on the acoustical environment.
- Hearing protection to help protect from impulse and steady state noise.



3M™ SecureFit™ 500 Series Safety Glasses

Innovative temple design features slotted ribs that provide comfortable pressure equalisation.

- 3M™ Pressure Diffusion Temple (PDT) technology provides a more personalised fit.
- Curved temples help achieve a comfortable fit even during rapid head movement.

Department of Corrections

Risk management and mitigation is an integral component of ensuring opportune and effective rehabilitative interventions. 3M's protective equipment can help corrections workers mitigate injuries and illnesses caused by operational violence or exposure to hazardous substances.



3M™ PELTOR™ ComTac™ VIII Headset

The trusted and proven standard for communications and hearing protection worldwide.

- Environmental listening, featuring 3M Mission Audio Profiles (MAP), helps maintain auditory situational awareness.
- Soundscaping to help with radio communication speech intelligibility.
- Earplug mode to help maintain auditory situational awareness when used in combination with earplugs.



3M™ Scott™ M95 & M98 Civil Defense Respirators

Designed for civil defense, law enforcement and public order applications.

- 3M™ M95 & M98 are EN 136 Class 3 certified.
- Tested against CWA's (CBRN) and riot control agents.
- EN 148-1 DIN40 filter connection.
- Built-in hydration port
- CBRN and riot control canisters available.
- M98 features speech diaphragm and panoramic visor.



3M™ Scott™ AV-3000 HT Facepiece with Air Purifying Canister

Proven performance against occupational hazards.

- Air-purifying canisters, cartridges, and filters for use with 3M™ Scott™ Facepieces.
- 3M™ Scott™ Canisters where exposure to tear gases, pepper spray, and CBRN agents may exist in riot and crowd control operations.



3M™ Scott™ ProPak SCBA + Promask PP

A firefighting-rated CBRN certified SCBA ensemble for challenging environments. Select ProPak-f or height-adjustable ProPak-fx with Promask PP.

- ProPak is EN 137 Type-2 certified
- Promask PP is EN 136 Class 3 certified
- ProPak with Promask is AS/ NZS 1716 certified
- ProPak-f/fx + Promask PP is BS 8468-1:2020 CBRN certified



3M™ Aura™ Particulate Respirator 9322A+, P2

A flat fold, valved N95 respirator

- Unique three-panel design fits a wide range of face shapes/sizes and accommodates facial movements while talking.
- 3M™ Cool Flow™ Exhalation Valve helps release warm and moist exhaled breath from inside the respirator.

Evidence Response Team

3M provides a wide spectrum of personal protective equipment to help ensure health and safety procedures are met when arriving at complex and catastrophic crime scenes and while handling hazardous materials.

3M™ Protective
Coverall 4570



3M™ Secure Click™ Full Facepiece Reusable Respirator FF-800 Series

3M's newest line of reusable respirators for comfort, breathability, and simplicity.

- Compatible with a wide variety of approved 3M™ Secure Click™ cartridges and filters.
- Helps protect law enforcement personnel against a wide variety of particulate, gas, and vapor respiratory hazards.



3M™ Versaflo™ TR-600 Series PAPR

Designed to help protect against particulates, certain organic vapors and acid gases.

- Compatible with the 3M™ Versaflo™ family of components.
- Features adjustable airflow options and an expanded range of filters and cartridges.



3M™ Ultimate FX FF-400 Series Full Facepiece Respirators with 3M™ Multi-gas Cartridge Filter 6099 A2B2E2K2HgFormP3

- Silicone face seal helps provide comfort and durability, and is easy to clean.
- Filter protects for organic, inorganic, acid, mercury gases, and dust and particles.




3M™ GoggleGear™ 500 Series

Fog-resistant safety goggles designed to seal to the face and help operate effectively in hot and humid conditions or climate-controlled areas.

- 3M™ Scotchgard™ Protector Anti-Fog Coating helps minimise lens fogging and provide scratch resistance.
- Features a low-profile design with an adjustable strap and indirect ventilation.

Explosive Ordnance Disposal

For technicians responsible for the detection, field evaluations, and disposal of unexploded ordnances and munitions, protective measures are a priority. 3M offers reliable and innovative safety solutions to help ensure EOD personnel can respond to incidents and emergency events with confidence in their equipment.



3M™ PELTOR™ Tactical Earplug TEP-300

- Near Field Magnetic Induction (NFI)
- Wireless connection to 3M™ PELTOR™ System control Units, SCU-300 - IP68 Water and Dust Resistant
- In Ear Speech Microphone



3M™ Scott™ M95 & M98 Civil Defense Respirators

Designed for civil defense, law enforcement & public order applications.

- M95 & M98 are EN 136 Class 3 certified
- Tested against CWA's and riot control agents
- EN 148-1 DIN40 filter connection
- Built-in hydration port
- CBRN and riot control cannisters available



3M™ Scott™ ProPak SCBA + Promask

A firefighting-rated CBRN certified SCBA ensemble for challenging environments. Select ProPak-fx or height-adjustable ProPak-fx with Promask PP.

- ProPak is EN 137 Type-2 certified
- Promask PP is EN 136 Class 3 certified
- ProPak + Promask is AS/NZS 1716:2012 certified
- ProPak-f/fx + Promask PP is BS 8468-1:2020 CBRN certified

M95 & M98 Filter Cartridges



5-year shelf life
dual-use license

3M™ Scott™ CFR22 NBC 2200 A1P3 RD Filter for Riot Control, Public Order and Security applications, helping to protect against tear gas (CS & CN) and Toxic Industrial Chemicals (TIC).



5-year shelf life
dual-use license

3M™ Scott™ CFR32 Reactor Hg-P3 RD Filter for First Responder applications protecting against radioactive iodine and its organic compounds, solid and liquid toxic and radioactive particulates, micro-organisms, bacteria and viruses.



10-year shelf life
dual-use license

3M™ Scott™ CFR32 CBRN A2B2E2K2-P3 R Filter for Military and First Responder applications protecting against Toxic Industrial Chemicals and CBRN warfare agents, including gases and vapours from organic compounds.



10-year shelf life
dual-use license

3M™ Scott™ CFR32 CBRN A2B2E2K2-P3 RD Filter for Military and First Responder applications protecting against Toxic Industrial Chemicals and CBRN warfare agents, including gases and vapours from organic compounds.

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted. **Respiratory Protection Warning:** These respirators help to protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of AS/NZS 1715 or SA/SNZ ISO 16975.1 including training, fit testing and medical evaluation. Improper use may result in sickness or death. For correct use, see supervisor and User Instructions, or contact 3M PSD Customer Service in Australia at 1300 363 565 or 3msupport.safety.au@mmm.com and in New Zealand at 0800 252 627 or 3msupport.safety.nz@mmm.com. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application including conducting a workplace hazard assessment and reviewing all applicable national and/or local regulations and standards. Failure to properly evaluate select and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment or to meet all applicable safety regulations may result in injury sickness death and/or harm to property.

3M Australia Pty Ltd
Personal Safety Division
Bldg A, 1 Rivett Road North Ryde NSW 2113
Customer Service: 1300 363 565
Email: 3msupport.safety.au@mmm.com
Web: 3M.com.au/ppesafety

3M New Zealand Limited
Personal Safety Division
94 Apollo Drive, Rosedale, Auckland 0632
Customer Service: 0800 252 627
Email: 3msupport.safety.nz@mmm.com
Web: 3M.com/nz/ppesafety

3M, Scott, PELTOR, GoggleGear, Versaflo, Secure Click, ComTac, SecureFit, WS, Optime, Cool Flow and Maxim are trademarks of 3M. All other trademarks are the property of their respective owners.

For industrial/occupational use only.
Not for consumer sale or use. Please recycle.
© 3M 2024. All rights reserved.

