



# 3M™ Flame Barrier FRB-NT Series

Data Sheet

March 2023

**Description** 3M™ Flame Barrier FRB-NT Series provides flame resistance, arc resistance, and electrical insulation performance.

These barriers are available in roll or sheet form.

**Applications** The 3M Flame Barrier FRB-NT series provides both electric shock and flame protection for electrical and electronic device applications such as:

- General purpose lighting luminaires (including LED type)
- Battery housing barrier (including electric and hybrid vehicles)
- Appliance enclosure (e.g., timers, actuators, switches)

**Features** The 3M Flame Barrier FRB-NT series is:

- An inorganic-based, halogen free material (see regulatory section)
- UL 94-5VA rated
- Dimensionally stable – minimal to no shrinkage at elevated temperatures
- Available in thicknesses from 3 to 15 mil (0.08 to 0.38 mm)
- Densified for high dielectric strength and smooth surface

**Regulatory** The 3M Flame Barrier FRB-NT series is:

- For regulatory information visit [www.3m.com/regs](http://www.3m.com/regs)
- **Halogen Free** defined as both 1) no halogen compounds are intentionally added to the product or used in the manufacturing process for the product and 2) any impurities present are less than 900 ppm bromine, less than 900 ppm chlorine, and/or less than 1500 ppm total bromine and chlorine. The latter are the levels set forth in certain industry standards, such as the International Electrotechnical Commission (IEC) 61249-2-21 standard.
- The above information represents 3M's knowledge and belief which may be based in whole or in part on information provided by 3<sup>rd</sup> party suppliers to 3M.
- UL component recognized in accordance with UL 746 file # E65069

**Flammability** The UL 94 test method is used to classify materials based on results from specified small-scale flame tests. These classifications (5VA, 5VB, V-0, V-1, V-2, HB, listed in decreasing order of flame resistance) are used to distinguish a material's burning characteristics after test specimens have been exposed to a specified test flame under controlled laboratory conditions. These classifications typically apply to materials used in manufacturing enclosures, structural parts, and insulators found in consumer electronic products.

A material classified as 5VA or 5VB is subjected to a 500 W – 125 mm flame height ignition source that is more severe than the 50 W – 20 mm flame height ignition source that is used in the V-0, V-1, V-2 and HB tests. Furthermore, specimens in 5VA or 5VB may not drip any flaming particles and 5VA rated specimens may not develop any burn-through holes during the test.

## 3M™ Flame Barrier FRB-NT Series

### Average Properties

Technical information provided consists of average product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

3M™ Flame Barrier FRB-NT Series - Average Properties								
Property	Units	Test Method	FRB-NT076	FRB-NT102	FRB-NT127	FRB-NT178	FRB-NT254	FRB-NT381
Nominal Thickness	mm mil	ASTM D-645	0.076 3.0	0.102 4.0	0.127 5.0	0.178 7.0	0.254 10.0	0.381 15.0
<b>Physical Properties</b>								
Basis Weight	g/m <sup>2</sup> lb/yd <sup>2</sup>	ASTM D-202	103 0.19	156 0.29	195 0.36	274 0.49	410 0.76	561 1.04
Density	g/cc		1.4	1.5	1.5	1.5	1.5	1.5
Flame Rating (UL File E65069)	Flammability rating	UL94	V-0, 5VA	V-0, 5VA	V-0, 5VA	V-0, 5VA	V-0, 5VA	V-0, 5VA
Relative Thermal Index, Component, Electrical	°C	UL 746B	140	140	140	140	140	140
Relative Thermal Index, Component, Mechanical without impact	°C	UL 746B	130	130	130	130	130	130
<b>Electrical Properties</b>								
High-Voltage Arc Tracking Rate (HVTR)	PLC assigned	UL 746A	0	0	0	0	0	0
Comparative Tracking Index (CTI)	PLC assigned	UL 746A	0	0	0	0	0	0
Hot Wire Ignition (HWI)	PLC assigned	UL 746A	4*	4*	4*	4*	4*	4*
High Current Arc to Ignition (HAI)	PLC assigned	UL 746A	2	2	2	2	2	2
Glow wire ignition temperature (GWIT)	°C	IEC 60695-2-13	990	990	990	990	990	990
Glow wire flammability index (GWFI)	°C	IEC 60695-2-1	960	960	960	960	960	960
High Volt, Low Current Arc Resistance	PLC assigned	ASTM D-495	4	4	4	4	4	4
Dielectric Breakdown Voltage	kV	ASTM D-149	1.1	2.2	2.7	3.0	5.0	8.0
<b>Mechanical Properties</b>								
Tensile Strength, MD	lb/inch N/cm	ASTM D-828	11 19	22 39	31 54	41 72	53 93	100 175
Elongation to Break, MD	%	ASTM D-828	1.0	1.2	1.3	1.2	1.7	1.7

\* - Materials that do not comply with the minimum hot-wire ignition levels may be evaluated by an abnormal overload test or the glow-wire end-product test, per UL 746C

## 3M™ Flame Barrier FRB-NT Series

---

### Shelf Life & Storage

This product has a 5-year shelf life from date of manufacture when stored in a humidity controlled storage (from 10°C / 50°F to 27°C / 80°F and <75% relative humidity)

---

### Availability

For availability, please contact your local distributor. Names and addresses are available from [3M.com/electrical](http://3M.com/electrical) [Where to Buy] or call 1-800-676-8381.

---

3M is a trademark of 3M Company.

---

### TECHNICAL STATEMENT

#### **Automotive Disclaimer**

**Automotive Applications:** This product is an industrial product and has not been designed or tested for use in certain automotive applications, including, but not limited to, automotive electric powertrain battery or high voltage applications. This product does not fully adhere to typical automotive design or quality system requirements, such as IATF 16949 or VDA 6.3. This product may not be manufactured in an IATF certified facility and may not meet a Ppk of 1.33 for all properties. The product may not undergo an automotive production part approval process (PPAP). Customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's automotive application and for conducting incoming inspections before use of the product. Failure to do so may result in injury, death, and/or harm to property. No written or verbal statement, report, data or recommendation by 3M related to automotive use of the product shall have any force or effect unless in an agreement signed by the Technical Director of 3M's Automotive Division. Customer assumes all responsibility and risk if customer chooses to use this product in an automotive electric powertrain battery or high voltage application, and 3M will not be liable for any loss or damage arising from or related to the 3M product or customer's use of the product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity or recall costs), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. In no event shall 3M be liable for any damages in excess of the purchase price paid for the product.

NOTWITHSTANDING ANY OTHER STATEMENT TO THE CONTRARY, 3M MAKES NO REPRESENTATIONS, WARRANTIES OR CONDITIONS WHATSOEVER, EXPRESS OR IMPLIED, REGARDING THE PRODUCT IF USED IN AN AUTOMOTIVE ELECTRIC POWERTRAIN BATTERY OR HIGH VOLTAGE APPLICATION, INCLUDING, BUT NOT LIMITED TO, ANY WARRANTY ON PERFORMANCE, LONGEVITY, SUITABILITY, COMPATIBILITY, OR INTEROPERABILITY, OR ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE.

## TECHNICAL STATEMENTS Cont.

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).



**Electrical Markets Division**  
13011 McCallen Pass, Bldg C.  
Austin, TX 78753  
800.245.3573  
Fax 800.245.0329  
[www.3M.com/electrical](http://www.3M.com/electrical)

Please recycle  
© 3M 2023. All rights reserved.  
78-8141-5277-9 Rev F