

Commercial Branding and Transportation Division

3M™ Flexible Prismatic Retroreflective Prestriped Sheeting Series 3334i/3336i

With Pressure Sensitive Adhesive for Use on Traffic Control Barricades

Product Bulletin 3334i/3336i
December 2024

Initial Issue

1 Description

3M™ Flexible Prismatic Retroreflective Prestriped Sheeting Series 3334i/3336i (the “Sheeting”) is a prestriped prismatic lens reflective barricade sheeting with a pressure sensitive adhesive. It is designed for reflectorizing aluminum, wood, and flame treated rigid plastic traffic control barricades.

For details of the features and benefits of the Sheeting, please refer to www.3M.com.

The Sheeting is available in the following prestriped configurations.

Table 1. Available prestriped configurations by product number

| Color and Stripe* | Product Code |
|---------------------------------|--------------|
| Red/white 6 in. left stripe | 3326Li |
| Red/white 6 in. right stripe | 3326Ri |
| Orange/white 4 in. left stripe | 3334Li |
| Orange/white 4 in. right stripe | 3334Ri |
| Orange/white 6 in. left stripe | 3336Li |
| Orange/white 6 in. right stripe | 3336Ri |

* On horizontal panels, "Left" sheetings have stripes that slope from the upper left to lower right and are placed on the left side of the roadway to move traffic to the right. "Right" sheetings are the opposite.




Figure 1. Sheeting Striping Diagram

2 Specifications

The Sheeting meets the requirements of ASTM D4956-19 Types III, IV, and S2 Reboundable Sheeting Requirements.

3 Substrates

Refer to [3M Information Folder 1.7](#) for surface preparation recommendations. See [3M Information Folder 3.3](#) for instructions on application to reboundable traffic control devices. **Sheeting failures caused by substrate failures or improper surface preparations are not the responsibility of 3M.**

4 Shelf-Life, Storage, Shipping, and Cleaning

4.1 Shelf Life

Use the sheeting within two (2) years of the date of manufacture.

4.2 Storage Conditions

- Cool, dry place
- Store rolls of sheeting horizontally in their shipping cases
- Return partially used roles to their shipping cases, or suspend them horizontally via rods or pipes through their cores
- Store unimaged cut sheets flat

4.3 Shipping

The device with applied sheeting must be allowed to sit at room temperature for at least four hours prior to shipping.

Plastic devices can be stacked to ensure the product reaches the end customer without blemishes. Shrink-wrap the top device to help protect the sheeting during shipping.

Unassembled barricade boards must be unpackaged and unstacked immediately upon receipt to prevent the boards from bonding to each other. The longer boards remain stacked, the more likely they are to be damaged when users attempt to take the boards apart.

4.4 Cleaning

3M recommends cleaning reflectorized devices periodically with a mixture of a mild detergent and water.

5 Durability

The durability of the Sheeting depends upon many factors. Refer to [3M Information Folder 1.7](#) for details, and additionally see [3M Information Folder 3.3](#) when using the product for traffic control devices.

6 Health and Safety Information

Read all health hazard, precautionary, and first aid statements found in the Safety Data Sheets (SDS), Article Information Sheets, and products labels of any materials for important health, safety, and environmental information prior to handling or use. To obtain SDS and Article Information Sheets for 3M products, go to [3M.com/SDS](https://www.3m.com/SDS), contact 3M by mail, or for urgent requests call 1-800-364-3577.

7 Warranty Information

7.1 3M Standard Product Warranty

The Sheeting is warranted (“3M Standard Warranty”) to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in this product bulletin. If the Sheeting is proven not to have met the 3M Standard Warranty on their shipment date, then a buyer's exclusive remedy, and 3M's sole obligation, at 3M's option, will be refund or replacement of the Sheeting.

7.2 Disclaimer

THE 3M WARRANTY IS MADE IN LIEU OF ALL OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING OR OF PERFORMANCE, CUSTOM, OR USAGE OF TRADE.

7.3 Limitation of Liability

Except for the limited remedy stated above, and except where prohibited by law, 3M will not be liable for any loss or damage arising from any 3M product, whether direct, indirect, special, incidental, or consequential damages (including but not limited to lost profits, business, or revenue in any way), regardless of the legal theory asserted including warranty, contract, negligence, or strict liability.

8 Other Product Information

Always confirm that you have the most current version of the applicable product bulletin, information folder, or other product information from 3M's website at <https://www.3M.com>.

9 Literature References

| | |
|----------------------------|---|
| 3M IF 1.5 | Hand Application Instructions |
| 3M IF 1.6 | Hand Squeeze Roll Applicator |
| 3M IF 1.7 | Sign Base Surface Preparation |
| 3M IF 1.10 | Cutting, Premasking, and Prespacing |
| 3M IF 1.11 | Sign Maintenance Management |
| 3M IF 3.3 | Reflective Sheeting Procedures for Application to Reboundable Traffic Control Devices |

ASTM Test Methods are available from ASTM International, West Conshohocken, PA.

For Information or Assistance

Call: 1-800-553-1380

In Canada Call:

1-800-3M HELPS (1-800-364-3577)

Internet:

<https://www.3M.com>

3M and 3M Science. Applied to Life. are trademarks of 3M. Used under license in Canada.
All other trademarks are the property of their respective owners.

3M assumes no responsibility for any injury, loss, or damage arising out of the use of a product that is not of our manufacture. Where reference is made in literature to a commercially available product, made by another manufacturer, it shall be the user's responsibility to ascertain the precautionary measures for its use outlined by the manufacturer.

Important Notice

All statements, technical information and recommendations contained herein are based on tests we believe to be reliable at the time of this publication, but the accuracy or completeness thereof is not guaranteed, and the following is made in lieu of all warranties, or conditions express or implied. Seller's and manufacturer's only obligation shall be to replace such quantity of the product proved to be defective. Neither seller nor manufacturer shall be liable for any injury, loss, or damage, direct, indirect, special, or consequential, arising out of the use of or the inability to use the product. Before using, user shall determine the suitability of the product for his/her intended use, and user assumes all risk and liability whatsoever in connection therewith. Statements or recommendations not contained herein shall have no force or effect unless in an agreement signed by officers of seller and manufacturer.



Commercial Branding and Transportation

3M Center, Building 223-3N-30
St. Paul, MN 55144

3M Canada

P.O. Box 5757
London, ON N5A 4T1

Phone 1-800-553-1380

Web [3M.com/roadsafety](https://www.3M.com/roadsafety)

© 3M 2024

All rights reserved. Electronic only.