

Transportation Safety Division

3M™ High Intensity Prismatic Reflective Sheeting Series 3930

Product Bulletin Series 3930
May 2018

Replaces Product Bulletin 3930 Dated January 2013

1 Description

High Intensity Prismatic Reflective Sheeting Series 3930 (“Sheeting”) is a non-metalized microprismatic lens reflective sheeting designed for use in the production of durable reflective traffic control signs, work zone devices, and delineators that are exposed vertically in service (“Signs”). Applied to properly prepared Sign substrates, 3M Series 3930 prismatic Sheeting provides long-term reflectivity and durability.

Series 3930 Sheeting is available in the following colors.

Table 1. Product Codes by Color

Color	Product Code
White	3930
Yellow	3931
Red	3932
Orange	3934
Blue	3935
Green	3937
Brown	3939

2 Specifications

2.1 Daytime Color (x, y, Y)

The chromaticity coordinates and total luminance factors of the retroreflective Sheeting conform to the limits presented in Table 2.

Table 2. Daytime Color Specification Limits^a

Color	1		2		3		4		Reflectance Limit (Y)	
	x	y	x	y	x	y	x	y	Minimum	Maximum
White	0.303	0.300	0.368	0.366	0.340	0.393	0.274	0.329	27	
Yellow	0.498	0.412	0.557	0.442	0.479	0.520	0.438	0.472	15	45
Red	0.648	0.351	0.735	0.265	0.629	0.281	0.565	0.346	2.5	15
Orange	0.558	0.352	0.636	0.364	0.570	0.429	0.506	0.404	10	30
Blue	0.140	0.035	0.244	0.210	0.190	0.255	0.065	0.216	1	10
Green	0.026	0.399	0.166	0.364	0.286	0.446	0.207	0.771	3	12
Brown	0.430	0.340	0.610	0.390	0.550	0.450	0.430	0.390	1	9

a. The four pairs of chromaticity coordinates determine the acceptable color in terms of the CIE 1931 Standard Colorimetric System.

2.2 Color Test - Ordinary Colored Sheeting

Conformance to standard chromaticity (x, y) and luminance factor (Y%) requirements shall be determined instrumentally, in accordance with ASTM E1164, on Sheeting applied to smooth test panels cut from aluminum alloy 6061-T6 or 5052-H38. Chromaticity and luminance factor values shall be determined using a HunterLab ColorFlex 45/0 spectrophotometer.¹ Calculations shall be performed using CIE Illuminant D65 and the 2° standard observer.

2.3 Coefficient of Retroreflection (R_A)

The values shown in Table 3 are minimum coefficients of retroreflection, expressed in candelas per lux per square meter (cd/lux/m²).

Table 3. Minimum Coefficient of Retroreflection R_A for New Sheeting (cd/lux/m²)

Entrance Angle ^a	Sheeting Color	Observation Angle ^b	
		0.2°	0.5°
-4°	White	560	200
	Yellow	420	150
	Red	84	30
	Orange	210	75
	Blue	30	13
	Green	56	21
	Brown	18	7.5
-30°	White	280	100
	Yellow	210	75
	Red	42	15
	Orange	105	37
	Blue	14	6
	Green	28	10
	Brown	8.5	3.5

a. Entrance Angle – The angle from the illumination axis to the retroreflector axis. The retroreflector axis is an axis perpendicular to the retroreflective surface.

b. Observation Angle – The angle between the illumination axis and the observation axis.

1. The instrumentally determined color values of retroreflective sheeting can vary significantly depending on the make and model of colorimetric spectrophotometer used, as well as the color and retroreflective optics of the sheeting (David M. Burns and Timothy J. Donahue, Measurement Issues in the Color Specification of Fluorescent Retroreflective Materials for High Visibility Traffic Signing and Personal Safety Applications, Proceedings of SPIE: Fourth Oxford Conference on Spectroscopy, 4826, pp. 39-49, 2003). For the purposes of this document, the HunterLab ColorFlex 45/0 spectrophotometer shall be the referee instrument.

2.4 Test for Coefficient of Retroreflection

Conformance to coefficient of retroreflection requirements shall be determined instrumentally, in accordance with ASTM E-810 “Test Method for Coefficient of Retroreflection of Retroreflective Sheeting.” Per ASTM E-810, the values presented in Table 3 are averages of R_A values obtained at 0° and 90° rotations.

2.5 Entrance Angularity Performance and Orientation

3M High Intensity Prismatic Reflective Sheeting Series 3930 has been designed to be an effective wide angle reflective sheeting regardless of its orientation on the substrate or the ultimate orientation of the Sign after installation. However, because the efficiency of light return from cube corner reflectors is not equal at all application orientations, which is especially apparent at larger entrance angles, it is possible to get the widest entrance angle light return from a particular orientation. When high entrance angle ($>50^\circ$) performance is required for a given Sign (e.g. “keep right” symbols), it can be obtained easily by properly orientating the Sheeting on the completed Sign. In such situations, the completed Sign should have the Sheeting positioned at the 0° orientation (downweb direction perpendicular to the road). When the flat side of the diamond (direction of diamond chain links) is vertical in the completed Sign, Sheeting is said to be at a 0° orientation. When the “primary groove line” (or, flat side of the diamond shape) is horizontal on the completed Sign, the Sheeting is said to be at a 90° orientation. See Figure 1 for details.




Figure 1. Primary groove lines used to define Sheeting orientation.

Unless Sign location and/or position calls for extra-wide entrance angularity performance or a specific installation direction is required in a customer specification, Signs and applied copy (letters, arrows, borders, and shields) can be fabricated and installed using the application orientation that most efficiently utilizes the reflective Sheeting.

Note: For multi-panel Signs, it is recommended that all background panels be sheeted such that the Sheeting direction is the same for all panels.

2.6 Printed Colors and Overlay Films

When processed according to 3M recommendations, the coefficient of retroreflection of a screen-printed transparent color on white Sheeting shall be not less than 70% of the R_A value of the corresponding colored Sheeting presented in Table 3. White Sheeting covered with 3M ElectroCut™ Film Series 1170, when processed according to 3M recommendations, shall have a coefficient of retroreflection of not less than 100% of the value of the corresponding colored Sheeting, as presented in Table 3. The chromaticities and luminances of printed colors and overlay films shall conform to the specifications presented in Table 2.

3 Physical Properties

3.1 Fabrication Lines

The manufacture of prismatic Sheeting results in lines being present in the product, as shown in Figure 2. In prismatic Sheeting, these lines are slightly thicker than the seal pattern legs. Fabrication lines are noticeable in shop light but are not observable on the road, either in daylight or at night, under typical use conditions.




Figure 2. Fabrication lines.

3.2 Adhesive

Series 3930 Sheeting has a pressure-sensitive adhesive that is recommended for application at temperatures of 65°F (18°C) and higher.

4 Sign Fabrication Methods

4.1 Application

Series 3930 Sheeting should be applied to Sign substrates at temperatures of 65°F (18°C) and higher using any of the following methods:

Mechanical squeeze roll applicator – refer to [3M Information Folder 1.4](#). Applications to extrusions that are edge wrapped require sufficient softening of the Sheeting. This can be accomplished by directing additional heat to the “next to last” edge roller. This practice may increase productivity and minimize cracking.

Hand squeeze roll applicator – refer to [3M Information Folder 1.6](#).

Background or complete Sign applications of Series 3930 Sheeting must be performed with a roll laminator, either mechanical or hand driven.

4.2 Hand Application

Hand application is recommended for legend and copy only. Refer to [3M Information Folder 1.5](#) for more details.

Hand applications will show some visual irregularities which may be objectionable to aesthetically critical customers. These irregularities are more noticeable on darker colors. To obtain a uniform close-up appearance, a roll laminator must be used.

All direct applied copy and border **MUST** be cut and squeegeed at all metal joints.

4.3 Splices

Series 3930 Sheeting must be butt spliced when more than one piece of Sheeting is used on a single piece of substrate. Sheeting pieces should not touch one another. This is to prevent the buckling that can occur as Sheeting expands under extreme temperature and humidity conditions.

4.4 Double Faced Signs

The Sheeting on the bottom side of a double faced Sign can be damaged if rolled through a squeeze roll applicator with an unprotected steel bottom roller. The use of a semi-soft flat sheet between the steel roller and the applied Sign face will provide protection from damage. A material such as a rubber mat, tag board, or cardboard is recommended.

5 Substrates

For traffic Sign use, the substrates that have been found to be most reliable and durable are properly prepared aluminum sheets and extrusions. **Users are urged to carefully evaluate adhesion and Sign durability properties of all other substrates.** Other substrates suitable for secure and durable applications of Series 3930 Sheeting have the following characteristics:

- Clean
- Smooth
- Flat
- Rigid
- Dimensionally stable
- Weather resistant
- Non-porous
- High surface energy (pass water break test)

Refer to [3M Information Folder 1.7](#) for surface preparation recommendations. Substrates with low surface energies may require additional preparation steps, such as flame treatment, mechanical abrasion, or use of adhesion promoters prior to Sheeting application. Guide Sign extrusions may be edge wrapped. Flat panels and unwrapped extrusions must be carefully trimmed so that Sheeting sections on adjacent panels do not touch on assembled Signs.

High intensity prismatic Sheeting has been designed primarily for application to flat substrates. Any application to a substrate with a radius of curvature of less than five inches should also be supported by rivets or bolts. Plastic substrates are not recommended where cold shock performance is required. **Sign failures caused by substrate failures or improper surface preparations are not the responsibility of 3M.**

6 Imaging

High intensity prismatic Sheeting may be processed into traffic Signs using any of the imaging methods described below. 3M assumes no responsibility for the failures of Sign face legends or backgrounds that have been processed with non-3M process colors or with matched component imaging materials other than those listed below.

6.1 Digital Imaging

3M High Intensity Prismatic Reflective Sheeting Series 3930 is compatible with the HP Latex 360/365 printers in combination with HP 831/HP 871 Latex inks. This compatibility is backed with a 3M MCS™ Warranty and 3M MCS Warranty for Traffic when the printing guidelines in [3M Information Folder 1.18](#) are followed and 3M ElectroCut™ Film 1170C Clear is applied over the finished graphics. See the “Limited Warranty” section of this document for more information on the MCS Warranties.

6.2 Screen Processing

Series 3930 Sheeting may be screen processed into traffic Signs using 3M Process Colors Series 880I or Series 880N before or after being mounted onto a substrate. Series 880I and 880N process colors can be screened at temperatures of 60-100°F (16-38°C) and at relative humidities of 20-50%. A P.E. 157 screen mesh with a fill pass is recommended. Refer to [3M Information Folder 1.8](#) for details. Clear coating is neither required nor recommended. Use of process color series other than 880I or 880N is not recommended.

6.3 3M ElectroCut™ Film

3M ElectroCut Film Series 1170 may be used on Series 3930 prismatic Sheeting to provide transparent colored background copy for traffic control Signs. Refer to [3M Product Bulletin 1170](#) for fabrication procedures.

6.4 Applied Cut-Out Copy

Series 3930 Sheeting cut-out copy may be applied to Sheeting backgrounds to create Sign legends. Such cut-out copy may be applied directly to the background Sheeting or in a demountable form. Direct applied copy must be cut at all panel seams and carefully trimmed back so that the Sheeting sections of adjacent panels do not touch one another on assembled Signs. Refer to [3M Information Folder 1.10](#) for more information.

7 Cutting

Series 3930 Sheeting may be cut into letters and shapes with heights of at least 3 inches and stroke widths of at least ½ inch. Smaller sizes are not recommended. Sealing the cut edges of Series 3930 Sheeting is not required.

7.1 Plotter Cutting

Programmable knife cut (electronic cutting):

- 1 Flat bed plotters can be used to either die cut or kiss cut Series 3930 Sheeting and offer the most consistent and reliable performances.
- 2 Friction fed plotters can be used to kiss cut only. This is achieved using 600 grams of down force and a 60° cutting blade. Additional drive wheels may be needed to improve tracking. Alternatively, Series 3930 Sheeting can be cut from the liner side. To do so, the blade force and knife depth must be set to score, but not cut through, the topfilm. After scoring, break apart individual copy or apply premask to retain spacing.

7.2 Other Cutting Methods

Series 3930 Sheeting may be hand cut or die cut one sheet at a time, and band sawed or guillotined in stacks. Cutting equipment such as guillotines and metal shears, which place pressure plates on the Sheeting when cutting, may damage the optics. Padding the pressure plate and easing it down onto the sheets being cut will significantly reduce damage. Maximum stack height for cutting Series 3930 Sheeting is 1 ½ inches, or 50 sheets. Cutting procedure details can be found in [3M Information Folder 1.10](#).

8 Installation

Nylon washers are required when twist style fasteners are used to mount Signs.

9 Shelf-Life, Storage, and Packaging

Series 3930 Sheeting should be stored in a cool, dry area, preferably at 65-75°F (18-24°C) and 30-50% relative humidity, and applied within two years of date of manufacture. Rolls should be stored horizontally in their shipping cartons. Partially used rolls should be returned to their shipping cartons or suspended horizontally from rods or pipes through their cores. Unprocessed sheets should be stored flat. Finished Signs and applied blanks should be stored on edge.

Screen processed Signs must be protected with SCW 568 slipsheet paper. Place the glossy side of the slipsheet against the Sign face and pad the face with closed cell packaging foam. Double faced Signs must have the glossy side of a piece of slipsheeting against each face of the Sign.

Unmounted screened faces must be stored flat and interleaved with SCW 568 slipsheeting, glossy side against the Sign face.

Avoid banding, crating, or stacking Signs. Package for shipment in accordance with commercially accepted standards to prevent movement and chafing. Store Sign packages indoors on edges.

Panels and finished Signs must remain dry during shipment and storage. If packaged Signs become wet, unpack immediately and allow Signs to dry. Refer to [3M Information Folder 1.11](#) for instructions on packing for storage and shipment.

10 Cleaning

Signs that require cleaning should be flushed with water, then washed with a detergent solution and soft bristle brush or sponge. Avoid pressure that may damage Sign faces. Flush with water following washing. Do not use solvents to clean Signs.

11 Durability

The durabilities of Series 3930 Sheeting and finished Signs made using 3M Matched Component materials will depend upon substrate selection and preparation, compliance with recommended application procedures, geographic area, exposure conditions, and maintenance practices. Maximum durability of Series 3930 Sheeting can be expected in applications subject to vertical exposures on stationary objects, when processed and applied to aluminum substrates prepared according to the recommendations provided in [3M Information Folder 1.7](#). The user must determine the suitability of any nonmetallic Sign backing for its intended use. **Sign failures caused by substrate failures or improper surface preparations are not the responsibility of 3M.** Application to unprimed, excessively rough or non-weather-resistant surfaces, or exposure to severe or unusual conditions can shorten the performance lifetime of Series 3930 Sheeting. 3M process colors and ElectroCut™ Film, when used according to 3M recommendations, are generally expected to produce Signs with performances comparable to those of their colored reflective Sheeting components. Custom colors, certain lighter colors, heavily toned colors, and blends containing yellow or gold may have reduced durabilities. Atmospheric conditions in certain geographic areas may result in reduced durability.

Periodic Sign inspection and regular Sign replacement are strongly recommended in order to help Sign owners establish their own effective service life expectations, beyond the warranty period.

12 Health and Safety Information

Read all health hazard, precautionary, and first aid statements found in the Safety Data Sheets (SDS), Article Information Sheets, and products labels of any materials for important health, safety, and environmental information prior to handling or use. To obtain SDSs and Article Information Sheets for 3M products, go to 3M.com/SDS, contact 3M by mail, or for urgent requests call 1-800-364-3577.

13 Warranty Information

13.1 3M Basic Product Warranty and Limited Remedy

3M High Intensity Prismatic Reflective Sheeting Series 3930 (“Product”) is warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in this Product Bulletin. If Series 3930 Sheeting is proven not to have met the Basic Warranty on its shipment date, then a buyer’s exclusive remedy, and 3M’s sole obligation, at 3M’s option, will be refund or replacement of the Sheeting.

13.2 General Warranty Terms

- 3M makes the Additional Warranty (as defined below) as to any traffic control and guidance Sign in the United States and Canada made with 3M High Intensity Prismatic Reflective Sheeting Series 3930 and the Matched Component materials listed in Table 4, below. Any Additional Warranty is contingent on all components involved in the Additional Warranty being stored, applied, installed, and used only as 3M recommends in its Product Bulletins and Other Product Information.
- The Basic Warranty and any applicable Additional Warranty are collectively referred to as the “3M Warranty.”
- A Sign’s failure to meet the 3M Warranty must be solely the result of the Product or the matched component materials’ design or manufacturing defects. 3M has no obligation under the 3M Warranty if a Sign failure is caused by (a) outside causes including improper fabrication, handling, packing, storing, shipping, maintenance, or installation; (b) use of any material or product not recommended by 3M in this product bulletin, in the 3M information folders and product bulletins listed in Section 15, or in applicable 3M Technical Memorandums; (c) use of application equipment not recommended by 3M; (d) failure of Sign substrate; (e) loss of adhesion due to incompatible or improperly prepared substrate; (f) exposure to chemicals, abrasion, or other mechanical damage; (g) snow burial or any other Sign burial; (h) collisions, vandalism, or malicious mischief; or (i) an act of God.

- 3M reserves the right to determine method of replacement.
- Any replacement Product or Sign restoration will carry the unexpired warranty of the Product it replaces.
- Claims made under this warranty will be honored only if (a) the Sign was dated at the time of fabrication (“Fabrication Date”) using a permanent method (sticker, marker, metal stamp, etc.), (b) 3M is notified in writing of the claim within thirty days of discovery, (c) 3M is provided with the information reasonably required to validate the claim, and (d) 3M is permitted to verify the cause of the failure.
- 3M is not responsible for any additional warranties that the Sign Manufacturer offers to its customers beyond the 3M Warranty.

Table 4. Matched Component Materials

Matched Components	
Process Colors	Series 880I Series 880N
ElectroCut™ Film	Series 1170
Premium Protective Overlay Film	Series 1160

13.3 Additional Warranty and Limited Remedy

The Additional Warranty for a Sign made with the Product is that the Sign will: (a) remain effective for its intended use when viewed from a moving vehicle under normal day and night driving conditions by a driver with normal vision and (b) after cleaning, will meet the minimum coefficient of retroreflection value stated in Table 5 for the applicable Warranty Period, as measured from the Sign’s Fabrication Date.

Table 5. Minimum Percent of Initial R_A (See Table 3) Retained for Applicable Warranty Period for White, Yellow, Red, Green, Blue, and Brown Sheeting

Warranty Period	Minimum Percentage R_A Retained
1-7 Years	80%
8-10 Years	70%

- If any Sign made with the Product is proven not to have met the Additional Warranty, then a buyer’s **exclusive remedy**, and 3M’s sole obligation, at 3M’s option is:
- If this occurs within seven years of the Fabrication Date, then 3M will, at its expense, restore the Sign’s surface to its **original effectiveness**; or
- If this occurs during the remainder of the Additional Warranty Period, then 3M will furnish only the necessary Product and matched component materials quantities to restore the Sign’s surface to its original effectiveness.

13.4 Additional Warranty & Limited Remedy for 3934 Orange Product

The Additional Warranty for a Sign made with 3934 orange Sheeting (Orange Product) is that the Sign will: (a) remain effective for its intended use when viewed from a moving vehicle under normal day and night driving conditions by a driver with normal vision; (b) after cleaning, will retain the coefficient of retroreflection stated in Table 6 for three years, as measured from Fabrication Date; and (c) after cleaning, the Product will maintain daytime luminance equal to or greater than the minimum value specified in Table 2.

Table 6. Minimum Coefficient of Retroreflection for 3934 Orange Sheeting Product ($\text{cd}/\text{lux}/\text{m}^2$) (0.2° observation angle and -4° entrance angle)

Warranty Period	Minimum R_A
3 Years	80

If any Sign made with the Orange Product is proven not to have met the Additional Warranty, then a buyer’s **exclusive remedy**, and 3M’s sole obligation, at 3M’s option, is that 3M will provide pro-rated replacement of the 3M materials.

Refer to 3M Information Folders and Product Bulletins for detailed information about recommended application procedures and equipment.

13.5 Disclaimer

THE 3M WARRANTY IS MADE IN LIEU OF ALL OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING OR OF PERFORMANCE, CUSTOM, OR USAGE OF TRADE.

13.6 Limitation of Liability

Except for the limited remedy stated above, and except where prohibited by law, 3M will not be liable for any loss or damage arising from the Signs or any 3M product, whether direct, indirect, special, incidental, or consequential damages (including but not limited to lost profits, business, or revenue in any way), regardless of the legal theory asserted including warranty, contract, negligence, or strict liability.

14 Other Product Information

Always confirm that you have the most current version of the applicable product bulletin, information folder, or other product information from 3M's Website at <http://www.mmm.com/roadsafety>.

15 Literature References

3M IF 1.4	Instructions for Interstate Squeeze Roll Applicator
3M IF 1.5	Hand Application Instructions
3M IF 1.6	Hand Squeeze Roll Applicator
3M IF 1.7	Sign Base Surface Preparation
3M IF 1.8	Process Colors Series 880 and 900 Instructions for Use
3M IF 1.10	Cutting, Premasking, and Prespacing
3M IF 1.11	Sign Maintenance Management
3M IF 1.18	Digital Imaging with HP Latex 360/365 Printers on 3M™ Reflective Sheeting Series 4000 and 3930
3M IF 3.5	Digital Imaging with HP Latex 360/365/370/375 Printer on 3M™ Reflective Sheeting Series 4000 and 3930 for Rigid Temporary Traffic Control Signing Applications
3M PB 880I	3M™ Process Color Series 880I
3M PB 880N	3M™ Process Color Series 880N
3M PB 1160	Premium Protective Overlay Film
3M PB 1170	3M™ ElectroCut™ Film Series 1170

ASTM Test Methods are available from ASTM International, West Conshohocken, PA.

For Information or Assistance

Call: 1-800-553-1380

In Canada Call:

1-800-3M HELPS (1-800-364-3577)

Internet:

<http://www.3M.com/roadsafety>

3M, Science. Applied to Life., and ElectroCut are trademarks of 3M. Used under license in Canada.

3M assumes no responsibility for any injury, loss, or damage arising out of the use of a product that is not of our manufacture. Where reference is made in literature to a commercially available product, made by another manufacturer, it shall be the user's responsibility to ascertain the precautionary measures for its use outlined by the manufacturer.



Transportation Safety Division
3M Center, Building 0225-04-N-14
St. Paul, MN 55144-1000 USA

Phone 1-800-553-1380
Web 3M.com/roadsafety

Please recycle. Printed in USA © 3M 2018.
All rights reserved. Electronic Only