

### 3M Perimeter Limiter System Compatibility with 3M Self-Retracting Devices with Leading Edge Capabilities

3M Product	3M Legacy PN	ANSI Z359.14-2014		Current Part Number	CSA Z259.2.2-17		ANSI Z359.14-2021		OSHA 1910.140/1926.502		Perimeter Limiter
		MAF	AAF		MAF	AAF	MAF	AAF	MAF	AAF	Limit of 900AAF/ 1350MAF
Nano-Lok™ Edge (Single), Class 2, SRD-LE	3500212	1350 lbf	900 lbf	3500290	N/A	N/A	1350 lbf	900 lbf	1350 lbf	900 lbf	Compatible for use
	3500210			3500288	N/A	N/A					
	3500211			3500293	N/A	N/A					
	3500248			3500292	N/A	N/A					
	3500258			3500296	N/A	N/A					
Nano-Lok™ Edge (Twin), Class 2, SRD-LE	3500227	1350 lbf	900 lbf	3500276	N/A	N/A	1425 lbf	900 lbf	1350 lbf	900 lbf	Compatible for use
	3500225			3500279	N/A	N/A					
	3500226			3500282	N/A	N/A					
	3500246			3500278	N/A	N/A					
	3500257			3500283	N/A	N/A					
Ultra-Lok™ LE, OSHA only, SRD-LE	3504422	1350 lbf	900 lbf	N/A	N/A	N/A	N/A	N/A	1800 lbf	1350 lbf	Not Compatible
	3504500			N/A	N/A	N/A					
	3504600			3503885	N/A	N/A					
Smart Lock LE, Class 2, SRD-LE		1350 lbf	900 lbf	3503850	N/A	NA	1500 lbf	1125 lbf	1500 lbf	1125 lbf	Not Compatible
				3503890	N/A	N/A					
	3503802			3503880	N/A	N/A					

3M Product	3M Legacy PN	ANSI Z359.14-2014		Current Part Number	CSA Z259.2.2-17		ANSI Z359.14-2021		OSHA 1910.140/1926.502		Perimeter Limiter
		MAF	AAF		MAF	AAF	MAF	AAF	MAF	AAF	Limit of 900AAF/ 1350MAF
Smart Lock LE, Class 2, SRD-LE	3503822	1350 lbf	900 lbf	3503881	N/A	N/A	1500 lbf	1125 lbf	1500 lbf	1125 lbf	Not Compatible
Protecta® Cable LE, Class 2, 20' and 33' SRD-LE	3590540	1350 lbf	900 lbf	3590046	NA	N/A	1800 lbf	1350 lbf	1350 lbf	900 lbf	Compatible for use
	3590543			3590047	N/A	N/A					
Protecta® Cable LE, Class 2, 50' and 66' SRD-LE	3590546	1350 lbf	900 lbf	3590048	N/A	N/A	1800 lbf	1350 lbf	1800 lbf	N/A	Not Compatible
	3590548			3590049	N/A	N/A					
Protecta® Cable LE, CSA, 20'/33' SRD-LE		—	—	3590541	1460 lbf	900 lbf	N/A	N/A	1460 lbf	900 lbf	Not Compatible
		—	—	3590544	1460 lbf	900 lbf	N/A	N/A	1460 lbf	900 lbf	
Protecta® Cable LE, CSA, 50'/66' SRD-LE		—	—	3590547	1460 lbf	900 lbf	N/A	N/A	1460 lbf	900 lbf	Not Compatible
		—	—	3590549	1460 lbf	900 lbf	N/A	N/A	1460 lbf	900 lbf	
Smart Lock LE, CSA, 20'/30'/30'mod, SRD-LE		—	—	3503802	1350 lbf	860 lbf	N/A	N/A	1350 lbf	900 lbf	Compatible for use
		—	—	3503822	1350 lbf	860 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3503848	1350 lbf	860 lbf	N/A	N/A	1350 lbf	900 lbf	
Nano Lok™ Edge (Single, Twin, Tie-Back), CSA, SRD-LE		—	—	3500209	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	Compatible for use
		—	—	3500217	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500218	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500219	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500220	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	

3M Product	3M Legacy PN	ANSI Z359.14-2014		Current Part Number	CSA Z259.2.2-17		ANSI Z359.14-2021		OSHA 1910.140/1926.502		Perimeter Limiter
		MAF	AAF		MAF	AAF	MAF	AAF	MAF	AAF	Limit of 900AAF/ 1350MAF
Nano Lok™ Edge (Single, Twin, Tie-Back), CSA, SRD-LE		—	—	3500221	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	Compatible for use
		—	—	3500222	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500223	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500232	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500233	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500234	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
Nano Lok™ Edge (Single, Twin, Tie-Back), CSA, SRD-LE		—	—	3500235	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	Compatible for use
		—	—	3500236	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500237	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500238	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500250	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500251	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500252	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500253	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	
		—	—	3500259	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	

		ANSI Z359.14-2014			CSA Z259.2.2-17		ANSI Z359.14-2021		OSHA 1910.140/1926.502		Perimeter Limiter
3M Product	3M Legacy PN	MAF	AAF	Current Part Number	MAF	AAF	MAF	AAF	MAF	AAF	Limit of 900AAF/ 1350MAF
Nano Lok™ Edge (Single, Twin, Tie- Back), CSA, SRD-LE		—	—	3500260	1350 lbf	900 lbf	N/A	N/A	1350 lbf	900 lbf	Compatible for use

The user capacity range is 130 lb. to 310 lb. for all values listed. The Competent Person is responsible for reviewing the fall protection application, the SRD used, and for consulting the applicable user instructions to determine compatibility.

Rev 5 - 03/19/2025 - Future revisions to this document supersede this revision.

© 3M 2025. All Rights Reserved.



### 3M Personal Safety Division

#### 3M Fall Protection Business

3833 SALA Way  
Red Wing, MN 55066-5005

3M PSD products are occupational use only.

### 3M Canada

3M Fall Protection Business  
600 Edwards Blvd, Unit #2  
Mississauga, ON L5T 2V7

### In United States of America

Technical Service: 1-800-328-6146  
Customer Service: 1-800-328-1667  
3M.com/workersafety

### In Canada

Technical Service: 1-800-267-4414  
Customer Service: 1-800-364-3577  
3M.ca/Safety

© 3M, 2025. All Rights Reserved. 3M and DBI-SALA are trademarks of 3M.

Used under license in Canada. All other trademarks are property of their respective owners. Please recycle.