



Technical Data Sheet

3M™ Double Coated Tapes 9495MPF



[Product Details](#)

Product Description

3M™ Double Coated Tape 9495MPF is a double coated film tape which features a clear polyester film liner, 200MP acrylic adhesive, and a thin clear polyester film carrier.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Test Condition	Value
Color			Clear
Adhesive Carrier			PET
Adhesive Thickness		Faceside	0.07 mm (2.9 mil) ¹
Adhesive Thickness		Backside	0.06 mm (2.3 mil) ²
Carrier Thickness	PSTC-133		0.01 mm (0.5 mil)
Total Tape Thickness	ASTM D3652		0.14 mm (5.7 mil)
Liner			Clear PET
Liner Thickness			0.051 mm (2.0 mil)

¹ Faceside adhesive is on the interior of the roll, exposed when unwound and liner removed.

² Backside adhesive is on the exterior of the roll, exposed when liner is removed.

Typical Performance Characteristics

Backing: 2 mil Aluminum Foil

Test Method: ASTM D3330

Attribute Name	Dwell Time	Temperature	Substrate	Value
90° Peel Adhesion	15 min	23 °C (73 °F)	Stainless Steel	5.7 N/cm (52 oz/in) ¹
90° Peel Adhesion	72 h	23 °C (73 °F)	Stainless Steel	9.8 N/cm (89 oz/in) ¹
90° Peel Adhesion	72 h	70 °C (158 °F)	Stainless Steel	10.7 N/cm (97 oz/in) ¹
180° Peel Adhesion	72 h	23 °C (73 °F)	Stainless Steel	10.0 N/cm (91 oz/in) ¹
90° Peel Adhesion	72 h	23 °C (73 °F)	Aluminum	9.1 N/cm (83 oz/in) ¹
90° Peel Adhesion	72 h	23 °C (73 °F)	ABS	6.9 N/cm (63 oz/in) ¹
90° Peel Adhesion	72 h	23 °C (73 °F)	Acrylic (PMMA)	6.5 N/cm (59 oz/in) ¹
90° Peel Adhesion	72 h	23 °C (73 °F)	Polycarbonate (PC)	9.6 N/cm (87 oz/in) ¹

¹ 300 mm/min (12 in/min)

Static Shear

Substrate: Stainless Steel
Dwell Time: 72 h
Backing: 2 mil Aluminum Foil
Test Method: ASTM D3654

Temperature	Test Condition	Value
23 °C (73 °F)	1000 g	10,000 min ¹
70 °C (158 °F)	500 g	10,000 min ¹

¹ 25 x 25 mm (1 in x 1 in) sample area, test terminated after 10,000 minutes

Substrate: Stainless Steel
Test Condition: 500 g
Test Method: ASTM D3654

Attribute Name	Value
Short Term Temperature Resistance	177 °C (350 °F) ¹
Long Term Temperature Resistance	149 °C (300 °F) ²

¹ Maximum temperature where tape supports indicated load per 6.5cm² (1 in²) in static shear for 60 minutes.

² Maximum temperature where tape supports indicated load per 6.5cm² (1 in²) in static shear for 10,000 minutes.

Electrical and Thermal Properties

Attribute Name	Test Method	Temperature	Test Condition	Value
Thermal Conductivity	ASTM C518	43 °C (109 °F)		0.186 W/m·K ¹
Coefficient of Thermal Expansion	ASTM D696		First Heat	4.84 x 10 ⁻¹ m/m/°C

¹ results listed are at 43 °C (109° F)

Attribute Name	Test Method	Temperature	Test Condition	Value
Dissipation Factor	ASTM D150	23 °C (73 °F)		0.019
Dielectric Strength	ASTM D149		500 vac, rms[60 hz/sec]	1,354 V/mil
Volume Resistivity	ASTM D257	23 °C (73 °F)		2.7 X 10 ¹⁴ Ω-cm
Breakdown Voltage				7,200 V

Handling/Application Information

Application Techniques

For maximum bond strength the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane or isopropyl alcohol.*

*Note: Follow the manufacturer's precautions and directions for use when using solvents.

- Bond strength is dependent upon the amount of adhesive to surface contact developed. Firm application pressure helps develop better adhesive contact and thus improve bond strength.
- Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended for most pressure-sensitive adhesives because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Application Examples

- Graphic overlays
- Nameplates
- LED Lenses
- Appliques
- Decorative Trim

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Industrial Adhesives and Tapes Division
3M Center, St. Paul, MN 55144-1000
3M.com/iatd

©3M 2025 (4/25)