

# 3M™ Cleaning and Workplace Safety

Europe Middle East and Africa (EMEA)  
Full Line Catalogue



A large window in the background shows a person in a white protective suit and mask cleaning the exterior of a building. In the foreground, a grey floor buffer is positioned on a highly reflective, polished blue-grey floor. The room has light-colored walls and a baseboard heater.

**Discover a world of  
affordable, smart  
cleaning equipment  
and supplies, backed  
by practical advice and  
technical knowhow,  
to enhance your  
building and transform  
your business.**

3M provides facility managers and contract cleaners with innovative, sustainable, high-value solutions to help protect a building's life and enhance the performance and productivity of employees.

3M facilities care and cleaning solutions enhance protection, performance and productivity for the life of a building. Whether you need cleaning or janitorial supplies, or facility maintenance materials, 3M products deliver.

We also provide industry-leading Scotch-Brite™ products for food service cleaning needs, from griddle cleaning to appliance cleaning, as well as solutions for testing food quality and safety.



## Facility and operations managers

To help meet the important challenges faced by facilities managers, 3M has developed innovative cleaning and floor protection products that deliver measurable commercial benefits and sustainability advantages.

3M is committed to developing cleaning equipment and supplies that help lower your total maintenance costs. For example, floor care is not measured merely by the expense of cleaning and polishing floor pads, it also includes the cost and difficulty of effort, a measure of floor performance over time and the durability of the products used.

Our wide range of cleaning equipment and supplies are designed to:

- ▶ Safely clean and protect your building, especially in visible high traffic areas
- ▶ Deliver quality results
- ▶ Provide superior cleaning performance
- ▶ Be truly cost effective, by lowering your total costs

## Building service contractors

The key to running a successful cleaning business is the ability to provide outstanding services in a highly competitive environment. It requires hardworking, reliable and well-trained cleaners, backed by experienced cleaning supervisors – and the support of partners who understand what it takes to maintain a first-class reputation.

3M has supported successful contract cleaning firms with innovative janitorial cleaning supplies and maintenance products.

3M continuously innovates to create green cleaning products – making life easier for contract cleaners and helping you manage costs.



## Health care environmental services professionals

For more than 50 years, 3M has offered our health care and education industry partners innovative facility cleaning and facility maintenance and safety solutions to help protect patients, students and staff while reducing overall costs and providing the highest return on investment.

3M's goal is to provide healthy and clean environments. This is achieved by providing quality facility cleaning, maintenance and safety products, a thorough training curriculum and personnel documentation for regulatory compliance and quality assurance programmes. Specific products and programmes have been designed to help educational facility and maintenance managers decrease labour costs and effectively train employees.

3M helps validate the efficacy and performance of your cleaning.



## Food service professionals

The Scotch-Brite™ brand has been recognised as a leading restaurant cleaning supplies brand in the food service industry. The quality, durability and efficiency of Scotch-Brite™ cleaning products is why they have become a top choice for food service professionals around the world. Through innovation and technology, 3M continues to develop efficient and cost-effective products for your commercial kitchen cleaning needs.



## Solutions for architects

As an architect you simply can't afford to specify materials in your designs that might let you down. It's really not worth compromising on product performance and reliability when you could be putting your reputation at risk. 3M understands this and the demands your clients place on you – the need for performance, durability and long-term cost effectiveness. For this reason most architects worldwide feel confident in specifying 3M products and solutions, and work with us to help develop new and innovative solutions for the next generation of sustainable and more efficient buildings.





# Table of contents

## Hand pads and scourers 7

Why choose 3M?	8
Applications	8
Scotch-Brite™ White Cleaning Pad 98 – light duty	9
3M™ General Purpose – Economy Handpad	
Scotch-Brite™ Green Scouring Pad 86 – heavy duty	9
Scotch-Brite™ General Purpose Scouring Pad 96 – medium duty	10
Scotch-Brite™ Sandwich Pad	10
Scotch-Brite™ Thick Sourcing Pads	10
Scotch-Brite™ Slim Scouring Pad	11
Scotch-Brite™ Scouring Pad Rolls	11
Scotch-Brite™ General Purpose Scouring Pad 94 – medium duty	11
Scotch-Brite™ General Purpose Scouring Pads	12
Scotch-Brite™ Pot and Pan Scourer – extra heavy duty	12
Scotch-Brite™ Power Pad 2000 – heavy duty scouring pads	13
Scotch-Brite™ Dual Purpose Scour Pad 96HEX	13
Scotch-Brite™ Purple Pad 2020 – heavy duty	14
Scotch-Brite™ White Cleaning Pad 799 Less Scratching – light duty	15
Scotch-Brite™ Blue Cleaning Pad - light duty	15
Scotch-Brite™ Easy Erasing Pad 4004	15
Scotch-Brite™ Aqua Sponge Scourer – medium duty 74	16
Scotch-Brite™ Handpads	17
3M™ Nail Saver Handpads	17
Scotch-Brite™ High Performance Microfibres	18

## Food service accessories 20

3M™ Twist-Lok™ Pad Holder 961	20
3M™ Oil Quality Test Strips LRSM	20
3M™ Post-it™ Notes Printed	20

## Griddle and appliance cleaning 21

3M™ Twist-Lok™ Pad Holder 961	22
Scotchbrick™ Griddle Scrubber 9537	23
Scotch-Brite™ Griddle Kit High Temperature	23
Scotch-Brite™ Griddle Screen 200	24

## Surface Cleaning Chemicals 25

3M™ Stainless Steel Cleaner and Polish	26
Scotchgard™ Glass Cleaner and Protector	27
3M™ Graffiti Removers	27

## Floor cleaning and dusting tools 28

3M™ Doodlebug™ Pads	29
3M™ Doodlebug™ Holder & Pole 6472	29
3M™ Doodlebug™ Holder & Adaptor 6475	29
3M™ Doodlebug™ Hand Held 6473 Cleaning System	29
3M™ Doodlebug™ White Cleansing 8440 Pad – Light Duty	30
3M™ Doodlebug™ Blue 8242 Pad – Medium Duty	30
3M™ Doodlebug™ Brown Scrub 'n' Strip 8541 Pad – Heavy Duty	30
3M™ Doodlebug™ Hi-Pro 8550 Pad – Extra Heavy Duty	31

## 3M™ Easy Clean System 32

3M™ Easy Trap™ Duster System	32
------------------------------	----

## Floor finishes and coatings 33

Scotchgard™ Stone Floor Protector, 3.8l Bag	35
Scotchgard™ Resilient Floor Protector, 3.8l Bag	35



<b>Floor pads</b>	<b>36</b>
Floor Pads	37
Floor Stripping: Aggressiveness	38
Choosing the right pad for the right job	39
Choose the right 3M floor pad for the job	41
Alternate options	43
Sustainability Certifications for Floor Pads	44
3M™ Trizact™ Diamond TZ Discs	44
3M™ Trizact™ Diamond TZ Discs, Red	44
3M™ Trizact™ Diamond TZ Discs, Blue	44
Scotch-Brite™ Clean & Shine Pad	45
Scotch-Brite™ Surface Preparation Pads	46
Scotch-Brite™ Floor Pads	46
Scotch-Brite™ Eraser	49
Scotch-Brite™ Diamond Brushes	49
Scotch-Brite™ High Productivity	50
Scotch-Brite™ Natural	50
Scotch-Brite™ Autoscrubber	50
Scotch-Brite™ Speed Burnisher	51
Scotch-Brite™ Tan Burnisher	51
3M™ Black Stripper Pad	51
3M™ Brown Stripper Pad	52
3M™ Blue Cleaner Pad	52
3M™ Red Buffer Pad	52
3M™ White Buffer Pad	53
3M™ Basic Floor Floor Pad	53

<b>Floor safety</b>	<b>55</b>
3M™ Safety-Walk™ Slip-Resistant Fine Resilient Tapes and Treads – 200 Series	57
3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads – 300 Series	58
3M™ Safety-Walk™ Slip-Resistant Conformable Tapes and Treads – 500 Series	59
3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads – 600 Series	60
3M™ Safety-Walk™ Coarse Tapes and Treads – 700 Series	62
Primer for 3M™ Safety-Walk™ Applications	63
3M™ Safety-Walk™ Edge Sealing Compound	63
3M™ Safety-Walk™ Rubber Hand Roller	63

<b>Spill management</b>	<b>64</b>
Spill Management	65
Cost Benefits of 3M Sorbents	66
Different Types of Sorbents	67
3M Chemical Sorbents	68
3M Maintenance Sorbents	69
3M Oil Sorbents	70





# Hand pads and scourers

Scotch-Brite™ Commercial Hand Pads Scourers feature a uniform mineral/abrasive coating on fibres throughout the pad. As the pads are used, new mineral is continually exposed, ensuring optimum cleaning performance and a long life.

The quality, durability and efficiency of Scotch-Brite™ cleaning products is why they've become a top choice for food service professionals around the world.

3M provides the right tool for every cleaning task – from light-duty to extra-heavy applications.

Most 3M hand pads are HACCP approved.\*

\*Please contact 3M for HACCP endorsement certification details for specific products you are reviewing/purchasing.



# Why choose 3M?

## Quality

- ▶ Efficient and cost-effective products

## Durability

- ▶ Long lasting usage

## Performance

- ▶ Effective and consistent performance throughout the life of the pad

## Save money

- ▶ Durable, long lasting

## Save labour

- ▶ Scours faster, helping save time on each job

## Breadth of product line

- ▶ Variety of pads, right product for the right application

# Applications

Facilities	Type of soils	Application and services	
<b>Restaurants</b> <ul style="list-style-type: none"><li>▶ Quick serve</li><li>▶ Full serve</li></ul> <b>Food processing facilities</b> <ul style="list-style-type: none"><li>▶ Meat and seafood processing</li><li>▶ Vegetable processing</li><li>▶ Others</li></ul> <b>Commercial buildings</b> <ul style="list-style-type: none"><li>▶ Business</li><li>▶ Hospitals</li></ul> <b>Public buildings</b> <ul style="list-style-type: none"><li>▶ Government</li><li>▶ Schools and universities</li></ul>	<b>Non-food</b> <ul style="list-style-type: none"><li>▶ Stains, marks, scuffs</li><li>▶ Soap scum, hard water stains</li></ul> <b>Non-baked on food</b> <ul style="list-style-type: none"><li>▶ Thin, soft, non-sticky</li><li>▶ Thick, soft, sticky</li></ul> <b>Baked on and burnt food</b> <ul style="list-style-type: none"><li>▶ Thin, crispy</li><li>▶ Thick, hard, stubborn</li></ul>	<ul style="list-style-type: none"><li>▶ Acrylic</li><li>▶ Aluminium</li><li>▶ Appliance</li><li>▶ Baseboard</li><li>▶ Booths, tables and chairs</li><li>▶ Brass/silver</li><li>▶ Ceramic</li><li>▶ China</li><li>▶ Chrome</li><li>▶ Cooking equipment</li><li>▶ Copper</li><li>▶ Countertops/ laminates</li><li>▶ Desks</li><li>▶ Elevator doors</li><li>▶ Glass</li></ul>	<ul style="list-style-type: none"><li>▶ Glass cookware</li><li>▶ Griddle</li><li>▶ Kitchen equipment</li><li>▶ Maintenance equipment</li><li>▶ Mirrors</li><li>▶ Non-stick cookware</li><li>▶ Painted surfaces</li><li>▶ Plasticware</li><li>▶ Porcelain</li><li>▶ Pots and pans</li><li>▶ Railings</li><li>▶ Sinks/tubs/showers</li><li>▶ Stainless steel equipment</li><li>▶ Vinyl</li></ul>

# Hand pads and scourers

## Scotch-Brite™ White Cleaning Pad – 98 – light duty

Soft fibres and a mild abrasive enable this pad to clean most surfaces gently but thoroughly without scratching. Ideal for ‘non-stick’ and delicate surfaces including glass, plastic, fine china, rubber, porcelain, stainless steel and painted fixtures.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100169976	98	240mm x 158mm	3 × 20 pads/case
EMEA	7000089931	98	260mm x 102mm	100 pads/case
EMEA	7100169635	98	260mm x 102mm	60 pads/case



## 3M™ General Purpose – Economy Handpad

Economy pad suited to everyday cleaning of most cooking utensils and equipment.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000077799	12506	150mm x 226mm – white pad	10 × 20 pads/case
EMEA	700097967	12505	150mm x 226mm – green pad	10 × 20 pads/case
EMEA	7000077798	12507	150mm x 3m – black pad	10 × 20 pads/case



## Scotch-Brite™ Green Scouring Pad – 86 – heavy duty

The heavy duty cleaning power of this scourer makes for light work when cleaning grease, grime and baked-on foods.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100170149	86	158mm x 224mm	3 × 10 pads/case
EMEA	7000045876	86	152.4mm x 228.6mm	3 × 12 pads/case
EMEA	7000097754	86	Roll 134mm x 6m	6 rolls/case





## Scotch-Brite™ General Purpose Scouring Pad – 96 – medium duty

For everyday cleaning of most cooking utensils and equipment. High performance pads for every day use in commercial and industrial applications. Ideal for cleaning pots, cooking utensils, bench tops and metal surfaces. Multiple sizes available.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100171931	96	158mm x 224mm	60 pads/case
EMEA	7100171781	96	158mm x 224mm	200 pads/case
EMEA	7000099881	96	SB 96 green sponge	150 pads/case
EMEA	7000097776	96	158mm x 190mm	12 x 15 pads/case
EMEA	7100169682	96	224mm x 158mm	3 x 20 pads/case
EMEA	7100319251		125mm x 96mm	200 pads/case
EMEA	7100171626	96AO	200mm x 136mm	8 x 20 pads/case
EMEA	7100169509	96HPCC	230mm x 150mm	6 x 10 pads/case
EMEA	7100319250	96	105mm x 255mm	100 pads/case
EMEA	7000097777	96S	158mm x 120mm	18 x 15 pads/case
EMEA	7100053715	96		3 x 20 pads/case

## Scotch-Brite™ Sandwich Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100200353	4594	87mm x 131mm	40 pads/case



## Scotch-Brite™ Thick Scouring Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100181560	76	158 mm x 95 mm - black	6 x 10 pads/case
			134mm x 6m	
EMEA	7100180770	350	158mm x 95 mm x 28 mm – white	5 x 6 pads/case
EMEA	7100204484	551	Scotch-Brite™ Thick Scouring Pad green	4 x 10 pads/case
EMEA	7100046567	9000	132mm x 101mm x 23 mm – blue	40 pads/case



## Scotch-Brite™ Slim Scouring Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100169620	Slim	Scotch-Brite™ Slim Black Pad 158mm x 224mm	200 pads/case



## Scotch-Brite™ Scouring Pad Rolls

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000097753	96	240mm x 10m	2 rolls/case
EMEA	7100172468	Black 530	158mm x 3m – roll black	6 rolls/case
EMEA	7100170092	Green	100mm x 10m – roll green	9 rolls/case
EMEA	7100169472	Green 630	158mm x 3m – roll green	6 rolls/case
EMEA	7100169612	Green 650	158mm x 5m – roll green	6 rolls/case
EMEA	7100172215	White	158mm x 10m – roll white	6 rolls/case
EMEA	7100172199	White	100mm x 10m – roll white	9 rolls/case
EMEA	7100170091	Blue 640	200mm x 4m – pre-cut roll blue	6 rolls/case
EMEA	7100171782	Green 670	200mm x 4m – pre-cut roll green	6 rolls/case
SP	7000098181	Green 96	134mm x 6m – pre-cut roll green	2 rolls/ case
EMEA	7100171803	White 690	200mm x 4m – pre-cut roll white	6 rolls/case



## Scotch-Brite™ General Purpose Scouring Pad – 94 – medium duty

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000099880	94 Green	Scotch-Brite™ Scour Pad medium 2.5m	6 rolls/case
EMEA	7100169448	94	Scotch-Brite™ Deep Fat Fryer Scour Pad	60/case





## 3M™ General Purpose Scouring Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000086545	Blue	150mm x 230mm	10 pads/pack
EMEA	7000097788	Green	Roll 6m x 135mm	6 rolls/case
EMEA	7000097801	RB1	Green Pad 110mm x 158mm	100 pads/case
EMEA	7000097803	RB3	Green Pad Heavy Duty Pad 158mm x 224mm	50 pads/case
EMEA	7000086425	RB6B	Green Pad 93mm x 154mm	500 pads/case



## Scotch-Brite™ Pot and Pan Scourer – extra heavy duty

The hardest working pad available; even the most stubborn deposits are scoured clean, especially useful for heavily encrusted pots and pans, kitchen and maintenance equipment. Ideal replacement for stainless steel wool and metal scourers. Open weave construction for easy cleaning.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100157791	450	158mm x 95mm – Blue	10 × 6 pads/case
EMEA	7000089930	88	87mm x 125mm – Green	100 pads/case
EMEA	7000089928	76	103mm x 180mm – Green	100 pads/case



## Scotch-Brite™ Power Pad 2000 – heavy duty scouring pads




Scours 2–4 times faster than conventional commercial scouring pads, and is 6–10 times less abrasive than other medium/heavy-duty commercial scouring products to reduce scratching.\*

- ▶ **Fibre:** durable synthetic fibres that are crimped and heat set to create a strong web
- ▶ **Scouring particles:** unique soil-removing particles for effective scouring, cleaning and scrubbing. Particles are evenly distributed throughout the pad to ensure effective, consistent scouring and lasting performance throughout the life of the pad
- ▶ **Resin:** high-quality bonding resin system designed to provide resistance to degradation from exposure to hot water, detergents and normal cleaning liquids

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100034383	2000	Scotch-Brite™ Power Pad 99mm x 139mm	20 pads/case

## Scotch-Brite™ Dual Purpose Scour Pad 96HEX




Features a yellow raised power dot side that aggressively scours away tough messes with less elbow grease. The smooth side scours away fine particles and grease, leaving a clean and shiny surface.

Use for general purpose cleaning, including:

- ▶ Pots and pans
- ▶ Cooking appliances and utensils
- ▶ Kitchen and maintenance equipment
- ▶ Stainless steel

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100206773	96HEX	146mm x 127mm – Heavy Duty scouring pad	15 pads/case
EMEA	7100208418	96HEXFL	113mm x 98mm – Heavy Duty scouring pad with foam	4 x 4 pads/case
EMEA	7100197274	2000HEX	146mm x 127mm – Medium Duty scouring pad	15 pads/case
EMEA	7100202994	3001HEX	113mm x 98mm – Medium Duty scouring sponge	4 x 4 sponges/case



\*Internal test conducted in the 3M USA laboratory



## Scotch-Brite™ Purple Pad 2020 – heavy duty

Cleans your dirtiest pots and pans twice as fast as conventional heavy duty scouring with less scratching.\* Food debris rinses out of the pad easily. Unique web construction stands up to your toughest jobs. Scratches less than other heavy duty pads.

- ▶ Designed to provide heavy-duty scouring and scrubbing capability with significantly lower scratching potential
- ▶ Contains durable synthetic fibres that are manufactured to develop a strong, open pad surface
- ▶ Mineral particles are distributed evenly on the surface and through the pad to provide consistent scouring over the life of the pad
- ▶ Constructed with resin that resists degradation from exposure to hot water, detergents and most cleaning liquids
- ▶ A good replacement for most applications where steel wool and stainless steel scrubbers are currently used



Country	3M order code	Product no.	Product detail	Packout
	7100079881	2020	114mm x 70mm	24 pads/case



\*Internal test conducted in the 3M USA laboratory

## Scotch-Brite™ White Cleaning Pad 799

### Less Scratching – light duty


A No. 449 Light Duty Scourer Pad on one side and sponge on the other. Ideal for light duty cleaning jobs as it will not scratch most surfaces. Ideal for stainless steel, glass, ceramic, fine china, porcelain, countertops and non-stick surfaces.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100157793	799	131mm x 88mm x 27mm	24 x 10 sponges/case

## Scotch-Brite™ Blue Cleaning Pad – light duty

A light duty scourer pad on one side and sponge on the other. Ideal for light duty cleaning jobs as it will not scratch most surfaces. Ideal for stainless steel, glass, ceramic, fine china, porcelain, countertops and non-stick surfaces.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100157792	770	131mm x 88mm x 27mm	24 x 10 sponges/case

## Scotch-Brite™ Easy Erasing Pad 4004

Soft, flexible pad cleans many surfaces. Innovative white polymeric foam erases hard-to-clean stains, marks and scuffs. Unique blue urethane layer provides durability and keeps hands away from messes. Easy-to-use. Simply wet pad and squeeze out excess water. Use white side of pad to erase marks. Use blue side to wipe away residue.



- ▶ Trademarked bow-tie shape
- ▶ Soft, flexible pad cleans many surfaces without using additional chemicals – just use water
- ▶ Blue urethane foam sponge holds water to keep pad moist, can be used to wipe after use, and keeps the pad intact over its useful life
- ▶ Pad will not scratch glass, ceramic tile, fibreglass, porcelain, Formica®, metal, Corian®, marble, stainless steel, plastic, vinyl and most wall coatings
- ▶ Optimal performance of product is achieved when used with water alone. Detergents and sanitising cleaners are not recommended for use with this product

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100032938	4004CC	114mm x 71mm	3 x 4 pads/case



## Scotch-Brite™ Aqua Sponge Scourer – 74 – medium duty

For general scouring use, this scourer is especially effective for cleaning vats, tanks and cheese making equipment.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7000097835	74	Scotch-Brite™ Handpad Synthetic Laminate Green Pad 95mm x 158mm	8 × 6 sponges/case
EMEA	7100116534	74	Scotch-Brite™ Handpad Green/Brown 94mm x 180mm	12 × 6 sponges/case
EMEA	7100141979	74	Scotch-Brite™ Handpad Green 95mm x 158mm x 27mm	6 × 12 sponges/case
EMEA	7100259744	75	Scotch-Brite™ Handpad Antimicrobial Green 95mm x 158mm	12 × 6 sponges/case
EMEA	7100157863	740	Scotch-Brite™ Green 131mm x 88mm	24 × 10 sponges/case
EMEA	7000099879	740	Scotch-Brite™ Handpad Green 131mm x 88mm x 27mm	8 × 4 sponges/case
EMEA	7100157863	740	Scotch-Brite™ Handpad Green 113mm x 88mm	10 × 24 sponges/case
EMEA	7100157789	744	Scotch-Brite™ Handpad Green 112mm x 72mm x 27mm	6 × 20 sponges/case
EMEA	7100157787	740E	Scotch-Brite™ Handpad Green 131mm x 88mm x 27mm	10 × 6 sponges/case
EMEA	7100117464	740-T	Scotch-Brite™ Handpad Synthetic Laminate Green Pad	96 sponges/case
EMEA	7100116539	74CC	Scotch-Brite™ Handpad Blue Brown	4 × 15 sponges/case
EMEA	7010028899	74SB	Scotch-Brite™ Handpad Green	20 sponges/case
EMEA	7100117266	74T	Scotch-Brite™ Synthetic Handpad Green	4 × 15 sponges/case

## Scotch-Brite™ Handpads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000037575	55	Scotch-Brite™ Grooved Handpad Beige/Blue 70mm x 130mm	10 × 10/case
EMEA	7000037577	57	Scotch-Brite™ Grooved Handpad Beige/Yellow 70mm x 130mm	10 × 10/case
EMEA	7000037578	58	Scotch-Brite™ Grooved Handpad Beige/Green 70mm x 130mm	10 × 10/case
EMEA	7100259745	63	Scotch-Brite™ DEL SPG White/Pink 95mm x 158mm	12/case
EMEA	7000107401	799	Scotch-Brite™ Sensitive Surface Pink	
EMEA	7100106786	13-21 Blue	Scotch-Brite™ Handpad Blue Grooved 150mm x 375mm	8 × 10/case
EMEA	7100106895	13-21 Green	Scotch-Brite™ Handpad Green Grooved 150mm x 395mm	8 × 10/case
EMEA	7100106908	13-32 Red-Blue	Scotch-Brite™ Handpad Red/Blue Grooved 150mm x 375mm	8 × 10/case
EMEA	7100106896	13-33 Yellow-Blue	Scotch-Brite™ Handpad Yellow/Blue Grooved 150mm x 375mm	8 × 10/case
EMEA	7100106907	13-41 White	Scotch-Brite™ Handpad White Grooved 150mm x 395mm	8 × 10/case



## 3M™ Nail Saver Handpads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100145508	NS56	Beige/Red 70mm x 130mm, 10/PK, 10/CS	10 × 10/case
EMEA	7000097763	NS174	Green/Yellow 70mm x 92mm	10 × 20/case
EMEA	7100144307	NS245	White/Blue 95mm x 158mm	12 × 10/case
EMEA	7000097765	NS363	White/Pink 70mm x 150mm	10 × 10/case
EMEA	7000097764	NS374	Green/Yellow 70mm x 150mm	10 × 10/case
EMEA	7000098074	NS2020	Blue/Purple 130mm x 70mm	8 × 6 pads/case
EMEA	7000098073	NS2030	Black/Black 130mm x 70mm – Hi Pro	9 × 6 pads/case
EMEA	7000097767	NS2272	White/Blue 95mm x 150mm	10 × 10/case
EMEA	7000097797	NS2276	White/Blue 70mm x 150mm	20 × 6/case
EMEA	7000097768	NS2282	Sky Blue/Orange 95mm x 150mm	10 × 10/case
EMEA	7000097798	NS2286	Green/Yellow 70mm x 150mm	12 × 6/case
EMEA	7000097769	NS3372	White/Blue 70mm x 150mm	10 × 10/case
EMEA	7000097770	NS3381	Sky Blue/Orange 70mm x 92mm	10 × 20/case
EMEA	7000097771	NS3382	Sky Blue/Orange 70mm x 150mm	10 × 10/case
EMEA	7000097772	NS4600	Blue/Blue 70mm x 150mm	10 × 10/case
EMEA	7100144451	NS274	Green/ Yellow 95mm x 158mm	6 × 10/case
EMEA	7000097785	NS105	White/ Blue 70mm x 130mm	10 × 10/case
EMEA	7000097784	NS106	White/Red 70mm x 130mm	10 × 10/case
EMEA	7000097787	NS107	White/Yellow 70mm x 130mm	10 × 10/case
EMEA	7000097786	NS108	White/Green 70mm x 130mm	10 × 10/case
EMEA	7000037574	NS274	Yellow/Green 95mm x 150mm	10 × 10/case






## Scotch-Brite™ High Performance Microfibres

The High Performance microfibre is an effective way to clean and polish almost any surface without the use of chemicals. The microfibre itself is chemical-free and picks up dirt, oil and grease without streaking or smearing. The microfibre can be reused by throwing it in the washing machine. The microfibre can be used on virtually any surface. Try it on plastic, glass, mirrors, brass, stainless steel, chrome, metal, marble, painted metals, ceramic, fibreglass, electronic equipment, computer monitors. Great for removing lipstick from cups and glasses.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100314526	2011Y	360mm x 360mm – Yellow High Perf	8 × 50 microfibres/case
EMEA	7100314672	2010W	360mm x 360mm – White Economy	10 cloths/pack, 5 packs/case
EMEA	7100314694	2011B	360mm x 360mm – Blue High Perf	8 × 50 microfibres/case
EMEA	7100314748	2011G	360mm x 360mm – Green High Perf	8 × 50 microfibres/case
EMEA	7100314800	2011R	360mm x 360mm – Red High Perf	8 × 50 microfibres/case
EMEA	7100315137	2010R	360mm x 360mm – Red Economy	10 cloths/pack, 5 packs/case
EMEA	7100315156	2011M	360mm x 360mm – Assorted Colours High Perf	10 × 3 microfibres/case
EMEA	7100315157	2011BI	360mm x 360mm – Blue Industry	8 × 50 microfibres/case
EMEA	7100315159	2010G	360mm x 360mm – Green Economy	10 cloths/pack, 5 packs/case
EMEA	7100315160	2010B	360mm x 360mm – Light Blue Economy	10 cloths/pack, 5 packs/case
EMEA	7100315160	2010Y	360mm x 360mm – Yellow Economy	10 cloths/pack, 5 packs/case



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100024779	Chamois	Heavy Duty Chamois Wipe 210mm x 280mm	20 × 5 wipes/case
EMEA	7012769510	HP Green	Scotch-Brite™ High Performance Green 32cm x 36cm	
EMEA	7100044261	MD Blue	Scotch-Brite™ Micro Duett Pad Blue 350mm x 400mm	20 × 5 wipes/case
EMEA	7100043533	MD Green	Scotch-Brite™ Micro Duett Pad Green 350mm x 400mm	20 × 5 wipes/case
EMEA	7100043535	MD Red	Scotch-Brite™ Micro Duett Pad Red 350mm x 400mm	20 × 5 wipes/case
EMEA	7100043536	MD Yellow	Scotch-Brite™ Micro Duett Pad Yellow 350mm x 400mm	20 × 5 wipes/case
EMEA	7000061419	MFU14	3M™ Universal 14 Blue 400mm x 400mm	10 × 10 wipes/case
EMEA	7000103428	SB2010 Green	Scotch-Brite™ 2010 Green 320mm x 360mm	10 × 5 wipes/case
EMEA	7100010928	SB2011	Scotch-Brite™ High Performance Blue 320mm x 360mm	400/case
EMEA	7100064687	SB2012 Blue	Scotch-Brite™ 2012 Blue, Personalised 320mm x 360mm	
EMEA	7100087025	SB2012 Blue	Scotch-Brite™ 2012 Blue 360mm x 360mm	10/pack
EMEA	7100087024	SB2012 Green	Scotch-Brite™ 2012 Green 360mm x 360mm	10/pack
EMEA	7100087657	SB2012 Red	Scotch-Brite™ 2012 Red 360mm x 360mm	10/pack
EMEA	7100087026	SB2012 Yellow	Scotch-Brite™ 2012 Yellow 360mm x 360mm	10/pack
EMEA	7000077816	SB2030 Red	Scotch-Brite™ 2030 Medium Performance Red 300mm x 400mm	10 × 5/case
EMEA	7000077817	SB2030 Yellow	Scotch-Brite™ 2030 Medium Performance Yellow 300mm x 400mm	10 × 5/case
EMEA	7000114219	HP 2010 Blue	SQ21 High Performance Blue	25 wipes/case
EMEA	7000114221	HP 2010 Green	SQ21 High Performance Green	25 wipes/case
EMEA	7000114220	HP 2010 Red	SQ21 High Performance Red	25 wipes/case
EMEA	7000114222	HP 2010 Yellow	SQ21 High Performance Yellow	25 wipes/case



# Food service accessories

## 3M™ Twist-Lok™ Pad Holder 961

A holder specially designed for use with every Scotch-Brite™ hand pad which makes cleanup jobs faster, easier and safer.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100247093	961	Hand Pad/ Scourer Holder	10 holders/case



## 3M™ Oil Quality Test Strips LRSM

A paper test strip with four coloured bands that change colour from blue to yellow as the levels of free fatty acids increase in your shortening.


Country	3M order code	Product no.	Product detail	Packout
EMEA	7000038381	1005	Test strips	40 strips/bottle, 4 bottles/case
EMEA	7000077806	LRSM20	Test strips	10 × 20 strips/case
EMEA	7100036093	LRSM50	Test strips	4 × 50 strips/case
EMEA	7000038381	LRSM40	Test strips 1005	4 × 40 strips/case
EMEA	7000105447	SRSM40	Test strips 1024	40 strips/case



## 3M™ Post-it™ Notes Printed

Traceability for food processing.

Country	3M order code	Product no.	Product detail	Packout
Denmark	7100046103	1040DN	3M™ Post-it™ Notes Printed 76mm x 25mm	
France	7100038229	1040FR	3M™ Post-it™ Notes Printed 100mm x 40mm 50 sheets	12 × 6 packs/case
France	7100043411	1040FR	3M™ Post-it™ Notes Printed 76mm x 25mm	bulk
France	7100044992	1040FR100	3M™ Post-it™ Notes Printed 76mm x 25mm 100 sheets	20 × 10 packs/case
Norway	7100046104	1040NO	3M™ Post-it™ Notes Printed 76mm x 25mm	
Sweden	7100046107	1040SE	3M™ Post-it™ Notes Printed 76mm x 25mm	





A close-up photograph showing a person's hand holding a blue-handled metal griddle cleaning pad. The pad is being used to scrub a metal surface, likely a griddle, which is covered in a dark, greasy residue. The background is slightly blurred, showing more of the metal surface and some steam or smoke rising from it.

# Griddle and appliance cleaning

3M offers a wide portfolio of safe and effective cleaning solutions for griddles, fryers and beyond.

These solutions range from the traditional griddle brick cleaning system to our advanced Quick Clean Griddle cleaning system. 3M offers a range of scouring pads to suit your cleaning needs.

\*Please contact 3M for HACCP endorsement certification details for specific products you are reviewing/purchasing



# Griddle and appliance cleaning

## 3M™ Scotch-Brite™ Fryer and Kitchen Cleaning Tool

Scotch-Brite™ Fryer and Kitchen Cleaning Tool is your versatile, go-to solution to clean a wide range of commercial kitchen surfaces.

Grey heavy duty pad: heat resistant up to 176°C. Ideal for cleaning open vat style fryers and to remove soil build up on flat surfaces. Green medium duty pad: with polishing abrasive, heat resistant up to 176°C. Thin web suited to cleaning hard-to-reach areas. Use to remove grease and food soil between coils and on flat surfaces. Blue low scratch cleaning pad: low scratch pad that is heat resistant up to 176°C. Use to remove grease and food soil between coils and on flat surfaces.

- ▶ Designed to reach and clean tight spaces, gaps and hard-to-reach areas of fryers
- ▶ Adjustable to three different positions to provide leverage for cleaning various surfaces and hard to reach areas in fryers
- ▶ Ideal for cleaning most fryers and other flat surfaces
- ▶ Heat-resistant, durable and long lasting
- ▶ Extended position for longer reach – keeps your hands away from potential hot spots whilst delivering the leverage you need
- ▶ High-quality bonding resin system designed to provide resistance to degradation from exposure to hot water, detergents and normal cleaning liquids



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100135691	905SB	Fryer and Kitchen Cleaning Tool	1 tool/case
EMEA	7000127899	901SB	Heavy Duty Grey Cleaning Pad	6 pads/case
EMEA	7000127900	902SB	Medium Duty Green Cleaning Pad	6 pads/case
EMEA	7999127901	903SB	Light Duty Blue Cleaning Pad	6 pads/case
EMEA	7000127899	901	High Duty Grey Cleaning Pad	6 pads/case
EMEA	7000127900	902	Medium Duty Green Cleaning Pad	6 pads/case
EMEA	7000127901	903	Low Scratch Blue Clean Pad	6 pads/case
EMEA	7100135691	905	Fryer and Kitchen Cleaning Tool black/green 57mm x 457mm	1 tool/case
EMEA	7100247093	961	Twist-Lok Pad Holder	10 holders/case

## Scotchbrick™ Griddle Scrubber 9537

This easy-to-use, one-piece griddle scrubber is for flat griddles at any operating temperature. The built-in, heat-resistant handle helps protect hands from burns, grease and grime.

- ▶ Abrasive mineral particles evenly distributed throughout the pad ensure effective, consistent and long-lasting performance throughout the life of the pad
- ▶ A combination of pad and handle to function as a tool to help keep hands away from hot and dirty surfaces
- ▶ Aggressive, heavy duty and open pad construction to provide fast cleaning and multiple uses, resist clogging and rinse clean easily

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100195551	9537	Griddle Scrubber – Disposable	12 scrubbers/ case
EMEA	7100197488	46CC	Scotch-Brite™ Griddle Cleaner Pad	6 × 10 pads/ case
EMEA	7100064741	46SB	Scotch-Brite™ Griddle Polish Pad	3 × 20 pads/ case
EMEA	7000109262	82	Scotch-Brite™ Heavy Duty Griddle Cleaner Pad	40 pads/ case
EMEA	7000079857	9537 Red	ScotchBrick™ Griddle Scrubber 82mm x 140mm x 44mm	3 × 4 scrubbers/ case
EMEA	7100169610	9537 Red	ScotchBrick™ Griddle Scrubber 82mm x 140mm x 44mm	12 scrubbers/ case
EMEA	7100082545	9537	ScotchBrick™ Griddle Scrubber 102mm x 152mm x 76mm	12 scrubbers/ case



## Scotch-Brite™ Griddle Kit High Temperature

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100085576	482	Pad Holder 200°C	10 holders/ case
EMEA	7000000655	82G	114mm x 140mm – Brown Pad 200°C	4 × 10 pads/ case






## Scotch-Brite™ Griddle Screen 200

Designed for heavy duty cleaning and removal of carbonised grease and food build-up on flat top griddles.

- ▶ High-quality synthetic fabric backing to provide long lasting usage
- ▶ Abrasive minerals selected to provide remarkable scouring for the griddle cleaning
- ▶ Aggressive, heavy-duty and open screen construction to provide fast cleaning and multiple uses, resist clogging and rinse clean easily
- ▶ Heat-resistant screen to allow for griddle cleaning at operating temperature throughout the day



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100231996	Griddle Screen 200	101mm x 139mm	10 × 20 screens/case

A woman with long brown hair in a ponytail, wearing a dark grey short-sleeved shirt and black trousers, is cleaning a large glass window. She is holding a blue cloth in her right hand and a white spray bottle with a blue label in her left hand. The window reflects the sky and shows a view of green trees outside. The floor is covered with a patterned carpet.

# Surface cleaning chemicals

Cleaning power where and when you need it.



# Surface cleaning chemicals

## 3M™ Stainless Steel Cleaner and Polish

Ideal for stainless steel, chrome, laminated plastics and aluminium surfaces. With a high-gloss formula, it wipes clean with no streaks or build-up, resists fingerprints and masks surface blemishes. Pleasant citrus fragrance.

- ▶ Cleans and polishes in one step
- ▶ Pleasant citrus fragrance
- ▶ Leaves a light protective film
- ▶ Masks blemishes
- ▶ Slows resoiling
- ▶ Reduces fingerprinting
- ▶ Resists streaking
- ▶ Leaves no greasy build-up on surfaces
- ▶ HACCP certified product



Country	3M order code	Product no.	Product detail	Packout
FR, GER, IT, POL, BENELUX	7000042450		Aearosol spray can 600ml	12 cans/case
SP, PT, TUR, GR	7000116804		Aearosol spray can 600ml	12 cans/case
NO, SW, FI, DEN	7000116805		Aearosol spray can 600ml	12 cans/case
SA	7000000697		Aearosol spray can 621ml	12 cans/case





## Scotchgard™ Glass Cleaner and Protector

3M™ Glass Cleaner and Protector with Scotchgard™ Protection leaves an invisible layer of protection on glass for easier cleaning after routine use. It reduces fogging on windows and mirrors with repeated use, leaving an attractive shine. Cleans (but may not protect) other surfaces.

- ▶ Automatic dispensing eliminates measuring and mixing and helps ensure accurate dilutions
- ▶ Green Seal™ GS-37 Certification
- ▶ Streak-free formula
- ▶ HACCP certified product

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100038228	GLCLEAN	Pump spray bottle 950ml	12 bottles/case



## 3M™ Graffiti Removers

Efficient and environmentally friendly liquid form for faster removal without odour.

- ▶ Biodegradable raw materials, no aromatic, aliphatic or chlorinated solvent
- ▶ Easily neutralises with water
- ▶ Available in spray or 5l container

Country	3M order code	Product no.	Product detail	Packout
EU	7000082043	GR1500	Graffiti Remover – painted surfaces – Spray	4 × 500ml/ case
EU	7000082045	GR 1500	Graffiti Remover – painted surfaces – Refill	4 × 5l/case
EU	7100030785	GR 3000	Graffiti Remover – porous surfaces – Spray	4 × 500ml/ case
EU	7100030786	GR 3000	Graffiti Remover – porous surfaces – Refill	4 × 5l/case
UK MEA	7000082039	GR 1500	Graffiti Remover – painted surfaces – Spray	4 × 500ml/ case
UK MEA	7100030784	GR 3000	Graffiti Remover – porous surfaces – Spray	4 × 500ml/ case
UK MEA	7100030783	GR 3000	Graffiti Remover – porous surfaces – Refill	4 × 5l/case





# Floor cleaning and dusting tools

3M has a range of dusters, mops, sweepers and doodlebugs to make your facilities floors shine. 3M's specially designed 3M™ Easy Clean System is a more efficient way to dust, scrub and shine. The system helps to reduce labour costs, increase performance and cut chemical waste.

# Floor cleaning and dusting tools

## 3M™ Doodlebug™ Pads

3M™ Doodlebug™ Cleaning System – used as part of a general cleaning program to clean baseboards, under equipment and hard-to-reach areas. There are two types of holders and a variety of pads to ensure fast and efficient cleaning.

### 3M™ Doodlebug™ Holder and Pole 6472

This pad holder comes with a swivel joint which is ideal for reaching awkward areas. The supplied extension handle helps to clean floors, walls and other hard-to-reach places.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000002232	6472	Kit with pad	4 kits/case



### 3M™ Doodlebug™ Holder and Adaptor 6475

This pad holder also comes with a swivel joint, but instead of the extension handle, we have included an adaptor that will enable you to fit a pole of your choice (25mm diameter).

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100277508	6474	Swivel Head Pad Holder and Adaptor	6 packs/case
EMEA	7100193869	Kit	Doodlebug kit (Hand Held Pad Holder with White and Brown Pad)	6 kits/case



### 3M™ Doodlebug™ Hand Held 6473 Cleaning System

Used as part of a general cleaning program to clean under equipment and hard-to-reach areas.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000052233	6473	Hand Held Pad Holder with White and Brown Pad	4 packs/case





## 3M™ Doodlebug™ White Cleansing 8440 Pad Light Duty

For cleaning delicate surfaces. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.


Country	3M order code	Product no.	Product detail	Packout
EMEA	7100194291	8440	Light Duty 254mm x 117mm	3/pack, 10 packs/ carton



## 3M™ Doodlebug™ Blue 8242 Pad Medium Duty

For medium-duty cleaning and scrubbing. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100194280	8242	Medium Duty 254mm x 117mm	10 × 3 pads/case



## 3M™ Doodlebug™ Red 8343 Pad Heavy Duty

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100194315	8343	Heavy Duty 254mm x 117mm	10 × 3 pads/case



## 3M™ Doodlebug™ Brown Scrub 'n' Strip 8541 Pad Heavy Duty

Designed for tough jobs like removing finish and wax buildup from baseboards and floor edges. A great way to strip stairs. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100194278	8541	Heavy Duty 254mm x 117mm	10 × 3 pads/case
EMEA	7100181775	8541	Heavy Duty 120mm x 80mm	900/case



## 3M™ Doodlebug™ Hi Pro 8550 Pad Extra Heavy Duty

For extra heavy-duty cleaning and stripping. Uniform coating throughout every 3M™ Doodlebug™ pad reduces the number of knots and clumps. Will not be significantly affected by water, detergents or cleaners normally used for floor maintenance. Fits 3M™ Doodlebug™ Pad Holder 6472 or 3M™ Doodlebug™ Handblock Pad Holder 6473.



Country	3M order code	Product no.	Product detail	Packout
EMEA	7000052516	8550	Extra Heavy Duty 115mm x 250mm	40/case

# 3M™ Easy Clean System

## 3M™ Easy Trap™ Duster System

3M™ Easy Trap™ Duster – sweep and dust sheets reduce the risk of bad impressions by trapping up to 8 times more dirt, dust and sand than when using traditional dust mops or a competitive sweeping dust cloth brand. Convenient disposable sheets mean no laundering.

The Easy Trap™ Duster glides through and traps debris, especially hair. Use with any flat floor or high duster tool. Take as little or as much as needed – comes in rolls perforated every 15 cm (6"). Use both sides. Expect maximum results from minimum training in veterinary clinics, hair salons, hospitals, gyms, schools – nearly anywhere.

- ▶ Traps up to 8 times more dirt, dust and sand than conventional flat fringed cotton dust mops or a competitive sweeping dust cloth brand\*
- ▶ No special tool required. Use on existing floor tool or high duster
- ▶ Glides through and traps hair even on wet surfaces – convenient disposable sheets, no laundering required – ideal for picking up glitter and other small particles
- ▶ After one side is used, flip it over and use the other side. Sheets are made with a minimum of 60% recycled content
- ▶ Packaging is made from a minimum 65% total recycled content – a minimum 35% of the total recycled content comes from post-consumer waste



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100081547	Easy Trap™ White 60 sheets	27mm x 152mm x 9.1m	8 rolls/case
EMEA	7100081546	Easy Trap™ White 60 sheets	203mm x 152mm x 9.1m	8 rolls/case
EMEA	7100104251	Easy Trap™ White 60 sheets	127mm x 152mm x 38.1m	2 rolls/case
EMEA	7100081545	Easy Trap™ White 250 sheets	203mm x 152mm x 38.1m	1 roll/case
EMEA	7100104366	Easy Trap™ White 250 sheets	127mm x 152mm x 38.1m	2 rolls/case

\*Internal test conducted in the 3M USA laboratory







# Change your products, not your process.

Get a first-class shine without all the burnishing, scrubbing, stripping and recoating – or the harsh chemicals. The 3M™ Advanced Floor Care System helps you get the results you want with the tasks you do every day.

- ▶ **Beautiful appearance**  
High gloss with less labour and fewer chemicals
- ▶ **Cost savings**  
Fewer needed procedures and less equipment and product use means lower total cost of ownership
- ▶ **Less labour and disruption**  
Reduced need for the recurring maintenance tasks that are most disruptive to your facility and your guests
- ▶ **Protect your investment**  
As use of hand sanitisers becomes more widespread, protect your floors with a coating that can resist the surface damage they can cause

For best results, use all the elements of the 3M™ Advanced Floor Care System as part of your routine floor maintenance. Using the whole system can significantly reduce or eliminate the need for burnishing.





# Floor Finishes and Coatings

## Scotchgard™ Stone Floor Protector, 3.8L Bag

Every year, poorly maintained floors are responsible for more than two million customer and employee fall injuries. The result is billions of dollars in medical, insurance and litigation costs. In just two coats, Scotchgard™ Stone Floor Protector creates an NFSI-Certified 'high traction' surface that can help prevent slips and falls. What's more, you get a long-lasting, glossy, natural-looking floor that's less susceptible to scuffs, black marks, stains and scratches.

- ▶ No stripping or deep scrubbing required, eliminating operator exposure to and environmental release of potentially hazardous stripping chemicals
- ▶ Easy to spot-repair damaged areas
- ▶ Unique hybrid technology that densifies, increases hardness and improves wear

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100180836		3.8L	2 bags/case



## Scotchgard™ Resilient Floor Protector, 3.8L Bag

High Performance floor coating for vinyl and vinyl composition substrates which offers a good and clean appearance over time, with benefits of labour savings and elimination of stripping versus conventional acrylic finishes.

Water-based formula penetrates and protects resilient flooring surfaces such as vinyl, vinyl composition and solid vinyl tile.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100058130	12507	3.8L	2 bags/case



A person wearing a dark blue long-sleeved shirt and khaki pants is operating a 3M floor pad machine. The machine has a vertical silver frame with multiple yellow hoses attached. The person's hands are on the top handle. The machine's base is a large, circular, black and silver unit with a yellow brush or pad at the bottom, resting on a highly reflective, polished floor. The background shows a blurred office or industrial setting with white cabinets and a window.

# Floor Pads

Every 3M™ Floor Pad is made to high-quality standards. Ongoing innovation and advancements in technology make 3M™ Floor Pads more effective than ever.

Each floor pad in 3M's full line is engineered specifically for a particular maintenance task.



# Floor Pads

For over 50 years, high performing 3M™ Floor Pads have been an industry leader. High performance aligns well with durability.

When compared to the nearest competitor, 3M™ Floor Pads:

- ▶ Remove deep scuff marks 7 times faster\*
- ▶ Provide nearly 40% more aggressive floor stripping\*
- ▶ Have 25% better cut on Schiefer test\*
- ▶ Have 50% better burnishing durability\*

Every 3M™ Floor Pad is made to high-quality standards. Ongoing innovation and advancements in technology make 3M™ Floor Pads more effective than ever.




- ▶ Each floor pad in 3M's full line is engineered specifically for a particular maintenance task
- ▶ 3M™ Floor Pad uniformity and quality helps produce less machine wobble and vibration, less operator fatigue, prolonged useful life of the pad and better results on your floors
- ▶ Uniform coating throughout every 3M floor pad helps produce a long, useful life, resulting in less pad usage

## All floor pads are not created equally



The differences between floor pads may seem small but when added up, they can make a big difference to your bottom line in terms of productivity and labour costs.

Consider the following attributes of 3M™ Floor Pads that help set them apart from the competition:

- ▶ Uniform distribution of mineral abrasives throughout the pad – not just on the surface – offers impressive performance and a long, useful life
- ▶ Individually separated and coated fibres help produce more consistent, high-quality results
- ▶ The combination of highly conformable fibres help to provide maximum pad-to-floor contact



3M™ Floor Pads		Other floor pads	
			
<ul style="list-style-type: none"><li>▶ Fibres uniformly coated with resin and mineral throughout entire pad, producing more consistent results</li><li>▶ Combination of highly conformable fibres help to maximise pad-to-floor contact</li></ul>		<ul style="list-style-type: none"><li>▶ Fibres randomly coated with resin and mineral, which can produce inconsistent results</li><li>▶ Larger fibres are less conformable, providing fewer contact points with the floor</li></ul>	

## Floor Stripping: Aggressiveness




\*Pads worn via 50 passes over 3M™ Safety-Walk™ Slip-Resistant Treads 610 (swing machine)

## Floor Stripping: Aggressiveness



\*Worn pad average




\*Pads worn via 25 passes over 3M™ Safety-Walk™ Slip-Resistant Treads 610 (swing machine)


## Burnishing: Durability

### 3M™ Sky Blue Hi-Performance Burnish Pad 3050

After burnishing 350,000 square feet of flooring, pad weight loss was less than 15% versus 32% and 33% with competitive pads\*



\*Based on lab testing with battery burnisher



# Choosing the right pad for the right job

## Stripping



### 3M™ High Productivity Pad 7300 Pad

Most aggressive stripping pad.  
Resists loading and clogging.  
For fast removal of finish.



### Scotch-Brite™ Black Pad

Standard of the industry.  
Consistent proven performance.  
Long pad life.



### Scotch-Brite™ Brown Pad

Conformable for uneven floors.  
Heavy duty scrubbing for 2–4 coat removal.  
Strips prior to refinishing.

## Scrubbing



### Scotch-Brite™ Surface Prep Pad Plus

For heavy-duty scrubbing and for 2–4 coat removal prior to recoating.



### Scotch-Brite™ Blue Pad

For heavy-duty scrubbing for 1–2 coats prior to recoating.

## Cleaning and buffing



### 3M™ Topline Autoscrubber Pad 5000

Scrubs and cleans without dulling the finish.  
Ideal for use on an Autoscrubber.



### Scotch-Brite™ Red Pad

For everyday cleaning and light scrubbing.  
Removes light soil scuff marks and black heel marks.



### Scotch-Brite™ White Pad

For light cleaning to help remove soil and scuff marks with minimal dulling of finish.

## Cleaning and gloss recovery




### Scotch-Brite™ Clean & Shine Pad

Not only provides a deep clean but improves gloss levels over time.  
Ideal for use on an Autoscrubber.

\*See pages for list of floor pad sizes and codes.



## Burnishing



### **3M™ Eraser Burnish Pad 3600**

For harder finishes and high traffic areas.

Removes black marks and returns gloss in fewer passes.

## Best gloss




### **3M™ Natural Blend White Pad 3300**

Excellent results on a wide variety of finishes.

Provides consistent high gloss white minimising swirl marks.

Blend of natural and synthetic fibres.

## Diamond Coated Floor Pads



### **Scotch-Brite™ Sienna Diamond Floor Pad**

For worn and dull floors in poor initial condition.

Cleans, conditions and polishes to a medium shine.

Made of high-quality synthetic fibre, with abrasive particles, including high-quality synthetic diamonds for cleaning and conditioning marble, terrazzo, slate and polished concrete flooring.



### **Scotch-Brite™ Purple Diamond Floor Pad Plus**

For floors with medium shine in good initial condition.

Cleans and polishes floors to a brilliant gloss finish.

Made of high-quality synthetic fibre, with abrasive particles, including high-quality synthetic diamonds for cleaning and conditioning marble, terrazzo, slate and polished concrete flooring.

\*See price pages for list of floor pad sizes and codes.

# Why you should choose 3M™ Floor Pads?

Uniform coating throughout every 3M floor pad helps produce a long, useful life, resulting in less pad usage.

3M™ Floor Pads:

- ▶ Remove deep scuff marks 7 times faster\*
- ▶ Provide 40% more aggressive floor stripping\*
- ▶ Offer 50% better burnishing durability\*

\*When compared to closest competitor. Test done in USA laboratory.



## Maintenance operation

Equipment  
Speed

### Stripping

To remove finish, sealer and contaminants from the floor surface.

Rotary or automatic

Low speed  
175–600 RPM

### Scrubbing

To provide a fresh new surface for finishing.

Rotary or automatic

Low speed  
175–600 RPM

### Cleaning

To remove light soil and other contaminants.

Rotary or automatic

Low speed  
175–600 RPM

### Buffing

To remove scuffs and black heel marks and enhance floor appearance.

Rotary

Low speed  
175–600 RPM

### Burnishing

To remove scuffs and marks, repair finish and improve gloss and image clarity.

Electric,  
battery, propane

Ultra high speed  
1500 RPM  
and above

### Best gloss

To provide a high gloss finish.

Electric,  
battery, propane

Speed

### Stone floor conditioning

To clean and condition worn and dull stone floors.

Rotary, electric,  
automatic, battery  
or propane

Low to ultra  
high speed  
175–1500 RPM and  
above

### Stone floor polishing

To clean and polish stone floors with medium shine in good condition.

Rotary, electric,  
automatic, battery  
or propane

Low to ultra  
high speed  
175–1500 RPM  
and above

## First choice



### 3M™ High Productivity Pad 7300

Our most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping.



### Scotch-Brite™ Surface Preparation Pad Plus

Heavy-duty scrubbing for 2–4 coat removal prior to recoating.




### Scotch-Brite™ Clean & Shine Pad

Use the two-sided Scotch-Brite™ Clean & Shine Pad for daily cleaning and dustless polishing.



### Scotch-Brite™ White Pad

Ideal for removing soil and scuff marks with minimal dulling. Also used to polish wood floors.



### 3M™ Eraser Burnish Pad 3600

Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes and high traffic areas. Excellent durability and minimal finish removal.



### 3M™ Natural Blend White Pad 3300

Blend of natural and synthetic fibres. Excellent results on a wide variety of finishes and traffic conditions. Consistent high gloss with minimal swirl marks.



### Scotch-Brite™ Sienna Diamond Floor Pad Plus

Diamond-coated floor pads clean and condition worn and dull marble, terrazzo, slate and polished concrete, bringing it to a medium gloss.



### Scotch-Brite™ Purple Diamond Floor Pad Plus

Diamond-coated floor pads further enhance the appearance of terrazzo, slate and polished concrete.



## Other choices



### Scotch-Brite™ Black Pad

Standard of the industry.  
Consistent proven performance.  
Long pad life.



### Scotch-Brite™ Blue Pad

Heavy-duty scrubbing for 1–2 coat removal prior to recoating.



### 3M™ TopLine Autoscrubber Pad 5000

Scrubs and cleans. Open construction resists clogging. Ideal for autoscrubbers.



### Scotch-Brite™ Red Pad

Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.



### Scotch-Brite™ Natural Blend White Pad

Blend of natural and synthetic fibres. Ideal for harder finishes and high traffic conditions. Removes marks and scuffs while polishing.



### Scotch-Brite™ Brown Pad

Conformable stripping pad for uneven floors. Super heavy-duty scrubbing for 2–4 coat removal.



### 3M™ Red Buffer Pad 5100

Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.

## Choose the right floor pad for the job

No two floor maintenance jobs are exactly alike. That's why 3M, the inventor of floor pad technology manufactures a wide range of products designed for specific types of equipment and maintenance tasks.

### Green Seal



The Green Seal Environmental Innovation programme recognises products that significantly reduce environmental impact through product innovation. 3M™ Floor Pads\* are certified by Green Seal® for Environmental Innovation based on a design for significantly improved performance, durability, or both, extending the useful life of the floor pad and reducing solid waste generation.

\*3M™ and Scotch-Brite™ Brand Floor Pad families include: 7300, 7200, 5300, 3050, SPP Plus, SPP, Purple Diamond, and Clean & Shine Niagara™ Brand floor pad families include: 7400N, 7200N, 5300N, and Deep Scrubbing Pad.

### Greener Solutions



Greener Solutions is a 3M program for 3M™ Floor Pads\* that are made with at least 50% post-consumer recycled materials and water-based latex resins. Plus, our packaging is 100% recyclable and made with 50–100% recycled content. The polyester fibre used to make a range of floor pads\* contains a minimum of 50% post-consumer recycled content. The recycled polyester fibre used is third-party certified for post-consumer recycled content.


\* 3M™ Brand Floor Pad families include: 3300, 3400, 3500, 3600, 5000, 5100, Sienna and Purple Diamond Pad. Niagara™ Brand Floor Pad families include: 3300N, 3400N, 3500N, 3700N, 5100N, 5400N and 7200N.

# Floor pads

## 3M™ Trizact™ Diamond TZ Discs

Give marble, terrazzo, polished concrete and other porous stone floors new life with 3M™ Trizact™ Diamond TZ Discs featuring proprietary 3M technologies and manufacturing techniques, these advanced abrasives leave exceptionally consistent scratch patterns, maximising efficiency and reducing the number of steps in the restoration process.

- ▶ Uniform cutting surface stays sharp and effective through the life of the discs
- ▶ Wet process does not create dust
- ▶ Compatible with standard floor cleaning equipment (low speed rotary and automatic scrubber)
- ▶ Fast material removal rates
- ▶ Use on your existing flat grinding and finishing equipment – both single and double-sided lapping machines
- ▶ Cleaner operation – reduces machine wear
- ▶ Designed to work with aqueous coolants to reduce clean-up and toxic waste disposal issues associated with abrasive slurries
- ▶ Minimises sub-surface damage
- ▶ Designed for speed, consistency and control needed for flat finishing, grinding and lapping of technical ceramics, glass and exotic metals



## 3M™ Trizact™ Diamond TZ Discs, Red

Diamond disc system for refurbishing and initial finishing of worn and damaged stone floors using low-speed rotary or automatic equipment.

## 3M™ Trizact™ Diamond TZ Discs, Blue

For intermediate finishing and pre-polishing stone floors using low-speed rotary or automatic equipment.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100249986		Red Trizact Disc	4 × 4 discs/case
EMEA	7100249984		Blue Trizact Disc	4 × 4 discs/case

## Scotch-Brite™ Clean & Shine Pad

The Scotch-Brite™ Clean & Shine Pad shines the floor as you clean with it. With repeated use, your floors gradually achieve burnish-quality results without the extra step of actually burnishing. Using a low-speed autoscrubber with just plain water or neutral cleaner, it effectively removes scuff marks faster than traditional floor pads and lasts significantly longer. So you can maintain a shining reflection with less time, effort and equipment.

Use the two-sided Scotch-Brite™ Clean & Shine Pad for daily cleaning and dustless polishing.

- ▶ **Less time to clean**  
Removes black marks 3 times faster than traditional cleaning pads
- ▶ **Reduce burnishing**  
Shine increases with each use to reduce or even eliminate the need for burnishing
- ▶ **Less equipment**  
Clean and shine in the same step using only a lowspeed scrubber
- ▶ **Fewer chemicals**  
Effective with just water
- ▶ **Replace less often**  
Lasts longer than traditional cleaning pads
- ▶ **Versatile**  
Can be used on most coated and uncoated floors including VCT, vinyl, stone, terrazzo, concrete, marble, granite and rubber



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100148036	CS280	Scotch-Brite™ Clean & Shine 280mm	5 pads/case
EMEA	7100147921	CS305	Scotch-Brite™ Clean & Shine 305mm	5 pads/case
EMEA	7100148049	CS330	Scotch-Brite™ Clean & Shine 330mm	5 pads/case
EMEA	7100148038	CS355	Scotch-Brite™ Clean & Shine 355mm	5 pads/case
EMEA	7100148013	CS380	Scotch-Brite™ Clean & Shine 380mm	5 pads/case
EMEA	7100148035	CS406	Scotch-Brite™ Clean & Shine 406mm	5 pads/case
EMEA	7100148018	CS432	Scotch-Brite™ Clean & Shine 432mm	5 pads/case
EMEA	7100148034	CS460	Scotch-Brite™ Clean & Shine 460mm	5 pads/case
EMEA	7100148014	CS480	Scotch-Brite™ Clean & Shine 480mm	5 pads/case
EMEA	7100148015	CS505	Scotch-Brite™ Clean & Shine 505mm	5 pads/case
EMEA	7100148105	CS530	Scotch-Brite™ Clean & Shine 530mm	5 pads/case



## Scotch-Brite™ Surface Preparation Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100151278	SPP+ 305mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151296	SPP+ 330mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151064	SPP+ 355mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151277	SPP+ 380mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151377	SPP+ 406mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151294	SPP+ 432mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151265	SPP+ 460mm	Scotch-Brite™ SPP+ Floor Pad	5/case
EMEA	7100151264	SPP+ 505mm	Scotch-Brite™ SPP+ Floor Pad	5/case



## Scotch-Brite™ Floor Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100182710	Black 254mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182711	Black 280mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182712	Black 305mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182713	Black 330mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182714	Black 355mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182715	Black 380mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182716	Black 406mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182717	Black 432mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182718	Black 460mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182719	Black 480mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182720	Black 505mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182721	Black 530mm	Scotch-Brite™ Black Floor Pad	5/case
EMEA	7100182686	Blue 254mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182687	Blue 280mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182688	Blue 305mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182689	Blue 330mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182690	Blue 355mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182691	Blue 380mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182692	Blue 406mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182693	Blue 432mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182694	Blue 460mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182695	Blue 480mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182696	Blue 505mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182697	Blue 530mm	Scotch-Brite™ Blue Floor Pad	5/case
EMEA	7100182698	Brown 254mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182699	Brown 280mm	Scotch-Brite™ Brown Floor Pad	5/case



Continued...

## Scotch-Brite™ Floor Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100182700	Brown 305mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182701	Brown 330mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182702	Brown 355mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182703	Brown 380mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182704	Brown 406mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182705	Brown 432mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182706	Brown 460mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182707	Brown 480mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182708	Brown 505mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100182709	Brown 530mm	Scotch-Brite™ Brown Floor Pad	5/case
EMEA	7100159535	Green 254mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159890	Green 280mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159536	Green 305mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159894	Green 330mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159885	Green 355mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159879	Green 380mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159880	Green 406mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159881	Green 432mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159882	Green 460mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159889	Green 480mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7000052418	Green 480mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159895	Green 505mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7100159883	Green 530mm	Scotch-Brite™ Green Floor Pad	5/case
EMEA	7000062726	Melamine 330mm	Scotch-Brite™ Melamine Floor Pad	5/case
EMEA	7000062727	Melamine 370mm	Scotch-Brite™ Melamine Floor Pad	5/case
EMEA	7000062728	Melamine 406mm	Scotch-Brite™ Melamine Floor Pad	5/case
EMEA	7000032549	Melamine 432mm	Scotch-Brite™ Melamine Floor Pad	5/case
EMEA	7000062985	Melamine 508mm	Scotch-Brite™ Melamine Floor Pad	5/case
EMEA	7100159512	Purple 254mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159510	Purple 305mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159513	Purple 330mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159507	Purple 355mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case



Continued...

## Scotch-Brite™ Floor Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100159498	Purple 380mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159493	Purple 406mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159499	Purple 432mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159500	Purple 460mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159501	Purple 480mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159502	Purple 505mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159503	Purple 530mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100159505	Purple 685mm	Scotch-Brite™ Purple Diamond Floor Pad Plus	5/case
EMEA	7100182735	Red 203mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182723	Red 280mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182734	Red 280mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182724	Red 305mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182725	Red 330mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182726	Red 355mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182727	Red 380mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182728	Red 406mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182729	Red 432mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182730	Red 460mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182731	Red 480mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182732	Red 505mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182733	Red 530mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100182722	Red 254mm	Scotch-Brite™ Red Floor Pad	5/case
EMEA	7100200175	Sienna 406mm	Scotch-Brite™ Sienna Diamond Floor Pad	5/case
EMEA	7100200177	Sienna 432mm	Scotch-Brite™ Sienna Diamond Floor Pad	5/case
EMEA	7100200176	Sienna 505mm	Scotch-Brite™ Sienna Diamond Floor Pad	5/case
EMEA	7100159878	White 280mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159886	White 305mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159888	White 330mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159945	White 355mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159946	White 380mm	Scotch-Brite™ White Floor Pad	5/case



Continued...



## Scotch-Brite™ Floor Pads

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100159891	White 406mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159897	White 432mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159892	White 460mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159896	White 480mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159893	White 505mm	Scotch-Brite™ White Floor Pad	5/case
EMEA	7100159884	White 530mm	Scotch-Brite™ White Floor Pad	5/case



## Scotch-Brite™ Eraser

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000002119	Eraser Burnish 432mm	3M™ Eraser Burnish Floor Pad 3600	5/case
EMEA	7000052177	Eraser Burnish 480mm	3M™ Eraser Burnish Floor Pad 3600	5/case
EMEA	7000002120	Eraser Burnish 505mm	3M™ Eraser Burnish Floor Pad 3600	5/case
EMEA	7000052179	Eraser Burnish 685mm	3M™ Eraser Burnish Floor Pad 3600	5/case
EMEA	7000052178	Eraser Burnish 530mm	3M™ Eraser Burnish Floor Pad 3600	5/case



## Scotch-Brite™ High Productivity

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000045865	High Pro Black 330mm	3M™ High Productivity Floor Pad 7300	5/case
EMEA	7000045866	High Pro Black 380mm	3M™ High Productivity Floor Pad 7300	5/case
EMEA	7000045867	High Pro Black 406mm	3M™ High Productivity Floor Pad 7300	5/case
EMEA	7000028430	High Pro Black 432mm	3M™ High Productivity Floor Pad 7300	5/case
EMEA	7000045868	High Pro Black 460mm	3M™ High Productivity Floor Pad 7300	5/case
EMEA	7000000654	High Pro Black 505mm	3M™ High Productivity Floor Pad 7300	5/case



## Scotch-Brite™ Natural

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000046007	Natural Blend White 432mm	3M™ Natural Blend White Pad 3300	5/case
EMEA	7000000714	Natural Blend White 505mm	3M™ Natural Blend White Pad 3300	5/case



## Scotch-Brite™ Autoscrubber

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000045996	Almond 355mm	3M™ Topline Autoscrubber Pad 5000	5/case
EMEA	7000045997	Almond 380mm	3M™ Topline Autoscrubber Pad 5000	5/case
EMEA	7000045998	Almond 406mm	3M™ Topline Autoscrubber Pad 5000	5/case
EMEA	7000045999	Almond 432mm	3M™ Topline Autoscrubber Pad 5000	5/case
EMEA	7000046000	Almond 460mm	3M™ Topline Autoscrubber Pad 5000	5/case
EMEA	7000046001	Almond 480mm	3M™ Topline Autoscrubber Pad 5000	5/case



## Scotch-Brite™ Tan Burnisher

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000045914	Tan Burnish 432mm	3M™ Tan Burnish Floor Pad 3400	5/case
EMEA	7000120647	Tan Burnish 460mm	3M™ Tan Burnish Floor Pad 3400	5/case
EMEA	7000045915	Tan burnish 508mm	3M™ Tan Burnish Floor Pad 3400	5/case



## 3M™ Blue Cleaner Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000045904	Blue 5300 10"	3M™ Blue Cleaner Pad 5300 10in	5/case
EMEA	7000045905	Blue 5300 11"	3M™ Blue Cleaner Pad 5300 11in	5/case
EMEA	7000042729	Blue 5300 12"	3M™ Blue Cleaner Pad 5300 12in	5/case
EMEA	7100006172	Blue 5300 13"	3M™ Blue Cleaner Pad 5300 13in	5/case
EMEA	7000042730	Blue 5300 14"	3M™ Blue Cleaner Pad 5300 14in	5/case
EMEA	7000000673	Blue 5300 15"	3M™ Blue Cleaner Pad 5300 15in	5/case
EMEA	7000028444	Blue 5300 16"	3M™ Blue Cleaner Pad 5300 16in	5/case
EMEA	7000000674	Blue 5300 17"	3M™ Blue Cleaner Pad 5300 17in	5/case
EMEA	7100006200	Blue 5300 18"	3M™ Blue Cleaner Pad 5300 18in	5/case
EMEA	7100003274	Blue 5300 20"	3M™ Blue Cleaner Pad 5300 20in	5/case



## 3M™ Black Stripper Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000045896	Black 7200 11"	3M™ Black Stripper Pad 7200 11in	5/case
EMEA	7000028442	Black 7200 13"	3M™ Black Stripper Pad 7200 13in	5/case
EMEA	7000120627	Black 7200 14"	3M™ Black Stripper Pad 7200 14in	5/case
EMEA	7000002189	Black 7200 15"	3M™ Black Stripper Pad 7200 15in, 1in thick	5/case
EMEA	7000120629	Black 7200 16"	3M™ Black Stripper Pad 7200 16in	5/case
EMEA	7000045882	Black 7200 17"	3M™ Black Stripper Pad 7200 17in	5/case
EMEA	7000045883	Black 7200 20"	3M™ Black Stripper Pad 7200 20in	5/case
EMEA	7000002187	Black 7200 20"	3M™ Black Stripper Pad 7200 20in, 1in thick	5/case



## 3M™ Brown Stripper Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000144592	Brown 7100 12"	3M™ Brown Stripper Pad 7100 12in	5/case
EMEA	7000045899	Brown 7100 16"	3M™ Brown Stripper Pad 7100 16in	5/case
EMEA	7000000672	Brown 7100 17"	3M™ Brown Stripper Pad 7100 17in	5/case
EMEA	7000045902	Brown 7100 20"	3M™ Brown Stripper Pad 7100 20in	5/case





## 3M™ Red Buffer Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000000676	Red 5100 12"	3M™ Red Buffer Pad 5100 12in	5/case
EMEA	7000000677	Red 5100 13"	3M™ Red Buffer Pad 5100 13in	5/case
EMEA	7000000678	Red 5100 14"	3M™ Red Buffer Pad 5100 14in	5/case
EMEA	7000000679	Red 5100 15"	3M™ Red Buffer Pad 5100 15in	5/case
EMEA	7000000680	Red 5100 16"	3M™ Red Buffer Pad 5100 16in	5/case
EMEA	7000000662	Red 5100 17"	3M™ Red Buffer Pad 5100 17in	5/case
EMEA	7000045974	Red 5100	3M™ Red Buffer Pad 5100 12in x 18in	20/case
EMEA	7000000681	Red 5100 18"	3M™ Red Buffer Pad 5100 18in	5/case
EMEA	7000000663	Red 5100 20"	3M™ Red Buffer Pad 5100 20in	5/case



## 3M™ White Buffer Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000000684	White 4100 13"	3M™ White Polish Pad 4100 13in	5/case
EMEA	7000000685	White 4100 15"	3M™ White Polish Pad 4100 15in	5/case
EMEA	7000000686	White 4100 16"	3M™ White Polish Pad 4100 16in	5/case
EMEA	7000000664	White 4100 17"	3M™ White Polish Pad 4100 17in	5/case
EMEA	7000052402	White 4100 19"	3M™ White Polish Pad 19in	5/case
EMEA	7000000665	White 4100 20"	3M™ White Polish Pad 4100 20in	5/case
EMEA	7000045913	White 4101 21"	3M™ White Polish Pad 4100 21in	5/case



## 3M™ Basic Floor Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000002198	Basic Black 330mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000052393	Basic Black 355mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000052394	Basic Black 380mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000029751	Basic Black 406mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000029752	Basic Black 432mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000052395	Basic Black 460mm	3M™ Basic Floor Pad Black	5/case
EMEA	7000052420	Basic Blue 305mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000052407	Basic Blue 330mm	3M™ Basic Floor Pad Blue	5/case



Continued...

## 3M™ Basic Floor Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000052409	Basic Blue 381mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000029758	Basic Blue 406mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000029759	Basic Blue 432mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000052410	Basic Blue 460mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000029762	Basic Blue 508mm	3M™ Basic Floor Pad Blue	5/case
EMEA	7000052403	Basic Red 305mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000029764	Basic Red 330mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000002204	Basic Red 355mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000052404	Basic Red 380mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000029757	Basic Red 406mm	3M™ Basic Floor Pad Red	5/case
EMEA	7100064239	Basic Red 432mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000052405	Basic Red 457mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000029761	Basic Red 482mm	3M™ Basic Floor Pad Red	5/case
EMEA	7000052406	Basic Red 482mm	3M™ Basic Floor Pad Red	5/case
EMEA	7100061991	Basic Green 280mm	3M™ Basic Floor Pad Green	10/case
EMEA	7000052413	Basic Green 330mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000052414	Basic Green 355mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000052416	Basic Green 406mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000029760	Basic Green 432mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000052417	Basic Green 460mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000052419	Basic Green 505mm	3M™ Basic Floor Pad Green	5/case
EMEA	7000052397	Basic White 305mm	3M™ Basic Floor Pad White	5/case
EMEA	7000052398	Basic White 330mm	3M™ Basic Floor Pad White	5/case



Continued...

## 3M™ Basic Floor Pad

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000052399	Basic White 355mm	3M™ Basic Floor Pad White	5/case
EMEA	7000052400	Basic White 380mm	3M™ Basic Floor Pad White	5/case
EMEA	7000052401	Basic White 406mm	3M™ Basic Floor Pad White	5/case
EMEA	7000029754	Basic White 406mm	3M™ Basic Floor Pad White	5/case
EMEA	7100064238	Basic White 432mm	3M™ Basic Floor Pad White	5/case
EMEA	7000029757	Basic White 505mm	3M™ Basic Floor Pad White	5/case





A person's legs in blue jeans and brown leather shoes are visible, standing on a concrete floor. The floor is covered with several rectangular pieces of yellow and black diagonal striped safety tape. The background is a grey concrete wall.

# Floor safety

3M offers a full range of functional, slip-resistant tapes and treads suitable for industrial or residential applications in dry, wet or oily conditions.



# Protection that shines

---

As a leading global manufacturer of slip-resistance products, 3M offers a full range of functional, slip-resistant materials designed for the safety of people in the workplace.

These mineral and non-mineral coated products are suitable for industrial or residential applications in dry, wet or oily conditions. 3M™ Safety-Walk™ Slip-Resistant Tapes and Treads adhere to clean, dry surfaces without wrinkling, curling, tearing, shrinking or lifting and offer proven durability for long life. A pressure sensitive adhesive backing makes it easy to apply tapes and treads without the use of anchoring.


3M™ Safety-Walk™ Tapes and Treads meet or exceed the standards and recommended guidelines for slip resistance in accordance with EMEA requirements. Standard rolls and pre-cut treads are available in a variety of sizes, colours and textures ranging from fine resilient, medium resilient and general purpose to coarse and conformable material types.



## 3M™ Safety-Walk™ Slip-Resistant Fine Resilient Tapes and Treads – 200 Series

A fine-textured, slip-resistant surface with a pressure-sensitive adhesive backing provides enhanced safety and comfort in light and barefoot traffic areas.

- ▶ For wet, barefoot-traffic areas
- ▶ Non-mineral, fine-textured, slip-resistant vinyl surface
- ▶ High-performance, water-resistant, acrylate adhesive is ideal for wet conditions
- ▶ Applications include showers, tubs, surfboards, around hot tubs and pools
- ▶ Colours: white and clear




Country	3M order code	Product no.	Product detail	Packout
EMEA	7100139049	220 Clear	3M™ Safety-Walk™ Slip-Resistant Fine 25.4mm x 18.3m	4 rolls/case
EMEA	7000001996	220 Clear	3M™ Safety-Walk™ Slip-Resistant Fine 50.8mm x 18.3m	2 rolls/case
EMEA	7100117201	220 Clear	3M™ Safety-Walk™ Slip-Resistant Fine 50.8mm x 99.6m	1 roll/case
EMEA	7010296263	220 Clear	3M™ Safety-Walk™ Slip-Resistant Fine 101.6mm x 18.3m	1 roll/case
EMEA	7000029632	280 White	3M™ Safety-Walk™ Slip-Resistant Fine 25.4mm x 18.3m	4 rolls/case
EMEA	7000126123	280 White	3M™ Safety-Walk™ Slip-Resistant Fine 101.6mm x 18.3m	1 roll/case



## 3M™ Safety-Walk™ Slip-Resistant Medium Resilient Tapes and Treads – 300 Series

A soft-textured, non-mineral, medium resilient surface bonded to a pressure-sensitive adhesive backed plastic film.

- ▶ For barefoot or shoe-traffic areas
- ▶ Non-mineral, medium-textured, slip-resistant polyolefin surface
- ▶ Textured resilient high-friction surface and durable adhesive provide long-lasting performance
- ▶ Applications include locker rooms, around hot tubs and pools, boats, personal watercraft, water skis, exercise equipment and conveyers
- ▶ Colours: Black and grey



Country	3M order code	Product no.	Product detail	Packout
EMEA	7000126122	280 White	3M™ Safety-Walk™ Slip-Resistant Medium 50.8mm x 18.3m	2 rolls/case
EMEA	7000029629	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 25.4mm x 18.3m	4 rolls/case
EMEA	7000001994	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 50.8mm x 18.3m	2 rolls/case
EMEA	7000126119	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 101.6mm x 18.3m	1 roll/case
EMEA	7000029630	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 152.4mm x 18.3m	1 roll/case
EMEA	7000126120	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 304.8mm x 18.3m	1 roll/case
EMEA	7000001995	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 609.6mm x 18.3m	1 roll/case
EMEA	7100191938	310 Black	3M™ Safety-Walk™ Slip-Resistant Medium 609.6mm x 75m	1 roll/case
EMEA	7000051950	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 25.4mm x 18.3m	4 rolls/case
EMEA	7000001997	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 50.8mm x 18.3m	2 rolls/case
EMEA	7000126124	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 101.6mm x 18.3m	1 roll/case
EMEA	7000029634	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 152.4mm x 18.3m	1 roll/case
EMEA	7100132806	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 304.8mm x 18.3m	1 roll/case
EMEA	7000001998	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 609.6mm x 18.3m	1 roll/case
EMEA	7100158964	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 710mm x 18.3m	1 roll/case
EMEA	7100158875	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 810mm x 18.3m	1 roll/case
EMEA	7000010796	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 914.4mm x 18.3m	1 roll/case

## 3M™ Safety-Walk™ Slip-Resistant Conformable Tapes and Treads – 500 Series

A high-friction, slip-resistant material that has a special pressure-sensitive adhesive-backed aluminium film that conforms around corners and adheres to irregular surfaces.

- ▶ For irregular or contoured surfaces in light to heavy shoe-traffic areas
- ▶ Mineral-coated, high friction slip-resistant surface
- ▶ Aluminium backing conforms to corners, curves and irregular surfaces
- ▶ Aggressive, high performance adhesive forms an excellent bond for a secure hold
- ▶ Applications include stairs, ladders, loading ramps, platforms, irregular surfaces like diamond plating or flat surfaces with rivets or screw heads
- ▶ Safety yellow colour for high visibility and easy identification of hazard areas
- ▶ Colours: Black and yellow



Country	3M order code	Product no.	Product detail	Packout
EMEA	7000010831	510 Black	3M™ Safety-Walk™ Slip-Resistant Conformable 50.8mm x 18.3m	2 rolls/case
EMEA	7000126117	510 Black	3M™ Safety-Walk™ Slip-Resistant Conformable 101.6mm x 18.3m	1 roll/case
EMEA	7000029628	510 Black	3M™ Safety-Walk™ Slip-Resistant Conformable 152.4mm x 18.3m	1 roll/case
EMEA	7000051948	510 Black	3M™ Safety-Walk™ Slip-Resistant Conformable 304.8mm x 18.3m	1 roll/case
EMEA	7000001992	510 Black	3M™ Safety-Walk™ Slip-Resistant Conformable 609.6mm x 18.3m	1 roll/case
EMEA	7100000611	530 Yellow	3M™ Safety-Walk™ Slip-Resistant Conformable 50.8mm x 18.3m	2 rolls/case
EMEA	7100249014	588 White	3M™ Safety-Walk™ Slip-Resistant Conformable 1.2m x 18.3m	1 roll/case
EMEA	7100216201	588 White	3M™ Safety-Walk™ Slip-Resistant Conformable 1.2m x 45.7m	1 roll/case



## 3M™ Safety-Walk™ Slip-Resistant General Purpose Tapes and Treads – 600 Series

A mineral-coated, slip-resistant material adhered by a durable resin to a pressure-sensitive adhesive-backed plastic film.

- ▶ For light to heavy shoe-traffic areas
- ▶ Mineral-coated, high friction slip-resistant surface
- ▶ Highly durable surface withstands the rigors of equipment traffic
- ▶ Low-profile design helps reduce trip hazard
- ▶ High-performance pressure-sensitive adhesive for easy application
- ▶ Applications: flat surfaces, steps, stairways, entrances, ramps, ladders, lawn equipment, snowmobiles, scooters, construction machinery and vehicles
- ▶ Colours: Black, yellow, clear and black/yellow



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100122465	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 19mm x 610mm	50/case
EMEA	7100032939	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 19mm x 18.3m	4 rolls/case
EMEA	7000145695	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 25mm x 20m	24 rolls/case
EMEA	7100067526	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 25.4mm x 18.3m	4 rolls/case
EMEA	7000145696	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 50mm x 20m	12 rolls/case
EMEA	7100009880	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 50.8mm x 18.3m	2 rolls/case
EMEA	7000145697	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 100mm x 20m	12 rolls/case
EMEA	7100020921	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 101.6mm x 18.3m	1 roll/case
EMEA	7000145699	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 150mm x 20m	8 rolls/case
EMEA	7100056206	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 152mm x 610mm	50/case
EMEA	7100011625	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 152.4mm x 18.3m	1 roll/case
EMEA	7100247071	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 304.8mm x 18.3m	1 roll/case
EMEA	7100158973	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 510mm x 18.3m	1 roll/case
EMEA	7100009879	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 609.6mm x 18.3m	1 roll/case
EMEA	7100158552	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 609.6mm x 75m	1 roll/case
EMEA	7100139113	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 914.4mm x 18.3m	1 roll/case
EMEA	7100055223	610 Black	3M™ Safety-Walk™ Slip-Resistant General Purpose 1219.2mm x 50m	1 roll/case
EMEA	7100133324	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 25.4mm x 18.3m	4 rolls/case
EMEA	7000145698	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 50mm x 20m	12 rolls/case

Continued...



Country	3M order code	Product no.	Product detail	Packout
EMEA	7100133325	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 50.8mm x 18.3m	2 rolls/case
EMEA	7100143181	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 101.6mm x 18.3m	1 roll/case
EMEA	7100134978	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 152.4mm x 18.3m	1 roll/case
EMEA	7100143241	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 304.8mm x 18.3m	1 roll/case
EMEA	7100133326	613 Black/ Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 609.6mm x 18.3m	1 roll/case
EMEA	7100158876	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 19mm x 18.3m	4 rolls/case
EMEA	7000042869	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 25.4mm x 18.3m	4 rolls/case
EMEA	7000002135	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 50.8mm x 18.3m	2 rolls/case
EMEA	7100001946	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 101.6mm x 18.3m	1 roll/case
EMEA	7100146041	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 152.4mm x 18.3m	1 roll/case
EMEA	7100146101	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 304.8mm x 18.3m	1 roll/case
EMEA	7100158976	620 Clear	3M™ Safety-Walk™ Slip-Resistant General Purpose 1219.2mm x 50m	1 roll/case
EMEA	7100158961	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 19mm x 18.3m	4 rolls/case
EMEA	7000052247	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 25.4mm x 18.3m	4 rolls/case
EMEA	7000145700	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 50mm x 20m	12 rolls/case
EMEA	7100000852	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 50.8mm x 18.3m	2 rolls/case
EMEA	7000126472	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 101.6mm x 18.3m	1 roll/case
EMEA	7100158963	630 Yellow	3M™ Safety-Walk™ Slip-Resistant General Purpose 304.8mm x 18.3m	1 roll/case
EMEA	7100248893	688 White	3M™ Safety-Walk™ Slip-Resistant General Purpose Printable 1.2m x 18.3m	1 roll/case
EMEA	7100216202	688 White	3M™ Safety-Walk™ Slip-Resistant General Purpose Printable 1.2m x 45.7m	1 roll/case



## 3M™ Safety-Walk™ Coarse Tapes and Treads – 700 Series

Extra-large mineral particles and durable construction provide additional slip resistance in extreme conditions.

- ▶ For extreme, heavy-traffic areas
- ▶ Extra-large abrasive mineral particles help provide a stable slip-resistant surface even in the presence of water or oil
- ▶ High performance adhesive creates an excellent bond to most surfaces
- ▶ An open abrasive pattern resists clogging and reduces clean up time
- ▶ Applications include construction vehicles, ship and plane decks, trains, semi-trailers, oily wet areas, platforms and ramps, machine shops, agriculture and forestry equipment, recreational vehicles
- ▶ Colours: Black and grey



Country	3M order code	Product no.	Product detail	Packout
EMEA	7000145701	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 25mm x 20m	24 rolls/case
EMEA	7100158967	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 25.4mm x 18.3m	4 rolls/case
EMEA	7000145702	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 50mm x 20m	12 rolls/case
EMEA	7100158969	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 50.8mm x 18.3m	2 rolls/case
EMEA	7100159120	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 101.6mm x 18.3m	1 roll/case
EMEA	7000145703	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 101.6mm x 18.3m	6 rolls/case
EMEA	7100158971	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 152.4mm x 300mm	100/case
EMEA	7100158970	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 152.4mm x 18.3m	1 roll/case
EMEA	7100187918	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 304.8mm x 18.3m	1 roll/case
EMEA	7100158968	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 304.8mm x 36.6m	1 roll/case
EMEA	7100158972	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 609.6mm x 18.3m	1 roll/case
EMEA	4100024080	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 609.6mm x 36.6m	1 roll/case
EMEA	7100158966	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 914.4mm x 18.3m	1 roll/case
EMEA	7100158965	710 Black	3M™ Safety-Walk™ Slip-Resistant Coarse Tapes 1219.2mm x 18.3m	1 roll/case
EMEA	7000126124	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 101.6mm x 18.3m	1 roll/case
EMEA	7000001998	370 Grey	3M™ Safety-Walk™ Slip-Resistant Medium 609.6mm x 18.3m	1 roll/case

## Primer for 3M™ Safety-Walk™ Applications

Primer prepares surfaces for proper adhesion prior to application.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100003278	94 Primer	3M™ Primer 94 – various surfaces and substrates	12 × 236ml /case
EMEA	7000001584	94 Primer	3M™ Primer 94 – various surfaces and substrates	12 × 950ml /case



## 3M™ Safety-Walk™ Edge Sealing Compound

3M™ Safety-Walk™ Edge Sealing Compound is a liquid, solvent-based sealer that protects exposed edges of slip-resistant tapes and treads from excessive moisture or liquids.

One 147ml tube with convenient tube applicator seals approximately 22 to 30 linear metres.

Country	3M order code	Product no.	Product detail	Packout
EMEA	7100244310	14080 Sealant	3M™ Safety-Walk™ Edge Sealing Compound	12 tubes/ case



## 3M™ Safety-Walk™ Rubber Hand Roller

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000051951	903 Roller	3M™ Safety-Walk™ Rubber Hand Roller	1 roller/case






# Spill management

3M pioneered the development of synthetic sorbents while leveraging one of our core technologies. Our sorbents contain no abrasive granules that can damage expensive equipment. Instead, they're made from microfibre materials, which contain millions of tiny pockets that absorb and hold liquids.

Choose from petroleum (oil-only), maintenance (for non-aggressive liquids), and chemical (for most aggressive and non-aggressive liquids) formats.





# Spill management

## Now more options

3M Sorbents are available in high-capacity, medium-capacity and traditional absorbency so you can select the right product for the size of your potential spill.

These pads and rolls can be wrung out and reused many times with virtually no loss in absorbency. We complement our rolls and pads with booms, minibooms, pillows, drum covers, spill kits and response packs for use with many types of spills and tasks.

## Sustainability

Our high and medium capacity sorbents are lightweight to reduce the volume of waste going into landfill. 3M Sorbents can be incinerated with very low ash residue.

High-capacity sorbents contain at least 25% recycled content by weight.

Medium-capacity sorbents contain at least 50% recycled content by weight.

## Additional benefits

- ▶ 3M's microbundle technology employs millions of tiny voids to absorb liquid – effectively doubling the capacity of the material
- ▶ 3M Sorbents absorb more so you don't have to use as much and create less waste
- ▶ 3M Sorbents are made from inert polypropylene and polyester fibres that trap liquid in the voids
- ▶ 3M Sorbents are lightweight, non-abrasive and come in many shapes and sizes to perfectly fit your application
- ▶ 3M™ Petroleum Sorbents can be reused; 90 percent of the oil can be wrung out and reclaimed
- ▶ 3M™ High and Medium Capacity Sorbents are made with scrim on one or two sides to help eliminate linting



# Cost benefits of 3M sorbents

3M™ Sorbents' superior absorbency properties offer significant cost benefits associated with materials, labour and disposal.

## Sorbing a 94 litre spill

Number of pads required:

**77 pads**

3M HP-156

petroleum sorbent



**146 pads**

Competitive multi-layer,  
heavy oil only sorbent



## Kilograms (kg) of sorbent going into disposal

**3kg**

3M HP-156

petroleum sorbent

**11kg**

Competitive multi-layer,  
heavy oil only sorbent



## Cost comparison:

### 3M Sorbents vs. clay granules

Materials estimated for cleaning up  
94 litres of fluid

**0.77 case**

3M M-PD1520DD

Sorbent Pads (66 pads)



**5.70 bags**

(20kg/bag)

clay granules



## Labour to sorb 82kg of oil

**32 minutes**

3.1kg

3M Sorbent

Worker  
clean-up time

**2.7kg/min**


**234 minutes**

129kg

clay granules

Worker  
clean-up time  
plus breaks

**0.9kg/min**



## Drums and disposal

**0.5 drum**

3M Sorbent and fluid



**1.6 drums**

Clay granules and fluid





# Different types of sorbents

---



## 3M Oil and Petroleum Sorbents

- ▶ For control and clean-up of petroleum-based fluids
- ▶ Repels water and floats
- ▶ For use on land or water



## 3M Chemical Sorbents

- ▶ For control and clean-up of most hazardous liquids
- ▶ Resists reactions with most hazardous chemicals, including acids
- ▶ Absorbs petroleum-based and aqueous-based solutions



## 3M Maintenance Sorbents

- ▶ For control and clean-up of non-aggressive liquids
- ▶ Helps maintain a clean and safe working environment
- ▶ Absorbs petroleum-based liquids and aqueous-based liquids

# 3M chemical sorbents



Roll




Multiformat (folded)




Pads



Spill Kit



Pillow




Mini-boom

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000002024	C-FL550DD	3M™ Chemical Sorbent Folded 127mm x 15.2m	3 rolls/case
EMEA	7000001947	C-PD914DD	3M™ Chemical Sorbent Pad 235mm x 368mm	25 pads/case
EMEA	7100090373	DRSK-DP	3M™ Chemical Spill Kit 255mm x 300mm	12 kits/case
EMEA	7100090072	HSRK-210	3M™ Chemical Spill Kit 640mm x 1040mm	1 kit/case
EMEA	7100090074	HSRK-75	3M™ Chemical Spill Kit 530mm x 780mm	1 kit/case
EMEA	7100090374	HSRK-5	3M™ Chemical Spill Kit 70mm x 400 mm	5 kits/case
EMEA	7000088220	P-110	3M™ Chemical Sorbent Sheets 280mm x 330m	200 sheets/ case
EMEA	7000088218	P-130	3M™ Chemical Sorbent Rolls 330mm x 30m	2 rolls/case
EMEA	7000088219	P-190	3M™ Chemical Sorbent Rolls 480mm x 30m	2 rolls/case
EMEA	7000051994	P-200	3M™ Chemical Sorbent Mini-boom diameter 75mm x 1.2m	12 booms/case
EMEA	7000052037	P-300	3M™ Chemical Sorbent Pillows 180mm x 380mm	16 pillows/case

# 3M maintenance sorbents



Roll



Pads



Multiformat (folded)



Mini-boom



Pillow

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000001942	M-RGC36100E	3M™ Maintenance Sorbent Rug Coated 910mm x 30m	1 rug/case
EMEA	7100134258	MRG36300E	3M™ Maintenance Sorbent Rug 910mm x 91,4m	1 rug/case
EMEA	7000051875	M-M1003	3M™ Maintenance Sorbent Mini-boom diameter 76mm x 3.7m	4 booms/ case
EMEA	7000051876	M-M1002	3M™ Maintenance Sorbent Mini-boom diameter 76mm x 2.4m	6 booms/ case
EMEA	7000051877	M-M1001	3M™ Maintenance Sorbent Mini-boom diameter 76mm x 1.2m	12 booms/case
EMEA	7000051878	M-N1001	3M™ Maintenance Sorbent Pillows 180mm x 380mm	16 pillows/case
EMEA	7000051880	M-RL38150DD or B2002/07167 (AAD)	3M™ Maintenance Sorbent Rolls 960mm x 46m	1 roll/case
EMEA	7000001950	M-RL15150DD or B2001/07166 (AAD)	3M™ Maintenance Sorbent Rolls 400mm x 46m	2 roll/case
EMEA	7100003876	M-PD-1520DD or A2002/07164 (AAD)	3M™ Maintenance Sorbent Pads 400mm x 520mm	100 pads/case
EMEA	7000001951	M-F2001	3M™ Maintenance Sorbent Folded Multi-Format 120mm x 15.2m	3 sets/ case
EMEA	7000052037	P-300	3M™ Maintenance Sorbent Pillows 180mm x 380mm	16 pillows/case



# 3M oil sorbents



Roll




Sheets



Multiformat (folded)



Mini-boom



Pillow

Country	3M order code	Product no.	Product detail	Packout
EMEA	7000051869	HP-255	3M™ Oil Sorbents Sheets 470mm x 470mm	50 sheets/ case
EMEA	7000002025	P-FL550DD	3M™ Oil Sorbent Multi-Format 430mm x 480mm	3 sets/ case
EMEA	7000001941	HP-156	3M™ Oil Sorbent Sheets 127mm x 15.2m	100 sheets/ case
EMEA	7000088324	T-151	3M™ Oil Sorbent Sheets 390mm x 530mm	200 sheets/ case
EMEA	7000088229	T-270	3M™ Oil Sorbent Booms diameter 100mm x 3m	4 booms/ case
EMEA	7000088228	T-280	3M™ Oil Sorbent Booms diameter 200mm x 3m	4 booms/ case
EMEA	7100011409	T-30	3M™ Oil Sorbent Pillows 180mm x 380mm	16 pillows/ case
EMEA	7000029654	T-4	3M™ Oil Sorbent Mini-boom diameter 75mm x 1.2m	12 booms/ case
EMEA	7100090375	TSK-30	3M™ Tanker Spill Response Kit 430mm x 510mm x 210mm	2 kits/ case
EMEA	7100090376	TSK-15	3M™ Tanker Spill Response Kit 430mm x 490mm x 160mm	5 kits/ case
EMEA	7000001940	HP-100	3M™ Oil Sorbent Roll 960mm x 40m	1 roll/ case
EMEA	7000088321	T-150	3M™ Oil Sorbent Roll 480mm x 40m	1 roll/ case
EMEA	7000073485	T-151	3M™ Oil Sorbents Sheets 450mm x 450mm	200 sheets/ case







**3M United Kingdom PLC**  
3M Centre  
Cain Road,  
Bracknell  
RG12 8HT

**3M Ireland Limited,**  
The Iveagh Building,  
The Park, Carrickmines,  
Dublin  
D18 X015

© 3M 2025. 3M, Doodlebug, Easy Trap, Post it,  
Safety-Walk, Scotchbrick, Scotch-Brite, Scotchgard,  
Trizact are trademarks of 3M Company. All rights reserved.  
OMG1387663.