

3M™ Deadbreak Elbow 635-Series

600-Amp, 200 kV BIL, 35 kV

Data Sheet

September 2026

Product Description

The 3M™ Deadbreak Elbow 635-Series, 600-Amp, 200 kV BIL, 35 kV is a fully shielded separable connector system which meets the requirements of ANSI/IEEE Standard 386 – "Separable Insulated Connector Systems" and IEEE Standard 592 - "Exposed Semi-conducting Shields on High-Voltage Cable Joints and Separable Insulated. These modular kits are available for splicing, dead-ending and connecting to deadfront apparatus such as transformers, switches and switchgear equipped with 600 Amp bushings. The system has the capability for future modification by simply adding or removing components. By combining components, the system can accommodate 3-way, 4-way, parallel feed, etc. connections in various tap splicing configurations. These components are designed to mate with all other manufacturer's products that also conform to IEEE Std. 386, Interface 13.

These kits are designed for use on a 35 kV rated industrial shielded power cables. Kit instructions describe installations for tape shield, flat strap neutral, and jacketed concentric neutral types of solid dielectric cables with extruded semi-conductive insulation shields. A capacitive test point on the insulating plug and the body provides a safe means of testing the circuit without disturbing the bolted connection. The completed installation is fully shielded to provide a complete deadfront connection which is suitable for operation in submerged or direct burial locations.

Agency Approvals & Self Certifications

Meets the requirements of ANSI/IEEE Standard 386 – "Separable Insulated Connector Systems."

For RoHS and REACH information, please visit www.3M.com/regs

Kit Contents

A complete system installation may require one or more deadbreak kits. Each 3M Deadbreak Elbow 635-series kit contains the following materials:

- 1 T-Body; 600A, 35kV with Test Point
- 1 Dead End Plug with Cap
- 1 AL Stud; 35kV
- 1 Compression Connector or Shearbolt Lug
- 1 Copper Tape strip
- 1 Cable Adapter
- 1 3M™ Cold Shrink Jacketing Tube
- 1 Ground Braid Assembly
- 1 Bleeder Wire (for use on JCN & Flat Strap Cable)
- 1 Constant Force Spring
- 2 Mastic Sealing Strips
- 4 Silicone Lubricants
- 1 3M Cable Cleaning Kit CC-2
- 1 Instruction Sheet

3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Applications

The 3M™ Deadbreak Elbow 635-series system provides an easy and reliable method of terminating and splicing main feeder circuits. The T-Body is fully shielded, molded rubber and has been designed and tested to meet the requirements of IEEE Std. 386 and IEEE Std. 592.

This system is designed to terminate shielded power cables with aluminum or copper conductors ranging in size from #2 AWG to 1250 kcmil. It may be installed on any 600 A rated bushing apparatus that meets IEEE Std. 386, Interface 13. The cable adapters will accommodate cable insulation diameters from 0.75" - 2.145".

This system is designed to terminate medium voltage underground distribution cables to switchgear, transformers, sectionalizing cabinets and underground distribution vault applications. This system has also been submersion tested in accordance with IEEE Std. 386.

Characteristics

Voltage Ratings

Description	kV
Standard Voltage Class	35
Maximum Rating Phase-to-Ground	21.1
ac 60 Hz 1 Minute Withstand	50
dc 15 Minute Withstand	103
BIL and Full Wave Crest	200
Minimum Corona Voltage Level	26

Voltage ratings and characteristics are in accordance with ANSI/IEEE Standard 386.

Current Ratings

Description (600 A Interface)	Amperes
Continuous	600 A rms
4 Hour Overload	900 A rms
Short Time	25,000 A rms symmetrical for 0.17 s 10,000 A rms symmetrical for 3.00 s

Current ratings and characteristics are in accordance with ANSI/IEEE Standard 386.



Typical Splice Dimensions

Splice Assembly	Dimension "A" (inches/mm)
2-way Splice	24.68" (626,9mm)
3-way Splice	35.18" (893,6mm)
4-way Splice	45.68" (1160,3mm)
Equipment Connection	12.10" (307,3mm)

Note: All assemblies are approximately 13.5" 342,9mm) long.

3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Examples:



3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Specifications

Installation

A torque wrench and one-inch socket is used to tighten the insulating plug through the compression connector within the T-body, onto a deenergized 600 A bushing interface. Installation should be torqued to 55 ft-lbs of torque.

Interchangeability

All 3M™ Deadbreak Elbow 635-Series, 600 Amp, 200kV BIL, 35kV components conform to the electrical, mechanical and dimensional requirements of ANSI/IEEE Standard 386. The connectors can be used on any comparably rated bushing interface that also meets the requirements of this standard. In addition, all connecting plugs, dead-end plugs, compression connectors and connecting studs are designed to be interchangeable with those available from other major manufacturers.

Data

The 3M Deadbreak Elbow 635-series components can be used on shielded power cables with a rated operating temperature of 90°C and an emergency overload rating of 130°C. Connections made with these kits are rated for Voltages up to 35 kV and meet the requirements of ANSI/IEEE 386 for 600 Amp dead-break interfaces.

Production Tests

Test are conducted in accordance with ANSI/IEEE Standard 386:


- Ac 60 Hz 1 Minute Withstand - 50 kV
- Minimum Corona Voltage Level - 26 kV

Grounding

Grounding of the T-Body and cable metallic shield is performed using the Ground Braid Assembly provided with each kit. The assembly is an integrated design which incorporates both a ground braid for grounding the cable metallic shielding and a ground lead (bleeder wire) for connecting to the T-Body grounding tabs. A solderless connection is made to the cable metallic shield using a constant force spring.

- Ground Braid: 21,600 circular mils, tinned copper (7 AWG copper equivalent)
- Ground Lead (bleeder wire): 14 AWG solid, tinned copper

The typical fault current performance for the 21,600 circular mils Ground Braid can be plotted as follows:



3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Deadbreak Elbow 635-series, 600 Amp, 200kV BIL, 35kV Selection Charts

6 3 5 E W1 X

Table W1 – Cable Adapter	
Code	Insulation Range
D	0.750 – 0.985" (19,1 – 25,0 mm)
E	0.930 – 1.040" (23,6 – 26,4 mm)
F	0.980 – 1.115" (24,9 – 28,3 mm)
G	1.040 – 1.175" (26,4 – 29,9 mm)
H	1.095 – 1.240" (27,8 – 31,5 mm)
J	1.160 – 1.305" (29,5 – 33,2 mm)
K	1.220 – 1.375" (31,0 – 34,9 mm)
L	1.285 – 1.395" (32,6 – 35,4 mm)
M	1.355 – 1.520" (34,3 – 38,6 mm)
N	1.485 – 1.595" (37,7 – 40,5 mm)
P	1.530 – 1.640" (38,9 – 41,7 mm)
Q	1.575 – 1.685" (40,0 – 42,8 mm)
R	1.665 – 1.785" (42,3 – 45,3 mm)
S	1.755 – 1.875" (44,6 – 47,6 mm)
T	1.845 – 1.965" (46,9 – 49,9 mm)
U	1.935 – 2.055" (49,2 – 52,2 mm)
V	2.025 – 2.145" (51,4 – 54,5 mm)

Table X – Lug / Connector Selection				
QLS Code	SB Code	Compression Code	Concentric / Compressed	Compact / Solid
QLS-2-250	---	---	---	#2
QLS-2-250	SB1	22AL	#2	#1
QLS-2-250	SB1	23AL	#1	1/0
QLS-2-250	SB1	24AL	1/0	2/0
QLS-2-250	SB1	25AL	2/0	3/0
QLS-2-250	SB1	26AL	3/0	4/0
QLS-2-250	SB1	27AL	4/0	250
QLS-350-750	SB2	28AL	250	300
QLS-350-750	SB2	29AL	300	350
QLS-350-750	SB2	30AL	350	400
QLS-350-750	SB2	32AL	450	500/550
QLS-350-750	SB3	33AL	500	600
QLS-350-750	SB3	35AL	600	700
QLS-350-750	SB3	36AL	650	750/800
QLS-350-750	SB3	38AL	700/750	900
QLS-750-1250	SB4	39AL	800	900
QLS-750-1250	SB4	40AL	900	1000
QLS-750-1250	SB4	41AL	1000	---
QLS-750-1250	SB4	44AL	1250	---

Note: Not all adapter and lug combinations are valid. For any questions, please contact your local sales representative.

Shearbolt Connector Code Chart

Connector Code	Conductor Size	
	Stranded/Compressed	Compact/Solid
SB1	#2 - 250	#1 - 300
SB2	4/0 - 450	250 - 500
SB3	350 - 750	400 - 900
SB4	750 - 1250	800 - 1250
QLS-2-250	#2 – 250	#2 – 250
QLS-350-750	350 – 750	350 – 750
QLS-750-1250	750 - 1250	750 - 1250

3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Deadbreak Elbow 635-series, 600 Amp, 200kV BIL, 35kV Selection Charts Continued


635E-B series 35kV Base Kit Selection Chart (without connector or cable adapter)

PLEASE READ - - IMPORTANT NOTES:

All kits noted below contain all of the same kit components as are found in the standard kits with the exception of a connector and an adapter. Please utilize the appropriate compression connector or shearbolt connector selection chart and cable adapter selection chart to complete the construction of this kit for your specific application. For conductor sizes not noted on the chart below, please contact your local Sales Representative.

635E-B Series 35kV Base Kit Selection Chart (without connectors or cable adapter)

Kit #	Jacket OD Size	35 kV Conductor Size
635E-B1	0.83" - 1.64" (21,1 - 41,6 mm)	2 - 1/0 AWG (35 - 60 mm ²)
635E-B2	1.27" - 2.17" (32,3 - 55,1 mm)	2/0 AWG - 350 kcmil (70 - 200 mm ²)
635E-B3	1.70" - 2.60" (43,2 - 66,0 mm)	500 - 1250 kcmil (240 - 633 mm ²)



Cable Adapter Chart

Cable Adapter Code	Cable Insulation Range; in. (mm)	Cable Adapter Code	Cable Insulation Range; in. (mm)
635CAD	.750" - .985" (19.1 - 25.0)	635CAN	1.485" - 1.595" (37.7 - 40.5")
635CAE	.930" - 1.040" (23.6 - 26.4)	635CAP	1.530" - 1.640" (38.9 - 41.7)
635CAF	.980" - 1.115" (24.9 - 28.0)	635CAQ	1.575" - 1.685" (40.0 - 42.8)
635CAG	1.040" - 1.175" (26.4 - 29.9)	635CAR	1.664" - 1.785" (42.3 - 45.3)
635CAH	1.095" - 1.240" (27.8 - 31.5)	635CAS	1.755" - 1.875" (44.6 - 47.6)
635CAJ	1.160" - 1.305" (29.5 - 33.2)	635CAT	1.845" - 1.965" (46.9 - 49.9)
635CAK	1.220" - 1.375" (31.0 - 34.9)	635CAU	1.935" - 2.005" (49.2 - 52.2)
635CAL	1.285" - 1.395" (32.6 - 35.4)	635CAV	2.025" - 2.145" (51.4 - 54.5)
635CAM	1.355" - 1.520" (34.4 - 38.6)	- - -	- - -

Additional Connection Components

Part #	Description
635T	600A Deadbreak T-body with Test Point; 35kV
635IPC	Aluminum Insulation Plug with Cap
635CP	Aluminum Connecting Plug; 35kV
635SAL	Stud, AL; 35kV
635SIL5.3	Silicone Lubricant; 5.3 oz Tube

3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

Engineering/ Architectural	The 600 Amp separable insulated connector system shall be rated for continuous operation on single conductor shielded power cables rated up to 35 kV. The system components shall be designed in accordance with the specifications listed in ANSI/IEEE Standard 386 for 600 Amp deadbreak interfaces. The system shall be made up of specific kits designed for splicing, tapping (adding-on), deadending and 600 Amp equipment (apparatus) connecting. Each kit shall contain all of the components necessary for its intended application. The system shall be capable of making 2-way, 3-way or multiple tap splices, and of making connections to ANSI/IEEE 386 specified 600 Amp apparatus bushings.
Maintenance	The components of the 3M Deadbreak Elbow 635-series kits are stable under normal storage conditions. Normal storage and stock rotation are recommended. The rubber and molded epoxy components are not impaired by freezing.
Availability	Deadbreak Elbows 635-series kits are available for splicing and tapping (adding-on) 35 kV shielded power cables, and for equipment (apparatus) connecting to ANSI/IEEE 386 specified 600 Amp bushings. These kits are available from your local authorized 3M electrical distributor.

Note: The core material being removed from the Cold Shrink Tube is mixed polymers and can be recycled with other waste.

3M™ Deadbreak Elbow 635-Series 600-Amp, 200 kV BIL, 35 kV

3M is a trademark of 3M Company.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.



Electrical Markets Division

13011 McCallen Pass, Bldg C.
Austin, TX 78753
800.245.3573
Fax 800.245.0329
www.3M.com/electrical

Please recycle
© 3M 2026. All rights reserved.
78-9237-2597-8 Rev F