

One for All

Versatility applied to
your body shop

3M™ Performance Spray Gun 2 is our next generation of the 3M™ Performance Spray Gun. It's more than just a spray gun – it's an application tool with precision performance you can rely on.

It allows you to spray virtually all common automotive coatings. Just by changing the nozzle, you can switch material within seconds from a heavy textured coating to the finest clear coat atomization.

Use it with 3M™ HVLP or Fine Finish Atomising Heads ranging from 0.9 to 2.0 sizes – the choice is yours.

Additional benefits of
3M™ Performance Spray Gun Series:



Cleans in Seconds



Faster Cycle Times



Precision Performance





3M™ PPS™ Series 2.0 Spray Cup System

Choose the size that you need for your job, prepare and mix your material directly in the cup and connect it to the suitable atomising head for your 3M™ Performance Spray Gun.

This system offers a complete disposable spray cup solution for mixing/measuring, filtering, spraying and for temporary sealing and protection of sprayable coatings.

Designed for all textures

Match various coating textures from very coarse to fine finish by combining the 3M™ Performance Spray Gun 2 with the 3M™ PPS™ Series 2.0 Type H/O Pressure Cup and Conversion Pack.

This powerful combination is specifically designed for applying high viscosity materials, such as protective coatings, that require pressure assistance in a gravity-fed delivery system.

The choice is yours - choose your nozzle type and size, then please always refer to the individual paint manufacturers product recommendations.

Complete Coating Spray Solution

3M™ Performance Spray Gun 2

Optimised and redesigned for your application ease:

- Sleek gun frame – now made with carbon fibre - and smooth finish to help cleanability
- Laser marked control knobs
- Redesigned comfort trigger helps to provide an enhanced spraying experience

Adding to the ergonomic performance, its impact-resistant composite body makes it one of the lightest spray guns available. Designed to deliver best-in-class performance.

3M™ Performance Gravity Fine Finish Atomising Heads

Designed for high performance coatings and optimised for the latest coating technologies, 3M™ Performance Fine Finish Atomising Heads offer a controllable fine finish for all your applications.

3M™ Performance Gravity HVLP Atomising Heads

Superior transfer efficiency and optimization for consistent atomisation meet in our HVLP Atomising Head technology. Enhanced material usage and mixing less paint - yet getting the same or better coverage is possible.

	2.0		1.8		1.6		1.4		1.3		1.2		1.1		0.9	
	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲	● ▲
Automotive Coatings																
High Viscosity Coatings	● ▲		● ▲													
Sprayable Fillers	● ▲		● ▲													
High Build Primer			● ▲		● ▲		● ▲									
Primer Surfacer			● ▲		● ▲		● ▲									
Wet on Wet Primer							● ▲		● ▲							
Primer Sealer							● ▲		● ▲							
Direct Gloss							● ▲									
Single Stage Top Coat							● ▲									
Solvent Base Coat							● ▲		● ▲							
Clearcoat							● ▲		● ▲		● ▲					
Waterborne Base Coat									● ▲		● ▲		● ▲			
UV Primers									● ▲		● ▲		● ▲		● ▲	
Midcoat / Effect Coats									● ▲		● ▲		● ▲		● ▲	
Smart / Spot Repair													● ▲		● ▲	

3M™ Performance Spray Gun 2 with 3M™ Performance Air Flow Control Valve

Part Number	Color
26852	Black

3M™ Performance Gravity Fine Finish Atomising Head

Part Number	Color	Size
26909	White	0.9
26911	Yellow	1.1
26912	Blue	1.2
26913	Green	1.3
26914	Orange	1.4
26916	Purple	1.6
26918	Clear	1.8
26920	Red	2.0

3M™ Performance Gravity HVLP Atomising Head

Part Number	Color	Size
26709	White	0.9
26712	Blue	1.2
26713	Green	1.3
26714	Orange	1.4
26716	Purple	1.6
26718	Clear	1.8
26720	Red	2.0

3M™ Performance Spray Gun with air control valve

Part Number	Color
26832	Grey

3M™ Performance Spray Gun System with PPS™ 2.0

Kit incl. 3M™ Performance Spray Gun, 3M™ Air Flow Control Valve,
3M™ PPS Series 2.0 cup, lids, liners and 15 assorted Atomising Heads

Part Number	Type	Nozzle Size
26978	Fine Finish	1.2, 1.3, 1.4
26778	HVLP	1.2, 1.3, 1.4

3M™ PPS™ Series 2.0 Spray Cup System Kit

Part Number	Filter	Size	Volume
26752	125 micron	Mini	200 ml
26114	200 micron	Mini	200 ml
26312	125 micron	Midi	400 ml
26112	200 micron	Midi	400 ml
26030	80 micron	Standard	650 ml
26026	125 micron	Standard	650 ml
26000	200 micron	Standard	650 ml
26740	125 micron	Large	850 ml
26024	200 micron	Large	850 ml
20730	125 micron	Standard UV-Kit	650 ml
26710	200 micron	Standard UV-Kit	650 ml

3M™ PPS™ Series 2.0 Type H/O Pressure Cup and H/O Conversion Pack

Part Number	Filter	Size	Volume
26124	H/O Cup	Standard/ Large	650 - 850 ml
26121	H/O Cup	Mini/Midi	200 - 400 ml
26837	Conversion Kit		

For more information, visit us at: [3M.co.uk/spray-guns](https://www.3m.co.uk/spray-guns)



3M United Kingdom PLC
Automotive Aftermarket
3M Centre
Cain Road
Bracknell, RG12 8HT
+44 (0)161 237 6391
aadukenquiries@mmm.com

For additional information, including important safety
and warranty information, regarding 3M Automotive
Aftermarket Products, please visit: www.3m.co.uk/aad-info

3M and PPS are trademarks of 3M Company. All other trademarks
are property of their respective owners. Please recycle.
© 3M 2025. All rights reserved.