

**3M** Science.  
Applied to Life.™








Introducing the

# 3M™ Clean Sanding System

Designed with technicians and shop owners in mind.

# 3M™ Clean Sanding System

The 3M™ Clean Sanding System is a complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic and/or electric random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.

-  Designed to reduce dust in the air from sanding for a cleaner workspace.
-  Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time.
-  Compact and mobile. Designed for easy, flexible use around the shop.
-  Compatible with pneumatic and/or electric sanders.
-  Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights.



## How to Setup 3M™ Clean Sanding System

### Step 1: Dust Extractor

Begin by selecting the 3M™ Clean Sanding System Dust Extractor. Included with the dust extractor is a pneumatic hose (33645), y-adapter, filter, and filter bag.

Dust Extractor  
33774



Included in 33774

### Step 2: Power Source, Hoses & Tools

#### Pneumatic

For pneumatic setups, chose desired pneumatic sander(s). Additional hoses can be purchased to run two pneumatic sanders.



#### Electric

For electric set-ups, select desired electric sander(s) and an electric hose. Separate purchase required for electric hose.



	Pneumatic Sander		Electric Sander	
Orbit	3"	6"	3"	6"
2.5 mm (3/32")	33797	33632	33804	33798
5 mm (3/16")	38505	33633	–	33779
8 mm (5/16")	–	33634	–	–
Sheet Sander	33796 (2.75"x7.75")		–	
Length	Pneumatic Hose (Optional)		Electric Hose (Required)	
5m	33645		33646	
8m	33783		–	
10m	33790		–	

### Step 3: Organization

Choose organization accessories to keep tools and product accessible to support an efficient workflow. See the last page for filters, filter bags, and other sanding accessories.



Abrasive Organizer

Handle

33784

33765



Workstation

Workstation Extension





33653

33654

\*33645 Pneumatic hose included in 33774 dust extractor

# 3M™ Abrasive Discs for Collision Repair

Abrasives that meet your needs and dust extraction that helps to improve cut performance and extends disc life. A powerful combination.



## Cubitron™ II

## Blue

## Blue Net New and Improved

## Gold

### Cut Rate



### Cut Rate



### Cut Rate



### Cut Rate



### Disc Life



### Disc Life



### Disc Life



### Disc Life



### Dust Extraction



### Dust Extraction



### Dust Extraction



### Dust Extraction



### Grades

40+, 80+, 120+,  
150+, 180+, 220+,  
240+, 320+, 400+, 500+,  
600+, 800+, 1000+

### Grades

36E, 40E, 40, 80, 80E,  
120, 150, 180, 220, 240,  
320, 400, 500, 600,  
800

### Grades

80, 120, 150,  
180, 220, 240,  
320, 400

### Grades

40D, 80D, 120, 150,  
180, 220, 240, 320,  
400, 500, 600,  
800

### Sizes

3 in, 5 in,  
6 in, 8 in

### Sizes

3 in, 5 in,  
6 in, 8 in

### Sizes

3 in, 5 in,  
6 in, 8 in

### Sizes

3 in, 5 in,  
6 in, 8 in

### Technology

3M™ Precision  
Shaped Grain

### Technology

Engineered Ceramic  
Mineral Blend

### Technology

Engineered Ceramic  
Mineral Blend

### Technology

Aluminum Oxide  
Mineral Blend

### Material

Paper (Multi-Hole)

### Material

Paper (Multi-Hole  
& No Hole)

### Material

Net

### Material

Paper (Multi-Hole  
& No Hole)

### Attachment Type

Hookit™

### Attachment Type

Hookit™ and Stikit™

### Attachment Type

Hookit™

### Attachment Type

Hookit™ and Stikit™

# 3M™ Clean Sanding System

With the 3M™ Clean Sanding System, you have a complete solution that can help create a cleaner workspace and more efficient cycle times.

## Dust Extractor

### 3M™ Dust Extractor

33774 45 Liter, 120V, Plug Type B\*

## Random Orbital Sanders

### 3M™ Precision Random Orbital Sander - Pneumatic

33632 6 in (150 mm), 3/32 (2.5 mm) Orbit\*\*

33633 6 in (150 mm), 3/16 (5 mm) Orbit\*\*

33634 6 in (150 mm), 5/16 (8 mm) Orbit\*\*

33797 3 in (75 mm), 3/32 in (2.5 mm) Orbit\*\*

38505 3 in (75 mm), 3/16 mm (5 mm) Orbit\*\*

### 3M™ Electric Random Orbital Sander

33798 6 in (150 mm), 3/32 in (2.5 mm) Orbit, 120V, Plug Type B\*\*

33779 6 in (50 mm), 3/16 (5 mm) Orbit, 120V, Plug Type B\*\*

33804 3 in (75 mm), 3/32 in (2.5 mm) Orbit, 120V, Plug Type B\*\*

## Orbital Sheet Sander

### 3M™ Precision Orbital Sheet Sander - Pneumatic

33796 7-3/4 in x 2-3/4 in (198 mm x 70 mm)\*\*

## Sanding Blocks

### 3M™ Hookit™ Dust Extraction Flexible Sanding Block

35825 133 mm x 67 mm

35826 178 mm x 67 mm

35827 273 mm x 67 mm

35828 406 mm x 67 mm

35829 Kit (273 mm, 178 mm, 133 mm included)

### 3M™ Hookit™ Dust Extraction Flexible Radius Sanding Block

35830 133 mm x 66 mm

35831 178 mm x 66 mm

35832 273 mm x 66 mm

35833 Kit (273 mm, 178 mm, 133 mm included)

\* One unit of 33652 Y-connector and one unit of 33645 5 m hose included

\*\* One Back-up Pad included

## Hoses

### 3M™ Antistatic Pneumatic Hose

33645 3M™ Antistatic Pneumatic Hose, 5 m

33783 3M™ Antistatic Pneumatic Hose, 8 m

33790 3M™ Antistatic Pneumatic Hose, 10m

### 3M™ Antistatic Electric Hose

33646 3M™ Antistatic Electric Hose, 5 m

33747 3M™ Clean Sanding System Electric Hose Sleeve, 4.5 m

### 3M™ Dust Free Hose (for use with flexible sanding blocks)

05215 3M™ Dust Free Hose Extension Kit, 20 ft

33748 3M™ Clean Sanding System Antistatic Hand Block Hose, 6 m

## Organizational Accessories and Maintenance

### Organizers, Handles and Workstations

33784 3M™ Abrasives Organizer

33765 3M™ Dust Extractor Handle Extension

33653 3M™ Clean Sanding System Workstation

33654 3M™ Clean Sanding System Workstation Extension

### Filters and Bags

33647 3M™ Dust Extractor Filter, 2 Filters/Pack

33648 3M™ Dust Extractor Filter Bag, 5 Filter Bags/Pack

### Back-Up Pads and Accessories

30160 3M™ Hookit™ Low Profile Disc Back-up Pad, 6 in, 53 Holes, Red Foam, 10/Case

30062 3M™ Hookit™ Clean Sanding Multi-Connection Disc Pad, 6 in (150 mm), 53 Holes, 5/Case

20350 3M Xtract™ Low Profile Back-up Pad, 3 in, 10/Case

30063 3M™ Hookit™ Clean Sanding Abrasive Sheet Back-up Pad, 2-3/4 in x 7-3/4 in, 10/Case

05771 3M™ Hookit™ Soft Interface Pad, 3 in, 10/Case

05777 3M™ Hookit™ Soft Interface Pad, 6 × 1/2 × 3/4 in, 10/Case

33652 3M™ Dust Extractor Y-Connector

33771 3M™ Dust Extractor Straight Adaptor, 38 mm, 4/Case

33772 3M™ Dust Extractor Adaptor, 29 mm, 4/Case

33770 3M™ Random Orbital Sander Adaptor for Hose Assembly, 57 mm, 4/Case



Automotive Aftermarket Division  
3M Center  
Building 223-06S-07  
St. Paul, MN 55144-1000

For more information, visit us at  
[3M.com/cleansandingsystem](http://3M.com/cleansandingsystem)

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability. For industrial/occupational use only. Not for consumer sale or use.

3M, Cubitron, Hookit and Stikit are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle. © 3M 2026. All rights reserved. 60-4402-8103-5