

Introducing the

3M™ Hookit™ Flexible Foam Abrasives



Take it to the edge. Versatility at its finest.

**Highly flexible foam backed abrasive
which conforms to irregular surfaces**

Reduce the risk of burn through when sanding near edges,
bodylines or thinly coated surfaces. Available in discs and sheets.


3M™ Hookit™ Flexible Foam Abrasives are ideal for:

- Primer finishing: P400, P600
- Blend preparation: P800, P1000
- Clear coat rectification: P1200, P1500, P2000

3M™ Hookit™ Flexible Foam Abrasive Discs



Achieve a more uniform matte finish faster while feeling comfortable working closer to edges and bodylines with random orbital sanders.



3M™ Hookit™ Flexible Foam Abrasive Discs combine flexible aluminum oxide abrasives with a soft foam backing to create a high performing, versatile blending abrasive for dry or wet sanding use by machine or hand.

	6 inches 20 Discs/Carton 4 Cartons/Case	5 inches 20 Discs/Carton 4 Cartons/Case	3 inches 20 Discs/Carton 4 Cartons/Case
Grade	3M Part No.	3M Part No.	3M Part No.
P400	33538	33555	33557
P600	33539	33556	33558
P800	33540	33545	33550
P1000	33541	33546	33551
P1200	33542	33547	33552
P1500	33543	33548	33553
P2000	33544	33549	33554

3M™ Hookit™ Flexible Foam Abrasive Sheets



The soft foam construction conforms to irregular surfaces, ensuring a uniform and consistent finish, especially around panel edges and corners.

The perforated double sheet can be folded in half to enhance grip and control of the abrasive.



These innovative sanding sheets are designed for use by hand or with a sheet sander, offering versatility for blending, primer finishing, and scuffing applications.



Confidently sand body lines while evenly applying pressure across the pad, helping ensure less chances of scratch unevenness from finger pressure.


5.5 in x 6.8 in 10 Sheets/Carton 6 Cartons/Case	
Grade	3M Part No.
P400	33531
P600	33532
P800	33533
P1000	33534
P1200	33535
P1500	33536
P2000	33537

Reasons to Choose 3M™ Hookit™ Flexible Foam Abrasives

Reduce the risk of burn through on edges, bodylines and thinly coated surfaces to help minimize rework.

Flexible and long lasting, delivering an excellent finish.

Product has a great initial and sustained cut for use on clear coats, paint, primer and plastics.



Recommended Grades for Use

Grade	Applications
P400	Final DA primer refinement before paint application, plastic bumper cover sanding, prep for base coat and clear coat application
P600	Final primer sanding for critical colors and refining previous sanding scratches
P800	Blend sanding and final primer sanding for critical colors
P1000	Blend sanding while retaining clear coat texture (uniform matte finish)
P1200	Preparation for clear coat
P1500	Defect removal - clear coat rectification
P2000	Minor defect removal - clear coat rectification

Warranty and Limited Remedy: 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES OR CONDITIONS, INCLUDING ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal or equitable theory asserted. For industrial/occupational use only. Not for consumer sale or use.



3M Automotive Aftermarket Division
3M Center, Bldg 223-04-S-04
St. Paul, MN 55144-1000 USA

Hookit and 3M are trademarks of 3M Company.
© 3M 2025. 60-4405-0295-7. All rights reserved.