

**3M** Science.  
Applied to Life.™

Introducing 3M™ Hookit™ Flexible Foam Abrasives in sheets —

# Versatility at its finest.

**Highly flexible foam backed abrasive  
which conforms to irregular surfaces**

- Available in sheets and discs
- Excellent dust and water control to help ensure a clean sanding environment
- Delivers a uniform, consistent finish with excellent cut

# 3M™ Hookit™ Flexible Foam Abrasive Sheets



The soft foam construction conforms to irregular surfaces, ensuring a uniform and consistent finish, especially around panel edges and corners.

# 3M™ Hookit™ Flexible Foam Abrasive Discs



Flexible and durable, provides sustained cutting performance and an excellent finish, whether used wet or dry.


These innovative sanding sheets are designed for use by hand or with a sheet sander, offering versatility for blending, primer finishing, and scuffing applications.

The perforated double sheet can be folded in half to enhance grip and control of the abrasive.



Grade	3M Part No.
P400	33531
P600	33532
P800	33533
P1000	33534
P1200	33535
P1500	33536
P2000	33537

139 mm x 172 mm  
10 Sheets/Case  
6 Cases/Case



3M™ Hookit™ Flexible Foam Abrasive Discs combine flexible aluminum oxide abrasives with a soft foam backing to create a high performing, versatile blending abrasive for wet or dry use by hand or machine.


Grade	3M Part No.		
	75 mm 20 Discs/Case 4 Cases/Case	125 mm 20 Discs/Case 4 Cases/Case	150 mm 20 Discs/Case 4 Cases/Case
P400			33538
P600			33539
P800	33550	33545	33540
P1000	33551	33546	33541
P1200	33552	33547	33542
P1500	33553	33548	33543
P2000	33554	33549	33544

# Top Reasons to Choose 3M™ Flexible Foam Abrasives

▼  
Hundreds of laser perforated holes mean excellent dust and water control when used wet or dry creating a clean sanding environment.

▼  
Flexible and long lasting, delivering an excellent finish.

▼  
Product has a very good initial and sustained cut for use on clear coats, paint, primer and plastics.



## Recommended Grades for Use

Grade	Applications
P400	Final DA primer refinement before 2K paint application - Plastic bumper sanding - Stone chip sanding - prep for base coat and clear coat application
P600	Final primer sanding for critical colors and refining previous sanding marks. (water-based base coat)
P800	Final primer sanding for critical colours and blending
P1000	Blending/Matting (while retaining paint structure/texture)
P1200	Preparation for clear coat
P1500	Defect removal - Paint Rectification
P2000	Minor defect removal - Paint Rectification

Sign up for the latest  
Collision Repair news



3M Automotive Aftermarket Division India  
48-51 Electronic City, Hosur Road,  
Bengaluru, Karnataka -560100

For additional information, including important safety and warranty information regarding 3M Automotive Aftermarket products, visit:

[www.3mindia.in/3M/en\\_IN/collision-repair-in/](http://www.3mindia.in/3M/en_IN/collision-repair-in/)

Hookit and 3M are trademarks of 3M Company. © 3M 2025. All rights reserved.