



Total Solutions for Marine Repairs

Trusted Products for the Marine Industry

3M Marine solutions for repair, maintenance and boatbuilding.

Marine Sanding & Surface Prep	4
Marine Fillers	23
Marine Sealing	24
Marine Surface Protection & Masking	28
Marine Paint & Gelcoat Application	32
Marine Surface Finishing	40
Tools & Accessories	48
Personal Safety Equipment	58






For all your needs from stem to stern.

At 3M, our solutions in boatbuilding, watercraft repair and boat maintenance are about as broad as you might expect from a company with 50-plus years of expertise in the marine industry. In fact, we have products to keep any area of your boat looking and performing its best. Explore each one.

Marine Sanding & Surface Prep

For all your surface conditioning and multistep finishing needs, 3M offers a complete portfolio of marine abrasives for every kind of substrate. Designed for quick and easy results, our products are optimized for deburring edges and hard-to-reach places, as well as removing oxidation and grinding large areas. Renowned for their durability, efficiency and ease of use, they offer many unique capabilities that ensure a smooth finish.

Selection Guide	5
Surface Preparation	6
Metal and Fiberglass Grinding	19
Top Coat Sanding	21
Marine Fillers	23



Get underway with the right abrasive sequence.

Premium

3M™ Cubitron™ II and Purple Abrasives

Repair work and intermediate sanding



3M™ Cubitron™ II Abrasive Discs 737U


- Starting point for all applications
- Precision-shaped ceramic grain
- C-weight paper
- 40+ to 1000+ grades

Fine sanding



3M™ Film Disc 260L

- For finishing applications
- Aluminum oxide
- 3 mil film
- P600 to P2000 grades



3M™ Flexible Foam Abrasive Discs and Sheets

- Featuring flexible aluminum oxide abrasives and a soft foam backing
- Sanding discs and sheets for versatile blending
- Suitable for wet or dry use by hand or machine.
- 400 to 2000 grades

Coarse grade sanding



3M™ Blue Abrasive Discs 521U

- Extremely durable for sanding paint, metal, or fiberglass
- Ceramic aluminum oxide blend
- E-weight paper
- 36, 40, 80 grades

*Available in 3M™ Hookit™ and Stikit™ Attachment Systems

*6 inch and 8 inch disc sizes

Advanced

3M™ Blue Abrasives


Repair work and intermediate sanding



3M™ Blue Abrasive Disc 321U

- Starting point for paper
- Engineered ceramic mineral blend
- Available in 3M™ Hookit™ and Stikit™ Attachment Systems
- C-weight paper
- 40+ to 800+ grades

OR




3M™ Hookit™ Blue Net Abrasive Disc

- Designed with a balanced ceramic and aluminium oxide mineral blend
- Net backing for optimum dust extraction
- 80 to 400 grades

Standard

3M™ Gold Abrasives

Repair work and intermediate sanding



3M™ Gold Abrasive Discs 288U


- General purpose; all applications
- Aluminium oxide mineral blend
- Available in 3M™ Hookit™ and Stikit™ Attachment Systems
- D-weight paper: 40 and 80
- C-weight paper: 120+
- 40 to 800 Grades



CUBITRON™ II
Abrasive Discs

All 3M™ Cubitron™ II Abrasives feature our 3M Precision-Shaped Grain (PSG). 3M™ Cubitron™ II Abrasives feature at least 30% faster cut and at least 30% longer life than other traditional ceramic abrasives.




Faster cut. Longer life. Consistent finish.




3M PSG


Conventional Grain

Surface Preparation



Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Premium							
  3M™ Cubitron™ II Hookit™ Clean Sanding Disc 737U 	00051131313613	31361	80+	3 in	50 Discs/Case, 4 Cases/Case	3M™ Cubitron™ II Hookit™ Clean Sanding Abrasive Discs 737U are the premium solution for demanding surface preparation and finishing applications.	
	00051131313620	31362	120+				
	00051131313637	31363	150+				
	00051131313644	31364	180+				
	00051131314610	31461	220+				
	00051131314627	31462	240+				
	00051131314634	31463	320+				
	00051131314641	31464	400+				
	00068060061041	31465	500+				
	00068060061034	31466	600+				
	00068060061010	31467	800+				
	00068060060952	31468	1000+				
	00051131313705	31370	40+	6 in	25 Discs/Box, 4 Boxes/Case	3M™ Cubitron™ II Abrasives feature at least 30% faster cut and at least 30% longer life than other traditional ceramic abrasives. Featuring advanced 3M triangular shaped grain and a multi-hole pattern for effective dust extraction, these discs are designed for long life, fast cut, and consistent performance. Available in a wide range of grades, 40+ to 1000+, they support applications from aggressive material removal to fine sanding and blending, while the 3M™ Hookit™ attachment system enables quick disc change-outs.	
	00051131313712	31371	80+				
	00051131313729	31372	120+				
	00051131313736	31373	150+				
	00051131313743	31374	180+				
	00051131314818	31481	220+				
	00051131314825	31482	240+				
	00051131314832	31483	320+				
	00051131314641	31484	400+				
	00068060061072	31485	500+				
	00068060061065	31486	600+				
	00068060061058	31487	800+				
	00068060060969	31491	1000+				
	00051131313750	31375	40+	8 in	25 Discs/Box, 4 Boxes/Case		
	00051131313767	31376	80+				
	00051131313774	31377	180+				

See page 48 for Tools & Accessories.



Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Advanced							
 3M™ Hookit™ Blue Abrasive Disc 321U 	00051131361423	36142	80	3 in	50 Discs/Case, 4 Cartons/Case	3M™ Hookit™ Blue Abrasive Discs deliver best-in-class performance at a mid-tier price point for paint preparation and coatings removal. Featuring a ceramic and premium aluminum oxide mineral blend, they provide an effective balance of cut, life, and efficiency across a wide range of sanding applications, from aggressive paint removal and fresh filler sanding to blend preparation and primer sanding. The multi-hole pattern helps reduce loading, support dust extraction, and extend disc life, while the 3M™ Hookit™ attachment system allows quick disc changes.	
	00051131361447	36144	120				
	00051131361454	36145	150				
	00051131361461	36146	180				
	00051131361478	36147	220				
	00051131361485	36148	240				
	00051131361508	36150	320				
	00051131361515	36151	400				
	00051131361522	36152	500				
	00051131361539	36153	600				
	00051131361546	36154	800				
	00051131361706	36170	40	6 in			
	00051131361720	36172	80				
	00051131361744	36174	120				
	00051131361720	36175	150				
	00051131361768	36176	180				
	00051131361775	36177	220				
	00051131361782	36178	240				
	00051131361805	36180	320				
	00051131361812	36181	400				
	00051131361621	36183	600				
	00051131361638	36184	800				
 3M™ Stikit™ Blue Abrasive Disc Roll 321U	00051131362000	36200	40	6 in	25 Discs/Roll, 5 Rolls/Case	3M™ Hookit™ Blue Abrasive Discs deliver best-in-class performance at a mid-tier price point for paint preparation and coatings removal. Featuring a ceramic and premium aluminum oxide mineral blend, they provide an effective balance of cut, life, and efficiency across a wide range of sanding applications, from aggressive paint removal and fresh filler sanding to blend preparation and primer sanding. The multi-hole pattern helps reduce loading, support dust extraction, and extend disc life, while the 3M™ Hookit™ attachment system allows quick disc changes.	
	00051131362024	36202	80		50 Discs/Roll, 5 Rolls/Case		
	00051131362048	36204	120		100 Discs/Roll, 5 Rolls/Case		
	00051131362055	36205	150				
	00051131361829	36206	180				
	00051131362079	36207	220				
	00051131362086	36208	240				
	00051131362109	36210	320				
	00051131362116	36211	400				
	00051131362123	36212	500				
	00051131361911	36213	600				
	00051131361928	36214	800				

Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Advanced							
 3M™ Hookit™ Blue Net Abrasive Discs	00068060065469	36449	80	3 in	50 Discs/Case 4 Cartons/Case	3M™ Hookit™ Blue Net Abrasive Disc is a fast-cutting and long-lasting net abrasive disc with an increased edge retention strength and excellent wrinkling resistance. Its mineral abrasive blend is designed for improved durability and delivering a consistent, high quality finish. When used with dust extraction systems, 3M™ Hookit™ Blue Net Abrasive Disc delivers excellent dust removal, helping minimize dust on the work surface or in the environment.	
	00068060065445	36450	120				
	00068060065483	36451	150				
	00068060065506	36452	180				
	00068060065520	36453	220				
	00068060065544	36454	240				
	00068060065568	36455	320				
	00068060065582	36456	400				
	00068060065605	36435	80	5 in			
	00068060065629	36436	120				
	00068060065643	36437	150				
	00068060065667	36438	180				
	00068060065681	36439	220				
	00068060065704	36440	240				
	00068060065728	36441	320				
	00068060065742	36442	400				
	00068060065964	36420	80	6 in			
	00068060065926	36421	120				
	00068060065940	36422	150				
	00068060065988	36423	180				
	00068060066008	36424	220				
	00068060066022	36425	240				
	00068060066046	36426	320				
	00068060066060	36427	400				
	00068060066084	36411	80	8 in			
	00068060066107	36412	120				
	00068060066121	36413	150				
	00068060066145	36414	180				
	00068060066169	36415	220				
	00068060066183	36416	240				
	00068060066206	36417	320				
	00068060066220	36418	400				



See page 48 for Tools & Accessories.


Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Advanced							
 3M™ Hookit™ Blue Abrasive Disc 521U (Heavy E-weight Paper)	068060061591	36522	36E	6 in (no holes)	50 Discs/Box, 4 Boxes/Case	3M™ Hookit™ Blue Abrasive Disc 521U is a paper-backed abrasive disc with excellent performance and cut. It is available in a range of grades and sizes. Use the 3M™ Hookit™ Blue Abrasive Disc 521U for sanding on repair substrates like paint, primer, metal and composites. It is a fast-cutting paper-backed disc with durable E-weight paper backing for excellent cut and long lasting performance. The Hookit™ system features hook-and-loop attachment for easy, reusable application.	
	068060061614	36523	40E				
	068060061652	36524	80E				
	068060061539	36510	36E	6 in (with holes)			
	068060061553	36520	40E				
	068060061577	36521	80E				
	068060061676	36530	36E	8 in (no holes)			
	068060061638	36531	40E				
	068060061690	36532	80E				
 3M™ Stikit™ Blue Abrasive Disc 521U (Heavy E-weight Paper)	068060061751	36560	36E	6 in (no holes)	50 Discs/Box, 4 Boxes/Case	3M™ Stikit™ Blue Abrasive Disc 521U is a paper-backed abrasive disc with excellent performance and cut. It is available in a range of grades and sizes. Use the 3M™ Stikit™ Blue Abrasive Disc 521U for sanding on substrates like paint, primer, metal and composites. It is a fast-cutting paper-backed disc with durable E-weight paper backing for excellent cut and long lasting performance. The Stikit™ system features a pressure-sensitive adhesive coating for easy attachment and removal.	
	068060061775	36561	40E				
	068060061799	36580	36E	8 in (no holes)			
	068060061812	36581	40E				
	068060061836	36582	40E	8 in (with holes)			

See page 48 for Tools & Accessories.


Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Standard							
 3M™ Hookit™ Gold Abrasive Discs (Multi-Hole)	00068060063960	09280	40D	6 in	50 Discs/Case 4 Cartons/Case	3M™ Hookit™ Gold Abrasive Disc 288U is a paper-backed abrasive disc designed for use in repair. It is available in a range of sizes, grades, and hole patterns. Its durable construction and anti-loading coating help reduce loading for longer disc life and provide a smooth consistent finish.	
	00068060063205	09281	80D		100 Discs/Case 4 Cartons/Case		
	00068060063182	09282	120				
	00068060063168	09283	150				
	00068060063144	09284	180				
	00068060063120	09285	220				
	00068060063106	09286	240				
	00068060063083	09287	320				
	00068060063069	09288	400				
	00068060063045	09289	500				
	00068060063021	09290	600				
	00068060062949	09291	800				
	 3M™ Hookit™ Gold Abrasive Discs (No Hole)	00068060062147	09210				80D
00068060062161		09211	120				
00068060062185		09212	150				
00068060062208		09213	180				
00068060062222		09214	220				
00068060062246		09215	240				
00068060062260		09216	320				
00068060062284		09217	400				
00068060062307		09218	500				
00068060062321		09219	600				
00068060062345		09220	800				
00068060062604		09250	40D	6 in			
00068060062628		09251	80D				
00068060062642		09252	120				
00068060062666		09253	150				
00068060062680		09254	180				
00068060062703		09255	220				
00068060062727		09256	240				
00068060062741		09257	320				
00068060062765		09258	400				
00068060062789		09259	500				
00068060062802		09260	600				
00068060062826		09261	800				
00068060062840		09270	40D	8 in			
00068060062864		09271	80D				

See page 48 for Tools & Accessories.


Sanding Abrasives		UPC	Part #	Grade	Size	Qty/Case	Description
Standard							
 3M™ Stikit™ Gold Abrasive Discs Rolls 	00068060061959	09310	40D	6 in	100 Discs/Roll 6 Rolls/Case	3M™ Stikit™ Gold Abrasive Disc 288U is a paper-backed abrasive disc roll designed for use in repair. It is available in a range of sizes, grades, and hole patterns. A durable high-quality construction and anti-loading coating reduce loading for longer disc life and provide a smooth consistent finish.	
	00068060061966	09311	80D				
	00068060061973	09312	120				
	00068060061980	09313	150				
	00068060061997	09314	180				
	00068060062000	09315	220				
	00068060062017	09316	240				
	00068060062024	09317	320				
	00068060062031	09318	400				
	00068060062048	09319	500				
	00068060062055	09320	600	8 in			
	00068060062062	09321	800				
	00068060062079	09350	80D				
	00068060062086	09351	120				
	00068060062093	09352	150				
	00068060062109	09353	180				
	00068060062116	09354	220				
	00068060062123	09355	240				
	00068060067784	09359	320				
 3M™ Stikit™ Gold Abrasive Disc Rolls	00068060067791	61645	80D	6 in	100 Discs/Roll 6 Rolls/Case		
	00068060067722	61644	120				
	00068060067739	61643	150				
	00068060067746	61642	180				
	00068060067753	61641	220				
	00068060067760	61640	320				
	00068060067777	61639	500				
 3M™ Stikit™ Gold Abrasive Discs	00068060062925	09356	40D	8 in	100 Discs/Case 4 Cartons/Case		
	00068060062888	09357	80D				
 3M™ Stikit™ Gold Abrasive Discs (8-Hole)	00068060062901	09358	80D				


Fine Abrasive Discs	UPC	Part #	Grade	Size	Qty/Case	Description
 3M™ Hookit™ Flexible Foam Abrasive Discs 	068060067623	33557	P400	3 in	20 Sheets/Box, 4 Boxes/Case	3M™ Hookit™ Flexible Foam Abrasive Discs are sanding discs for versatile blending, featuring flexible aluminum oxide abrasives and a soft foam backing. The soft foam construction conforms to irregular surfaces which helps deliver a uniform and consistent finish with excellent cut particularly around panel edges or corners, helping to reduce the risk of burn through. The discs feature laser-perforated holes that offer excellent dust control, helping maintain a cleaner working environment and provide a precise cut and finish.
	068060067616	33558	P600			
	068060067609	33550	P800			
	068060067593	33551	P1000			
	068060067586	33552	P1200			
	068060067579	33553	P1500			
	068060067562	33554	P2000			
	068060067487	33538	P400	6 in		
	068060067470	33539	P600			
	068060067463	33540	P800			
	068060067456	33541	P1000			
	068060067449	33542	P1200			
	068060067630	33543	P1500			
	068060067432	33544	P2000			
 3M™ Hookit™ Flexible Foam Abrasive Sheets	068060067364	33531	P400	5-1/2 in x 6-4/5 in	10 Sheets/Box, 6 Boxes/Case	3M™ Hookit™ Flexible Foam Abrasive Sheets are designed for versatile sanding applications by hand or with a sheet sander. They feature aluminum oxide abrasive and a soft foam construction that conforms to irregular surfaces to help deliver a uniform, consistent finish with excellent cut, especially around edges and corners, while helping reduce the risk of burn through. Well suited for blending, primer finishing, and scuffing, they support efficient sanding across a range of applications.
	068060067371	33532	P600			
	068060067388	33533	P800			
	068060067395	33534	P1000			
	068060067401	33535	P1200			
	068060067418	33536	P1500			
	068060067425	33537	P2000			

See page 48 for Tools & Accessories.

Fine Abrasive Discs		UPC	Part #	Grade	Size	Qty/Case	Description
 3M™ Hookit™ Flexible Abrasive Dust Free Disc 270J		00051131348004	34800	P400	6 in	25 Discs/Box, 5 Boxes/Case	Precision coated with high quality minerals and resins to deliver longer-lasting performance for primer sanding, blend preparation and paint finishing.
		00051131348011	34801	P600			
		00051131348028	34802	P800			
		00051131348035	34803	P1000			
		00051131348042	34804	P1200			
		00051131348059	34805	P1500			
 3M™ Hookit™ Flexible Abrasive Hand Sheet 270J		00051131343375	34337	P400	5-1/2 in x 6-4/5 in	25 Sheets/Box, 5 Boxes/Case	Features a very thin, extremely flexible film backing that conforms effortlessly to tools and contoured surfaces.
		00051131343399	34339	P600			
		00051131343405	34340	P800			
		00051131343412	34341	P1000			
		00051131343429	34342	P1200			
		00051131343436	34343	P1500			
 3M™ Hookit™ Purple Finishing Film Abrasive Disc 260L		00051131306714	30671	P600	6 in	50 Discs/Box, 4 Boxes/Case	Features an updated coating that levels surface defects on clear coat and greatly reduces pigtails. Aluminum oxide abrasive cuts fast, lasts a long time, resists loading with or without hole pattern designs and leaves a consistent, easy-to-polish finish. Our 3M™ Hookit™ attachment system makes disc change-outs fast and easy.
		00051131306707	30670	P800			
		00051131306691	30669	P1000			
		00051131306684	30668	P1200			
		00051131306677	30667	P1500			
		00051131306660	30666	P2000			
 3M™ Stikit™ Film Disc 260L		00051131013216	01321	P600	6 in	100 Discs/Box, 4 Boxes/Case	Ideal for blending, scuffing, paint prep and removing paint defects.
		00051131013209	01320	P800			
		00051131013193	01319	P1000			
		00051131013186	01318	P1200			

See page 48 for Tools & Accessories.

Fine Abrasive Discs		UPC	Part #	Grade	Size	Qty/Case	Description
	3M™ Hookit™ Purple Finishing Film Disc 260L — Dust Free	00051131307711	30771	P600	6 in	50 Discs/Box, 4 Boxes/Case	Features 5- or 6-hole design to help keep dust away from the disc surface.
		00051131307704	30770	P800			
		00051131307698	30769	P1000			
		00051131307681	30768	P1200			
		00051131307674	30767	P1500			
		00051131307667	30766	P2000			
	3M™ Trizact™ Hookit™ Clear Coat Sanding Disc	00051131020887	02088	P1500	6 in	25 Discs/Box, 4 Boxes/Case	Ideal for spot repairs, including leveling dust nibs and orange peel, before sand scratch removal.
	3M™ Trizact™ Hookit™ Blending Abrasive Disc	00051131020900	02090	P1000	6 in	15 Discs/Box, 4 Boxes/Case	Foam abrasive discs for scuff sanding, blending and removing fine grade sand scratches prior to compounding.
	3M™ Trizact™ Hookit™ Foam Abrasive Disc	00051131020856	02085	P3000	6 in	15 Discs/Box, 4 Boxes/Case	
		00051131306622	30662	P5000			
		00051131308060	30806	P8000			
Marine Fairing		UPC	Part #	Grade	Size	Qty/Case	Description
Premium							
	3M™ Cubitron™ II Hookit™ Clean Sanding Sheet Roll 737U	00051131344402	34440	40+	2-3/4 in x 8-3/4 yd	5 Rolls/Case	3M™ Cubitron™ II Hookit™ Clean Sanding Abrasive Sheet Roll 737U are the premium solution for demanding surface preparation and finishing applications.
		00051131344426	34442	80+	2-3/4 in x 13 yd.		
		00051131344440	34444	120+			
		00051131344457	34445	150+			
		00051131344464	34446	180+			
		00051131344471	34447	220+			
		00051131344488	34448	240+			
		00051131344495	34449	320+			
		00051131344501	34450	400+			
		00068060061157	34451	500+	4-1/2 in x 8-3/4 yd.		
		00068060061140	34452	600+			
		00068060061133	34453	800+			
		00068060061126	34454	1000+			
		00051131344600	34460	40+		3 Rolls/Case	
		00051131344624	34462	80+			
		00051131344648	34464	120+			
		00051131344655	34465	150+			
		00051131344662	34466	180+			
		00051131344679	34467	220+			
		00051131344686	34468	240+			
		00051131344693	34469	320+	5 Rolls/Case		
		00051131344709	34470	400+			
		00068060061119	34471	500+			
		00068060061102	34472	600+			
		00068060061096	34473	800+			
		00068060061089	34474	1000+			



Marine Fairing	UPC	Part #	Grade	Size	Qty/Case	Description
Advanced						
 3M™ Hookit™ Blue Abrasive Sheet Roll 321U	00051131361874	36187	80	2-3/4 in x 13 yd.	4 Rolls/Case	Engineered for best-in-class performance at every stage of paint prep and body repair. Multi-hole pattern delivers excellent dust extraction and reduces loading.
	00051131361898	36189	120			
	00051131361904	36190	150			
	00051131361935	36191	180			
	00051131361928	36192	220			
	00051131361935	36193	240			
	00051131361720	36195	320			
	00051131361744	36196	400			
	00051131361751	36197	500			
	00051131361768	36198	600			
 3M™ Stikit™ Blue Abrasive Sheet Roll 321U	00051131362154	36215	40	2-3/4 in x 10 yd.	5 Rolls/Case	Engineered for best-in-class performance at every stage of paint prep and body repair. Multi-hole pattern delivers excellent dust extraction and reduces loading.
	00051131362178	36217	80	2-3/4 in x 20 yd.		
	00051131362192	36219	120	2-3/4 in x 30 yd.		
	00051131362208	36220	150			
	00051131362215	36221	180			
	00051131362222	36222	220			
	00051131362239	36223	240			
	00051131361461	36225	320	2-3/4 in x 45 yd.		
	00051131361454	36226	400			
	00051131361447	36227	500			
	00051131361423	36228	600			
 3M™ Hookit™ Blue Net Abrasive Sheet Roll 	00068060065797	36466	220	2-3/4 in x 10-9/10 yd	5 Rolls/Case	3M™ Hookit™ Blue Net Abrasive Sheet Roll is a fast-cutting and long-lasting net abrasive sheet roll with an increased edge retention strength and excellent wrinkling resistance. Its mineral abrasive blend is designed for improved durability and delivering a consistent, high quality finish. When used with dust extraction systems, 3M™ Hookit™ Blue Net Abrasive Sheet Roll delivers excellent dust removal, helping minimize dust on the work surface or in the environment.
	00068060065803	36467	240			
	00068060065810	36468	320			
	00068060065827	36469	400			
	00068060065872	36474	220	4-1/2 in x 10-9/10 yd	3 Rolls/Case	
	00068060065889	36475	240			
	00068060065896	36476	320			
	00068060065902	36477	400			

See page 48 for Tools & Accessories.

Marine Fairing		UPC	Part #	Grade	Size	Qty/Case	Description
Standard							
 3M™ Stikit™ Blue Abrasive Sheet 521U (Heavy E-weight Paper)	068060066428	37450	36E	2-3/4 in x 26-1/4 ft	5 Rolls/Case	E-Weight, paper-backed abrasive sheet roll with excellent performance and cut. It is available in a range of grades.	
	068060066435	37451	40E				
	068060066473	37452	80E				
	068060066442	37453	36E	4-1/2 in x 26-1/4 ft	3 Rolls/Case		
	068060066459	37454	40E				
	068060066466	37455	80E				
 3M™ Stikit™ Blue Abrasive Sheet 521U (Heavy E-weight Paper)	068060063922	37220	36E	2-3/4 in x 16-1/2 in	25 Sheets/Box, 5 Boxes/Case		
	068060063946	37211	40E				
 3M™ Hookit™ Gold Abrasive Sheet Rolls (Dust-Free)	00068060070715	32777	40D	2-3/4 in x 8-7/10 yd	5 Rolls/Case	Use the 3M™ Hookit™ Gold Abrasive Sheet Roll 288U for sanding repair substrates like paint, primer, metal and composites. It is a paper-backed sheet roll with high-quality minerals for a long lasting cut and has a load-resistance coating to help reduce clogging and extend abrasive life. The Hookit™ system features hook-and-loop attachment for easy, reusable application, fitting standard hand blocks and orbital sanders. With 3M™ Gold Abrasive Sheet Roll 288U, you can achieve a uniform consistent finish, making it a valuable addition to any repair toolkit.	
	00068060070692	32778	80D	2-3/4 in x 13-1/10 yd			
	00068060070746	32779	120				
	00068060070760	32780	150				
	00068060070784	32781	180				
	00068060070807	32782	220				
	00068060070814	32783	240				
	00068060070838	32784	320				
 3M™ Hookit™ Gold Abrasive Sheet Rolls	00068060066336	02767	40D	2-3/4 in x 8-7/10 yd	5 Rolls/Case		
	00068060066275	02768	80D	2-3/4 in x 13-1/10 yd			
	00068060066480	02769	120				
	00068060066282	02770	150				
	00068060066305	02771	180				
	00068060066299	02772	220				
	00068060066312	02773	240				
	00068060066329	02774	320				

See page 48 for Tools & Accessories.

Marine Fairing		UPC	Part #	Grade	Size	Qty/Case	Description
Standard							
 3M™ Stikit™ Gold Abrasive Sheet Rolls 	00068060063502	02780	40D	2-3/4 in x 25 yd	10 Rolls/Case	Use the 3M™ Stikit™ Gold Abrasive Sheet Roll 288U for sanding on repair substrates like paint, primer, metal and composites. It is a paper-backed sheet with high-quality minerals for a long lasting cut and has a load-resistance coating to help reduce clogging and extend the abrasive life. The Stikit™ system features a pressure-sensitive adhesive coating for easy attachment. It can be used on power or hand sanding equipment & can be cut to fit standard hand blocks and orbital sanders. With 3M™ Stikit™ Gold Abrasive Sheet Roll 288U, you can achieve a uniform consistent finish, making it a valuable addition to any repair toolkit.	
	00068060063519	02781	80D				
	00068060063649	02782	120	2-3/4 in x 30 yd			
	00068060063526	02783	150	2-3/4 in x 45 yd			
	00068060063540	02784	180				
	00068060063533	02785	220				
	00068060063557	02786	240				
	00068060063564	02787	320				
	00068060063571	02788	400				
	00068060063588	02789	500				
	00068060063595	02775	80D	4-1/2 in x 25 yd	6 Rolls/Case		
	00068060063601	02776	120	4-1/2 in x 30 yd			
	00068060063618	02777	150	4-1/2 in x 45 yd			
	00068060063625	02778	180				
	00068060064677	02790	220				
	00068060064660	02791	320				
	00068060063632	02779	400				
	 3M™ Stikit™ Gold Abrasive Sheets	00068060063885	02799	40D	2-3/4 in x 16-1/2 in		25 Sheets/ Carton 5 Cartons/Case
00068060063908		02798	80D				
 3M™ Gold Abrasive Sheets	00068060064691	12552	40D	9 in x 11 in	50 Sheets/Pack 5 Packs/Case	3M™ Gold Abrasive Sheet 288U is a durable abrasive sheet with long lasting, consistent sanding performance. The sheet is suitable for a wide variety of applications in the repair process. Its durable construction and anti-loading coating help reduce loading for longer sheet life and provide a smooth consistent finish.	
	00068060064752	12549	80D				
	00068060064776	12547	120				
	00068060064714	12546	150				
	00068060064790	12545	180				
	00068060064813	12544	220				
	00068060064837	12543	240				
	00068060064851	12541	320				
	00068060064875	12539	400				
	00068060064899	12538	500				
	00068060064905	12537	600				
	00068060064936	12536	800				


Paint Preparation		UPC	Part #	Color	Grade	Size	Qty/Case	Description
 3M™ Two-Sided Sanding Sponges		00068060070340	23808	Red	Medium 120-180	4-4/5 in x 3-4/5 in	20 Sponges/ Carton 9 Cartons/ Case	Use 3M™ Two-Sided Sanding Sponge for wet or dry sanding on a variety of surface materials. The low-density, soft foam construction provides flexibility for hand sanding on shapes and contours. The two-sided abrasive feature of the sponge allows for extended use, effectively doubling the product's life compared to a single-sided abrasive. The color-coded grade range simplifies the process of selecting the right sponge for each task, helping to enhance workflow efficiency. This product is engineered to meet the rigorous demands of professionals in the marine industries.
		00068060070364	23809	Orange	Fine 320-400			
		00068060070548	23810	Green	Superfine 500-600			
		00068060070388	23811	Blue	Ultrafine 600-800			
		00068060070401	23812	Gray	Microfine 1000-1200			
		00068060070425	23813	Assorted, 4x Each	Multi-Pack, Assorted			
		00068060070432	23814	Red	Medium 120-180		100 Sponges/ Case	
		00068060070456	23815	Orange	Fine 320-400			
		00068060070470	23816	Green	Superfine 500-600			
		00068060070494	23817	Blue	Ultrafine 600-800			
		00068060070517	23818	Gray	Microfine 1000-1200			
 Softback Sanding Sponges		00051131026001	02600	N/A	Microfine	4-1/2 in x 5-1/2 in	20 Sponges/ Carton 6 Cartons/ Case	Foam backing adapts to unique contours and helps you access hard-to-reach areas. Aluminum oxide abrasive offers a long life and fast cut. Versatile hand sanding sponges work on many surface materials. Waterproof bonding system allows for either wet or dry sanding applications.
		00051131026018	02601	N/A	Ultrafine			
		00051131026025	02602	N/A	Superfine			
		00051131026049	02604	N/A	Fine			
		00051131026063	02606	N/A	Medium			
 Scotch-Brite™ 7447 Pro Hand Pad		00048011649269	64926	Maroon	A VFN	6 in x 9 in	60/Case	Breakthrough nonwoven web technology allows for a faster cut and produces a more consistent scratch — reducing the time it takes to scuff, prep or finish parts. Ideal for prepping surfaces for paint and primer, general scuffing and t
	Scotch-Brite™ 7448 Pro Hand Pad		00048011649351	64935	Gray	S ULF	6 in x 9 in	


Metal and Fiberglass Grinding

Prop Repair and Metal Fabrication			UPC	Part #	Grade	Size	Max RPM	Qty/Case	Description
 3M™ Cubitron™ 3 Cut-Off Wheels CAUTION: Do not use without guards	04064035174231	33457	3 in x 1/16 in x 3/8 in			25,465	5 Each/Pack, 6 Packs/Case	3M™ Cubitron™ 3 Cut-Off Wheels with their fast cutting and long-lasting performance improve productivity and efficiency in various cutting processes. These Cut-Off Wheels are built with the 3M™ Cubitron™ 3 Precision Shaped Grains – designed with sharp, angular structures that continuously fracture to form fresh, sharp points that allow the discs to slice faster, and last longer. They will cut through most materials, including high strength steels, stainless and mild steel. 40% more life than the previous generation of Cubitron™ II Cut-Off Wheels. Remove up to 40% more material than Cubitron™ II Cut-Off Wheels.	
	04064035174262	33458	3 in x 1/25 in x 3/8 in						
	04064035174316	33459	4 in x 1/25 in x 3/8 in			19,100			
	04064035174156	33463	4-1/2in x 1/25 in x 7/8 in			13,300			
 3M™ Cubitron™ 3 File Belt	00068060066886	33479	40+	3/8 in x 13 in	N/A	10 Belts/ Carton 5 Cartons/ Case	Use 3M™ Cubitron™ 3 Abrasive File Belt for enhanced productivity and efficiency in your workshop. This upgraded file belt features re-engineered precision-shaped ceramic grains with a proprietary breakthrough in grain shape, including curved sides, offering faster cutting and longer-lasting performance compared to predecessors		
	00068060066947	33480	60+						
	00068060067005	33481	80+						
	00068060066862	33469	40+	1/2 in x 18 in			Ideal for tough detail work such as cleaning, deburring, blending, and finishing, it excels in small, confined spaces. Its extended life and reduced need for changeouts help decrease waste and lower overall grinding costs, contributing to maximizing productivity in the workshop.		
	00068060066923	33473	60+						
	00068060066985	33478	80+						
	 Scotch-Brite™ Durable Flex Low Stretch Belt	00048011644752	64475					A CRS	1/2 in x 18 in
00048011644585		64458	A MED						

Prop Repair and Metal Fabrication		UPC	Part #	Grade	Size	Max RPM	Qty/Case	Description
 Scotch-Brite™ Durable Flex Low Stretch Belt	00048011644752	64475	A CRS	1/2 in x 18 in	N/A	20/Case		Engineered to perform tough detail work such as deburring, blending and finishing on a variety of metals. Conformable, nonwoven abrasives refine and prep metal surfaces without significantly altering the metal underneath.
	00048011644585	64458	A MED					
 Scotch-Brite™ Clean and Strip XT Pro Extra Cut Disc	00638060210321	10321	XC-DC	4-1/2 in x 7/8 in	13,300	10/Case		QUICK REMOVAL: Efficiently removes heavy rust, thick paint, corrosion and cleans welds while providing fast and effective removal. AGGRESSIVE MINERAL PERFORMANCE: Aluminum oxide mineral aggressively removes top layer and refines to the bare metal underneath. HIGH CONFORMABILITY: Provides a larger contact patch, enabling faster removal rates.
 Scotch-Brite™ Clean and Strip XT Pro Disc	00638060055861	55861	XO-DC	4-1/2 in x 7/8 in	18,000	60/Case		RECOMMENDED APPLICATIONS: Cleaning, finishing, surface preparation, rust removal, light scale removal and coating removal WORKS EFFICIENTLY AND FAST: Quickly removes rust, paint, light mill scale and coatings from metal RE-ENGINEERED FIBER: High strength fiber resists chunking and performs well on edges
 Scotch-Brite™ Roloc™ Clean and Strip XT Pro Disc	00638060215388	21538	S XCS	2 in	18,000	60/Case	40/Case	Designed with conformable, high-strength fibers that deliver quick and consistent performance that quickly removes rust, paint, adhesives and other coatings. Rated for high speeds, both discs spin easily onto your angle grinder with a quick-change threaded hub — no accessories needed.
	00638060215401	21540	S XCS	3 in	15,000	10/Case		
	00638060215418	21541	S XCS	3 in	15,000			
	00638060215425	21542	S XCS	4 in	11,000			
 Scotch-Brite™ Roloc™ Clean and Strip XT Pro Extra Cut Disc	00638060215432	21543	A XCS	2 in	18,000	60/Case	40/Case	
	00638060215449	21544	A XCS	3 in	15,000	10/Case		
	00638060215456	21545	A XCS	3 in	15,000			
	00638060215463	21546	A XCS	4 in	11,000			

Blister Repair		UPC	Part #	Grade	Size	Max RPM	Qty/Case	Description
 3M™ Cubitron™ 3 File Belt	00068060066862	33469	40+	1/2 in x 18 in	10 Belts/ Carton 5 Cartons/ Case	10 Belts/Box, 5 Boxes/Case		Designed for tasks like grinding out rivets and removing spot welds. Its fast cutting action helps eliminate burning or other forms of thermal damage.
	00068060066923	33473	60+					
	00068060066985	33478	80+					

Blister Repair		UPC	Part #	Grade	Size	Max RPM	Qty/Case	Description
 3M™ Cubitron™ 3 Fibre Roloc™ Disc	00068060067906	33489	36+	2 in	20,000	15 Discs/Box, 6 Boxes/Case	Use 3M™ Cubitron™ 3 Roloc™ Abrasive Fibre Disc for grinding, weld blending, deburring, and other demanding metal finishing jobs. This upgraded disc features re-engineered precision-shaped ceramic grains with a proprietary breakthrough in grain shape, including curved sides, which result in less heat development when cutting*, increases material removal rates*, and reduces the need for frequent change-outs. The 3M™ Roloc™ Attachment System allows for quick change outs of discs, making it ideal for applications requiring frequent grade or disc size changes. The 3M™ Cubitron™ 3 Roloc™ Abrasive Fibre Disc is engineered to last longer than its predecessors*.	
	00068060067944	33490	60+					
	00068060067982	33491	80+					
	00068060067920	33493	36+	3 in	15,000			
	00068060067968	33494	60+					
	00068060068002	33495	80+					
Large Area Grinding		UPC	Part #	Grade	Size/Dia.	Max RPM	Qty/Case	*Based upon 3M internal automated testing against Cubitron™ II in 2025
 3M™ Cubitron™ 3 Abrasive Fibre Disc	00068060066725	33499	36+	5 in x 7/8 in	12,000	5 Discs/ Carton 5 Cartons/ Case		
	00068060066763	33503	60+					
	00068060066800	33505	80+					
	00068060066749	33496	36+	7 in x 7/8 in	8,600			
	00068060066787	33497	60+					
	00068060066824	33498	80+					

Large Area Grinding		UPC	Part #	Grade	Size/Dia.	Max RPM	Qty/Case	Description
 3M™ Green Corps™ Roloc™ Discs		00051131365254	36525	40	2 in	20,000	25 Discs/Box, 10 Boxes/Case	Coarse grinding disc for removing paint, rust and welds. Small diameter for grinding in hard-to-reach areas. Quick twist-on, twist-off disc changes.
		00051131365261	36526	60				
		00051131365278	36527	80				
		00051131365346	36534	40	3 in	25,000		
		00051131365353	36535	60				
		00051131365360	36536	80				
 3M™ Green Corps™ File Belt		00051131365162	36516	40	1/2 in x 18 in	N/A	20 Belts/Box, 5 Boxes/Case	Removes spot weld and hem flanges and grinds in tight areas for fast and efficient removal of paint, corrosion and rust.
		00051131365179	36517	60				
		00051131365186	36518	80				
 3M™ Green Corps™ Fibre Discs		00051131365070	36507	40	5 in	12,000	20 Discs/Box, 5 Boxes/Case	Holds up to a heavy workload. Use for coating and paint removal, gasket removal, rust and weld removal, general metal work, and clear coat applications on metal, plastic or fiberglass.
		00051131365087	36508	60				
		00051131365094	36509	40	7 in	6,600		
		00051131365100	36510	60				
 3M™ Green Corps™ Cut-Off Wheels CAUTION: Do not use without guards		00051131019874	01987	3 in x 3/100 in x 3/8 in	25,465	5 Wheels/Box, 10 Boxes/Case	Ideal for cutting sheet metal, fiberglass, stainless steel, mild steel, frames, rails, bars, clamps and rusted bolts.	
		00051131019881	01988					
		00051131019911	01991		20,100			

CAUTION: Do not use without guards

See page 48 for Tools & Accessories.

Marine Fillers

Fillers and Accessories

Fine Abrasive Sheets		UPC	Part #	Size	Qty/Case	Description
	3M™ Marine High Strength Repair Filler	00051131460140	46014	1 Gallon	4/Case	Restores damaged areas of fiberglass hulls, decks and other areas on boats. A high performance product that is reinforced with short strands of fiberglass for added strength.
	3M™ Marine Premium Filler	00051131460065	46006	1 Gallon		Repairs defects in fiberglass, wood, aluminum and steel for applications both above and below the waterline. Our filler is a unique vinyl ester formula that offers resistance to water absorption.
	3M™ Spreader Assortment	00051131058446	05844	4 in, 5 in, 6 in Yellow Plastic	3/Pack, 24 Packs/Case	Designed for spreading body and fiberglass fillers, finishing putties and resins. Reusable tool is flexible and easy to grasp through protective gloves and its sharp edge makes for precise application.
	Dynatron™ Yellow Spreader	00076308003548	00354	5 in Yellow Plastic	150/Case	Specially designed for use in auto body shops, this durable spreader is easy to hold and even easier to use. Its flexibility combined with a lightly tapered edge makes it ideal for applying, spreading, shaping and smoothing a variety of mixed body fillers, glazes and putties for consistently excellent auto body work. Spreader is reusable and requires very little cleaning time.

See page 48 for Tools & Accessories.

Marine Sealing



Whether you're boatbuilding, maintaining a fleet or repairing a single watercraft, you expect your adhesive sealants to create watertight seals. But the right ones will do much more. They will resist weathering, shock, vibration, swelling and shrinkage over time. It also means they will earn your trust. We have spent more than 50 years developing marine sealant and adhesive solutions, and proving them in a vast variety of applications. Explore how we can help keep you afloat, today and for years to come.

Selection Guides	26
------------------	----

Marine Adhesive Sealants	27
--------------------------	----



Watertight. Tried and true.



Choose the best Marine Sealant for your project.

Selection Guides



Features	4000 UV	4200 FC	5200	5200 FC	Marine Grade Silicone
Sealing	Yes	Yes	Yes	Yes	Yes
Bonding	Excellent	Good	Excellent	Excellent	Poor
Strength	Medium	Medium	High	High	Low
Chemical base	SMP	Polyurethane	Polyurethane	Polyurethane	Silicone
Curing time	24 hrs	24 hrs	5 – 7 days	24 hrs	24 hrs
Tack free time (70°F/21°C @ 50% RH)	30 min	2 hrs	24 – 48 hrs	1 hr	10 min
Cure rate (mm per 24 hrs)	>3.5	>3	<1	3	3

+ Good ++ Better +++ Best

Applications	4000 UV*	4200 FC	5200	5200 FC	Marine Grade Silicone
Deck to hull bonding	++	+	+++	+++	
General purpose sealing and bonding	+++	++	+++	+++	
Bedding	+++	++	+	+	
Keel sealing 5200 is not recommended for bonding bare aluminum where the bondline is continuously exposed to water.	+	+	+++	+++	
General interior sealing	++	++			+++
Bonding wood to deck or superstructure	+	++	+++	+++	
Plastic acrylic window sealing	+++				
Interior wood deck caulking Not recommended for teak deck caulking.	++	++	+++	+++	
Bonding anti-slip plates in engine rooms	+	++	+++	+++	
Sealing exterior strong UV radiation zones	+++	+	+	+	
Bonding decorative panels (vertical); work surfaces (horizontal); deck hardware (deck/fittings); wood to wood	++	++	+++	+++	
Bonding thru hull; hatches and port lights; fiberglass to fiberglass	+++	++	+++	+++	

*3M™ Marine Adhesive Sealant Fast Cure 4000 UV black is recommended for applications that will be continuously exposed to UV radiation.

Marine Adhesive Sealants

Sealants		UPC	Part #	Color	Size	Qty/Box	Description
 3M™ Marine Adhesive Sealant 5200	00051135052068	05206	White	1 oz. Tube	12/Box	An exceptionally strong, high performance polyurethane. Maintains its flexibility, absorbing shocks, vibrations, swelling, shrinking and structural movements. Tack-free in 24–48 hours; cures in 5–7 days without shrinking. Ideal for large surface-area applications requiring long open times.	
	00051135052037	05203	White	3 oz. Tube	6/Box		
	00051135052051	05205	Black				
	00051135065006	06500	White	10 oz. Cartridge	12/Box		
	50051135065049	06504	Black				
	00051135065013	06501	Tan				
	00051135065020	06502	Mahogany				
 3M™ Marine Adhesive Sealant Fast Cure 5200 FC	00051135065358	06535	White	1 oz. Tube	12/Box	Fast-cure version of 5200. Tack-free in 1 hour; completely cures within 24 hours. Ideal for applications requiring a fast, long-term seal: hull-to-deck seams, wood to fiberglass, marine hardware, hull and stern joints.	
	00051135052204	05220		3 oz. Tube	6/Box		
	00051135065204	06520		10 oz. Cartridge	12/Box		
 3M™ Marine Adhesive Sealant Fast Cure 4200 FC	00051135052600	05260	White	3 oz. Tube	6/Box	A one-component, medium-strength, moisture-curing, gap-filling adhesive sealant that cures to form a firm, flexible and waterproof seal on aluminum, wood, gelcoat and fiberglass, making it well-suited for marine applications above or below the waterline. This product has a low VOC and a 50-minute skin time.	
	00051135065600	06560		10 oz. Cartridge	12/Box		
	00051135065648	06564	Black				
 3M™ Marine Adhesive Sealant Fast Cure 4000 UV	00051135052808	05280	White	3 oz. Tube	6/Box	This one-part sealant cures to form a firm, rubbery waterproof seal. Its flexibility allows for the dissipation of stress caused by shock, vibration, swelling or shrinking. Designed for marine applications above and below the waterline. Its UV resistance properties make this a good cosmetic sealant.	
	00051135065808	06580		10 oz. Cartridge	12/Box		
	00076308143169	14316	Black				
	00051135065860	06586	White	400mL Sausage			
	00051135055083	05508		600mL Sausage			
	00076308143435	N/A	Black				
 3M™ Marine Grade Silicone Sealant	00051135080177	08017	White	3 oz. Tube	6/Box	A non-sagging, moisture-curing silicone rubber sealant. Remains flexible. Ideal for head sealing applications. Also excellent gasket adhesive and formed-in-place gasket material. For above the waterline only.	
	00051135080191	08019	Clear				
	00051135080276	08027	White	10 oz. Cartridge	12/Box		
	00051135080290	08029	Clear				

Marine Surface Protection & Masking

To get the job done right the first time, you need the right tools. That's why we offer a full line of dependable masking solutions engineered for the demands of marine applications. From specialized surface protection, paint masking tapes, and protective sheeting to duct tapes made for everyday jobs, you can trust 3M to help you consistently deliver superior results.

Protective Fabric & Sheeting	29
Masking Paper	30
Welding Protection	30
Paint Masking Tapes	30
Critical Edge Masking Tapes	31
General Outdoor Applications	31



Protective Fabric & Sheeting

Protect your valuable surfaces.

Protective Fabric		UPC	Part #	Size	Qty/Box	Description
	3M™ Surface Protection Fabric	00051131368767	36876	4 in x 300 ft	6/Box	Engineered for the non-stop demands of marine environments where protection from water, solvents, oil and other fluids is vital. It can help boost your productivity, reduce maintenance and cleanup time, preserve your workspaces and eliminate re-work on finished surfaces.
		00051131368774	36877	6 in x 300 ft	1/Box	
		00051131368781	36878	14 in x 300 ft		
		00051131368798	36879	28 in x 300 ft		
		00051131368804	36880	36 in x 300 ft		
		00051131368811	36881	48 in x 300 ft		
		00051131368828	36882	56 in x 300 ft		
	3M™ Surface Protection Material Dispenser, Applicators and Cutter	00051131368620	36862	28 in	1/Box	Magnetic Dispenser
		00051131368651	36865	28 in		Floor Applicator
		00051131368644	36864	56 in		Floor Applicator Frame
		00051131368675	36867	36 in–56 in		Floor Applicator Foam Roller
		00051131368866	36886	28 in		
		00051131368682	36868	36 in		
		00051131368699	36869	48 in		
		00051131368705	36870	56 in		
		00051131368668	36866	28 in		Wall Applicator
		00051131368859	36885	N/A	6/Box	Cutter

Important Note: For more complete product information, instructions and warnings, please refer to the 3M Product Technical Data Sheet for this product which is available at 3M.com/SurfaceProtection.


Protective Sheeting	UPC	Part #	Size	Mils	Qty/Box	Description
 3M™ Moisture Resistant Protective Sheeting	0005113167257	06725	16 ft x 250 ft	0.65	1/Box	3M offers durable protective sheeting options that are puncture and tear resistant, and waterborne system compatible. Formulated to provide excellent paint adherence and cling to prevent bleed through. Protective sheeting minimizes the risk of imprinting or “ghosting” on damp surfaces, and prevents moisture staining in sheeting.
 3M™ Overspray Protective Sheeting	00051131067271	06727	12 ft x 400 ft	0.375		
	00051131067288	06728	16 ft x 400 ft			
	00051131067424	06742	20 ft x 250 ft			
 3M™ Plastic Sheeting	00051131067233	06723	12 ft x 400 ft	0.3		
	00051131067240	06724	16 ft x 40 ft			


No matter your masking challenge

there's a 3M masking solution that's right for you.

Masking Paper		UPC	Part #	Size	Color	Qty/Box	Description
	Scotch® Steel Gray Masking Paper	00021200065361	06536	36 in x 1000 ft	Gray	1/Box	3M offers an assortment of tightly bonded masking paper options that conform to a wide range of shapes and protect against fiber contamination. Specially formulated to protect against bleed-through from a variety of marine coatings.
	3M™ Scotchblok™ Masking Paper	00051131067325	06732	12 in x 180 ft	Gold	12/Box	
		00051131067387	06738	18 in x 180 ft			
		00051131067127	06712	12 in x750 ft		3/Box	

Welding Protection		UPC	Part #	Size	Color	Qty/Box	Description
	3M™ Weld and Spark Deflection Paper	00051131059160	05916	24 in x 150 ft	Tan	2 Rolls/Box	Deflection paper helps protect vertical surfaces from sparks and spatter. Recommended wherever welding or grinding tasks are performed. Adhesive backing allows for simple installation and is re-positionable to allow for adjustments and repeat uses.

Paint Masking Tapes		UPC	Part #	Size		Qty/Box	Description
	Scotch® Performance Green Masking Tape 233+	00051131263345	26334	3/4 in x 60 yd.		48/Box	Delivers consistently superior performance with a balanced four-part construction includes flexible backing that applies easily around curves and contours and our patented adhesive that sticks at a touch, stays put and removes without transfer for consistently outstanding paint lines.
		00051131263369	26336	1 in x 60 yd.		24/Box	
		00051131263383	26338	1-1/2 in x 60 yd.		16/Box	
		00051131263406	26340	2 in x 60 yd.		12/Box	
	3M™ Automotive Refinish Masking Tape 388N	00051131066526	06652	3/4 in x 60 yd.		48/Box	The robust crepe-paper backing offers good conformability, so you can stretch and manipulate the tape to fit curves and contours without tearing. The thin and flexible backing heightens the ability of the tape to conform and produce sharp, clean paint lines.
		00051131066533	06653	1 in x 60 yd.		36/Box	
		00051131066540	06654	1-1/2 in x 60 yd.		24/Box	
		00051131066564	06656	2 in x 60 yd.		24/Box	
	Scotch® High Performance Masking Tape 3434	7100037748	07895	3/4 in x 55 yd.		48/Box	Our high-performance blue crepe paper masking tape is solvent and water resistant and can be used in environments up to 110°C (230°F). Engineered as one of the highest-adhesion 3M masking tapes. It delivers excellent performance in humid environments. Scotch® High Performance Masking Tape 3434 has excellent holding power, even on plastic and rubber surfaces.
		7100037749	07897	1 in x 55 yd.		36/Box	
		7100037750	07898	1-1/2 in x 55 yd.		24/Box	
		7100037744	07899	2 in x 55 yd.		20/Box	
	Scotch® Painter's Tape 2080	00051131797482	79748	1 in x 60 yd.		36/Box	Delivers sharp paint lines with clean removal and no residue up to 14 days . Use with marine varnish and paints.
		00051131797505	79750	2 in x 60 yd.		12/Box	
		00051131809888	80988	7/10 in x 60 yd.		32/Box	
		00051131797499	79749	1-41/100 in x 60 yd.		24/Box	
	ScotchBlue™ Painter's Tape 2090	00051115036804	03680	7/10 in x 60 yd.		48/Box	Recommended for wood, metal, glass and painted surfaces with clean removal up to 14 days .
		00051115036811	03681	1 in x 60 yd.		36/Box	
		00051115092213	09221	1-41/100 in x 60 yd.		24/Box	
		00051115091681	09168	22/55 in x 60 yd.		24/Box	

Critical Edge Masking Tapes		UPC	Part #	Size	Qty/Case	Description
	3M™ Precision Masking Tape	00051131066205	06620	1 in x 60 yd.	12/Case	Excellent for critical edge paint performance, helping painters produce sharp paint lines using solvent and waterborne paint systems. The ultra-thin paper backing helps produce very low paint edges, yet it's strong enough to pull through layers of color and clear coat.
		00051131065253	06525	1/4 in x 60 yd.	144/Case	
		00051131065260	06526	3/4 in x 60 yd.	16/Case	
	Scotch® Fine Line Masking Tape 218	00021200063060	06306	1/16 in x 60 yd.	12/Box, 12 Boxes/Case	A high-performance polypropylene plastic tape that has both a low profile and high adhesion for use in painting long straight lines and sweeping curves where a crisp, sharp paint line is desired. It is often used as a layout tape for high value multi-color and custom painted graphics.
		00021200063022	06302	3/8 in x 60 yd.		
		00021200046988	04698	1/2 in x 60 yd.	18/Box, 4 Boxes/Case	
		00051115070741	07074	1-1/4 in x 60 yd.	28/Case	
		00021200047015	04701	2-1/4 in x 60 yd.	12/Case	
		00021200444524	44452	3 in x 60 yd.		
		00021200055003	05500	4 in x 60 yd.	8/Case	

General Outdoor Applications		UPC	Part #	Size	Qty/Box	Description
 3M™ Outdoor Masking Poly Tape, Red		00051135318429	05903	1-7/8 in x 179 ft 9-1/2 in 48mm x 54-4/5m	24/Box	Resists curling and tears off the roll cleanly for easy application on challenging, coated exteriors. This economical tape was constructed to allow for permanent and temporary applications. Outdoor use clean removal up to 1 month.
 3M™ Performance Plus Duct Tape 8979		00021200564680	56468	1-7/8 in x 179 ft 9-1/2 in 48mm x 54-4/5m	24/Box	Resists curling and tears off the roll cleanly for easy application on rough surfaces. It is removable with little or no adhesive residue up to six months after application.
		00021200564697	56469	2-7/8 in x 179 ft 9-1/2 in 72mm x 54-4/5m	12/Box	

Marine Paint & Gelcoat Application

Eliminate the complexity of traditional coating methods — along with the hassle and expense of constant cleaning and maintenance — with 3M™ Marine Paint and Gelcoat Application solutions.

3M™ Performance Spray Gun	34
3M™ PPS™ 2.0 System	37
Spray Gun Cleaner	39





The 3M™ Performance Spray Gun System was built with the industrial painter in mind.

The 3M™ Performance Spray Gun was designed specifically to deliver best-in-class performance while saving you time. You'll experience faster cleanup, faster changeovers and faster cycle times. It's the best of 3M Science, all packed into the lightest spray gun in the world.



Precision Performance

Spray solid colors, metallics, pearls, clear coats, sealers, and primers with the high transfer efficiency and atomization you expect from a premium professional spray gun.



Faster Cycle Times

Integrated system with 3M™ PPS™ Series 2.0 Spray Cups and replaceable nozzles means faster changeovers and more time in the zone.



Cleans in Seconds

Simply twist the locking collar, remove the atomizing head and wipe the needle clean. Swap with a new nozzle, and you're ready to spray your next job.



Ultra Lightweight

The advanced impact-resistant, stainless steel-reinforced composite body offers top-tier performance and durability all packed into the lightest spray gun in the world.

3M™ Performance Spray Gun

Paint like a pro with a simple, intuitive design.

3M™ Performance Industrial System	UPC	Part #	Qty/Box	Description
3M™ Performance Industrial Spray Gun System 	00051131268784	26878	2 Kits/Box	For Both Pressure Pot and Gravity Applications <u>Kit includes:</u> 1 – Performance Spray Gun 1 – Air Control Valve 1 – Pressure Whip 1 – Locking Collar 6 – Pressure Atomizing Heads (2 each of 1.1, 1.4, 1.8) 6 – Gravity Atomizing Heads (1 each of 1.2, 1.3, 1.4, 1.6, 1.8, 2.0) 1 – 3M™ PPS™ Series 2.0 (includes one cup, 5 liners, 5 lids, 3 sealing plugs)
3M™ Performance Spray Gun System with PPS™ 2.0 	04054596831346	26778		For Gravity Application <u>Kit includes:</u> 1 – Performance Spray Gun 1 – Air Control Valve 1 – Locking Collar 15 – Gravity Atomizing Heads (5 each of 1.2, 1.3, 1.4) 1 – 3M™ PPS™ Series 2.0 (includes one cup, 5 liners, 5 lids, 3 sealing plugs)
3M™ Performance Spray Gun 	00051131268326	26832	4/Box	<u>Includes:</u> 1 – Performance Spray Gun 1 – Air control valve Lightweight, impact-resistant body made from advanced composite material quickly converts between pressure-fed systems and gravity-fed 3M™ PPS™ Series 2.0 Spray Cup System. Easy to change, replaceable nozzles range from 1.1 – 2.0. Designed for comfort. The simple, innovative design means fewer parts to maintain or rebuild.
3M™ Performance Spray Gun 2 	00068060061287	26852		<u>Includes:</u> 1- Performance Spray Gun 2 1- Air control valve Optimized and redesigned for your application ease: • Sleek gun frame – now made with carbon fiber - and smooth finish to help cleanliness. • Laser marked control knobs. • Redesigned comfort trigger helps to provide an enhanced spraying experience Adding to the ergonomic performance, its impact-resistant composite body makes it one of the lightest spray guns available. Designed to deliver best-in-class performance.

3M™ Performance Pressure HVLP	UPC	Part #	Color	Size	Qty/Case	Description
3M™ Performance Pressure HVLP Atomizing Head Refill 	00051131268098	26809	White	0.9	10/Pack, 5 Packs/Case	Designed to deliver excellent spray performance for coatings including stains, primers, base coats, clear coats, topcoats and adhesives. Replaceable nozzles are built exclusively for pressure-feed applications using the 3M™ Performance Spray Gun.
	00051131268111	26811	Yellow	1.1		
	00051131268142	26814	Orange	1.4		
	00051131268180	26818	Clear	1.8		
	00051131268203	26820	Red	2.0		
3M™ Performance Pressure HVLP Atomizing Head Refill Kit	00051131268302	26830	Yellow, Orange, Clear	1.1–1.8	6/Kit, 5 Kits/Case	Kit includes two of each size: 1.1, 1.4, 1.8.

3M™ Performance Gravity HVLP System	UPC	Part #	Color	Size	Qty/Case	Description
3M™ Performance Gravity HVLP Atomizing Head Refill 	00051131267091	26709	White	0.9	5/Pack, 5 Packs/Case	Used for spraying a wide range of industrial and automotive coatings, including high-viscosity coatings, sprayable fillers, high-build primers, primer surfacers, sealers, single-stage top coats, solvent-based paints, waterborne paints and clearcoats.
	00051131267121	26712	Blue	1.2		
	00051131267138	26713	Green	1.3		
	00051131267145	26714	Orange	1.4		
	00051131267169	26716	Purple	1.6		
	00051131267183	26718	Clear	1.8		
	00051131267206	26720	Red	2.0		
3M™ Performance Gravity HVLP Atomizing Head Refill Kit	00051131267305	26730	Blue, Green, Orange, Red, Purple, Clear	1.2–2.0	6/Kit, 5 Kits/Case	Kit includes one of each size: 1.2, 1.3, 1.4, 1.6, 1.8, 2.0.

3M™ Performance Gravity Fine Finish System	UPC	Part #	Color	Size	Qty/Case	Description
3M™ Performance Gravity Fine Finish Atomizing Head Refill 	00068060060860	26909	White	0.9	5/Pack, 5 Packs/case	Spray today's most-challenging paints and clearcoats with 3M™ Performance Gravity Fine Finish Atomizing Heads. Built to work with the 3M™ Performance Spray Gun, they deliver finer atomization and a faster flow rate than typical HVLP spray equipment - helping you work faster, optimize your color match and lay down coatings like glass.
	00068060060914	26911	Yellow	1.1		
	00051131269125	26912	Blue	1.2		
	00051131269132	26913	Green	1.3		
	00051131269149	26914	Orange	1.4		
	00068060060907	26916	Purple	1.6		
	00068060060891	26918	Clear	1.8		
	00068060060884	26920	Red	2.0		

H/O Conversion Pack and Associated Parts (High Output)		UPC	Part #	Size	Qty/Box	Description
	3M™ Performance Spray Gun H/O Conversion Pack	00051131268371	26837	N/A	4/Box	Equips the 3M™ Performance Spray Gun to use 3M™ PPS™ Series 2.0 Type H/O Pressure Cups. This upgrade adds an air pressure port to the gun for spraying high-viscosity coatings.
	3M™ PPS™ Series 2.0 Type H/O Pressure Cup	00051131261211	26121	Midi (13.5 fl. oz.)	2/Box	A pressurized (H/O) hard cup and collar set that supports and holds 3M™ PPS™ flexible liner used in the 3M™ PPS™ (Legacy) paint preparation system. This product is intended for use in place of metal cups on most pressure spray guns.
		00051131261242	26124	Large (28 fl. oz.)		

Accessories and Replacement Parts		UPC	Part #	Qty/Box	Description
	Pressure Whip	00051131268333	26833	4/Box	Connects to the 3M™ Performance Spray Gun for use in pressure feed applications.
	Whip Pin	00051131268340	26834	4 Pins/Pack, 5 Packs/Box	Pin securely attaches whip hose to 3M™ Performance Spray Gun.
	Locking Collar	00051131268357	26835		Ensures a solid connection between the 3M™ Performance Spray Gun and atomizing heads.
	Spray Gun Needle	00051131268388	26838	1/Box	Use replacement needle when spray gun needle is damaged, bent or leaks.
	Ball Valve	00051131268395	26839	4/Box	Ball valve lets the painter stop fluid flow to spray gun.
	Rebuild Kit	00051131268401	26840	4 Kits/Box	Includes exterior replacement parts, all required interior seals, springs, screws and parts. Instruction manual provides specific details on how to rebuild.
	3M™ Performance Spray Gun Poppet	00068060060181	26842	4/Box	The 3M™ Performance Spray Gun Poppet is a replacement part for the original poppet and seal included in the 3M™ Performance Spray Gun. It comes with 5 extra replacement seals.
	3M™ Performance Spray Gun Service Kit	00068060060198	26850	4 Kits/Box	The 3M™ Performance Spray Gun Service Kit provides the most frequently needed replacement parts for the 3M™ Performance Spray Gun. It allows you to refresh the performance of the gun by replacing seals, o-rings, and other wear parts.



Engineered for peak performance.

3M™ PPS™ Series 2.0 is our most advanced Spray Cup System.
It's packed with features to help you perfect your paint jobs.

Domed Lid with Full-Diameter Filter.

More paint below the filter improves flow and consistency, while reducing spitting from start to finish.

New Cup in Every Lid and Liner Kit

Start with a clean cup more often, reducing paint build-up. On-cup ratios and fill markings eliminate traditional mixing cups.

Sealing Plug Included

Allows you to seal and protect coatings upside down with greater stability when not in use. Use fewer lids by keeping filters wet.



1 Wide Spout Adapter with Four-Point Connection

Maximizes stability while spraying. Makes cleaning easier.

2 Quarter-Turn Lid Locking System

Comes with every lid. Stays cleaner. Locks faster. Fewer parts to keep track of.

Access Window

Allows painter to hold the liner for cleaner, easier lid removal when refilling. Also easier to check paint levels.



3M™ PPS™ 2.0 System

Highest performing disposable spray cup system.

3M™ PPS™ 2.0 Spray Cup System		UPC	Part #	Size	Filter	Qty/Box	Description
 3M™ PPS™ Series 2.0 Spray Cup System Kit	00051131260245	26024	Large (28 oz., 850mL)	200 Micron	1 Kit/Box	Kit contains: 50 lids and liners, 32 sealing plugs, 1 hard cup.	
	00051131260009	26000	Standard (22 oz., 650mL)				
	00051131261129	26112	Midi (13.5 oz., 400mL)				
	00051131261143	26114	Mini (6.8 oz., 200mL)				
	00051131263253	26325	Large (28 oz., 850mL)	125 Micron	1 Kit/Box		
	00051131263017	26301	Standard (22 oz., 650mL)				
	00051131263123	26312	Midi (13.5 oz., 400mL)				
	00051131263147	26314	Mini (6.8 oz., 200mL)				
 3M™ PPS™ Series 2.0 Universal Shaker Core	0005113126458	26458	N/A	N/A	1/Box, 12 Boxes/Case	Fits on top of the domed lid and fits into the 1/4-turn lid locking system, creating a stable, durable and even surface for clamping cup tightly into paint shakers.	

For Industrial/Occupational use only.

Schedule a demo with your 3M Representative to learn more about the product.

3M™ PPS™ Legacy Lid and Liner Kits	UPC	Part #	Size	Filter	Qty/Case	Description
3M™ PPS™ Lid and Liner Kit	00051131160002	16000	Standard (22 oz., 650mL)	200 Micron	50 Lids & Liners/Kit	3M™ PPS™ (Legacy) Paint Preparation System is a complete painting system that allows the painter to measure, mix, filter and spray paint materials. Kits contain disposable lids with micron filters, liners and sealing plugs.
	00051131161122	16112	Midi (13.5 oz., 400mL)			
	00051131161146	16114	Mini (6.8 oz., 200mL)			
	00051131160286	16028	Micro (3 oz., 90mL)			

3M™ PPS™ Basic	UPC	Part #	Size	Volume	Filter	Content
 3M™ PPS™ Basic Series Lid and Liner Kit	00068060069955	PBS125	Standard	22 oz./650mL	125 Micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar
	00068060069962	PBS200	Standard	22 oz./650mL	200 Micron	
	00068060069979	PBL125	Large	28 oz./850mL	125 Micron	
	00068060069986	PBL200	Large	28 oz./850mL	200 Micron	

3M™ PPS™ Basic Collar	UPC	Part #	Size	Content
 3M™ PPS™ Basic Series Collar	00068060069993	PBC005	Std /Large	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar

3M™ PPS™ Basic Hard Cups	UPC	Part #	Items/Cartron	Items/Case
 3M™ PPS™ Series 2.0 Cups - Compatible with 3M™ PPS™ Basic Lids and Liners	00051131260238	26023	2	4
	00051131260016	26001		

Spray Gun Cleaner	UPC	Part #	Size	Qty/Box	Description
 3M™ High Power Spray Gun Cleaner	00051131266896	26689	15 oz. (426g) Aerosol Can	6/Box	Specifically formulated for removing waterborne and solvent-based coatings from metals, plastic and composite surfaces. This low VOC spray gun cleaner meets the requirements of SCAQMD Rule 1171. Can use for 3M™ Accuspray Guns and 3M™ Performance Spray Gun.

3M™ PPS™ Lid and Liner Dispenser	UPC	Part #	Size	Color	Qty/Box	Description
	3M™ PPS™ Liner Dispenser	00051131162198	16219	Large, Standard or Midi	Red	1/Box
	3M™ PPS™ Lid Dispenser	00051131162990	16299	Large, Standard, Midi or Mini	Red	

For best results, we recommend using 3M™ PPS™ Series 2.0 with 3M™ Performance Spray Gun Series. Alternatively choose one of the 3M™ PPS™ Series 2.0 Adapters to connect your spray gun to the spray system. For other spray guns, find a complete list of adapters at 3MCollision.com/PPSAdapters.

Marine Surface Finishing

Success or failure starts with choosing the right product for each surface, whether the surface is painted or gelcoat. To help you choose which compounds and polishes to use, 3M created product lines specifically for gelcoat surfaces and painted surfaces.

With the right system your finish will be faster, glossier and swirl free.

3M™ Perfect-It™ Gelcoat Finishing System	41
--	----

3M™ Perfect-It™ Paint Finishing System	42
--	----

3M™ Perfect-It™ Random Orbital Polishing System	43
---	----

3M Marine Boat Cleaning System	45
--------------------------------	----

3M™ Mechanical Cleaners and Lubricants	46
--	----

Adhesives and Tapes	46
---------------------	----



3M™ Perfect-It™ Gelcoat Finishing System


Our gelcoat buffing products are formulated specifically for your gelcoat surfaces, making it easier to achieve a perfect gelcoat finish, even in warm climates. In addition, Perfect-It™ for Gelcoat products now include a step-by-step process to help achieve dependable finishes every time, regardless of one-, two-, or three-step processes.

Gelcoat Finishing		UPC	Part #	Size	Qty/Box	Description
	3M™ Perfect-It™ Boat Wash	00051131090354	09035	1 Quart, (32 fl. oz.)	6/Box	Cleans grime, algae, dirt, and other common marine contaminants from stem to stern. High-sudsing formula is also gentle enough to clean without stripping wax.
	3M Perfect-It™ Gelcoat Heavy Cutting Compound	00051131361027	36102	1 Quart, (32 fl. oz.)	6/Box	Fast-cutting compound removes heavy oxidation, scratches, and other defects. Use for any heavy oxidation and P800 and finer scratches. Its improved formula has longer wet times for easier clean up and less dust. Works better in warm climates and allows you to use less material. Finish with a lighter cut or wax.
		00051131361034	36103	1 Gallon (128 fl. oz.)	4/Box	
	3M™ Perfect-It™ Gelcoat Compound + Polish	00051131303447	30344	1 Quart, (32 fl. oz.)	6/Box	Professional-grade formula offers a high gloss finish and provides longer wet time for extended product life and easier cleanup. Designed to be used as a single-step compound and polish or second step finish for eliminating P1000 and finer scratches, scuff marks, and other surface blemishes from gelcoat surfaces (even darker colored gelcoat).
		00051131303454	30345	1 Gallon (128 fl. oz.)	4/Box	
	3M™ Perfect-It™ Gelcoat Medium Cutting Compound + Wax (One-Step)	00051131361065	36106	1 Quart, (32 fl. oz.)	6/Box	Combines fast cutting power, a high gloss finish, and durable wax protection. Use for any medium oxidation and P1000 and finer scratches. Improved formula for longer wet times, easier clean up and less dust, even in warm climates.
		00051131361072	36107	1 Gallon (128 fl. oz.)	4/Box	
	3M™ Perfect-It™ Gelcoat Light Cutting Polish + Wax (One-Step)	00051131361102	36110	1 Quart, (32 fl. oz.)	6/Box	Use for brilliant finish and durable protection for light oxidation and P1500 and finer scratches on light or dark colored gelcoat. Improved formula for longer wet times, easier clean up, less dust, and more efficient use, even in warm climates.
		00051131361119	36111	1 Gallon (128 fl. oz.)	4/Box	
	3M™ Perfect-It™ Boat Wax	00051131361133	36113	1 Quart, (32 fl. oz.)	6/Box	Safe for gelcoat, paint, fiberglass, and metals and has a pleasant tropical scent. The pure wax finish protects against the elements. Use as a final step to any process where a wax finish is recommended.

3M™ Perfect-It™ Paint Finishing System


To give boats an enhanced shine, 3M compound and polishes work together, correcting painted surfaces and delivering superior finishing and refinishing results. Our compound products can help you quickly remove heavy scratches, oxidation, water marks and other defects before you apply a polish and buff to a high gloss. Our marine products are designed to minimize steps and cleanup, saving time, labor and expense.

Compound and Polishes	UPC	Part #	Size	Qty/Box	Description
 3M™ Perfect-It™ EX AC Rubbing Compound	00051131360600	36060	1 Quart, (32 fl. oz.)	6/Box	Our best-performing rubbing compound for removing P1200+ sand scratches and surface defects before polishing, even on the latest clear coats. It is formulated to perform in all conditions, including high heat and humidity, without sticking to panels or leaving film residue. It delivers a longer working time, yet still reduces sling for easier cleanup.
	00051131360617	36061	1 Gallon (128 fl. oz.)	4/Box	
 3M™ Perfect-It™ EX Machine Polish	00051131060944	06094	1 Quart, (32 fl. oz.)	6/Box	We've combined innovative ingredients with our high-performance liquid mineral technology to create a machine polish that cuts, handles, and cleans up better. Stays wetter longer, delivering a longer work time and less sling. It wipes up easily, saving you clean up time.
	00051131060951	06095	1 Gallon (128 fl. oz.)	4/Box	
 3M™ Perfect-It™ EX Ultrafine Machine Polish	00051131390621	39062	1 Pint, (16 fl. oz.)	6/Box	Our high-performance ultrafine machine polish has a unique formula to quickly and effectively eliminate swirl marks. It produces a high gloss finish, even on the most difficult dark-colored vehicles. It has good handling and easy cleanup allowing you to use less.
	00051131060685	06068	1 Quart, (32 fl. oz.)		
	00051131060692	06069	1 Gallon (128 fl. oz.)	4/Box	



Double Sided Paint and Gelcoat Finishing Pads and Adaptor	UPC	Part #	Color	Size	Qty/Box
3M™ Perfect-It™ Wool Compounding Pad	00051131057548	05753	White Wool	9 in	6/Box
3M™ Perfect-It™ Wool Polishing Pad	00051131057531	05754	Yellow Wool		
3M™ Perfect-It™ Foam Compounding Pad	00051131057067	05706	White Foam	8 in	
3M™ Perfect-It™ Foam Polishing Pad	00051131057074	05707	Black Foam		
3M™ Perfect-It™ Ultrafine Polishing Pad	00051131057081	05708	Blue Foam		
3M™ Perfect-It™ Quick Connect Adaptor	00051131057524	05752	Silver/Purple	5/8 in	10/Box

3M™ Perfect-It™ Random Orbital Polishing System



Achieve the best possible finish on a variety of paints and clear coats with the 3M™ Perfect-It™ Random Orbital Finishing System.



Polisher	UPC	Part #	Size	Orbit Diameter	Qty/Box	Description
 3M™ Perfect-It™ Random Orbital Polisher	00051131341005	34100	5 in (for use with 5 in pad size)	15mm	1/Box	Spend less time compounding and polishing while using less paint finishing liquids with the 3M™ Perfect-It™ Random Orbital Polisher and it's engineered liquids, polishes, and pads. Our Random Orbital Polishing System produces less sling and no swirl marks without the worry of burn through. It's easy-to-learn and easy-to-use, helping you deliver a consistent high-quality finish every time.
	00051131341012	34101	6 in (for use with 6 in pad size)	21mm		

Compound and Polishes	UPC	Part #	Size	Qty/Box	Description
 3M™ Perfect-It™ Random Orbital Compound	50051131341307	34130	1 Pint, (16 fl. oz.)	6/Box	3M™ Perfect-It™ Random Orbital Compound is the newest compound in the Perfect-It™ family. Our professional grade fast cutting compound formula is designed to be used with our 3M™ Random Orbital Polisher for quick removal of 1200 grade and finer sanding marks and can be used on fresh and cured paints and clear coats.
	50051131341314	34131	1 Quart, (32 fl. oz.)		
	50051131341321	34132	1 Gallon (128 fl. oz.)	4/Box	
 3M™ Perfect-It™ Random Orbital Polish	50051131341338	34133	1 Pint, (16 fl. oz.)	6/Box	Our 3M™ Perfect-It™ Random Orbital Pads are engineered to be used with our 3M™ Perfect-It™ Random Orbital Polisher and matched liquids for paint finishing and detailing professionals of all skill levels who want a perfect finish without haze and swirl.
	50051131341345	34134	1 Quart, (32 fl. oz.)		
	50051131341352	34135	1 Gallon (128 fl. oz.)	4/Box	

Compound and Polish Pads	UPC	Part #	Size*	Qty/Box	Description
 3M™ Perfect-It™ Random Orbital Coarse Wool Compounding Pad	50051131341208	34120	5 in White Wool	2 Pads/Bag, 6 Bags/Box	Our 3M™ Perfect-It™ Random Orbital Pads are engineered to be used with our 3M™ Perfect-It™ Random Orbital Polisher and matched liquids for paint finishing and detailing professionals of all skill levels who want a perfect finish without haze and swirl.
	50051131341246	34124	6 in White Wool		
 3M™ Perfect-It™ Random Orbital Medium Wool Compounding Pad	50051131341215	34121	5 in White Wool	2 Pads/Bag, 6 Bags/Box	Our 3M™ Perfect-It™ Random Orbital Pads are engineered to be used with our 3M™ Perfect-It™ Random Orbital Polisher and matched liquids for paint finishing and detailing professionals of all skill levels who want a perfect finish without haze and swirl.
	50051131341253	34125	6 in White Wool		
 3M™ Perfect-It™ Random Orbital Foam Compounding Pad	50051131341222	34122	5 in White Foam	2 Pads/Bag, 6 Bags/Box	Our 3M™ Perfect-It™ Random Orbital Pads are engineered to be used with our 3M™ Perfect-It™ Random Orbital Polisher and matched liquids for paint finishing and detailing professionals of all skill levels who want a perfect finish without haze and swirl.
	50051131341260	34126	6 in White Foam		
 3M™ Perfect-It™ Random Orbital Foam Polishing Pad	50051131341239	34123	5 in Purple Foam	2 Pads/Bag, 6 Bags/Box	Our 3M™ Perfect-It™ Random Orbital Pads are engineered to be used with our 3M™ Perfect-It™ Random Orbital Polisher and matched liquids for paint finishing and detailing professionals of all skill levels who want a perfect finish without haze and swirl.
	50051131341277	34127	6 in Purple Foam		

Accessories	UPC	Part #	Size*	Qty/Box	Description
 3M™ Perfect-It™ Random Orbital Backup Pad	04064035015411	34128	5 in	5/Box	3M™ Perfect-It™ Random Orbital Polisher Back-up Pads are part of easy-to-use 3M™ Perfect-It™ Random Orbital Paint Finishing System, includes matched pads, liquids and tools deliver high quality finishes for technicians of every skill level. Experience no more swirls, holograms, burn-through with the 3M™ Random Orbital Polisher and Finishing system; achieve consistent high-gloss finish on variety paints and clear coats.
	04064035015435	34129	6 in		

*Use 5 in pads with 15mm polisher. Use 6 in pads with 21mm polisher.

3M Marine Boat Cleaning System

Make the “new look” last. 3M Marine boat maintenance products are designed to simplify some of your most difficult cleaning applications. Easily and effectively remove dirt, grime, algae, oil, fish blood, waterline stains, mildew and black streaks from your boat’s surface. Products are safe for use on fiberglass, metal and painted surfaces.

Boat Cleaning		UPC	Part #	Size	Qty/Box	Description
	3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover	50048011193446	19344	1 Quart	12/Box	No rinse formula cleaner for quick, easy removal of soil and grease from almost any washable hard surface. This powerful ready-to-use cleaner penetrates and loosens buildup quickly.
		50048011137020	13702	5 Gallon	1/Box	
	3M™ Marine Non-Skid Cleaner	00051131090637	09063	33-4/5 fl. oz.	6/Box	Use for cleaning ground-in dirt and stains on non-skid areas — the textured surfaces on boats where dirt and grime can settle and become very difficult to remove. Easy-to-use cleaner simply pours on, brushes in and rinses off. Safe for fiberglass, gelcoat, metal and painted surfaces.
	3M™ Marine Black Streak Remover	00051131090477	09047	16-9/10 fl. oz.	6/Box	Specially formulated to instantly remove difficult black streaks with minimal time and effort from your boat caused by water runoff, bumpers, shoe treads and more. Though it's tough on streaks, the remover is safe for fiberglass, metal and painted surfaces.
	3M™ Mildew Remover	00051131090675	09067	16-9/10 fl. oz.	6/Box	3M Marine Mildew Remover quickly removes mildew stains on vinyl, covers, cushions and other marine surfaces. Spray and wipe formula requires minimal scrubbing. Follow-up with 3M Marine Mildew Block for long-lasting protection.
	3M™ Marine Aluminum Restorer and Polish	00051131090200	09020	18 oz.	6/Box	Use this product to restore the beauty and pride of ownership in your boat. Our product comes in a concentrated formula so a small amount provides a lot of restoration and polishing.

Boat Cleaning		UPC	Part #	Size	Qty/Box	Description
 3M™ General Purpose Adhesive Cleaner		00051135089873	08987	15 oz. Net. Wt.	12/Box	Makes the job of removing adhesive residue an easier task. More effective than plain water, our solvent works by softening sticky substances that are often stubborn to remove. It penetrates into sticky residue, allowing you to wipe it away with greater ease. What's left behind is a clean surface free of film or stickiness.
		00051135089842	08984	32 fl. oz.	6/Box	
 3M™ Specialty Adhesive Remover		00051135389874	38987	15 fl. oz.	6/Box	Versatile application: Removes reactive adhesives from a variety of substrates; reactive adhesives include adhesives that require a hardener or catalyst in order for the bond to occur, such as epoxies, urethanes, and silicones. Easy to use: Spray-on delivery optimizes coverage and application versatility. Residue-free finish: Specially engineered for added ease during the removal of residue. Solvent based: A strong, solvent-based formula acts fast on stubborn adhesives.
		00051131389847	38984	1 Quart	6/Box	
 3M™ Perfect-It™ Detailing Cloths		50051131060178	06017	12 in x 14 in	50/Pack	This cloth removes oily or filmy residue including waxes, polishes, glazes and fingerprints and is ideal for paint, chrome, glass, dashboards and more. Paint shop safe.

Mechanical Cleaners		UPC	Part #	Size	Qty/Box	Description
 3M™ Industrial Cleaner Citrus Base		00021200763946	CIT CLNR	24 fl. oz., (18-1/2 oz. Net. Wt.)	12/Box	Used to help dissolve and remove dirt, grease, tar and many non-curing adhesives. It cleans without streaking and has a fresh citrus scent. In some Boxes it can be used in place of chlorinated or petroleum-based solvents for degreasing and other industrial applications. NOT FOR SALE IN CA AND OTHER STATES.

Adhesives and Tapes		UPC	Part #	Size	Qty/Box	Description
 3M™ Black Super Weatherstrip and Gasket Adhesive		00051135080085	08008	5 fl. oz.	6/Box	Forms a flexible, waterproof bond that resists vibration and is easy to brush and spread right from the tube. Resists oils, solvents, detergents and temperature changes for permanent repairs. Bonds to a range of surfaces including vinyl, metal, fabrics and rubber.
 Scotch® Super 33+ Vinyl Electrical Tape		00054007061335	06133	3/4 in x 52 ft	100/Box	A premium, 7 mil tape that provides electrical insulation for all wires and cables rated up to 600V. The flame retardant tape withstands a temperature range of 0–221°F (18–105°C). It is compatible with solid dielectric cable insulation, synthetic cable insulation, jackets and splicing compounds.



Tools & Accessories

Choosing the right abrasives and dust extraction for your surface finishing and marine repair project is critical — and so is using the right tool. 3M offers full systems of high-quality metal grinding and sanding tools, disc backup pads and accessories to optimize abrasive performance and maximize productivity. Whether your job calls for an angle grinder, a sanding tool or a buffer, 3M has you covered with the power tools, accessories and service you need.

3M™ Clean Sanding System	50
--------------------------	----

3M™ Power Tool Accessories	54
----------------------------	----

3M™ Accessories	57
-----------------	----





3M™ Clean Sanding System

Designed with technicians and shop owners in mind.

A complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic and/or electric random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.



Designed to reduce dust in the air from sanding for a cleaner workspace



Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time



Compact and mobile — designed for easy, flexible use around the shop



Compatible with pneumatic and/or electric sanders



Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights

Marine Sanding Systems

Build your perfect system.

Dust Extractors		UPC	Part #	Size	Qty/Box	Description
	3M™ Clean Sanding System Dust Extractor	00051131337749	33774	45L	1/Box	120V, Plug Type B Compact and lightweight. Designed to help reduce dust in the air from sanding for a cleaner workspace. Less dust can mean less rework and less cleanup time, helping to improve overall efficiency. Can be set up for either pneumatic or electric sanders.
						<u>Dust Extractor includes:</u> 5m pneumatic hose, y-connector, filter and filter bag.

3M™ Clean Sanding System Random Orbital Sanders		UPC	Part #	Orbit	Size	Max RPM	Qty/Box	Description
	3M™ Precision Random Orbital Sander	00068060061324	33797	3/32 in (2.5mm)	3 in	12,000	1/Case	Pneumatic Designed to deliver high-quality surface preparation and finishing results while helping to improve the performance of your 3M™ Abrasives. Variable speed adjustment helps gives the technician added control. Vacuum-ready.
		06940544232113	38505	3/16 in (5mm)				
		06940544232588	33632	3/32 in (2.5mm)	6 in			
		06940544232571	33633	3/16 in (5mm)				
		00068060061171	33634	5/16 in (8mm)				
	3M™ Electric Random Orbital Sander	00068060061362	33804	3/32 in (2.5mm)	3 in	10,000	1/Case	Electric 120V, Plug Type B, Vacuum-Ready
		00068060061447	33798	3/32 in (2.5mm)	6 in			
		00051131337794	33779	3/16 in (5mm)				

3M™ Clean Sanding System Orbital Sheet Sanders		UPC	Part #	Orbit	Size	Max RPM	Qty/Box	Description
	3M™ Precision Random Orbital Sander	00068060061454	33796	1/8 in (3.0mm)	2-3/4 in x 7-3/4 in (70mm x 198mm)	10,000 OPM	1/Case	Pneumatic Use 3M™ Pneumatic Precision Orbital Sheet Sander to efficiently sand and flatten metal, paint, filler and primer for repair. This pneumatic sander is designed for technicians who need reliable and effective tools for surface preparation and finishing work.

See page 57 for power tool accessories, including back-up pads and interface pads.

3M™ Clean Sanding System Dust Extractor Hoses		UPC	Part #	Length	Qty/Box	Description
	3M™ Antistatic Pneumatic Hose	00051131336452	33645	5m (16-2/5 ft)	1/Case	The 3M™ Antistatic Pneumatic Hose works with the 3M™ Clean Sanding System. The built-in air regulator collar allows the operator to adjust suction. The air hose is built into the vacuum hose to help reduce snagging, clutter and tangling.
		00051131337831	33783	8m (26-1/4 ft)		
		00068060061263	33790	10m (32-4/5 ft)		
	3M™ Antistatic Electric Hose	00051131336469	33646	5m (16-2/5 ft)	1/Case	The 3M™ Antistatic Electric Hose is designed for use with the 3M™ Clean Sanding System when using electric sanders or hand blocks. The built-in air regulator collar allows the operator easily to adjust suction. Its quick-connection couplings allow easy attachment to tools and the 3M dust extractor.
	3M™ Clean Sanding System Electric Hose Sleeve	00068060070654	33747	4-1/2m (14-3/4 ft)	1/Case	The 3M™ Clean Sanding System Hose Sleeve secures your electric sander power cable to your dust extraction hose, keeping work areas tidy and protecting your repair, protecting hoses and cables from abrasion and wear. Made of flexible woven plastic mesh, it features a dust-protected zip for full opening and a secure end closure, helping keep work areas organized.

3M™ Clean Sanding System Block Hoses		UPC	Part #	Length	Qty/Box	Description
	3M™ Dust Free Hose Extension Kit	00051131052154	05215	6m (20 ft)	1/Case	The 3M™ Antistatic Pneumatic Hose works with the 3M™ Clean Sanding System. The built-in air regulator collar allows the operator to adjust suction. The air hose is built into the vacuum hose to help reduce snagging, clutter and tangling.
	Clean Sanding System Antistatic Hand Block Hose	00068060071880	33748	6m (20 ft)	1/Case	Use 3M™ Clean Sanding System Antistatic Hand Block Hose to help achieve a dust free and cleaner sanding environment. The antistatic hose connects a manual hand block to the 3M™ Clean Sanding System Dust Extractor. Paired with a suitable dust-free hand sheet on the block, the hand block hose facilitates dust extraction and its length allows for a larger radius of movement.

Accessories and Maintenance		UPC	Part #	Size	Qty/Box	Description
	3M™ Dust Extractor Handle Extension	00051131337657	33765	—	1/Box	Fits the 3M™ Clean Sanding System 45-liter dust extractor. Helps to facilitate easy transport of the extractor base from a standing position. Attaches easily to the extractor unit.
	3M™ Clean Sanding System Workstation	00051131336537	33653	—	1/Box	The steel cart holds one 45-liter 3M™ Dust Extractor base. Includes two repositionable tool hangers and two repositionable hose hangers; a two-shelf locking cabinet; waste compartment; large smooth-riding rubber wheels, and a rubberized work surface.
	3M™ Clean Sanding System Workstation Extension	00051131336544	33654	—	1/Box	Fits workstation. Three panels allow customization of storage using the 15 included hooks. Provides additional mounting locations for the Workstation's tool holder and hose hooks.
	3M™ Abrasives Organizer Box	00068060061317	33784	—	1/Case	The 3M™ Abrasives Organizer Box is a robust black plastic container designed to neatly hold abrasives. It features three drawers and can be fitted onto a 3M™ Dust Extractor.



3M™ Clean Sanding System Accessories and Maintenance		UPC	Part #	Size	Qty/Box	Description
	3M™ Dust Extractor Filter Bag	00051131336483	33648	—	5 Each/ Pack, 1 Pack/ Box	Designed to maximize the dust collection capacity of 3M™ Dust Extractors. Tough, flexible non-woven plastic material. Easy close plastic closure cap helps prevent leakage during disposal.
	3M™ Dust Extractor Filter	00051131336476	33647	—	2 Each/ Pack, 1 Pack/ Box	Two pack of polyester replacement filters for the 3M™ Dust Extractors. Helps protect the motor unit of the extractor and filter the unit's exhaust air.

Dust Extractor Accessories		UPC	Part #	Size	Qty/Box	Description
	3M™ Dust Extractor Y-Connector	00051131336520	33652	Overall diameter: 1.142 in 29mm Inside diameter: 0.98 in 25mm	1/Box	Allows a 3M™ Dust Extractor to support two vacuum tools at the same time. The user can connect two tools simultaneously.
	3M™ Random Orbital Sander Adaptor for Hose Assembly	00051131337701	33770	2-1/4 in 57mm	4/Box	Connect select 3M™ Random Orbital Sanders and hose assemblies to existing central vacuum systems.
	3M™ Dust Extractor Straight Adaptor	00051131337718	33771	1-1/2 in 38mm		Securely attaches a hose of selected electric random orbital sanders to the 3M™ Dust Extractor.
	3M™ Dust Extractor Adaptor	00051131337725	33772	1-1/8 in 29mm		

Sanding Blocks		UPC	Part #	Size	Qty/Box	Description
	3M™ Hookit™ Dust Extraction Flexible Sanding Block	00051131358256	35825	5-1/4 in x 2-5/8 in 133mm x 67mm	24/Box	These 3M™ Hookit™ blocks combine the lightweight flexibility of traditional foam blocks with the dust extraction power and control of rigid dust-free sanding blocks. They feature a convex face which can help you easily restore contours and bodylines, while still providing a firm backing for abrasives. They include a vacuum regulator that lets the operator adjust suction for easier block control when sanding.
		00051131358263	35826	7 in x 2-5/8 in 178mm x 67mm		
		00051131358270	35827	10-3/4 in x 2-5/8 in 273mm x 67mm	12/Box	
		00051131358287	35828	16 in x 2-5/8 in 406mm x 67mm	8/Box	
		00051131358294	35829	Kit – 5-1/4 in, 7 in, 10-3/4 in 133mm, 187mm, 273mm	10/Box	
	3M™ Hookit™ Dust Extraction Flexible Radius Sanding Block	00051131358300	35830	5-1/4 in x 2-5/8 in 133mm x 66mm	24/Box	These blocks combine the lightweight flexibility of traditional foam blocks with the dust extraction power and control of dust-free sanding blocks. The blocks flex to help easily restore contours and bodylines, while providing a firm backing for abrasives. Features 3M™ Hookit™ attachment system. They include a vacuum regulator that lets the operator adjust suction for easier block control when sanding.
		00051131358317	35831	7 in x 2-5/8 in 178mm x 66mm		
		00051131358324	35832	10-3/4 in x 2-5/8 in 273mm x 66mm	12/Box	
		00051131358331	35833	Kit – 5-1/4 in, 7 in, 10-3/4 in 133mm, 187mm, 273mm	10/Box	

Non-Vacuum Conversion Kits		UPC	Part #	Size	Qty/Box	Description
	3M™ Pneumatic Precision Random Orbital Sander Non-Vacuum Conversion Kit	00068060069146	33745	3 in	10 Kits / Case	This small accessory replaces the tool's current shroud with a non-vacuum shroud, enabling the sander to be used without dust extraction.
		00068060069153	33746	6 in		
	3M™ Electric Random Orbital Sander Non-Vacuum Conversion Kit	00068060069115	33742	3 in	10 Kits / Case	
		00068060069122	33743	6 in		

3M™ Power Tool Accessories for Boat Repairs

Sanding Discs and Blocks	UPC	Part #	Size	Qty/Box	Description
 3M™ Hookit™ Clean Sanding Multi-Connection Disc Pad	00068060060051	30062	6 in Diameter 59/125 in Thick	5/Box	A replacement backup pad that provides a stronger, more reliable attachment for net, paper, and film backed abrasives to 6-inch dual-action sanders. Connects to 3M and most other dual-action sanders. Its versatile multi-hole design works seamlessly with dust-extraction abrasives, helping reduce the need for hole alignment.
 3M™ Hookit™ Low Profile Disc Back-up Pad	00051131301603	30160	6 in Diameter	10/Case	The 3M™ Hookit™ Low Profile Abrasive Disc Back-up Pad is designed specifically for better leveling and faster material removal during flat sanding. Its low profile and medium density foam construction afford excellent control, and its 15-degree blunt tapered edge holds up under tough conditions. Specially designed for use with 3M™ Hookit™ Abrasive Discs for fast change-outs.
 3M Xtract™ Low Profile Back-up Pad	00051141203508	20350	3 in Diameter		3M Xtract™ proprietary multi-hole pattern provides superior dust extraction to prevent loading, increase productivity, and provide a cleaner work environment
 3M™ Hookit™ Clean Sanding Abrasive Sheet Back-up Pad	00068060068040	30063	2-3/4 in x 7-3/4 in		3M™ Hookit™ Clean Sanding Abrasive Sheet Sander Back-up Pad is a medium density backup pad for abrasive sheets to be used on the on 3M™ Pneumatic Precision Orbital Sheet Sander. This multihole back-up pad supports optimal dust control and surface finishing, contributing to a cleaner and more efficient body shop environment.
 3M™ Hookit™ Clean Sanding Low Profile Finishing Disc Pad	00051141204253	20425	6 in Diameter 11/16 in Thick	10/Box	Multi-hole pattern maximizes dust extraction. Soft density foam provides flexibility for reduced edge cutting and increased conformability. Loading is significantly reduced to prolong life of abrasive. 3M™ Hookit™ for quick disc changeouts. 10 degree blunt tapered edge.
	00051141202907	20290	5 in Diameter 11/16 in Thick		
 3M™ Hookit™ Clean Sanding Low Profile Disc Pad	00051141204659	20465	6 in Diameter 3/8 in Thick	10/Box	Constructed of soft density foam with a 10 degree blunt tapered edge and is recommended for finishing applications on flat or contoured surfaces where dust evacuation is needed.
 3M™ Hookit™ Clean Sanding Disc Pad Hook Saver	00051141204451	20445	6 in Diameter 1/2 in Thick	20/Box	Protects and extends the life of the hooks on a new Hookit™ Clean Sanding Disc Pad. This hook saver provides an additional low cost replaceable layer of hooks that can be consumed during use, in place of those on the disc pad itself. This extends the life of the pad and minimizes costly replacements where repeated disc changes occur.
 3M™ Hookit™ Soft Interface Pad	00051131057777	05777	6 in Diameter 3/4 in Thick	10/Box	Adds support to disc pad for improved abrasive cut and closer edge sanding. Soft foam construction conforms to contours for a finer finish. Hole configurations help clear dust from the work surface. Reduces vibration from orbital sanding tool. 3M™ Hookit™ for quick disc changeouts.
	00051131057715	05771	3 in Diameter 1/2 in Thick		
 3M™ Hookit™ Flexible Abrasive Interface Foam Pad	00051131343504	34350	3 in x 5 in	10/Box	Interface foam pad provides flexibility to sand curves and contours and hard-to-reach locations. Use for sanding primer, blending and paint finishing. Use with 3M™ Orbital Sander, PN 20331 and 3M™ Hookit™ Flexible Abrasive Hand Sheets.

Sanding Discs and Blocks		UPC	Part #	Size	Qty/Box	Description
    3M™ Hookit™ Sanding Block Dust Free	00051131052161	05216	4-1/2 in x 11-1/2 in	3/Box	Has small holes for use with a vacuum system to limit dust and loading. Helps reduce hand fatigue and make sanding challenging locations easier. Sanding blocks deliver more consistent and effective hand sanding results.	
	00051131052093	05209	2-3/4 in x 15-3/5 in	1/Box		
	00051131052086	05208	2-3/4 in x 7-1/2 in	5/Box		
	00051131052079	05207	2-3/4 in x 5 in			


Power Tools	UPC	Part #	Size	Max RPM	Motor HP (W)	Qty/Box	Description
 3M™ File Belt Sander	00051131335752	33575	H: 2-87/100 in L: 15-3/20 in	17,000	13/20 (485)	1/Box	Lightweight file belt sander is ideal for cutting and finishing repair work. Rotatable housing allows for use in a versatile range of tight spaces.
 3M™ Mini File Belt Sander	00051131335738	33573	H: 2-87/100 in L: 12-1/2 in				
 3M™ Pistol Grip Disc Sander	00051131335776	33577	H: 2-1/20 in L: 7-1/2 in	18,000	9/20 (336)	1/Box	Lightweight for versatility and ease of use in tight spaces. Variable speed control at the trigger increases operator precision to help reduce rework.
 3M™ Cut-Off Wheel Tool	00051131335790	33579	3 in	20,000	7/10 (522)	1/Box	Compact design with built-in safety features for easy handling. Featuring a light-weight composite body for greater user comfort. Slice through high-strength steel and aluminum with clean, straight lines and minimal effort.
 3M™ Disc Sander	00051141284088	28408	4 in–5 in x 5/8 in–11 EXT	12,000	1 (744)	1/Box	Lightweight and rugged, designed with a high power-to-weight ratio. 3M™ Gripping Material and a 97-degree angle head allow more comfort and control. Great for grinding, blending, weld leveling, metal prep and more.
 3M™ Non-Vacuum Orbital Sander — Original Series	00051141203317	20331	3 in x 4 in 1/8 in Orbit	10,000	6/25 (179)	1/Box	Ideal for sanding in tight areas or on vertical surfaces. Non-Vac 3M™ Hookit™ 20433

Marine Sanding Systems

Build your perfect system.

Tool + Accessories + 3M Abrasive + Optimized System

Right Angle System




3M™ Disc Pad Hub

3M™ Disc Pad Face Plate

Abrasive Disc with
7/8 Center Hole

3M™ Disc Retainer Nut

3M™ Roloc™ System




Sander Adapter

3M™ Roloc™ Disc Pad

Abrasive Disc

3M™ Roloc™ + Holder


Abrasive Disc Wheel



Power Tool Accessories	UPC	Part #	Size	Feature	Qty/Box	Description
Right Angle System						
 3M™ Disc Pads	00051141286266	45205	2-1/2 in x 5/8–11 in INT	Use with all 4 in–9 in face plates	10/Box	Has a threaded metal insert and can be used on most 5/8–11 shafts.
	00051144451906	45190	4-1/2 in x 5/8–11 in INT	Use with 7 in, 8 in, 9 in face plates		
 3M™ Disc Pad Face Plates — Ribbed	00051144817337	81733	5 in	Hard Black	10/Box	Use with 3M™ Fibre Discs and Disc Pad Hubs for heavy metal removal, large welds, etc. 3M™ Disc Pad Face Plates can be easily changed without removing the hub.
	00051144805150	80515	7 in			
	00051144817290	81729	9 in			
 3M™ Disc Retainer Nuts	00051111510476	02618	5/16 in x 5/8–11 in INT	1/4 in Hole	10/Box	Use with 3M™ Disc Pad Face Plates, Disc Pad Hubs and Fibre Disc Holders. Has 1/4 in diameter holes for use with a spanner wrench.
	00051144056224	05622	3/8 in x 5/8–11 in INT			
3M™ Roloc™ System						
 3M™ Roloc™ Disc Pad Assembly	00051144055395	05539	2 in	Max RPM 25,000	10/Box	Hard rubber backup pad provides firm support for 3M™ Roloc™ Abrasive Discs. A 1/4–20 INT thread allows pad to be mounted directly to tools with 1/4–20 EXT threaded shafts. Assembly includes a 3M™ Roloc™ Disc Pad, shaft and adapter.
	00051144055401	05540	3 in			
 3M™ Roloc™ + Holder	00051144055401	07500	2 in 1/4 in shank	Max RPM 25,000	10/Box	Allows use of Scotch-Brite™ Roloc™ + Clean and Strip Disc on your tool. The 1/4 in shank fits into any recommended standard tool with 1/4 in collet. Quick and easy to use.

3M™ Accessories for Boat Repairs

Tools and Accessories	UPC	Part #	Size	Qty/Box	Description
 3M™ Masking Machine	00051131301818	30181	Rectangle Weight 53 lbs	1/Case	The 3M™ Masking Machine dispenses up to three sizes of masking paper with tape attached for fast and easy masking. Holds two rolls of masking paper up to 18 inches wide and one roll up to 12 inches wide. The masking machine maintains proper paper and tape alignment reducing the need for adjustment. Does not include tape and masking paper.
 3M™ Sealers, Coatings, and Adhesives Organizer	00051131025080	02508	30-1/8 in high, 14-1/8 in wide and 12-1/8 in deep 26 pounds	1/Case	3M™ Sealers, Coatings, and Adhesives Organizer, PN02508, Provides storage for various body shop materials. Shelves allow for organizing supplies. The one-door cabinet is equipped with a closable, lockable door

Hand Sanding Accessories		UPC	Part #	Size	Qty/Box	Description
 3M™ Hookit™ Hand Sanding Blocks	00051131056886	05688	Rectangle 1-1/2 in x 2-5/8 in x 16 in	8/Box	24/Box	Helps make sanding more comfortable and more productive in hard-to-sand locations. Range of sizes increases capabilities for precision hand sanding. Bright yellow design helps to stand out in dusty shop conditions.
	00051131056879	05687	Rectangle 1-1/2 in x 2-5/8 in x 10-3/4 in	12/Box		
	00051131056862	05686	Rectangle 1-1/2 in x 2-5/8 in x 5-1/4 in			
	00051131056855	05685	Rectangle 7/8 in x 1-3/8 in x 10-3/4 in			
	00051131056909	05690	Rectangle 5/8 in x 2-1/2 in x 5-3/8 in			
	00051131056893	05689	Round 1-1/4 in x 10-3/4 in			
	00051131056916	05691	Teardrop 2-1/8 in x 10-3/4 in	12/Box		
	00051131056848	05684	Various Shapes 6 Block Sizes	6 Kits/ Box		
 3M™ Stikit™ Hand Sanding Blocks	00051131056923	05692	Various Shapes 6 Block Sizes	6 Kits/ Box		

3M Marine Fairing Boards	UPC	Part #	Size	Qty/Box	Description
 3M™ Hookit™ Marine Fairing Board	00051144834976	83497	4-1/2 in x 30 in	1/Box	Two-level design for secure grasp and handling. Ideal for a range of marine finishing from freeboard and deck sanding to finishing plugs and molds.
	00051144839780	83978			Lightweight, double-handle design that affords a secure grasp and easy handling, with a flexible facing for working smoothly across concaves, convexes and curves.
 3M™ Stikit™ Hand File Board	00051144054442	05444	2-3/4 in x 16-1/2 in	1/Box	Achieve a more even and consistent application of pressure, which delivers more uniform results on flat surface.
	00051131057449	05744			

Personal Safety Equipment

Providing PPE to help protect the health of your technicians helps protect the whole business. 3M's personal protective products can help you protect workers: A marine repair shop's most valuable resource!

Powered Air Purifying Respirator System	59
---	----

Respirators	62
-------------	----

Hearing Protection	63
--------------------	----

Eye & Face Protection	64
-----------------------	----

Coveralls	65
-----------	----

Spill Management	66
------------------	----

Not a complete list. Please choose the right products for each application and exposure assessment.

Visit [3M.com/ppesafety](https://www.3m.com/ppesafety) for more information.



Powered Air Purifying Respirator System

Painters Kit	SKU	UPC	Product #	Part #	Qty/Box	Description
3M™ Versaflo™ Powered Air Purifying Respirator Painters Kit TR-800 	7100150922	00076308942489	TR-800-PSK	94248	1/Box	Personalized protection that's easy to use. The TR-800 PAPR is designed to help provide personalized comfort and versatility. Equipped with color-coded, intuitive touch points and multiple rates of airflow to choose from, this respirator can help keep you comfortable and focused on the job. Bright yellow details differentiate the PAPR from non-intrinsically safe 3M models,* while visual and audible alarms alert users when the battery is low or filter is loaded. An all-in-one respiratory protection solution.

*The 3M™ Versaflo™ Powered Air Purifying Respirator TR-800 Motor/Blower, with the 3M™ Battery Pack TR-830 attached, has been tested and classified for intrinsic safety in Hazardous Locations (Exia) by Underwriters Laboratory (UL) for the following: Exia Division 1: IS Class I, II, III; Division 1 (Includes Division 2), Groups C, D, E, F, G; T4; Ex ia I Ma; Class I, Zone 0, AEx ia IIB, T4; Class I, Zone 0, Ex ia IIB, T4; Zone 20, AEx ia IIIC, T135; Zone 20, Ex ia IIIC, T135; -20°C ≤ Ta ≤ 55°C.

Common Replacement Items	SKU	UPC	Product #	Part #	Qty/Box
 3M™ Versaflo™ Respiratory Systems Carry Bag	7100061107	00051141567259	TR-991	56725	1/Box
 3M™ Versaflo™ Easy Clean Backpack TR-927	7100300071	04064035103477	TR-927	10347	1/Box
 3M™ Versaflo™ Peel-Off Visor Cover M-926 (for use with M-925 Visor only)	7000127689	50051131373223	M-926	37322	40/Box
 3M Versaflo Peel-Off Visor Cover M-928 (for use with M-927 Visor only)	7100138631	50051131374527	M-928	37452	40/Bag
 3M™ Versaflo™ Standard Visor M-925	7000127690	00051131373235	M-925	37323	5/Box
 3M™ Versaflo™ Premium Visor M-927	7000052876	00051131373242	M-927	37324	5/Box

⚠ WARNING: RESPIRATORS

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the *User Instructions* provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For correct use, consult supervisor and the products *User Instructions*, or call 3M Technical Service in U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.



Common Replacement Items		SKU	UPC	Product #	Part #	Qty/Box
	Organic Vapor/HEPA Cartridge TR-6510N	7100021253	50051131373612	TR-6510N	37361	5/Box
	3M™ Versaflo™ Filter Cover (for use with TR-6510 cartridge)	7100021252	00051131373815	TR-6500FC	37381	1/Box
	3M™ Versaflo™ Breathing Tube	7000002343	00051131373105	BT-20L	37310	1/Box
	3M™ Versaflo™ Breathing Tube Cover BT-922	7100077588	00051131373112	BT-922	37311	10/Box
	3M™ Versaflo™ Prefilter TR-6600	7100021255	50051131373544	TR-6600	37354	10/Box
	3M™ Versaflo™ Comfort Face Seal M-936	7000127692	00051131373266	M-936	37326	5/Box
	3M™ Versaflo™ Forehead Comfort Pad/ Sweat Pad M-957/L-115	7100043088	00051131370104	M-957/L-115	37010	10/Box

⚠ WARNING: RESPIRATORS

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the *User Instructions* provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For correct use, consult supervisor and the products *User Instructions*, or call 3M Technical Service in U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.



Common Replacement Items	SKU	UPC	Product #	Part #	Qty/Box
 3M™ Versaflo™ Powered Air Purifying Respirator Unit TR-802N	7100150821	00076308942427	TR-802N	94242	1/Box
 3M™ Versaflo™ Battery Attachment Tool TR-838 (for TR-800 PAPR and TR-830 Battery)	7100150921	00076308942441	TR-838	94244	1/Box
 3M™ Versaflo™ Battery TR-830, Intrinsically Safe (for TR-800 PAPR 1)	7100150925	00076308942434	TR-830	94243	1/Box
 3M™ Versaflo™ Single Station Battery Charger Kit (for Versaflo™ TR-600 & TR-800)	7100342017	00068060858214	TR-642N	8582	1/Box
 3M™ Versaflo™ PAPR Cover TR-681 (for TR-600/800 PAPR)	7100260718	50638060432162	TR-681	43126	10/Box

⚠ WARNING: RESPIRATORS

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the *User Instructions* provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For correct use, consult supervisor and the products *User Instructions*, or call 3M Technical Service in U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.



Respirators

Respirators and Filters	SKU	UPC	Product #	Size	Qty/Box
 3M™ Particulate Respirator 8511, N95	7000002056	50051138543438	8511/54343	N/A	80/Box
 3M™ Particulate Welding Respirator 8515/07189(AAD), N95	7000002112	50051131071891	8515/07189	N/A	80/Box
 3M™ Aura™ Particulate Respirator 9211+, N95	7100303148	58887862965589	9211+	N/A	120/Box
 3M™ Ultimate FX Full Face Respirator	7000029940	50051135894182	FF-401/89418	S	4/Box
	70071510807	50051135894212	FF-402/89421	M	
	7100001847	50051135894243	FF-403/89424	L	
 3M™ 6000 Series Full Facepiece Reusable Respirator	7000002029	50051138541458	6700/54145	S	4/Box
	70070709053	50051138541465	6800/54146	M	
	7000002037	50051138541595	6900/54159	L	
 3M™ 5000 Series Half Facepiece Disposable Respirator, Organic Vapor, P95	70070797173	50051138660685	51P71/07191	S	12/Box
	70070797181	50051138660692	52P71/07192	M	
	70070797199	50051138660708	53P71/07193	L	
 3M™ 7500 Series Half Facepiece Reusable Respirator	70071042785	50051131370826	7502/37082	M	10/Box
	70071042793	50051131370833	7503/37083	L	
 3M™ 6000 Series Half Facepiece Reusable Respirator	7010383694	50051131070016	6291/07001	S	20/Box
	7000126163	50051131070023	6291/07002	M	
	7000126164	50051131070030	6391/07003	L	
 3M™ Particulate Filter 2091, P100	70070614410	50051131070009	2091/07000	N/A	100/Box
 3M™ Particulate Filter, 5P71 P95	70070757417	50051131071945	5P71/07194	N/A	100/Box
 3M™ Organic Vapor Cartridge, 6001	70070316776	50051138216745	6001/07046	N/A	60/Box
 3M™ Filter Retainer 501 Retainer	7100211073	5005113876681	76681	N/A	60/Box

Not a complete list. Please choose the right products for each application and exposure assessment. Visit [3M.com/ppesafety](https://www.3m.com/ppesafety) for more information.

⚠ WARNING: RESPIRATORS

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the *User Instructions* provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For correct use, consult supervisor and the products *User Instructions*, or call 3M Technical Service in U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.



Hearing Protection

Earmuffs	SKU	Part #	NRR	Earmuff Style	Electrically Insulated	Size	Earcup Material	Hygiene Kit	Qty/Box
 3M™ PELTOR™ Optime™ 105 Earmuffs	7000009665	H10A	30 dB	Over-the-Head	No	One Size	ABS	HY54	10/Box
	7000009664	H10B	29 dB	Behind-the-Head					
 3M™ PELTOR™ X4 Earmuffs	7000104073	X4A	27 dB	Over-the-Head	Yes	One Size	ABS/ Poly-urethane	HYX4	
Earplugs	SKU	Part #	NRR	Cord	Cord Material	Size	Material	Shape	Qty/Box
 3M™ E-A-R™ Classic Earplugs	7000002300	312-1201	29 dB	Uncorded	—	Regular	PVC	Cylinder	2,000/Box
	7000002301	311-1101		Corded	Vinyl				
 3M™ E-A-Rsoft™ Yellow Neons™ Earplugs	7000002303	312-1250	33 dB	Uncorded	—	Regular	PU	Bullet	
	7000002306	311-1250		Corded	Vinyl				
 3M™ E-A-R™ Push-Ins™ Corded Earplugs	7000127213	318-1000	28 dB	Uncorded	—	Regular	PU	Hemi-sphere	400/Box
	7000052745	318-1001		Corded	Vinyl				
 3M™ E-A-R™ UltraFit™ Corded Earplugs	7000002322	340-4002	25 dB	Corded	Vinyl	Regular	TPE	Tri-Flange	200/Box (Comes with Carry Case)
	7000002320	340-4004							400/Box
 3M™ No-Touch™ Push-to-Fit Earplugs	7000127180	P2000	29 dB	Uncorded	—	Regular	PU	Bell	400/Box
	7000052722	P2001		Corded	Vinyl				

Not a complete list. Please choose the right products for each application and exposure assessment. Visit [3M.com/ppesafety](https://www.3m.com/ppesafety) for more information.

⚠ WARNING: HEARING PROTECTION

These hearing protectors help reduce exposure to hazardous noise and other loud sounds. **Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury.** For correct use, consult supervisor and the products *User Instructions*, or call 3M Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414. If there is any drainage from your ear or you have an ear infection, consult with your physician before wearing ear plugs. Failure to do so may result in hearing loss or injury.

Eye Protection

Safety Glasses and Faceshield		SKU	Product #	Frame Color	Lens Tint	Coating	Qty/Box		
   3M™ SecureFit™ Protective Eyewear - 3M Pressure Diffusion Temple Technology is designed to provide a secure and comfortable fit for an extended period of time - Select models offered with 3M™ Scotchgard Anti-fog Protector - SF400 Series provides padded temples, an adjustable nose bridge, and optional foam gaskets or brow guards - SF300 Series provides an Asian fit option to help accommodate high cheekbone structure and low nose bridge - SF200 Series provides an economical option with no removable parts - Meets requirements of ANSI/ISEA Z87.1-2020 as an Impact Rated Spectacle - Absorbs 99.9% of UVA, UVB, and UVC rays between 200 nm and 380 nm		SF400 - Standard AntiFog	7100112435	SF401AF	Green/Black	Clear	AF/AS	20/Box	
			7100112433	SF402AF		Gray			
			7100180047	SF401XAF-GRN		Clear			
			7100180047	SF402XAF-GRN		Gray			
			7100115326	SF415AF		Clear		20/Box (+1.5 Diopter)	
			7100115325	SF420AF				20/Box (+2.0 Diopter)	
			7100115329	SF425AF				20/Box (+2.5 Diopter)	
		SF400 - Scotchgard	7100150838	SF401SGAF-BLU	Black/Blue	Clear	SGAF/AS	20/Box	
			7100156101	SF402SGAF-BLU		Gray			
			7100156103	SF407SGAF-BLU		I/O			
			7100180049	SF401XSGAF-BLU	Blue/Gray	Clear			
			7100180050	SF402XSGAF-BLU		Gray			
			7100180051	SF407XSGAF-BLU		I/O			
			7100156104	SF401SGAF-BLU-F	Black/Blue	Clear			
			7100156137	SF402SGAF-BLU-F		Gray			
			7100156126	SF407SGAF-BLU-F		I/O			
		SF300 - Asian Fit	7010315373	SF301AF	Clear	Clear	AF/AS	20/Box	
			7010315385	SF302AF		Gray			
			7100202277	SF301SGAF-LBL	Ice Blue	Clear	SGAF/AS		
			7100202278	SF302SGAF-LBL		Gray			
		SF200 - Economy	7100090435	SF201AFP	Clear	Clear	AF/AS	20/Box	
			7100022210	SF202AFP	Gray	Gray			
			7100180044	SF201SGAF-BLU	Blue	Clear	SGAF/AS		
			7100180046	SF204SGAF-BLU		Blue			
		    3M™ SecureFit™ 500 Series Protective Eyewear - New Securefit™ temple design featuring adjustable ratcheting temples to help improve the positioning of the eyewear - Meets the requirements of ANSI/ISEA Z87.1-2020 as an Impact Rated Spectacle - Absorbs 99.9% of UVA, UVB, and UVC rays between 200 nm and 380 nm - Select models offered with 3M™ Scotchgard Anti-fog Protector - Lens shape & temple design combines well with other personal protective equipment (hearing protection, 1/2 face respirators)		7100228736	SF501AF-BLK	Black	Clear	AF/AS	20/Box
				7100228722	SF502AF-BLK		Gray		
				7100228721	SF507AF-BLK		I/O		
				7100238910	SF501SGAF-BLK		Clear	SGAF/AS	
7100239089	SF502SGAF-BLK			Gray					
7100239091	SF507SGAF-BLK			I/O					
7100238909	SF501SGAF-BLK-FM			Clear					
7100239195	SF502SGAF-BLK-FM			Gray					
7100239092	SF507SGAF-BLK-FM			I/O					
7100239204	SF517AF-GRN			Black/Green	IR 1.7 Gray	AF/AS			
7100239086	SF530AF-GRN				IR 3.0 Gray				
7100239205	SF550AF-GRN				IR 5.0 Gray				
3M™ Virtua™ Protective Eyewear   - Meets the requirements of ANSI/ISEA Z87.1-2020 as an Impact Rated Spectacle - Absorbs 99.9% of UVA, UVB, and UVC rays between 200 nm and 380 nm - Bulk package option				7000030053	11818-00000-20	Clear	Clear	AF/AS	20/Box
		7000030054	11819-00000-20	AS					
		7000030052	11817-00000-20		Amber	Amber			
		7000030051	11816-00000-20		Light Blue	Light Blue			
		7000030050	11815-00000-20		Gray	Gray			
		7000030055	11847-00000-20		Mirror	I/O Mirror			
		3M™ Ratchet Headgear H8A, with 3M™ Clear Faceshield 		7000127243	82782-00000	Clear Propionate		5/Box	
7000127244	82783-00000			Clear Polycarbonate					

⚠ WARNING: PROTECTIVE EYEWEAR

These eye and face protection products help provide limited eye and face protection. **Misuse or failure to follow warnings and instructions may result in serious potential injury, including blindness or death.** For correct use, selection, and applications against flying particles, optical radiation and/or splash consult supervisor, and the products *User Instructions* and **WARNINGS** on the package, or call 3M Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.

Coveralls

Coveralls	SKU	UPC	Product #	Size	Color	Material	Particle	Liquid	Qty/Box
3M™ Protective Coverall 4520 Made from lightweight and extremely breathable material and is designed to offer protection against hazardous dusts and limited liquid splashes. 	7000034761	04046719401093	4520	M	White/ Green	SMS	Type 5	Splash Type 6	20/Box
	7000034762	04046719401109	4520	L					
	7000034763	04046719401123	4520	XL					
	7000034764	04046719401147	4520	2XL					
	7000089643	04046719401178	4520	3XL					
	7000089644	04046719401192	4520	4XL					
3M™ Protective Coverall 4535 Provides a superb balance of comfort and protection. The microporous PE laminate at the front of the garment is designed to offer a good barrier to limited liquid splash, while the large SMMMS breathable back panel helps increase wearer comfort. 	7100217011	00638060434277	4535	M	White/ Blue	PE laminate (front) SMS (Back)	Type 5	Splash Type 6	20/Box
	7100217010	08887862357051	4535	L					
	7100216848	08887862357068	4535	XL					
	7100216889	08887862357075	4535	2XL					
	7100216850	08887862357082	4535	3XL					
	7100216888	08887862357099	4535	4XL					

Not a complete list. Please choose the right products for each application and exposure assessment. Visit [3M.com/ppesafety](https://www.3m.com/ppesafety) for more information.


Spill Management

for control and cleanup of petroleum-based fluids.

3M™ Oil and Petroleum Sorbents are ideal for absorbing oil from areas where water may also be present — including outdoor locations like ditches, streams, rivers, lakes, and terminal docks and piers. They are designed to not disintegrate or sink, even when saturated with oil, and are easy to dispose of. Multiple formats allow for control, cleanup and recovery of petroleum-based liquids in and around your shop.

Oil and Petroleum Sorbents		SKU	UPC	Product #	Size	Qty/Box	Description
 3M™ Oil Sorbent Sheets, High Capacity		70070405785	50051138289916	HP156	17 in x 19 in/Sheet, 37-1/2 Gallons/Box	100/Box	Can be quickly spread on and in the path of a thin spill. May be used on a work surface in anticipation of a spill. Ideal for use under docks, in shallow water, rocky shorelines, marshes, and beaches.
		70070408557	00051138291167	HP157	34 in x 38 in/Sheet, 75 Gallons/Box	50/Box	
		70070405793	50051138289923	HP255	17 in x 19 in/Sheet, 66 Gallons/Box	50/Box	
		70070313807	50051138215441	HP256	17 in x 19 in/Sheet, 66 Gallons/Box	100/Box	
 3M™ Oil Sorbent Boom, High Capacity		98071106334	50021200160542	T-270	8 in x 10 ft/Boom, 20 Gallons/Boom, 80 Gallons/Box	4/Box	Repels water and floats. Built in attachment clips allow booms to be linked together. Unique double-cylinder design maximizes absorption and minimizes the escape of traces of oil in flowing water. UV resistant.
		98071108074	00021200160851	T-280	(2) 4 in x 10 ft/Booms, 10 Gallons/Boom, 80 Gallons/Box	4/Box	
 3M™ Oil Sorbent Mini-Boom		70070221372	50051138213553	T8	3 in x 8 ft/Boom, 2 Gallons/Boom, 12 Gallons/Box	6/Box	Use to encircle spills and to contain leaks and are a selective sorbent which will "sorb" hydrocarbon based liquids (oleophilic) and repel aqueous based liquids (hydrophobic).
		70070221380	50051138213560	T12	3 in x 12 ft/Boom, 3 Gallons/Boom, 12 Gallons/Box	4/Box	
		70070221364	50051138213546	T4	3 in x 4 ft/Boom, 1 Gallon/Boom, 12 Gallons/Box	12/Box	

From metal and plastic repair, to sanding, paint finishing and boat clean-up, 3M has the products and repair processes for you. These procedures will help you consistently produce quality, time-proven solutions for any of your marine repair needs.



3M makes marine products that are used around the globe, from salt water to fresh water — from backyards to boatyards and everywhere in between.



3MMarine.com



Automotive Aftermarket Division
3M Center, Building 223-4S-04
St. Paul, MN 55144-1000

Phone 1-877-666-2277
Web 3MMarine.com

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit 3M.com.

3M, 3M Xtract, Accuspray, Cubitron, E-A-R, E-A-Rsoft, Green Corps, Hookit, No-Touch, Optime, PELTOR, Perfect-It, PPS, Production, Push-Ins, Regalite, Roloc, Scotch, Scotchblok, ScotchBlue, Scotch-Brite, SecureFit, Sharpshooter, Stikit, Trizact, UltraFit, Versaflo, Virtua and Yellow Neons are trademarks of 3M Company. All other trademarks are property of their respective owners. © 3M 2026. All rights reserved. 60-4405-0055-5, Rev. 8/2026