



## 3M™ Coarse Antislip Tape (black)

### Technical Data Sheet

TD 805

#### Product description:

The product consists of a large Aluminumoxide particles bonded by a durable polymer to a flexible PVC film.

The reverse side is coated with a pressure sensitive adhesive, covered by a removable protective paper liner. The product provides a durable, high slip resistant surface for extreme conditions.

#### Intended Use:

Primarily for use as a durable, extreme slip resistant surface for dry, wet, oily floors in industrial, agricultural, forestry, building and road construction applications with intensive pedestrian or heavy vehicle traffic.

It is designed to prevent slips and trips in the workplaces like ramps and heavy traffic corridors, fire escapes, ladders, stairs and in kitchens with dirty, wet oily floor areas.

For extreme conditions at agricultural, forestry, road and building vehicles power machines and auto-repair shops.

**Colour:** black

#### Product Advantages:

- Safe, extreme slip resistant surface
- durable
- Easy to install
- good bond to most dry, clean, smooth surfaces

#### Sizes and Packaging

Rolls:		
Black		
25 mm x 20 m	24 rolls/box	
50 mm x 20 m	12 rolls/box	
100 mm x 20 m	6 rolls/box	

#### Labeling:

Each box shall be labeled with product name, size, color and manufacturer's trade name.

#### Product Characteristics

Properties	Typical values
Total thickness	1,48 +/- 0,3mm
Paper liner	0,1 +/- 0,01mm
Adhesion to steel Afera 5001 / ISO 29862:2007	>15,0 N/25mm
Elongation at break Afera 5004 ISO 29864:2008	>25%
Application temperature	10°C to 40°C
Service temperature range	-5°C to 50°C
Resistance to water	good
Slip Resistance Test DIN 51130:10-2010	R13 / V6

#### Installation

Ensure that the surface is very clean and dry, having no dust, water or oil on it.

Please use rubber wheel and overroll by applying pressure on the 3M Antislip Tape.

Ensure to apply the Antislip Tape before 24 hrs to use.

#### Storage conditions:

At RT / 65% RH



**Important Notice to Purchaser / Converter / Wearer:**

All statements, technical information and recommendations herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. We shall not be liable and no warranty shall apply for products not applied according to our published information folder.

Before using/converting, the user/converter must determine the suitability of the product for its intended use/converting, and the user/converter assumes all risk and liability whatsoever in connection therewith. All questions of warranty and liability relating to this product are governed by the terms of the sale subject where applicable to the prevailing law. No statement or recommendation not contained herein shall have any force or effect unless in an agreement signed by officers of us.

**3M Deutschland GmbH**  
**Building & Commercial Services**  
D-41453 Neuss, Germany

