




Wiper Blade checklist

水撥對照表



車廠品牌	車款	型號 MODEL CODE	年份	通用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch) 尺寸(吋機)	英寸(Inch) 尺寸(乘客)
ALFA ROMEO	145	930	04.97 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
ALFA ROMEO	146	930	04.97 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
ALFA ROMEO	147	937	04.05 - 12.10	3M™ 至尊鍍膜水撥	F	A+1	22	16
ALFA ROMEO	147	937	11.00 - 06.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
ALFA ROMEO	155	167	02.92 - 04.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
ALFA ROMEO	164	164	06.87 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
ALFA ROMEO	166	936	07.98 - 10.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
ALFA ROMEO	156 Berlina	932	10.97 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
ALFA ROMEO	156 Sport Wagon	932	06.00 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
ALFA ROMEO	159 Berlina	939	06.05 - 12.11	3M™ 至尊鍍膜水撥	F	A+1	22	18
ALFA ROMEO	159 Sport Wagon	939	03.06 - 12.11	3M™ 至尊鍍膜水撥	F	A+1	22	18
ALFA ROMEO	Brera	939	01.06 - 12.10	3M™ 至尊鍍膜水撥	F	A+1	22	18
ALFA ROMEO	Giulia	952	03.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	18
ALFA ROMEO	Giulietta	940	04.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	22	18
ALFA ROMEO	GT	937	04.05 - 12.10	3M™ 至尊鍍膜水撥	F	A+1	22	16
ALFA ROMEO	GT	937	10.03 - 06.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
ALFA ROMEO	Mito	955	05.08 - 12.18	3M™ 至尊鍍膜水撥	D	A+3	26	14
ALFA ROMEO	Spider	939	03.06 - 12.10	3M™ 至尊鍍膜水撥	F	A+1	22	18
ALFA ROMEO	Stelvio	949	12.16 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
ALFA ROMEO	Tonale	965	03.22 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	80	8C2,B4	09.91 - 05.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	80 Avant	8C5,B4	03.92 - 07.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A1	8X1	05.10 - 10.18	3M™ 至尊鍍膜水撥	B	A+6	24	14
AUDI	A1 Allstreet	GBH	07.19 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A1 City Carver	GBH	07.19 - 06.22	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A1 Sportback	GBA	07.18 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A1 Sportback	8XA	09.11 - 10.18	3M™ 至尊鍍膜水撥	B	A+6	24	14
AUDI	A2	8Z0	07.01 - 08.05	3M™ 至尊鍍膜水撥	F	A+1	30	
AUDI	A2	8Z0	09.99 - 06.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	
AUDI	A3	8P1	12.04 - 03.13	3M™ 至尊鍍膜水撥	D	A+3	24	19
AUDI	A3	8V1, 8VK	04.12 - 10.20	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A3	8P1	05.03 - 03.13	3M™ 至尊鍍膜水撥	F	A+1	24	19
AUDI	A3	8P1	05.03 - 11.04	3M™ 至尊鍍膜水撥	F	A+1	24	19
AUDI	A3	8L1	09.96 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
AUDI	A3 Allstreet	8YH	11.19 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	19
AUDI	A3 Cabriolet	8P7	04.08 - 05.13	3M™ 至尊鍍膜水撥	D	A+3	24	18
AUDI	A3 Cabriolet	8V7	10.13 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A3 Limousine	8Y5	03.20 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A3 Limousine	8V5	05.13 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
AUDI	A3 Sportback	8YA	11.19 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	19
AUDI	A3 Sportback	8PA	12.04 - 03.13	3M™ 至尊鍍膜水撥	D	A+3	24	19
AUDI	A3 Sportback	8VA, 8VF	09.12 - 10.20	3M™ 至尊鍍膜水撥	B	A+6	26	18
AUDI	A3 Sportback	8PA	09.04 - 03.13	3M™ 至尊鍍膜水撥	F	A+1	24	19
AUDI	A3 Sportback	8PA	09.04 - 11.04	3M™ 至尊鍍膜水撥	F	A+1	24	19
AUDI	A4	8K2,B8	11.07 - 12.15	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4	8W2,B9	05.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4	8D2,B5	11.94 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A4	8D2,B5	08.98 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A4	8E2,B6	10.00 - 03.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A4 Allroad	8KH	04.09 - 04.16	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4 Allroad	8WH	01.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4 Avant	8K5,B8	11.07 - 12.15	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4 Avant	8W5,B9	05.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A4 Avant	8D5,B5	11.94 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A4 Avant	8D5,B5	08.98 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
AUDI	A5 Cabriolet	8F7	03.09 - 01.17	3M™ 至尊鍍膜水撥	B	A+6	24	21
AUDI	A5 Coupé	8T3	11.07 - 01.17	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A5 Coupé	8T3	06.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A5 Coupé	F53	06.07 - 10.07	3M™ 至尊鍍膜水撥	B+C	A+2	24	20
AUDI	A5 Sportback	8TA	05.09 - 01.17	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A5 Sportback	F5A	06.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A6	4A2,C8	04.18 →	3M™ 至尊鍍膜水撥	J	A+6	24	20
AUDI	A6	4A2,C8	04.18 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
AUDI	A6	4G2,C7	11.10 - 09.18	3M™ 至尊鍍膜水撥	B	A+6	26	21
AUDI	A6	4B2,C5	04.97 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20

車廠品牌	車款	型號 MODEL CODE	年份	適用水喉款式	水喉臂及接頭款式	3M™ 水喉接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(英寸)
AUDI	A6	4A2,C4	06.94 - 10.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	A6 Avant	4A5,C8	02.18 →	3M™ 至尊鍍膜水喉	J	A+6	24	20
AUDI	A6 Avant	4A5,C8	02.18 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	A6 Avant	4G5,C7	05.11 →	3M™ 至尊鍍膜水喉	B	A+6	26	21
AUDI	A6 Avant	4B5,C5	04.97 - 05.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	A6 Avant	4A5,C4	06.94 - 10.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	A6 Avant Allroad	4A4,C8	11.18 →	3M™ 至尊鍍膜水喉	J	A+6	24	20
AUDI	A6 Avant Allroad	4GH,C7	01.12 - 09.18	3M™ 至尊鍍膜水喉	B	A+6	26	21
AUDI	A6 Avant Allroad	4BH,C5	05.00 - 12.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	A7 Sportback	4KA,C8	10.17 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	A7 Sportback	4GA	07.10 - 05.18	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	A8	4N2,4N8	08.17 →	3M™ 至尊鍍膜水喉	B	A+6	26	20
AUDI	A8	4HD,4	11.09 →	3M™ 至尊鍍膜水喉	B	A+6	28	20
AUDI	A8	4D2,D2	06.94 - 09.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	Cabriolet	8G7,B4	06.91 - 08.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	Coupé	89,B3	11.88 - 12.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	E-TRON	GEN	09.18 →	3M™ 至尊鍍膜水喉	B	A+6	26	20
AUDI	E-TRON GT Saloon	F83	11.20 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	E-TRON Sportback	GEA	09.19 →	3M™ 至尊鍍膜水喉	J	A+6	24	20
AUDI	E-TRON Sportback	GEA	09.19 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q2	GAB	06.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	19
AUDI	Q3	F3B	07.18 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q3	8UB, 8UG	06.11 - 03.20	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	Q3 Sportback	F3N	06.19 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q4 Sportback	F4N	06.21 →	3M™ 至尊鍍膜水喉	B+C	A+2	28	18
AUDI	Q4 SUV	F4B	07.20 →	3M™ 至尊鍍膜水喉	B+C	A+2	28	18
AUDI	Q5	8RB	11.08 - 12.17	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q5	FYB	05.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q5 Sportback	FYT	11.20 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	Q7	4LB	03.06 - 01.16	3M™ 至尊鍍膜水喉	D	A+3	26	24
AUDI	Q7	4MB, 4MG	01.15 →	3M™ 至尊鍍膜水喉	B	A+6	28	20
AUDI	Q8	4MN, 4MT	02.18 →	3M™ 至尊鍍膜水喉	B	A+6	26	20
AUDI	RS Q3	8UB	10.13 →	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	RS3 Limousine	8V5	02.17 →	3M™ 至尊鍍膜水喉	B	A+6	26	19
AUDI	RS3 Sportback	8PA	01.11 - 12.12	3M™ 至尊鍍膜水喉	D	A+3	24	19
AUDI	RS3 Sportback	8VA	02.15 →	3M™ 至尊鍍膜水喉	B	A+6	26	18
AUDI	RS4 Avant	8W5,B9	09.17 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	RS4 Avant	8K5,B8	05.12 - 08.15	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	RS4 Avant	8D5,B5	05.00 - 09.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
AUDI	RS5 Cabriolet	8F7	11.12 - 08.15	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	RS5 Coupé	F53	03.17 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	RS5 Coupé	8T3	03.10 - 08.15	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	RS5 Sportback	F5A	06.18 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	RS6 [4B4]	8B4	07.02 - 04.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	RS6 Avant	4GH,C7	01.13 →	3M™ 至尊鍍膜水喉	B	A+6	26	21
AUDI	RS6 Avant	4B6	05.02 - 09.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	RS7 Sportback	4GA	05.13 →	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	S1	8X	01.14 →	3M™ 至尊鍍膜水喉	B	A+6	24	14
AUDI	S1 Sportback	8X	01.14 →	3M™ 至尊鍍膜水喉	B	A+6	24	14
AUDI	S3	8P1	11.06 - 03.13	3M™ 至尊鍍膜水喉	D	A+3	24	19
AUDI	S3	8V1	11.12 →	3M™ 至尊鍍膜水喉	B	A+6	26	18
AUDI	S3	8L1	08.98 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
AUDI	S3 Cabriolet	8V7	05.14 →	3M™ 至尊鍍膜水喉	B	A+6	26	18
AUDI	S3 Limousine	8V5	10.13 →	3M™ 至尊鍍膜水喉	B	A+6	26	18
AUDI	S3 Sportback	8PA	07.08 - 03.13	3M™ 至尊鍍膜水喉	D	A+3	24	19
AUDI	S3 Sportback	8VA	05.13 →	3M™ 至尊鍍膜水喉	B	A+6	26	18
AUDI	S4	8K2,B8	03.09 - 12.15	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S4	8D2,B5	10.97 - 09.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
AUDI	S4 Avant	8K5,B8	03.09 - 12.15	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S4 Avant	8W5,B9	05.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S4 Avant	8D5,B5	10.97 - 09.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
AUDI	S5 Cabriolet	8F7	05.09 →	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	S5 Coupé	8T3	11.07 - 01.17	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S5 Coupé	F53	07.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S5 Sportback	8TA	01.10 - 01.17	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S5 Sportback	F5A	07.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	S6	4G2,C7	04.12 →	3M™ 至尊鍍膜水喉	B	A+6	26	21
AUDI	S6	4A2,C4	06.94 - 10.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	S6	4B,C5	09.99 - 05.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	S6 Avant	4GH,C7	04.12 →	3M™ 至尊鍍膜水喉	B	A+6	26	21
AUDI	S6 Avant	4A5,C4	06.94 - 10.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	S6 Avant	4B,C5	09.99 - 01.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	S7 Sportback	4GA	04.12 →	3M™ 至尊鍍膜水喉	B	A+6	24	21
AUDI	S8	4HD,4	04.12 →	3M™ 至尊鍍膜水喉	B	A+6	28	20
AUDI	S8	4D2	09.96 - 01.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
AUDI	SQ5	8RB	12.12 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	SQ5	FYB	11.16 →	3M™ 至尊鍍膜水喉	B	A+6	24	20
AUDI	SQ7	4MB	04.16 →	3M™ 至尊鍍膜水喉	B	A+6	28	20
AUDI	TT Coupé	8J3	07.06 - 08.15	3M™ 至尊鍍膜水喉	D	A+3	22	21
AUDI	TT Coupé	FV3	07.14 →	3M™ 至尊鍍膜水喉	B	A+6	24	21

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
AUDI	TT Coupé	8N3	05.03 - 06.06	3M™ 至尊鍍膜水撥	F	A+1	21	21
AUDI	TT Coupé	8N3	07.98 - 04.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
AUDI	TT Roadster	8J9	02.07 - 06.14	3M™ 至尊鍍膜水撥	D	A+3	22	21
AUDI	TT Roadster	FV3	11.14 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
AUDI	TT Roadster	8N9	05.03 - 06.06	3M™ 至尊鍍膜水撥	F	A+1	21	21
AUDI	TT Roadster	8N9	03.99 - 04.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
AUDI	TT RS Coupé	8J3	07.09 - 06.14	3M™ 至尊鍍膜水撥	D	A+3	22	21
AUDI	TT RS Coupé	FV3	05.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
AUDI	TT RS Roadster	8J9	07.09 - 06.14	3M™ 至尊鍍膜水撥	D	A+3	22	21
AUDI	TT RS Roadster	FV9	05.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
AUDI	TTS Coupé	8J3	05.08 - 08.15	3M™ 至尊鍍膜水撥	D	A+3	22	21
AUDI	TTS Coupé	FV3	11.14 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
AUDI	TTS Roadster	8J9	05.08 - 06.14	3M™ 至尊鍍膜水撥	D	A+3	22	21
AUDI	TTS Roadster	FV	02.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
BMW	i3	I01	11.13 →	3M™ 至尊鍍膜水撥	F	A+1	28	21
BMW	i8	I12	06.14 - 06.20	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	24
BMW	iX3	G08	09.20 →	3M™ 至尊鍍膜水撥	G	B+8	26	20
BMW	M3	F80	06.14 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	M4	F82	06.14 →	3M™ 至尊鍍膜水撥	D	A+3	24	18
BMW	Serie 1	F40	07.19 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	16
BMW	Serie 1	F20	07.11 - 06.19	3M™ 至尊鍍膜水撥	D	A+3	22	18
BMW	Serie 1	F21	12.11 →	3M™ 至尊鍍膜水撥	D	A+3	22	18
BMW	Serie 1	E81/E87	09.04 - 12.11	3M™ 至尊鍍膜水撥	D	A+3	20	20
BMW	Serie 1 Cabrio	E88	03.08 - 10.13	3M™ 至尊鍍膜水撥	D	A+3	20	20
BMW	Serie 1 Coupé	E82	10.07 - 10.13	3M™ 至尊鍍膜水撥	D	A+3	20	20
BMW	Serie 2 Active Tourer	U06	11.21 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
BMW	Serie 2 Active Tourer	F45	11.13 - 10.21	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BMW	Serie 2 Cabrio	F23	09.14 →	3M™ 至尊鍍膜水撥	D	A+3	22	18
BMW	Serie 2 Coupé	F22	09.13 →	3M™ 至尊鍍膜水撥	D	A+3	22	18
BMW	Serie 2 Gran Tourer	F46	07.14 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BMW	Serie 3	E90	09.09 - 08.13	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3	F30, F80	11.11 - 10.18	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3	G20, G80, G28	11.18 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3	E90	03.05 - 08.09	3M™ 至尊鍍膜水撥	F	A+1	24	19
BMW	Serie 3	E46	04.98 - 04.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
BMW	Serie 3	E36	09.90 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Serie 3 Cabrio	E93	09.09 - 10.13	3M™ 至尊鍍膜水撥	D	A+3	24	16
BMW	Serie 3 Cabrio	E93	09.06 - 08.09	3M™ 至尊鍍膜水撥	F	A+1	24	16
BMW	Serie 3 Cabrio	E46	03.00 - 08.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
BMW	Serie 3 Cabrio	E36	03.93 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Serie 3 Compact	E46	06.01 - 12.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
BMW	Serie 3 Compact	E36	03.94 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Serie 3 Coupé	E92	09.09 - 08.13	3M™ 至尊鍍膜水撥	D	A+3	24	16
BMW	Serie 3 Coupé	E92	09.06 - 08.09	3M™ 至尊鍍膜水撥	F	A+1	24	16
BMW	Serie 3 Coupé	E46	04.98 - 05.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
BMW	Serie 3 Coupé	E36	03.91 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Serie 3 GT	F34	06.13 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3 Touring	E91	09.09 - 05.13	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3 Touring	F31	09.12 - 06.19	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3 Touring	G21, G81	07.19 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 3 Touring	E91	09.05 - 08.09	3M™ 至尊鍍膜水撥	F	A+1	24	19
BMW	Serie 3 Touring	E46	10.98 - 09.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
BMW	Serie 3 Touring	E36	03.95 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Serie 4 Cabrio	F33, F83	10.13 - 08.20	3M™ 至尊鍍膜水撥	D	A+3	24	18
BMW	Serie 4 Cabrio	G23, G83	11.20 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 4 Coupé	F32	09.13 →	3M™ 至尊鍍膜水撥	D	A+3	24	18
BMW	Serie 4 Gran Coupé	F36	03.14 - 05.21	3M™ 至尊鍍膜水撥	D	A+3	24	18
BMW	Serie 4 Gran Coupé	G26	07.21 →	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	Serie 5	E60	07.03 - 02.10	3M™ 至尊鍍膜水撥	D	A+3	24	22
BMW	Serie 5	G30	09.16 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BMW	Serie 5	F10	03.10 - 10.16	3M™ 至尊鍍膜水撥	F	A+1	26	18
BMW	Serie 5	E34	01.88 - 12.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
BMW	Serie 5	G60/G61/G68	07.23 →	3M™ 至尊鍍膜水撥	D	A+3	26	19
BMW	Serie 5 GT	F07	09.09 →	3M™ 至尊鍍膜水撥	F	A+1	26	19
BMW	Serie 5 Touring	E61	05.04 - 08.10	3M™ 至尊鍍膜水撥	D	A+3	24	22
BMW	Serie 5 Touring	G31	06.17 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BMW	Serie 5 Touring	F11	11.09 - 02.17	3M™ 至尊鍍膜水撥	F	A+1	26	18
BMW	Serie 5 Touring	E34	11.91 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
BMW	Serie 6	E63	01.04 - 07.10	3M™ 至尊鍍膜水撥	D	A+3	24	22
BMW	Serie 6	F13	07.11 - 10.17	3M™ 至尊鍍膜水撥	F	A+1	26	16
BMW	Serie 6 Cabrio	E64	04.04 - 07.10	3M™ 至尊鍍膜水撥	D	A+3	24	22
BMW	Serie 6 Cabrio	F12	12.10 - 06.18	3M™ 至尊鍍膜水撥	F	A+1	26	16
BMW	Serie 6 GC	F06	03.12 - 10.18	3M™ 至尊鍍膜水撥	F	A+1	26	16
BMW	Serie 6 Gran Turismo	G32	10.17 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	18
BMW	Serie 7	G70	07.22 →	3M™ 至尊鍍膜水撥	D	A+3	26	19
BMW	Serie 7	G11, G12	09.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BMW	Serie 7	F01, F02, F04	02.08 - 12.15	3M™ 至尊鍍膜水撥	F	A+1	26	19
BMW	Serie 7	E38	06.94 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
BMW	X1	E84	10.09 - 06.15	3M™ 至尊鍍膜水撥	D	A+3	24	19
BMW	X1	F48	11.14 →	3M™ 至尊鍍膜水撥	B	A+6	26	16

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
BMW	X1	U11	07.22 →	3M™ 至尊鍍膜水撥	B	A+6	26	16
BMW	X2	F39	11.17 →	3M™ 至尊鍍膜水撥	H	請與經銷商聯絡	24	20
BMW	X2	U10	11.23 →	3M™ 至尊鍍膜水撥	B	A+6	24	19
BMW	X3	G01, F97	07.17 →	3M™ 至尊鍍膜水撥	G	B+8	26	20
BMW	X3	F25	10.10 - 08.17	3M™ 至尊鍍膜水撥	F	A+1	26	20
BMW	X3	E83	01.04 - 08.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
BMW	X4	G02, F98	04.18 →	3M™ 至尊鍍膜水撥	G	B+8	26	20
BMW	X4	F26	05.13 - 03.18	3M™ 至尊鍍膜水撥	F	A+1	26	20
BMW	X5	E70	10.11 - 06.13	3M™ 至尊鍍膜水撥	B+C	A+2	24	20
BMW	X5	G05, F95	08.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
BMW	X5	E70	11.06 - 09.11	3M™ 至尊鍍膜水撥	F	A+1	24	20
BMW	X5	E70	11.06 - 06.13	3M™ 至尊鍍膜水撥	F	A+1	24	20
BMW	X5	F15, F85	08.13 - 07.18	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
BMW	X5	E53	03.99 - 10.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
BMW	X6	E71, E72	05.08 - 09.11	3M™ 至尊鍍膜水撥	B+C	A+2	24	20
BMW	X6	G06, F96	08.19 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
BMW	X6	E71, E72	06.07 - 07.14	3M™ 至尊鍍膜水撥	F	A+1	24	20
BMW	X6	F16, F86	11.14 - 07.19	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
BMW	X7	G07	03.19 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
BMW	XM	G09	12.22 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	20
BMW	Z3	E36/7	03.95 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Z3 Coupé	E36/8	09.97 - 06.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Z4	G29	11.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	22	21
BMW	Z4	E85	10.02 - 07.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Z4	E89	04.09 - 08.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BMW	Z4 Coupé	E86	03.06 - 07.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
BYD	ATTO 3		02.22 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
BYD	Dolphin		05.23 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
BYD	Han		04.22 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
BYD	Seal		07.22 →	3M™ 至尊鍍膜水撥	C	A+2	24	18
BYD	Sealion 7			3M™ 至尊鍍膜水撥	C	A+2	26	18
BYD	Tang II		08.20 →	3M™ 至尊鍍膜水撥	C	A+2	26	18
DAIHATSU	Charade	NSP90	3.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
DAIHATSU	Charade	G2	06.94 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	16
DAIHATSU	Charade Hatchback	G2	01.93 - 04.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	16
DAIHATSU	Cuore	L7	10.98 - 03.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	14
DAIHATSU	Cuore	L5	08.94 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
DAIHATSU	Gran Move	G3	11.96 - 07.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
DAIHATSU	Hijet		12.92 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
DAIHATSU	Materia		09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
DAIHATSU	Move		08.95 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	14
DAIHATSU	Rocky		03.93 - 03.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
DAIHATSU	Sirion I	M1	04.98 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	16
DAIHATSU	Sirion II	M3	10.04 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
DAIHATSU	Terios	J1	03.97 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
DAIHATSU	Terios	J2	01.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
DAIHATSU	Travis	L6	08.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
DAIHATSU	YRV	M2	08.00 - 07.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
Denza	D9		Z3-	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	19
FIAT	126		09.87 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	14	14
FIAT	500	312.	07.07 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FIAT	124 Spider	348	03.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	19
FIAT	500 EV	CFF	03.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
FIAT	500C	312.	07.09 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FIAT	500e	332	10.2.0 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FIAT	500L	199.,CFA	09.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	14
FIAT	500X	334	11.14 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	14
FIAT	Albea	172.	01.02 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Barchetta	183.	01.95 - 02.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FIAT	Brava	182.	10.95 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FIAT	Bravo	198	03.07 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
FIAT	Bravo	182.	10.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FIAT	Cinquecento	170.	07.91 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FIAT	Coupé	175.	02.94 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
FIAT	Croma	194.	06.05 - 12.10	3M™ 至尊鍍膜水撥	F	A+1	24	16
FIAT	Croma	154.	07.90 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
FIAT	Doblo	263.	02.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
FIAT	Doblo	223.	07.00 - 08.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Doblo Cargo	263.	02.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
FIAT	Doblo Cargo	223.	07.00 - 08.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Doblo MPV	510, 511	06.22 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
FIAT	Ducato	250,251,290	06.06 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	22
FIAT	Ducato	230,231,232,234	03.94 - 03.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FIAT	Ducato	243,244,245,247	04.02 - 12.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FIAT	Egea		11.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
FIAT	Florino	225.	12.07 →	3M™ 至尊鍍膜水撥	E	A+4	26	19
FIAT	Florino	255.	01.88 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	19
FIAT	Freemont	JC	06.11 - 12.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
FIAT	Fullback	JC	05.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Grande Punto	199.	10.05 - 12.11	3M™ 至尊鍍膜水撥	D	A+3	26	14

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
FIAT	Idea	350	04.08 - 12.12	3M™ 至尊鍍膜水撥	B+C	A+2	22	14
FIAT	Idea	350	01.06 - 03.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
FIAT	Idea	350	01.04 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Linea	323	03.07 →	3M™ 至尊鍍膜水撥	D	A+3	26	14
FIAT	Marea	185..	10.96 - 12.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
FIAT	Marengo	285..	01.97 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
FIAT	Marengo	259..	02.90 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FIAT	Multipla	186..	01.06 - 12.10	3M™ 至尊鍍膜水撥	D	A+3	24	22
FIAT	Multipla	186..	01.99 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
FIAT	Palo	178..	03.98 - 12.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Palo Weekend	178..	09.97 - 12.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Panda	312..	02.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FIAT	Panda	169..	10.03 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Panda	141..	01.93 - 09.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	
FIAT	Punto	199..	01.12 →	3M™ 至尊鍍膜水撥	D	A+3	26	14
FIAT	Punto	176..	08.93 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Punto	188..	07.99 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Punto Cabrio	176..	04.94 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Punto Evo	199..	10.09 - 12.12	3M™ 至尊鍍膜水撥	D	A+3	26	14
FIAT	Punto Grande	199..	10.05 - 12.11	3M™ 至尊鍍膜水撥	D	A+3	26	14
FIAT	Punto GT	176..	08.93 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Punto VAN	276..	05.97 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FIAT	Punto VAN	288..	05.99 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Qubo	300..	09.08 →	3M™ 至尊鍍膜水撥	E	A+4	26	19
FIAT	Scudo	222..	10.95 - 01.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
FIAT	Scudo	272..	01.07 - 04.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
FIAT	Sedici	189..	05.06 - 12.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
FIAT	Seicento	187..	03.98 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FIAT	Siena	178..	04.97 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Stilo	192..	07.05 - 12.07	3M™ 至尊鍍膜水撥	D	A+3	22	19
FIAT	Stilo	192..	10.01 - 06.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
FIAT	Stilo Multi Wagon	192..	07.05 - 12.07	3M™ 至尊鍍膜水撥	D	A+3	22	19
FIAT	Stilo Multi Wagon	192..	10.02 - 06.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
FIAT	Strada	278	03.99 - 12.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
FIAT	Talento '16	296	06.16 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
FIAT	Tempra	159	02.90 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FIAT	Tempra SW	159	02.90 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FIAT	Tipo	356	11.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
FIAT	Tipo Hatchback	357	11.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
FIAT	Tipo Station Wagon	358	06.16 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
FIAT	Ulysse	121..	09.94 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
FIAT	Ulysse	179..	10.02 - 10.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	26
FIAT	Ulysse	179..	11.05 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	26
FIAT	Uno	146..	09.87 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	
FIAT	Uno	158..	01.96 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	
FORD	B-MAX		08.12 →	3M™ 至尊鍍膜水撥	D	A+3	30	26
FORD	C-MAX I	7	03.07 - 07.10	3M™ 至尊鍍膜水撥	F	A+1	26	19
FORD	C-MAX II	11	08.10 - 03.15	3M™ 至尊鍍膜水撥	D	A+3	30	24
FORD	C-MAX II	15	04.15 →	3M™ 至尊鍍膜水撥	D	A+3	30	24
FORD	Cougar		08.98 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Econovan		08.85 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
FORD	Ecosport	14	10.16 - 10.17	3M™ 至尊鍍膜水撥	B+C	A+2	22	16
FORD	Ecosport	14	11.17 →	3M™ 至尊鍍膜水撥	B+C	A+2	22	16
FORD	Edge 16		01.16 →	3M™ 至尊鍍膜水撥	D	A+3	28	28
FORD	Escort VII	95	01.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Escort VII Cabrio	95	01.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Escort VII Express	95	01.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Escort VII Turnier	95	01.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Explorer	EX	09.10 →	3M™ 至尊鍍膜水撥	D	A+3	26	22
FORD	Explorer	EX	01.91 - 08.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
FORD	Festiva		01.93 - 10.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
FORD	Fiesta III	89	03.89 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Fiesta III Courier	89	09.91 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Fiesta IV/V	96	10.95 - 12.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Fiesta IV/V Courier	96	10.95 - 12.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Fiesta VI	2	11.01 - 09.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FORD	Fiesta VII	8	07.08 - 11.12	3M™ 至尊鍍膜水撥	B+C	A+2	26	14
FORD	Fiesta VII	13	11.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
FORD	Fiesta VIII	17	05.17 →	3M™ 至尊鍍膜水撥	B+C	A+2	28	14
FORD	Figo		02.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FORD	Five Hundred		09.05 - 08.07	3M™ 至尊鍍膜水撥	F	A+1	24	20
FORD	Focus C-MAX	4	06.03 - 03.07	3M™ 至尊鍍膜水撥	F	A+1	26	19
FORD	Focus I	99	08.98 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
FORD	Focus I Sedan	99	08.98 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
FORD	Focus I Turnier	99	11.98 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
FORD	Focus II	4	07.04 - 01.06	3M™ 至尊鍍膜水撥	F	A+1	26	16
FORD	Focus II	04,08	02.06 - 12.11	3M™ 至尊鍍膜水撥	F	A+1	26	16
FORD	Focus II Cabriolet	6	07.06 - 07.10	3M™ 至尊鍍膜水撥	F	A+1	26	16
FORD	Focus II Sedan	4	07.04 - 01.06	3M™ 至尊鍍膜水撥	F	A+1	26	16
FORD	Focus II Turnier	04,08	07.04 - 10.08	3M™ 至尊鍍膜水撥	F	A+1	26	16

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
FORD	Focus II Turnier	08	11.08 - 12.11	3M™ 至尊鍍膜水撥	F	A+1	26	16
FORD	Focus III	11,15	07.10 - 02.20	3M™ 至尊鍍膜水撥	B+C	A+2	28	28
FORD	Focus III Sedan	11,15	07.10 - 02.20	3M™ 至尊鍍膜水撥	B+C	A+2	28	28
FORD	Focus III Turnier	11,15	07.10 - 02.20	3M™ 至尊鍍膜水撥	B+C	A+2	28	28
FORD	Focus IV	18	05.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
FORD	Focus IV Turnier	18	05.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
FORD	Fusion	2	10.02 - 06.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
FORD	Galaxy	15	05.15 - 06.18	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	Galaxy	15	07.18 →	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	Galaxy	6	03.06 - 09.08	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
FORD	Galaxy	6	10.08 - 06.14	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
FORD	Galaxy	0	04.01 - 08.06	3M™ 至尊鍍膜水撥	F	A+1	28	28
FORD	Galaxy	95	02.95 - 03.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
FORD	Galaxy	00	04.00 - 04.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
FORD	Grand C-MAX	15	04.15 →	3M™ 至尊鍍膜水撥	D	A+3	30	24
FORD	Grand C-MAX	11	08.10 - 03.15	3M™ 至尊鍍膜水撥	D	A+3	30	24
FORD	Ka I	97	09.96 - 09.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	16
FORD	Ka II	8	11.10 - 05.16	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FORD	Ka II	8	09.08 - 10.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
FORD	Ka+		07.16 →	3M™ 至尊鍍膜水撥	B	A+6	22	16
FORD	Kuga I	CBV	02.08 - 11.12	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
FORD	Kuga II	DM2	11.12 →	3M™ 至尊鍍膜水撥	D	A+3	28	28
FORD	Kuga III	DFK	07.19 →	3M™ 至尊鍍膜水撥	D	A+3	24	20
FORD	Maverick	1EZ,1N2	10.00 - 01.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Maverick	94,96	06.93 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo I	93	01.93 - 07.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo I Sedan	93	01.93 - 07.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo I Turnier	93	04.93 - 07.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo II	97	08.96 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo II Sedan	97	08.96 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo II Turnier	97	08.96 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Mondeo III	1	10.00 - 03.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Mondeo III Sedan	1	10.00 - 03.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Mondeo III Turnier	1	10.00 - 03.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Mondeo IV	7	02.07 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
FORD	Mondeo IV Sedan	7	02.07 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
FORD	Mondeo IV Turnier	7	02.07 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
FORD	Mondeo V	15	09.14 →	3M™ 至尊鍍膜水撥	D	A+3	26	26
FORD	Mondeo V Turnier	15	09.14 →	3M™ 至尊鍍膜水撥	D	A+3	26	26
FORD	Mustang		03.09 →	3M™ 至尊鍍膜水撥	D	A+3	22	20
FORD	Mustang		09.04 - 02.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Probe		09.88 - 08.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Puma		09.19 →	3M™ 至尊鍍膜水撥	B+C	A+2	28	14
FORD	Puma		06.97 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Ranger	TKE	09.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
FORD	Ranger	TKE	09.11 - 08.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
FORD	Ranger		06.94 - 06.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
FORD	Scorpio II	95	01.95 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	Scorpio II Turnier	95	01.95 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
FORD	S-MAX	15	05.15 - 06.18	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	S-MAX	[15]	07.18 →	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	S-MAX	6	03.06 - 01.09	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
FORD	S-MAX	6	02.09 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
FORD	Streetka		12.02 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
FORD	Tourneo Connect	13	09.13 →	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	Tourneo Connect	2	05.02 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Tourneo Courier		04.14 →	3M™ 至尊鍍膜水撥	D	A+3	28	14
FORD	Tourneo Custom	13	09.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	30	28
FORD	Transit	14	01.14 →	3M™ 至尊鍍膜水撥	B+C	A+2	30	20
FORD	Transit	95	08.94 - 08.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Transit	00	01.00 - 07.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
FORD	Transit	06,12	04.06 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
FORD	Transit Connect	13	09.13 →	3M™ 至尊鍍膜水撥	D	A+3	30	30
FORD	Transit Connect	2	05.02 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Transit Courier		04.14 →	3M™ 至尊鍍膜水撥	D	A+3	28	14
FORD	Transit Custom	13	09.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	30	28
FORD	Transit Tourneo	95	08.94 - 08.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
FORD	Transit Tourneo	00	08.00 - 07.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
FORD	Transit Tourneo	06,12	04.06 - 09.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
GAC	Aion V			3M™ 至尊鍍膜水撥	B	A+6	26	16
GAC	Aion Y			3M™ 至尊鍍膜水撥	B	A+6	26	16
GAC	E9		23-25	3M™ 至尊鍍膜水撥	B	A+6	28	16
HONDA	Accord	CL/CN/CM	02.03 - 06.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	Accord	CU/CW	07.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
HONDA	Accord Aerodeck	CB/CC/CD/CE	09.93 - 06.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
HONDA	Accord Coupé	CG	12.97 - 12.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
HONDA	Accord Coupé	CB/CC/CD/CE	01.92 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
HONDA	Accord Hatchback	CG/CH/CL	10.98 - 11.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
HONDA	Accord Hatchback	CG/CH/CL	12.99 - 02.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
HONDA	Accord Sedan	CG/CH/CL	10.98 - 02.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
HONDA	Accord Sedan	CA/CB/CD	01.90 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
HONDA	Accord Sedan	CC/CE/CF	03.93 - 10.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
HONDA	Accord Tourer	CL/CN/CM	02.03 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	Accord Tourer	CU/CW	09.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
HONDA	Civic Aerodeck	MB/MC	03.98 - 02.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Coupé	EK	05.01 - 12.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
HONDA	Civic CRX	EG/EH	03.92 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Fastback	MA	09.94 - 01.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Fastback	MB/MC	09.94 - 02.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Hatchback	FL	01.21 →	3M™ 至尊鍍膜水撥	B	A+6	24	19
HONDA	Civic Hatchback	EU/EP	02.01 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
HONDA	Civic Hatchback	EG/EH	10.91 - 09.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Hatchback	EJ/EK	10.95 - 02.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Hatchback	FK	09.11 - 02.17	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
HONDA	Civic Hatchback	FC/FK	03.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
HONDA	Civic Hatchback	FK/FN	09.05 - 12.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	22
HONDA	Civic Hybrid	FA	01.06 - 08.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
HONDA	Civic Hybrid	FD	01.08 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
HONDA	Civic Hybrid	FD	01.06 - 12.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	22
HONDA	Civic Sedan	FE	11.21 →	3M™ 至尊鍍膜水撥	B	A+6	24	19
HONDA	Civic Sedan	EJ/EK	10.95 - 02.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Sedan	ES	02.01 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Sedan	FC	03.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
HONDA	Civic Sedan	FD6	06.06 - 08.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
HONDA	Civic Sedan	FB	09.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
HONDA	Civic Sedan	FD	01.08 - 12.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
HONDA	Civic Sedan	FD	09.05 - 12.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	22
HONDA	Civic Sedan	EG/EH	10.91 - 09.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Civic Shuttle	EC/ED/EE	01.88 - 06.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	16
HONDA	Civic Tourer	FK	12.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
HONDA	Crosstour		09.09 - 08.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	19
HONDA	CR-V	RE	01.07 - 11.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	CR-V	RE/RM	10.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	CR-V	[RW]	09.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	CR-V	RD	10.95 - 07.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
HONDA	CR-V	KL	07.03 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
HONDA	CR-V	RD	07.02 - 09.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
HONDA	CR-V Hybrid	[RT]	12.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	CR-Z	ZF	03.10 - 02.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
HONDA	e	ZC7	09.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
HONDA	eNvy1		03.23 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
HONDA	Fit		06.01 - 10.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
HONDA	FR-V	BE	01.05 - 06.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	19
HONDA	HR-V	GH	12.98 - 02.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
HONDA	HR-V	RV	09.21 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	HR-V	RU	08.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
HONDA	Insight Coupé	ZE	01.00 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Insight Hatchback	ZE	03.09 - 02.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HONDA	Integra Type R	DC	01.98 - 10.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	Jazz	GE/GG/GP	10.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
HONDA	Jazz	GK	09.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
HONDA	Jazz	GD	03.02 - 12.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
HONDA	Jazz V	GR	02.20 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
HONDA	Legend		04.98 - 12.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
HONDA	Logo		09.96 - 06.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HONDA	NSX Coupé	NA	06.90 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
HONDA	Odyssey	RA	03.00 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	22
HONDA	Pilot	YF	01.09 - 08.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
HONDA	Prelude	BB	02.92 - 09.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
HONDA	S2000	S2000	04.99 - 06.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
HONDA	Shuttle		01.95 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	22
HONDA	Stepwgn	RK	10.09 - 12.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
HONDA	Stepwgn	RP	14.15 -	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
HONDA	Stream	RN	10.00 - 07.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
HONDA	ZR-V eHEV	RZ4	04.23 →	3M™ 至尊鍍膜水撥	B	A+6	26	16
HUMMER	H2		09.02 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
HUMMER	H3		09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
HYUNDAI	Accent	MC	04.06 - 02.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
HYUNDAI	Accent	RB	11.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HYUNDAI	Accent	X3	04.94 - 07.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HYUNDAI	Accent	LC	05.99 - 06.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HYUNDAI	Accent Blue	RB	01.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
HYUNDAI	Accent Hatchback	MC	04.06 - 02.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
HYUNDAI	Accent Hatchback	X3	07.94 - 07.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HYUNDAI	Accent Hatchback	LC	08.99 - 06.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HYUNDAI	Atos	MX	09.97 - 12.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
HYUNDAI	Atos Prime	MX	09.99 - 03.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
HYUNDAI	Bayon	BC3, BI3	05.21 →	3M™ 至尊鍍膜水撥	D	A+3	24	14
HYUNDAI	Coupé	FX	07.96 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
HYUNDAI	Coupé	RD	05.96 - 04.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
HYUNDAI	Coupé	GK	10.01 - 08.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Creta		01.16 - 01.21	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Elantra	MD	02.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	Elantra	AD	03.16 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Elantra	J1	10.90 - 04.95	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Elantra	J2	05.95 - 09.00	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Elantra	XD	06.00 - 09.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Elantra	HD	09.05 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Elantra Hatchback	XD	06.00 - 09.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Equus		10.09 - 11.12	3M™ 至尊鏡膜水撥	D	A+3	24	19
HYUNDAI	Equus		12.12 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	19
HYUNDAI	Excel	X3	07.94 - 07.99	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Excel Hatchback	X3	11.95 - 07.99	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Galloper		12.97 - 08.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
HYUNDAI	Genesis Coupe	BK	11.08 - 03.16	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	Genesis Sedan	DH	01.14 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Genesis Sedan	BH	05.11 - 03.16	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	19
HYUNDAI	Getz	TB	09.02 - 06.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	14
HYUNDAI	Grand Santa Fe		08.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	Grandeur	TG	06.03 - 06.12	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	Grandeur	HG	01.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	H 100		09.96 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
HYUNDAI	H 350		04.14 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	24
HYUNDAI	H-1		03.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	H-1		10.97 - 12.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	20
HYUNDAI	i10	PA	10.07 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	16
HYUNDAI	i10	IA	09.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	16
HYUNDAI	i10	AC3, AI3	09.19 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
HYUNDAI	i20	BC3, BI3	08.20 →	3M™ 至尊鏡膜水撥	D	A+3	24	14
HYUNDAI	i20	PB	12.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
HYUNDAI	i20	GB	11.14 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
HYUNDAI	i30	FD	09.07 - 03.10	3M™ 至尊鏡膜水撥	B+C	A+2	24	18
HYUNDAI	i30	GD	12.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	i30	PD	12.16 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	i30	FD	04.10 - 01.13	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
HYUNDAI	i30 Coupé	GD	02.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	i30 CW Kombi	GD	03.12 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	i30 CW Kombi	PD	03.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	i30 CW Kombi	FD	04.10 - 09.12	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
HYUNDAI	i30 CW Kombi	FD	02.08 - 03.10	3M™ 至尊鏡膜水撥	B+C	A+2	24	18
HYUNDAI	i30 Fastback	[PD]	11.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	i35		02.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	i40	VF	03.12 - 05.19	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	i40 CW Kombi	VF	07.12 - 05.19	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Ioniq	AE	03.16 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	Ioniq 5	NE	07.20 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	Ioniq 6	CE	10.22 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	ix20	JC	10.10 →	3M™ 至尊鏡膜水撥	B+C	A+2	26	14
HYUNDAI	ix35	LM/EL	01.10 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
HYUNDAI	ix55	EN	09.08 - 12.12	3M™ 至尊鏡膜水撥	B+C	A+2	24	20
HYUNDAI	Kona	OS	06.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Kona	SX2	04.23 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Lantra	J1	10.90 - 04.95	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Lantra	J2	05.95 - 09.00	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Lantra Kombi	J2	05.95 - 09.00	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Matrix	FC	07.01 - 04.10	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	16
HYUNDAI	Nexo		03.18 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Pony	X3	07.94 - 07.99	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Porter 507		09.00 - 12.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
HYUNDAI	Santa Fe	DM	09.12 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	14
HYUNDAI	Santa Fe	TM	02.18 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Santa Fe	CM	03.06 - 12.12	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
HYUNDAI	Santa Fe	SM	09.99 - 12.05	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
HYUNDAI	Scoupe		02.90 - 04.95	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	19	16
HYUNDAI	Solaris	YC	02.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
HYUNDAI	Solaris	RB	01.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Solaris Hatchback	RB	01.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Sonata II	Y3	11.93 - 04.98	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
HYUNDAI	Sonata III	EF	03.98 - 03.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	19
HYUNDAI	Sonata IV	EF	04.01 - 01.05	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
HYUNDAI	Sonata V	NF	08.04 - 12.10	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	Sonata VI	YF	09.09 - 12.15	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	19
HYUNDAI	Sonata VII	LF	06.14 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	Sonata VIII	DN8	03.19 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	Starex		05.07 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
HYUNDAI	Starex		10.02 - 01.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	20
HYUNDAI	Terracan	HP	01.01 - 10.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
HYUNDAI	Trajet	FO	01.00 - 06.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	22
HYUNDAI	Tucson	NX4E, NX4A	10.20 →	3M™ 至尊鏡膜水撥	B	A+6	26	16
HYUNDAI	Tucson	JM	08.04 - 03.10	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
HYUNDAI	Tucson	TL	06.15 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
HYUNDAI	Veloster		06.11 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
HYUNDAI	Venue	QX, QXI	07.19 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
HYUNDAI	Veracruz		09.06 →	3M™ 至尊鏡膜水撥	B+C	A+2	24	20
HYUNDAI	Verna	LC	07.99 - 03.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
HYUNDAI	Verna	MC	10.06 - 05.11	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	19
HYUNDAI	XG	F	12.98 - 12.05	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
INFINITI	EX	J50	04.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
INFINITI	FX	S51	07.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	19
INFINITI	FX	S50	11.02 - 08.08	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
INFINITI	Q30		11.15 →	3M™ 至尊鏡膜水撥	D	A+3	24	19
INFINITI	Q45	F50	01.01 - 12.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
INFINITI	Q50	V37	07.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
INFINITI	Q70	Y51	10.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	19
INFINITI	QX30		09.16 →	3M™ 至尊鏡膜水撥	D	A+3	24	19
INFINITI	QX4	JR50	09.96 - 08.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
INFINITI	QX50		10.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
INFINITI	QX56	Z62	0.10 - 06.14	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	19
INFINITI	QX56	A60	04.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	22
INFINITI	QX60		09.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
INFINITI	QX70	S51	11.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	19
INFINITI	QX80		07.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
ISUZU	D-MAX		05.02 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	19
ISUZU	Trooper	UBS	08.92 - 09.04	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
IVECO	Daily	14	05.14 →	3M™ 至尊鏡膜水撥	D	A+3	24	24
IVECO	Daily	00/06/09/12	05.99 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
IVECO	Daily, Grinta		07.89 - 05.99	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
IVECO	Massif		06.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	16
JAGUAR	Daimler		01.99 - 08.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	
JAGUAR	E-Pace	X540	09.17 →	3M™ 至尊鏡膜水撥	G	B+8	26	20
JAGUAR	F-Pace	X761	04.16 →	3M™ 至尊鏡膜水撥	B+C	A+2	26	19
JAGUAR	F-Type		10.12 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JAGUAR	I-Pace	X590	02.18 →	3M™ 至尊鏡膜水撥	B	A+6	26	20
JAGUAR	S-Type	CCX	10.01 - 03.08	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
JAGUAR	S-Type	CCX	10.98 - 04.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
JAGUAR	XE		06.15 →	3M™ 至尊鏡膜水撥	B+C	A+2	28	16
JAGUAR	XF	X250	03.08 - 10.15	3M™ 至尊鏡膜水撥	D	A+3	24	18
JAGUAR	XF	X260	10.15 →	3M™ 至尊鏡膜水撥	B+C	A+2	28	16
JAGUAR	XF Sportbrake		09.12 - 06.17	3M™ 至尊鏡膜水撥	D	A+3	24	18
JAGUAR	XF Sportbrake	X260	07.17 →	3M™ 至尊鏡膜水撥	B+C	A+2	28	16
JAGUAR	XJ	X351	11.09 →	3M™ 至尊鏡膜水撥	D	A+3	24	18
JAGUAR	XJ 8		09.97 - 01.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	
JAGUAR	XJ S Cabrio		09.81 - 12.97	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	14	14
JAGUAR	XJ S Coupé		09.75 - 12.97	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	14	14
JAGUAR	XJR 8		09.97 - 09.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	
JAGUAR	XK	X150	03.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JAGUAR	XK 8 Convertible	QDV	03.96 - 02.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JAGUAR	XK 8 Coupé	QEV	03.96 - 02.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JAGUAR	XKR 8 Convertible	QDV	03.96 - 02.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JAGUAR	X-Type	CF1	03.01 - 06.10	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	19
JAGUAR	X-Type Estate	CF1	03.03 - 12.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	19
JEEP	Avenger	J2	12.22 →	3M™ 至尊鏡膜水撥	B+C	A+2	24	16
JEEP	Cherokee	XJ	01.87 - 09.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
JEEP	Cherokee	KL	01.14 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
JEEP	Cherokee	KJ	03.01 - 12.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	19	19
JEEP	Cherokee	KK	01.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	19	19
JEEP	Commander	XH	01.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
JEEP	Compass	[MX]	06.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
JEEP	Compass	MK,PK	10.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
JEEP	Gladiator Pickup	JT	04.19 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	16	16
JEEP	Grand Cherokee	ZG	09.92 - 04.99	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JEEP	Grand Cherokee	WG	09.00 - 12.04	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JEEP	Grand Cherokee	WH	03.05 - 10.11	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JEEP	Grand Cherokee	WK	09.03 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JEEP	Grand Cherokee	WK2	09.10 - 08.13	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
JEEP	Grand Cherokee	WK2	09.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
JEEP	Liberty	KK	09.07 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	19	19
JEEP	Patriot	MK	10.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
JEEP	Renegade		07.14 →	3M™ 至尊鏡膜水撥	B+C	A+2	22	20
JEEP	Wrangler	TJ	01.97 - 12.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	14	14
JEEP	Wrangler	JK	01.07 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	14	14
JEEP	Wrangler	JL	11.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	16	16
KIA	Carens	FG	09.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
KIA	Carens	FC	04.99 - 08.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
KIA	Carens	RP	01.13 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	28	28
KIA	Carnival	MB	04.06 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
KIA	Carnival	KA4	09.20 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
KIA	Carnival	UP	06.98 - 06.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
KIA	Cee'd	ED/FF2	11.06 - 06.09	3M™ 至尊鏡膜水撥	B+C	A+2	24	18

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
KIA	Cee'd	JD	05.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
KIA	Cee'd	CD	07.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Cee'd	ED/FF2	07.09 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Cee'd Sports Wagon	CD	11.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Cee'd Sporty Wagon	ED/FF2	09.07 - 06.09	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
KIA	Cee'd Sporty Wagon	JD	08.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
KIA	Cee'd Sporty Wagon	ED/FF2	07.09 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Cerato	FE	03.04 - 11.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
KIA	Cerato	TD	12.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Cerato Hatchback	FE	03.04 - 11.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
KIA	Cerato Koup	TD	08.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Clarus	GC	05.96 - 11.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Clarus II Kombi	GC	06.98 - 11.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	EV6	CV	07.21 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	EV9	MV	06.23 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
KIA	Joice	MT	08.99 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	Joice	MT	09.01 - 03.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	K 2500		09.01 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	K 2700	SD	04.98 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	K 2700		08.04 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	K 2900		05.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	K9	RJ	03.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Magentis	GE	02.06 - 04.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Magentis	GD	09.00 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
KIA	Mentor II	FX	01.01 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Mentor II Hatchback	FX	01.01 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Mohave		01.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Niro	DE	09.16 - 08.22	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Niro	SG2	01.22 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Opirus	LD	03.03 - 07.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Optima	TF	09.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Optima	JF	07.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
KIA	Optima Sports Wagon	JF	07.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
KIA	Picanto	JA	03.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
KIA	Picanto	BA	05.04 - 01.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
KIA	Picanto	TA	05.11 - 05.17	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
KIA	Pregio	TB	02.97 - 04.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	Pregio	TB	05.04 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Pride	DA	05.90 - 02.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
KIA	Pro Cee'd	CD	03.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Pro Cee'd	ED/FF2	10.07 - 06.09	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
KIA	Pro Cee'd	JD	01.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
KIA	Pro Cee'd	ED/FF2	07.09 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Retona	CE	04.98 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	14	14
KIA	Rio	DE	03.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
KIA	Rio	UB	06.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Rio	DC	07.00 - 02.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	Rio Hatchback	DE	03.05 - 09.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
KIA	Rio Hatchback	UB	06.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Rio Hatchback	YB	02.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Rio Kombi	DC	09.02 - 02.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
KIA	Sedona		06.98 - 09.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
KIA	Seltos	SP2, SP2I	08.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Sephia I	FA	01.92 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Sephia I Hatchback	FA	09.96 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Shuma I	FB	01.98 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Shuma I Hatchback	FB	01.98 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Shuma II	FB	01.01 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Shuma II Hatchback	FB	01.01 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
KIA	Sorento	UM	02.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Sorento	MQ4, MQ4A	03.20 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Sorento	JC	07.02 - 08.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Sorento	XM	09.09 - 04.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Soul	AM	02.09 - 12.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Soul	PS	02.14 - 12.18	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Soul	SK3	01.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
KIA	Spectra		01.01 - 12.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
KIA	Sportage	JE	09.04 - 05.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
KIA	Sportage	QL	01.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Sportage	NQS	09.21 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Sportage	SL	07.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Sportage	JA	05.93 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
KIA	Sportage R	SL	03.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
KIA	Stinger	CK	05.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
KIA	Stonic	YB	09.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
KIA	Venga		12.09 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	14
KIA	XCEED	CD	06.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
LAND ROVER	Defender		08.90 - 02.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	14	14
LAND ROVER	Defender Station Wagon	L663	09.19 →	3M™ 至尊鍍膜水撥	B	A+6	22	22
LAND ROVER	Discovery I		09.89 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18

車廠品牌	車款	型號 MODEL CODE	年份	適用水喉款式	水喉臂及接頭款式	3M™ 水喉接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
LAND ROVER	Discovery II		11.98 - 06.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
LAND ROVER	Discovery III		09.04 - 08.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LAND ROVER	Discovery IV		09.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LAND ROVER	Discovery Sport	B5	09.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
LAND ROVER	Discovery V	LR/B6	04.17 →	3M™ 至尊鍍膜水喉	G	B+8	24	20
LAND ROVER	Freelander I	LN	09.97 - 10.06	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LAND ROVER	Freelander II	LF	10.06 - 11.14	3M™ 至尊鍍膜水喉	D	A+3	24	20
LAND ROVER	Range Rover Evoque	LZ,L551	11.18 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	21
LAND ROVER	Range Rover Evoque	LVL538	9.11 →	3M™ 至尊鍍膜水喉	B+C	A+2	22	21
LAND ROVER	Range Rover Evoque Cabrio		3.16 →	3M™ 至尊鍍膜水喉	B+C	A+2	22	21
LAND ROVER	Range Rover I		11.88 - 04.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	18
LAND ROVER	Range Rover II		09.94 - 08.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	22
LAND ROVER	Range Rover IV	LG	09.16 →	3M™ 至尊鍍膜水喉	G	B+8	24	20
LAND ROVER	Range Rover IV	LG	2.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
LAND ROVER	Range Rover Sport I	LS	03.05 - 08.13	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LAND ROVER	Range Rover Sport II		09.16 →	3M™ 至尊鍍膜水喉	G	B+8	24	20
LAND ROVER	Range Rover Sport II	LW	9.13 - 08.16	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
LAND ROVER	Range Rover Velar	LS60	08.17 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	19
LEXUS	CT200h	CT200h	12.10 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	ES	V6	09.12 - 06.18	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	ES	Z10, A10, H10	07.18 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	ES	V	03.06 - 09.12	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	19
LEXUS	GS	L1	01.12 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	GS	GS	03.93 - 08.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
LEXUS	GS	GS	08.97 - 01.12	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
LEXUS	GX 460	J1	11.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
LEXUS	GX 470	J1	11.02 - 08.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LEXUS	IS	E3	04.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
LEXUS	IS	E1	01.99 - 07.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	19
LEXUS	IS	E2	08.05 - 04.13	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LEXUS	IS F	E2	12.07 - 05.14	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LEXUS	IS Wagon	E1	07.01 - 07.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	19
LEXUS	LC	Z1	03.17 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	LS	F3	08.00 - 08.06	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
LEXUS	LX	LX J1	01.98 - 08.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
LEXUS	LX	J2	11.07 - 01.12	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	22
LEXUS	LX	J2	02.12 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	22
LEXUS	NX	Z1	11.14 →	3M™ 至尊鍍膜水喉	G	B+8	26	16
LEXUS	RC	C1	09.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
LEXUS	RX	L2	09.15 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	20
LEXUS	RX	LA1, LH1	06.22 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	18
LEXUS	RX	U1	01.98 - 02.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
LEXUS	RX	U3	02.03 - 12.08	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	22
LEXUS	RX	L1	12.08 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	22
LEXUS	RZ		01.23 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
LEXUS	SC Cabrio	Z4	05.01 - 08.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
LEXUS	UX		10.18 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
LOTUS	Eilan		09.89 - 09.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
LOTUS	Elise Cabrio		09.07 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
LOTUS	Europa		07.06 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
LOTUS	Evora		05.09 →	3M™ 至尊鍍膜水喉	F	A+1	26	20
LOTUS	Exige		04.06 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
MASERATI	420		01.87 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
MASERATI	430		02.88 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
MASERATI	Biturbo		03.89 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
MASERATI	Ghibli	M157	01.13 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	18
MASERATI	Karif		04.88 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
MASERATI	Levante	M161	06.16 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	18
MASERATI	Quattroporte	M156	11.12 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	19
MAZDA	2	DE	06.07 - 12.14	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	14
MAZDA	2	DJ	10.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
MAZDA	2	DY	02.03 - 06.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
MAZDA	3	BK	07.03 - 12.08	3M™ 至尊鍍膜水喉	F	A+1	21	19
MAZDA	3	BM	08.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
MAZDA	3	BL	12.08 - 12.13	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	19
MAZDA	5	CR	02.05 - 12.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
MAZDA	5	CW	06.10 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
MAZDA	121	DB	11.90 - 12.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	16
MAZDA	121	JA/JB	01.96 - 01.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
MAZDA	121	Soho	01.97 - 12.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
MAZDA	323	BJ	05.98 - 09.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
MAZDA	626	GF	05.97 - 07.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
MAZDA	626	GE	08.91 - 03.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
MAZDA	2 Hatchback	KB	03.2022 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
MAZDA	3	BP	01.19 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
MAZDA	3 Hatchback	BP	11.18 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
MAZDA	3 Hatchback	BM	07.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
MAZDA	3 Hatchback	BN	06.16 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
MAZDA	3 Hatchback	BK	07.03 - 12.08	3M™ 至尊鍍膜水喉	F	A+1	21	19

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
MAZDA	3 Hatchback	BL	12.08 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
MAZDA	323 F Hatchback	BA	05.94 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Hatchback	BA	06.94 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Hatchback	BG	03.91 - 05.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Hatchback	BJ	06.98 - 09.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Sedan	BA	06.94 - 06.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Sedan	BG	06.89 - 02.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	323 Wagon	BW	09.89 - 10.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	6 Fastback	GH	08.07 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MAZDA	6 Fastback	GG/GY	04.02 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MAZDA	6 Sedan	GH	08.07 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MAZDA	6 Sedan	GG/GY	02.02 - 08.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MAZDA	6 Sedan	GJ	09.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
MAZDA	6 Wagon	GH	12.07 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MAZDA	6 Wagon	GY	06.02 - 12.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MAZDA	6 Wagon	GJ/GL	10.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
MAZDA	626 Fastback	GF	08.99 - 04.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	626 Hatchback	GF	04.97 - 07.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	626 Hatchback	GE	09.91 - 06.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MAZDA	626 Wagon	GW	10.97 - 04.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	626 Wagon	GV	03.92 - 10.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MAZDA	BT-50		03.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	CX-3	DK	02.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MAZDA	CX-30	DM	04.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
MAZDA	CX-5	KF	02.17 →	3M™ 至尊鍍膜水撥	G	B+8	24	18
MAZDA	CX-5	KE	11.11 - 02.17	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
MAZDA	CX-60	KH	03.22 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
MAZDA	CX-7	ER	09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
MAZDA	CX-9	TB	09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
MAZDA	Demio	DW	07.96 - 02.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	16
MAZDA	MPV	LV	07.94 - 04.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MAZDA	MPV	LW	05.99 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	22
MAZDA	MX-3	EC	11.93 - 02.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	MX-30	DR	05.20 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
MAZDA	MX-5	NA	08.89 - 11.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	MX-5	NB	01.98 - 07.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	MX-5	NC	07.05 - 03.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	MX-5	ND	05.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	19
MAZDA	MX-6	GE	07.91 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MAZDA	Premacy	CP	03.99 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MAZDA	RX-7 Coupé	FD	01.92 - 02.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MAZDA	RX-8	FE/SE	04.03 - 04.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MAZDA	Serie B	UF/UN	03.96 - 03.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MAZDA	Serie E		02.84 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
MAZDA	Tribute	EP	02.01 - 09.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MAZDA	Xedos-6	CA	01.92 - 02.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MAZDA	Xedos-9	TA	07.93 - 11.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MERCEDES-BENZ	Citan		07.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MERCEDES-BENZ	EQA	H243	02.21 →	3M™ 至尊鍍膜水撥	I	B+7	26	19
MERCEDES-BENZ	EQB	X243	09.21 →	3M™ 至尊鍍膜水撥	I	B+7	24	21
MERCEDES-BENZ	EQC	N293	05.19 - 07.23	3M™ 至尊鍍膜水撥	I	B+7	22	22
MERCEDES-BENZ	EQE	V295	02.22 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	20
MERCEDES-BENZ	EQE SUV	X294	12.22 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	20
MERCEDES-BENZ	EQS	V297	08.21 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	20
MERCEDES-BENZ	EQS SUV	X296	10.22 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	26	20
MERCEDES-BENZ	EQT	W420	01.23 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	18
MERCEDES-BENZ	Serie E (T-Modell)	213	06.16 →	3M™ 至尊鍍膜水撥	I	B+7	24	22
MERCEDES-BENZ	Serie E (T-Modell)	212	03.14 - 08.16	3M™ 至尊鍍膜水撥	B+C	A+2	24	24
MERCEDES-BENZ	Serie E (T-Modell)	212	08.09 - 02.14	3M™ 至尊鍍膜水撥	F	A+1	24	24
MERCEDES-BENZ	Serie E (T-Modell)	211	02.03 - 08.09	3M™ 至尊鍍膜水撥	F	A+1	26	26
MERCEDES-BENZ	Serie E (T-Modell)	124	07.93 - 05.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	
MERCEDES-BENZ	Serie E (T-Modell)	210	05.96 - 02.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	
MERCEDES-BENZ	Serie 190	201	09.86 - 09.93	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	
MERCEDES-BENZ	Serie 190	201	09.90 - 09.93	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	
MERCEDES-BENZ	Serie A	176	06.12 - 06.15	3M™ 至尊鍍膜水撥	D	A+3	24	19
MERCEDES-BENZ	Serie A	169	09.04 - 06.12	3M™ 至尊鍍膜水撥	D	A+3	26	22
MERCEDES-BENZ	Serie A	176	07.15 →	3M™ 至尊鍍膜水撥	I	B+7	24	19
MERCEDES-BENZ	Serie A	177	02.18 →	3M™ 至尊鍍膜水撥	I	B+7	24	19
MERCEDES-BENZ	Serie A	168	10.97 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
MERCEDES-BENZ	Serie B	246	09.11 - 06.15	3M™ 至尊鍍膜水撥	D	A+3	26	19
MERCEDES-BENZ	Serie B	245	04.05 - 05.11	3M™ 至尊鍍膜水撥	D	A+3	26	22
MERCEDES-BENZ	Serie B	246	07.15 →	3M™ 至尊鍍膜水撥	I	B+7	24	19
MERCEDES-BENZ	Serie C	206	02.21 →	3M™ 至尊鍍膜水撥	K	請與經銷商聯絡	22	22
MERCEDES-BENZ	Serie C	205	11.13 - 10.14	3M™ 至尊鍍膜水撥	D	A+3	22	22
MERCEDES-BENZ	Serie C	205	08.14 →01.21	3M™ 至尊鍍膜水撥	I	B+7	22	22
MERCEDES-BENZ	Serie C	204	03.13 - 12.14	3M™ 至尊鍍膜水撥	B+C	A+2	24	24
MERCEDES-BENZ	Serie C	204	01.07 - 11.08	3M™ 至尊鍍膜水撥	F	A+1	24	24
MERCEDES-BENZ	Serie C	204	12.08 - 04.13	3M™ 至尊鍍膜水撥	F	A+1	24	24
MERCEDES-BENZ	Serie C	202	03.93 - 08.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	
MERCEDES-BENZ	Serie C	203	05.00 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	

車廠品牌	車款	型號 MODEL CODE	年份	適用水喉款式	水喉臂及接頭款式	3M™ 水喉接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
MERCEDES-BENZ	Serie C (Sportcoupe)	203	01.01 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie C (T-Modell)	205	05.14 - 07.14	3M™ 至尊鍍膜水喉	D	A+3	22	22
MERCEDES-BENZ	Serie C (T-Modell)	205	08.14 →	3M™ 至尊鍍膜水喉	I	B+7	22	22
MERCEDES-BENZ	Serie C (T-Modell)	204	03.13 - 12.14	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie C (T-Modell)	204	09.07 - 11.08	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie C (T-Modell)	204	12.08 - 04.13	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie C (T-Modell)	202	05.96 - 02.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie C (T-Modell)	203	01.01 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie C Coupé	205	10.15 →	3M™ 至尊鍍膜水喉	I	B+7	22	22
MERCEDES-BENZ	Serie C Coupé	204	03.11 - 04.13	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie CL (Coupé)	215	03.00 - 08.06	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie CL (Coupé)	216	06.06 →	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie CL (Coupé)	140	06.96 - 08.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	28	24
MERCEDES-BENZ	Serie CL (Coupé)	215	09.99 - 02.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	27	26
MERCEDES-BENZ	Serie CLA	118	03.19 →	3M™ 至尊鍍膜水喉	I	B+7	24	19
MERCEDES-BENZ	Serie CLA	117	12.12 - 06.15	3M™ 至尊鍍膜水喉	D	A+3	24	19
MERCEDES-BENZ	Serie CLA	117	07.15 →	3M™ 至尊鍍膜水喉	I	B+7	24	19
MERCEDES-BENZ	Serie CLA Shooting Brake	117	01.15 - 06.15	3M™ 至尊鍍膜水喉	D	A+3	24	19
MERCEDES-BENZ	Serie CLA Shooting Brake	117	07.15 - 03.19	3M™ 至尊鍍膜水喉	I	B+7	24	19
MERCEDES-BENZ	Serie CLA Shooting Brake	118	06.19 →	3M™ 至尊鍍膜水喉	I	B+7	24	19
MERCEDES-BENZ	Serie CLK (Cabrio)	208	09.96 - 01.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie CLK (Coupé)	208	01.97 - 09.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	
MERCEDES-BENZ	Serie CLS	219	06.04 - 02.11	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie CLS Coupé	218	03.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie CLS Coupé	218	07.10 - 02.14	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie CLS Shooting Brake	218	03.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie CLS Shooting Brake	218	06.12 - 02.14	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie E	213	01.16 →	3M™ 至尊鍍膜水喉	I	B+7	24	22
MERCEDES-BENZ	Serie E	212	03.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie E	212	08.08 - 02.14	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie E	211	03.02 - 08.09	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie E	124	07.93 - 07.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie E	210	06.95 - 08.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie E	214	07.23 →	3M™ 至尊鍍膜水喉	K	請與經銷商聯絡	22	22
MERCEDES-BENZ	Serie E (Cabrio)	207	01.13 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie E (Cabrio)	207	01.10 - 04.13	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie E (Cabrio)	124	05.93 - 06.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie E (Coupé)	207	1.13 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	24
MERCEDES-BENZ	Serie E (Coupé)	207	02.09 - 04.13	3M™ 至尊鍍膜水喉	F	A+1	24	24
MERCEDES-BENZ	Serie E (Coupé)	124	07.93 - 06.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie G	463	09.89 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	16	16
MERCEDES-BENZ	Serie GL	164	02.06 - 12.12	3M™ 至尊鍍膜水喉	D	A+3	28	21
MERCEDES-BENZ	Serie GL	166	08.12 - 09.15	3M™ 至尊鍍膜水喉	B+C	A+2	26	22
MERCEDES-BENZ	Serie GLA	156	10.13 - 06.15	3M™ 至尊鍍膜水喉	D	A+3	24	19
MERCEDES-BENZ	Serie GLA	156	07.15 →	3M™ 至尊鍍膜水喉	I	B+7	24	19
MERCEDES-BENZ	Serie GLA	H247	02.20 →	3M™ 至尊鍍膜水喉	I	B+7	26	19
MERCEDES-BENZ	Serie GLB	X247	08.19 →	3M™ 至尊鍍膜水喉	I	B+7	24	21
MERCEDES-BENZ	Serie GLC	253	07.15 →	3M™ 至尊鍍膜水喉	I	B+7	22	22
MERCEDES-BENZ	Serie GLC	254	06.22 →	3M™ 至尊鍍膜水喉	K	請與經銷商聯絡	22	22
MERCEDES-BENZ	Serie GLC (Coupé)	253	06.16 →	3M™ 至尊鍍膜水喉	I	B+7	22	22
MERCEDES-BENZ	Serie GLC (Coupé)	254	04.23 →	3M™ 至尊鍍膜水喉	K	請與經銷商聯絡	22	22
MERCEDES-BENZ	Serie GLE	V167	10.18 →	3M™ 至尊鍍膜水喉	I	B+7	26	22
MERCEDES-BENZ	Serie GLE	166	04.15 - 10.18	3M™ 至尊鍍膜水喉	B+C	A+2	26	22
MERCEDES-BENZ	Serie GLE (Coupé)	C167	11.19 →	3M™ 至尊鍍膜水喉	I	B+7	26	22
MERCEDES-BENZ	Serie GLE (Coupé)	292	04.15 - 10.18	3M™ 至尊鍍膜水喉	B+C	A+2	26	22
MERCEDES-BENZ	Serie GLK	204	02.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	22	19
MERCEDES-BENZ	Serie GLK	204	06.08 - 01.14	3M™ 至尊鍍膜水喉	F	A+1	22	19
MERCEDES-BENZ	Serie GLS	X167	04.19 →	3M™ 至尊鍍膜水喉	I	B+7	26	22
MERCEDES-BENZ	Serie GLS	166	09.15 - 04.19	3M™ 至尊鍍膜水喉	B+C	A+2	26	22
MERCEDES-BENZ	Serie MB		01.87 - 01.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	18
MERCEDES-BENZ	Serie ML	164	03.05 - 08.11	3M™ 至尊鍍膜水喉	D	A+3	28	21
MERCEDES-BENZ	Serie ML	166	06.11 - 08.11	3M™ 至尊鍍膜水喉	D	A+3	28	21
MERCEDES-BENZ	Serie ML	166	09.11 - 04.15	3M™ 至尊鍍膜水喉	B+C	A+2	26	22
MERCEDES-BENZ	Serie ML	163	03.98 - 06.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
MERCEDES-BENZ	Serie R	251	09.05 - 10.12	3M™ 至尊鍍膜水喉	D	A+3	28	21
MERCEDES-BENZ	Serie S	222	05.13 →	3M™ 至尊鍍膜水喉	D	A+3	26	22
MERCEDES-BENZ	Serie S	220	03.00 - 08.06	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie S	221	09.05 - 12.13	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie S	140	02.91 - 09.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	28	24
MERCEDES-BENZ	Serie S	220	10.98 - 02.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	27	26
MERCEDES-BENZ	Serie S (Coupé)	140	09.92 - 09.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	28	24
MERCEDES-BENZ	Serie SL	230	10.01 - 11.12	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie SL	129	03.89 - 08.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	
MERCEDES-BENZ	Serie SLC	172	12.15 →	3M™ 至尊鍍膜水喉	D	A+3	22	22
MERCEDES-BENZ	Serie SLK	171	04.04 - 02.11	3M™ 至尊鍍膜水喉	D	A+3	22	22
MERCEDES-BENZ	Serie SLK	172	01.11 - 12.15	3M™ 至尊鍍膜水喉	D	A+3	22	22
MERCEDES-BENZ	Serie SLK	170	09.96 - 03.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
MERCEDES-BENZ	Serie SLR	199	04.04 - 12.09	3M™ 至尊鍍膜水喉	F	A+1	26	26
MERCEDES-BENZ	Serie V	447	04.14 →	3M™ 至尊鍍膜水喉	I	B+7	28	18
MERCEDES-BENZ	Serie X	470	09.17 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	18

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
MERCEDES-BENZ	Sprinter	NCV3	04.06 →	3M™ 至尊鍍膜水撥	D	A+3	26	24
MERCEDES-BENZ	Sprinter	T1N	02.95 - 05.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
MERCEDES-BENZ	Sprinter Classic	909	11.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
MERCEDES-BENZ	Vaneo	414	02.04 - 08.05	3M™ 至尊鍍膜水撥	D	A+3	26	22
MERCEDES-BENZ	Vaneo	414	02.02 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
MERCEDES-BENZ	Viano	639TON	09.05 - 08.10	3M™ 至尊鍍膜水撥	D	A+3	28	26
MERCEDES-BENZ	Viano	639TON	09.10 - 12.14	3M™ 至尊鍍膜水撥	D	A+3	28	26
MERCEDES-BENZ	Viano	639TON	09.03 - 08.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
MERCEDES-BENZ	Vito	639TON	09.05 - 08.10	3M™ 至尊鍍膜水撥	D	A+3	28	26
MERCEDES-BENZ	Vito	639TON	09.10 - 12.14	3M™ 至尊鍍膜水撥	D	A+3	28	26
MERCEDES-BENZ	Vito	447	09.14 →	3M™ 至尊鍍膜水撥	I	B+7	28	18
MERCEDES-BENZ	Vito	639TON	10.03 - 08.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
MG	Marcel R EV	EP21	02.21 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	20
MG	MG 4 EV		07.22 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
MG	MG 6		11.10 →	3M™ 至尊鍍膜水撥	D	A+3	24	18
MG	MG HS	SAS23	09.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
MG	MGF		10.95 - 03.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MG	MGTF		03.02 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MG	ZR		10.01 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MG	ZS		10.01 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MG	ZT		10.01 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MG	ZT-Tourer		10.01 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MINI	Cooper	J01	11.23 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MINI	Mini	R56	04.12 - 11.13	3M™ 至尊鍍膜水撥	E	A+4	19	19
MINI	Mini	R56	11.06 - 03.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MINI	Mini	F55,F56	09.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	19
MINI	Mini	R50,R53	06.01 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MINI	Mini	R50,R53	08.04 - 11.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MINI	Mini Cabrio	R57	04.12 →	3M™ 至尊鍍膜水撥	E	A+4	18	19
MINI	Mini Cabrio	R52,R57	07.04 - 03.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MINI	Mini Clubman	F54	09.15 →	3M™ 至尊鍍膜水撥	B	A+6	22	20
MINI	Mini Clubman	R55	04.12 - 08.14	3M™ 至尊鍍膜水撥	E	A+4	18	19
MINI	Mini Clubman	R55	11.07 - 03.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MINI	Mini Clubman	R55	02.13 - 06.14	3M™ 至尊鍍膜水撥	E	A+4	18	19
MINI	Mini Countryman	R60	09.10 →	3M™ 至尊鍍膜水撥	D	A+3	19	20
MINI	Mini Countryman	F60	09.16 →	3M™ 至尊鍍膜水撥	H	請與經銷商聯絡	22	21
MINI	Mini Countryman	U25	11.23 →	3M™ 至尊鍍膜水撥	B	A+6	22	22
MINI	Mini Coupé	R58	09.11 →	3M™ 至尊鍍膜水撥	D	A+3	20	20
MINI	Mini Coupé Roadster	R59	02.12 →	3M™ 至尊鍍膜水撥	D	A+3	20	20
MINI	Mini Paceman	R61	03.13 →	3M™ 至尊鍍膜水撥	D	A+3	19	20
MITSUBISHI	[CS/CT]	CS/CT	06.03 - 06.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
MITSUBISHI	3000 GT		06.92 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	ASX	VSX, VSE	01.23 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	14
MITSUBISHI	ASX	GA	04.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
MITSUBISHI	Attrage	A1	03.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
MITSUBISHI	Canter	FE	10.96 - 10.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Carisma	DA	05.96 - 12.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Carisma Hatchback	DA	05.95 - 12.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Colt	CZ	10.08 - 04.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
MITSUBISHI	Colt	CA/CC,C5	04.88 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Colt	CJ	11.95 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Colt	CZ	04.04 - 04.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	
MITSUBISHI	Colt Cabrio	CZ	03.06 - 07.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	
MITSUBISHI	Eclipse Cross	GK	10.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
MITSUBISHI	Galant	EA	10.96 - 05.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Galant	E5.8	11.92 - 10.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Galant	EA	09.04 - 08.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	19
MITSUBISHI	Galant Fortis Sportback		12.08 - 12.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MITSUBISHI	Galant Hatchback	E5.8	11.92 - 10.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Galant Station Wagon	EA	10.96 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Galloper		05.98 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MITSUBISHI	Grandis		01.04 - 01.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	22
MITSUBISHI	Grandis		02.08 - 11.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	22
MITSUBISHI	i-Miev		10.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	
MITSUBISHI	L 200	KA,KB	11.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MITSUBISHI	L 200	KL,KK	02.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MITSUBISHI	L 200	K6/K7	01.96 - 12.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	L 200	KB	12.05 - 10.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	L 200 Forte	K7	01.96 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	L 300	P	12.87 - 12.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
MITSUBISHI	L 300 Exceed		02.00 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
MITSUBISHI	Lancer [C6/C7]	CY/CZ	03.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
MITSUBISHI	Lancer [C6/C7]	Lancer	04.88 - 07.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Lancer [C6/C7]	CA/CB/CD	12.91 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Lancer [C6/C7]	CS/CT	12.00 - 04.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
MITSUBISHI	Lancer [C6/C7]	CK/CP/CN	11.95 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Lancer Hatchback	C6/C7	06.92 - 07.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Lancer Sedan	CA/CB/CD	01.93 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Lancer Sedan	CK/CP/CN	05.96 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Lancer Sportback	CX	07.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
MITSUBISHI	Lancer Station Wagon	CA/CB/CD	06.92 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Mirage	A0	08.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
MITSUBISHI	Montero	V	12.90 - 06.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	Montero	V60,V70	02.00 - 08.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Montero	V80,V90	09.06 - 07.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MITSUBISHI	Montero	V80,V90	08.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MITSUBISHI	Outlander	GF	04.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
MITSUBISHI	Outlander	CU	02.03 - 09.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
MITSUBISHI	Outlander	CW	02.07 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
MITSUBISHI	Pajero	V	12.90 - 06.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	Pajero	V60,V70	02.00 - 08.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Pajero	V80,V90	09.06 - 07.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MITSUBISHI	Pajero	V80,V90	08.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
MITSUBISHI	Pajero Cabrio	V	12.90 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	Pajero IO		03.98 - 06.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	Pajero Pinin	H	10.99 - 02.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
MITSUBISHI	Pajero Sport	KH	07.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MITSUBISHI	Pajero Sport	KS	12.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	18
MITSUBISHI	Pajero Sport	K	07.96 - 02.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
MITSUBISHI	Sigma		12.90 - 03.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
MITSUBISHI	Space Runner		06.91 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Space Star	A0	11.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
MITSUBISHI	Space Star	DG	06.98 - 12.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
MITSUBISHI	Space Wagon	N9	07.98 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
MITSUBISHI	Space Wagon	N3	06.92 - 11.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
NISSAN	200 SX	S13,S14	09.88 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	300 ZX	Z32	01.90 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	350 Z	Z33	12.03 - 04.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	350 Z Cabriolet	Z33	09.03 - 04.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	350 Z Coupé	Z33	09.02 - 04.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Almera	G15RA	11.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Almera (Classic)	B10	01.06 - 11.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Almera Hatchback	N16E	01.00 - 09.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Almera Hatchback	N16E	10.02 - 11.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Almera Hatchback	N15	07.95 - 04.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
NISSAN	Almera Sedan	N16,N16E	04.00 - 11.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Almera Sedan	N15	07.95 - 04.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
NISSAN	Almera Tino	V10M	05.00 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
NISSAN	Altima	L32	11.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Ariva	FE0	07.20 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	19
NISSAN	Cabstar	TLO	10.98 - 08.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
NISSAN	Cabstar	F24	09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	Cube	Z12	08.09 - 03.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	Evalia	M20M	01.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	Interstar	X70	07.02 - 06.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
NISSAN	Juke	F16	09.19 →	3M™ 至尊鍍膜水撥	D	A+3	24	14
NISSAN	Juke	F15	07.10 - 03.17	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	14
NISSAN	Juke	F15	04.17 → 07.19	3M™ 至尊鍍膜水撥	D	A+3	24	14
NISSAN	Kubistar	X76	07.03 - 03.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	Leaf		10.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Leaf	ZE1E	01.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Maxima	A34	02.03 - 05.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Maxima	A35	09.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Maxima QX	CA33	01.00 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
NISSAN	Maxima QX	A32	10.94 - 01.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	Micra	K13K	07.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
NISSAN	Micra	K14FR	01.17 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
NISSAN	Micra	K11E	08.92 - 06.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Micra	K11E	07.00 - 10.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Micra	K12E	11.02 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Micra	K12E	06.05 - 10.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Micra CC	K12E	09.05 - 10.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
NISSAN	Murano	Z51	06.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Murano	Z50	09.02 - 12.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Murano	Z52R	06.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
NISSAN	Navara	D23M	11.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
NISSAN	Navara	D22	06.00 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
NISSAN	Navara	D40,D40M	05.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
NISSAN	Note	E11,E11E	01.05 - 08.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
NISSAN	NP200		10.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
NISSAN	NP300	D22	09.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
NISSAN	NV200	M20,M20M	08.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
NISSAN	NV300	X82	09.16 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
NISSAN	NV400	X62	09.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	26
NISSAN	Pathfinder	R52R	09.14 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
NISSAN	Pathfinder	R51	01.05 - 11.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
NISSAN	Pathfinder	R50	10.97 - 10.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
NISSAN	Patrol	Y62	03.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
NISSAN	Patrol	260	04.89 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
NISSAN	Patrol GR	Y60	09.88 - 09.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19

車廠品牌	車款	型號 MODEL CODE	年份	適用水喉款式	水喉臂及接頭款式	3M™ 水喉接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
NISSAN	Patrol GR	Y61	10.97 - 03.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Pickup	D21	08.87 - 02.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
NISSAN	Pickup	D22	02.97 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
NISSAN	Pixo Hatchback	UA0	03.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	14
NISSAN	Primastar	X83	07.02 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
NISSAN	Primera Hatchback	P10E	06.90 - 06.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Primera Hatchback	P12E	05.02 - 09.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
NISSAN	Primera Hatchback	P11E	06.96 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Primera Sedan	P10E	06.90 - 06.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Primera Sedan	P12E	12.01 - 09.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
NISSAN	Primera Sedan	P11E	06.96 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Primera Wagon	W10	07.90 - 12.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Primera Wagon	P12E	12.01 - 09.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
NISSAN	Primera Wagon	P11E	01.98 - 12.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Pulsar	C13	07.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	14
NISSAN	Pulsar	N16	12.99 - 07.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
NISSAN	Pulsar	N15	01.95 - 08.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
NISSAN	Pulsar Hatchback	N15	01.95 - 08.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
NISSAN	Qashqai	J10	12.06 - 12.13	3M™ 至尊鍍膜水喉	D	A+3	24	14
NISSAN	Qashqai	J11E,J11R	12.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
NISSAN	Qashqai	J12	04.21 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
NISSAN	Qashqai+2	J10	08.08 - 12.13	3M™ 至尊鍍膜水喉	D	A+3	24	14
NISSAN	Sentra	B17R,B17RR	09.14 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	14
NISSAN	Sentra	N16	12.99 - 07.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
NISSAN	Serena	C23M	07.92 - 11.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	24
NISSAN	Sunny		10.98 - 10.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
NISSAN	Sunny Hatchback	N14	10.90 - 05.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Sunny Liftback	N14	10.90 - 05.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Sunny Neo	N18	07.02 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
NISSAN	Sunny Sedan	N14	10.90 - 05.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Sunny Wagon	Y10	11.90 - 03.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
NISSAN	Teana	J32,J32R	02.08 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
NISSAN	Teana	J31,L41F	02.03 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	19
NISSAN	Terrano	H5	10.13 - 09.14	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Terrano I		11.88 - 08.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
NISSAN	Terrano I	WD21	09.95 - 12.06	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Terrano II	R20	02.93 - 10.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Terrano II	R20	11.99 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Tiida	C13R	04.15 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	14
NISSAN	Tiida	C11	02.07 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	14
NISSAN	Tiida Hatchback	C11	03.07 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	14
NISSAN	Tiida Latio	SC11	08.05 - 08.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	14
NISSAN	Townstar	X2i	12.21 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	18
NISSAN	Trade		03.87 - 12.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	20
NISSAN	Urvan	E24	11.86 - 06.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
NISSAN	Vanette Cargo	C23M	07.92 - 11.01	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	24
NISSAN	Versa	C11	09.10 - 08.12	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	14
NISSAN	X-Trail	T30	10.00 - 08.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
NISSAN	X-Trail	T31	04.07 - 12.14	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
NISSAN	X-Trail	T33	09.22 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
NISSAN	X-Trail	T32,T32R	04.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
PEUGEOT	108	B3	02.14 →	3M™ 至尊鍍膜水喉	D	A+3	26	
PEUGEOT	205		10.87 - 12.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	18
PEUGEOT	206	T1	06.98 - 02.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
PEUGEOT	208		01.12 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	16
PEUGEOT	301		09.12 →	3M™ 至尊鍍膜水喉	E	A+4	24	16
PEUGEOT	408		12.09 →	3M™ 至尊鍍膜水喉	B+C	A+2	30	26
PEUGEOT	508		10.10 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	26
PEUGEOT	2008		03.13 →	3M™ 至尊鍍膜水喉	B+C	A+2	26	16
PEUGEOT	4008		03.12 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
PEUGEOT	1007	A08	04.05 - 02.11	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
PEUGEOT	106	S1	09.91 - 04.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
PEUGEOT	106	S2	07.95 - 09.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
PEUGEOT	106	S2	10.99 - 05.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
PEUGEOT	107	B0	06.05 - 12.14	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	
PEUGEOT	2008 II	UD, US, UY, UK	08.19 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	16
PEUGEOT	205 Pickup		05.85 - 09.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	18
PEUGEOT	206 CC	T1	09.00 - 03.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
PEUGEOT	206 SW	T1	03.02 - 12.06	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
PEUGEOT	206+	T3	03.09 - 05.13	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
PEUGEOT	207	A7	05.06 - 04.12	3M™ 至尊鍍膜水喉	F	A+1	26	16
PEUGEOT	207 CC	A7	03.07 - 06.15	3M™ 至尊鍍膜水喉	F	A+1	26	16
PEUGEOT	207 SW	A7	06.07 - 12.13	3M™ 至尊鍍膜水喉	F	A+1	26	16
PEUGEOT	207+	A7	11.12 - 06.15	3M™ 至尊鍍膜水喉	F	A+1	26	16
PEUGEOT	208 II	UB, UP, UW, UJ	06.19 →	3M™ 至尊鍍膜水喉	B+C	A+2	24	16
PEUGEOT	3008	T8	05.09 - 12.16	3M™ 至尊鍍膜水喉	B+C	A+2	30	28
PEUGEOT	3008 II	P84	07.16 →	3M™ 至尊鍍膜水喉	B	A+6	28	16
PEUGEOT	306	N3	01.93 - 04.97	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
PEUGEOT	306	N5	05.97 - 12.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
PEUGEOT	306	N5	01.99 - 10.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
PEUGEOT	306 Break	N5	05.97 - 03.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	306 Cabriolet	N3,N5	01.93 - 10.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	307	T5	10.04 - 05.05	3M™ 至尊鍍膜水撥	D	A+3	28	26
PEUGEOT	307	T6	06.05 - 08.07	3M™ 至尊鍍膜水撥	D	A+3	28	26
PEUGEOT	307	T5	08.00 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
PEUGEOT	307 Break/SW	T6	06.05 - 12.09	3M™ 至尊鍍膜水撥	D	A+3	28	26
PEUGEOT	307 Break/SW	T5	03.02 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
PEUGEOT	307 Break/SW	T5	10.04-05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	26
PEUGEOT	307 CC	T5	10.03 - 05.05	3M™ 至尊鍍膜水撥	D	A+3	28	24
PEUGEOT	307 CC	T6	06.05 - 03.09	3M™ 至尊鍍膜水撥	D	A+3	28	26
PEUGEOT	308	T7	09.07 - 06.13	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
PEUGEOT	308 CC	T7	03.09 - 04.15	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
PEUGEOT	308 II	T9	09.13 - 06.21	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
PEUGEOT	308 III	FB, FH, FP, F3, FM	07.21 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
PEUGEOT	308 SW	T7	05.08 - 01.14	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
PEUGEOT	308 SW	T7	05.08 - 01.14	3M™ 至尊鍍膜水撥	B+C	A+2	30	26
PEUGEOT	308 SW II	T9	03.14 - 06.21	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
PEUGEOT	308 SW III	FC, FJ, FR, F4, FN	07.21 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
PEUGEOT	4007	I3	09.07 - 11.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
PEUGEOT	406	D8	10.95 - 03.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
PEUGEOT	406	D9	04.99 - 06.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
PEUGEOT	406 Break	D8,D9	10.96 - 06.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
PEUGEOT	406 Coupé	D8,D9	03.97 - 02.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
PEUGEOT	407	D2	05.04 - 02.11	3M™ 至尊鍍膜水撥	F	A+1	28	28
PEUGEOT	407 Coupé	D2	10.05 - 12.11	3M™ 至尊鍍膜水撥	F	A+1	28	28
PEUGEOT	407 SW	D2	05.04 - 02.11	3M™ 至尊鍍膜水撥	F	A+1	28	28
PEUGEOT	408 II	FP, F3	07.22 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
PEUGEOT	5008	T8	09.09 - 12.17	3M™ 至尊鍍膜水撥	B+C	A+2	30	28
PEUGEOT	5008 II	P87	01.17 →	3M™ 至尊鍍膜水撥	B	A+6	28	16
PEUGEOT	508 II	FB, FH, F3	09.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
PEUGEOT	508 RXH		09.11 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	26
PEUGEOT	508 SW		05.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
PEUGEOT	508 SW		10.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	26
PEUGEOT	605	Y30	06.89 - 05.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	22
PEUGEOT	806	U60	06.94 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
PEUGEOT	807	V2	06.02 - 07.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	26
PEUGEOT	807	V2	08.05 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	26
PEUGEOT	Blipper	A9	02.08 →	3M™ 至尊鍍膜水撥	E	A+4	26	19
PEUGEOT	Boxer	U9	06.06 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	22
PEUGEOT	Boxer	U3	02.94 - 02.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	Boxer	U5	02.02 - 05.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	Expert	K0	03.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
PEUGEOT	Expert	K0	03.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
PEUGEOT	Expert	U64	09.95 - 01.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
PEUGEOT	Expert	G9	02.07 - 12.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
PEUGEOT	ION		10.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	
PEUGEOT	P 4		10.86 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	14	14
PEUGEOT	Partner	B9	05.08 - 12.18	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
PEUGEOT	Partner	K9	09.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
PEUGEOT	Partner	M4	07.96 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	Partner	M5	09.02 - 10.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	Ranch	M4	07.97 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PEUGEOT	RCZ	T75	01.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	26
PEUGEOT	Rifter	K9	07.18 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
PEUGEOT	Traveller	K0	3.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
PEUGEOT	Traveller	K0	3.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
PORSCHE	968		08.91 - 11.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
PORSCHE	911	991	11.11 →	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	911	992	11.18 →	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	911	993	09.93 - 08.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	16
PORSCHE	911	996	09.97 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PORSCHE	911	996T, GT2,3	06.00 - 09.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PORSCHE	911	997, 997GT3	08.04 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PORSCHE	Boxster	981	04.12 - 08.16	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	Boxster	718	03.16 →	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	Boxster	986,987	10.96 - 09.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PORSCHE	Cayenne	9YA	09.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	21
PORSCHE	Cayenne	9PA	09.02 - 01.07	3M™ 至尊鍍膜水撥	F	A+1	26	26
PORSCHE	Cayenne	9PA	02.07 - 08.10	3M™ 至尊鍍膜水撥	F	A+1	26	26
PORSCHE	Cayenne	92A	09.10 →	3M™ 至尊鍍膜水撥	F	A+1	26	26
PORSCHE	Cayenne Coupe	9YB	01.19 →	3M™ 至尊鍍膜水撥	B	A+6	26	21
PORSCHE	Cayman	981C	03.13 - 08.16	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	Cayman	718C	09.16 →	3M™ 至尊鍍膜水撥	B	A+6	21	22
PORSCHE	Cayman	987C	11.05 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
PORSCHE	Macan	95B	03.14 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
PORSCHE	Panamera	971	09.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
PORSCHE	Panamera	970	09.13 - 10.16	3M™ 至尊鍍膜水撥	B	A+6	26	19
PORSCHE	Panamera	970	03.09 - 08.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
PORSCHE	Panamera Sport Turismo	971	03.17 →	3M™ 至尊鍍膜水撥	B	A+6	24	21
PORSCHE	Taycan	Y1A	05.19 →	3M™ 至尊鍍膜水撥	B	A+6	24	20

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
RENAULT	11	B37	01.85 - 03.95	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	16	16
RENAULT	19	X53	09.88 - 12.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	5		03.90 - 12.96	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
RENAULT	9	L42	01.85 - 12.95	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	16	16
RENAULT	Alaskan	[U3]	11.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
RENAULT	Arkana	LCM	08.19 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Austral		07.22 →	3M™ 至尊鏡膜水撥	B+C	A+2	26	19
RENAULT	Avantime	XEO	09.01 - 12.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
RENAULT	Captur	J5	03.16 →	3M™ 至尊鏡膜水撥	H	請與經銷商聯絡	26	14
RENAULT	Captur	J5	01.13 - 02.16	3M™ 至尊鏡膜水撥	E	A+4	26	14
RENAULT	Captur II		01.20 →	3M™ 至尊鏡膜水撥	B	A+6	26	14
RENAULT	Clio I	X57	03.94 - 02.98	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Clio II	BB./CB./SB.	03.98 - 05.09	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	18
RENAULT	Clio II (Campus)	BB./CB./SB.	06.09 - 12.15	3M™ 至尊鏡膜水撥	E	A+4	20	18
RENAULT	Clio III	BR./CR	06.05 - 05.07	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Clio III	BR./CR	06.07 - 12.15	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Clio III Grandtour	KR	08.07 →	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Clio IV	BH	05.12 →	3M™ 至尊鏡膜水撥	E	A+4	26	14
RENAULT	Clio IV Grandtour	KH	11.12 →	3M™ 至尊鏡膜水撥	E	A+4	26	14
RENAULT	Dokker	FE./FK	01.15 →	3M™ 至尊鏡膜水撥	H	請與經銷商聯絡	22	16
RENAULT	Duster	HS	12.16 →	3M™ 至尊鏡膜水撥	H	請與經銷商聯絡	24	18
RENAULT	Duster	HM	01.18 →	3M™ 至尊鏡膜水撥	E	A+4	22	19
RENAULT	Duster	HS	10.14 - 11.16	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Duster	HS	10.14 - 11.16	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Duster	HS	10.11 - 09.14	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Duster	HS	10.11 - 09.14	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Espace II	J63	01.91 - 09.96	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
RENAULT	Espace III	JE0	10.96 - 10.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	18
RENAULT	Espace IV	JK,JKO	11.02 - 12.15	3M™ 至尊鏡膜水撥	F	A+1	30	26
RENAULT	Espace V	JR	04.15 →	3M™ 至尊鏡膜水撥	B+C	A+2	30	28
RENAULT	Espace VI		05.23 →	3M™ 至尊鏡膜水撥	B+C	A+2	26	19
RENAULT	Express, Extra, Rapid	F40	09.94 - 10.97	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	18	18
RENAULT	Fluence	L3B	11.09 →	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Grand Scénic II	JM.	12.04 - 04.09	3M™ 至尊鏡膜水撥	E	A+4	26	22
RENAULT	Grand Scénic IV		11.16 →	3M™ 至尊鏡膜水撥	B+C	A+2	30	28
RENAULT	Kadjar	HL	06.15-04.17	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
RENAULT	Kadjar	HL	05.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	19
RENAULT	Kangoo I	FC./KC.	10.97 - 12.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Kangoo II	FW./KW.	01.08 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Koleos	HY.	09.08 →	3M™ 至尊鏡膜水撥	D	A+3	24	19
RENAULT	Koleos	HC	09.17 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	16
RENAULT	Laguna I	B56; 556	01.94 - 03.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Laguna I Grandtour	A56; K56; 556	02.95 - 02.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Laguna II	BG.	03.01 - 09.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
RENAULT	Laguna II Grandtour	KG.	03.01 - 09.07	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	20
RENAULT	Laguna III	BT.	07.07 →	3M™ 至尊鏡膜水撥	E	A+4	26	16
RENAULT	Laguna III Coupé	DT.	02.08 →	3M™ 至尊鏡膜水撥	E	A+4	26	16
RENAULT	Laguna III Grandtour	KT.	07.07 →	3M™ 至尊鏡膜水撥	E	A+4	26	16
RENAULT	Latitude		09.10 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	16
RENAULT	Logan	LS	07.04 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Logan II	L8	04.15 →	3M™ 至尊鏡膜水撥	E	A+4	22	19
RENAULT	Logan II	L8	08.12 - 03.15	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Logan MCV	KS/FS	01.07 - 12.13	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	20	20
RENAULT	Master I		09.80 - 09.97	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
RENAULT	Master II	X70	10.97 - 04.10	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	24
RENAULT	Master III		02.10 →	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	26	26
RENAULT	Mégane E-TECH SUB		11.21 →	3M™ 至尊鏡膜水撥	B+C	A+2	26	16
RENAULT	Mégane I	X64	01.96 - 10.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane I Cabrio	X64	09.96 - 09.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane I Classic	X64	09.96 - 09.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane I Coupé	X64	01.96 - 10.02	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane I Grandtour	X64	07.98 - 10.01	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane I Grandtour	X64	11.01 - 09.03	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	22	20
RENAULT	Mégane II	LM	02.06 - 10.09	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane II	LM	09.02 - 01.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Mégane II Hatchback	BM./CM./GM./SM.	02.06 - 10.08	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane II Hatchback	BM./CM./GM./SM.	11.02 - 01.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Mégane II Cabrio	EM	02.06 - 03.10	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane II Cabrio	EM	10.03 - 01.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Mégane II Grandtour	KM.	02.06 - 05.09	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane II Grandtour	KM.	10.03 - 01.06	3M™ 極致鏡膜水撥	A	極致鏡膜水撥	24	18
RENAULT	Mégane III CC	EZ	10.10 →	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Mégane III Coupé	DZ	01.09 →	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Mégane III Grandtour	KZ	06.09 - 12.15	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Mégane III Hatchback	BZ	11.08 →	3M™ 至尊鏡膜水撥	E	A+4	24	16
RENAULT	Mégane IV	B9	12.15 →	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane IV Grand Coupe	LV	02.17 →	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Mégane IV Grandtour	K9	12.15 →	3M™ 至尊鏡膜水撥	E	A+4	24	18
RENAULT	Modus	FP./JP.	06.04 - 05.05	3M™ 至尊鏡膜水撥	F	A+1	28	26
RENAULT	Modus	FP./JP.	06.05 - 12.15	3M™ 至尊鏡膜水撥	F	A+1	28	26

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋備)	尺寸(英寸)
RENAULT	Safrane	B54	04.92 - 01.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
RENAULT	Safrane	B54	02.99 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	24
RENAULT	Sandero I	B5	12.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
RENAULT	Sandero II	B8	04.15 →	3M™ 至尊鍍膜水撥	E	A+4	22	19
RENAULT	Sandero II	B8	12.14 - 03.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
RENAULT	Scénic I	JA	01.96 - 04.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
RENAULT	Scénic I	JA	03.00 - 04.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
RENAULT	Scénic II	JM	12.04 - 04.09	3M™ 至尊鍍膜水撥	E	A+4	26	22
RENAULT	Scénic III	JZ	05.09 - 12.16	3M™ 至尊鍍膜水撥	E	A+4	30	26
RENAULT	Scénic IV		11.16 →	3M™ 至尊鍍膜水撥	B+C	A+2	30	28
RENAULT	Symbol	LU	10.08 →	3M™ 至尊鍍膜水撥	E	A+4	24	16
RENAULT	Symbol	LB	04.15 →	3M™ 至尊鍍膜水撥	E	A+4	22	19
RENAULT	Symbol	LB	10.99 - 10.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
RENAULT	Symbol	LB	03.13 - 03.15	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
RENAULT	Talisman		12.15 →	3M™ 至尊鍍膜水撥	E	A+4	24	18
RENAULT	Talisman Grandtour		03.16 →	3M™ 至尊鍍膜水撥	E	A+4	24	18
RENAULT	Thalia	LU	10.08 →	3M™ 至尊鍍膜水撥	E	A+4	24	16
RENAULT	Thalia	LB	10.99 - 10.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
RENAULT	Trafic I		09.80 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
RENAULT	Trafic II	EL/FL/JL	05.01 - 12.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
RENAULT	Trafic III	EG/FG/JG	05.14 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
RENAULT	Twingo I	CO/SO	03.93 - 05.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	
RENAULT	Twingo II	CN; CN/GN	04.07 - 12.15	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
RENAULT	Twingo III	X07	12.15 →	3M™ 至尊鍍膜水撥	E	A+4	20	14
RENAULT	Twingo III	X07	09.14 - 11.15	3M™ 至尊鍍膜水撥	E	A+4	20	14
RENAULT	Twizy	MA	03.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	
RENAULT	Vel Satis	BJ	04.02 - 12.09	3M™ 至尊鍍膜水撥	F	A+1	30	26
RENAULT	Wind		04.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	16
RENAULT	ZOE	BF	01.13 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	14
ROVER	25		02.00 - 09.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
ROVER	25		10.04 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
ROVER	45		02.00 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
ROVER	75		01.99 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
ROVER	100 Metro		05.90 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
ROVER	100 Metro Cabrio		09.90 - 10.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
ROVER	75 Tourer		01.01 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
ROVER	Serie 200		10.89 - 03.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
ROVER	Serie 400		09.91 - 03.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
ROVER	Serie 400 Coupé		01.97 - 12.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
ROVER	Serie 400 Tourer		09.91 - 03.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
ROVER	Serie 600		04.93 - 09.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
ROVER	Serie 800		10.91 - 09.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
ROVER	Streetwise		09.03 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
SMART (MCC)	Forfour	453	11.14 →	3M™ 至尊鍍膜水撥	E	A+4	20	14
SMART (MCC)	Forfour	454	01.04 - 06.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
SMART (MCC)	Fortwo Cabrio	451	04.07 →	3M™ 至尊鍍膜水撥	D	A+3	22	21
SMART (MCC)	Fortwo Cabrio	453	09.15 →	3M™ 至尊鍍膜水撥	E	A+4	20	14
SMART (MCC)	Fortwo Cabrio	450	02.04 - 03.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SMART (MCC)	Fortwo Coupé	451	04.07 →	3M™ 至尊鍍膜水撥	D	A+3	22	21
SMART (MCC)	Fortwo Coupé	453	11.14 →	3M™ 至尊鍍膜水撥	E	A+4	20	14
SMART (MCC)	Fortwo Coupé	450	02.04 - 03.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SMART (MCC)	Roadster	452	04.03 - 11.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
SMART (MCC)	Roadster Coupé	452	04.03 - 11.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
SMART (MCC)	Smart Cabrio	Smart Cabrio	03.00 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SMART (MCC)	Smart Coupé	450	07.98 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SSANGYONG	Actyon		10.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
SSANGYONG	Actyon Sports		03.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
SSANGYONG	Chairman		09.03 - 01.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	
SSANGYONG	Korando	CK	07.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SSANGYONG	Korando	KJ	07.96 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
SSANGYONG	Korando C		02.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SSANGYONG	Kyron		05.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
SSANGYONG	Musso	MJ	07.93 - 12.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
SSANGYONG	Rexton		09.01 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SSANGYONG	Rexton II		10.08 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SSANGYONG	Rexton W		06.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
SSANGYONG	Rodius		08.04 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
SSANGYONG	Rodius II		05.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SSANGYONG	Tivoli		07.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SSANGYONG	XLV		04.16 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SUBARU	BRZ	Z10	01.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
SUBARU	BRZ	ZD8	10.21 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
SUBARU	Forester	SK	04.18 →	3M™ 至尊鍍膜水撥	G	B+8	26	16
SUBARU	Forester	S13	11.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
SUBARU	Forester	S12	12.07 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	18
SUBARU	Forester	SF	01.97 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
SUBARU	Forester	SG	06.02 - 05.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
SUBARU	Forester	SG	06.03 - 05.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
SUBARU	Forester	SG	06.05 - 11.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19

車廠品牌	車款	型號 MODEL CODE	年份	適用水喉款式	水喉臂及接頭款式	3M™ 水喉接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(呎者)
SUBARU	Impreza	G12/G22	06.07 - 12.11	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
SUBARU	Impreza	G13/G23	10.11 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Impreza Kombi	GD,GG	10.00 - 01.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
SUBARU	Impreza Kombi	GD,GG	02.04 - 06.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
SUBARU	Impreza Kombi	GC,GF	01.93 - 07.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Impreza Kombi	GC,GF	08.98 - 09.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Impreza Outback	GD,GG	10.00 - 06.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
SUBARU	Impreza Sedan	GD,GG	10.00 - 06.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
SUBARU	Impreza Sedan	G12	06.07 - 12.11	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	16
SUBARU	Impreza Sedan	G13	10.11 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Impreza Sedan	GC,GF	01.93 - 09.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Impreza Sports Wagon		11.92 - 07.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Justy	G3X	09.03 - 08.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	16
SUBARU	Justy	M3	09.07 - 12.10	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	16
SUBARU	Justy	KA,KD	05.87 - 10.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	18
SUBARU	Justy	MA	10.95 - 09.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Justy	MS	10.96 - 08.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Legacy	BN, BS	01.15 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Legacy	BC/BF/BJ	01.89 - 12.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUBARU	Legacy	BL/BP	07.03 - 05.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
SUBARU	Legacy	B14	06.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
SUBARU	Legacy Kombi	BL/BP	07.03 - 05.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
SUBARU	Legacy Kombi	BD/BG	01.94 - 11.98	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
SUBARU	Legacy Kombi	B14	06.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
SUBARU	Legacy Kombi	BE/BH	10.98 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
SUBARU	Legacy Outback	BL/BP	07.03 - 05.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	18
SUBARU	Legacy Outback	BD/BG	01.96 - 12.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
SUBARU	Legacy Outback	BE/BH	10.98 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
SUBARU	Legacy Sedan	BD/BG	01.94 - 03.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
SUBARU	Legacy Sedan	BE/BH	10.98 - 06.03	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
SUBARU	Levorg	VM	06.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Outback	B15	03.15 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Outback	BT	09.19 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	Outback	B14	06.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	19
SUBARU	SVX		09.92 - 12.96	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	20
SUBARU	Trezia		11.10 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	28	
SUBARU	Tribeca	B9	04.06 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	20
SUBARU	Vivio	R13	08.93 - 04.00	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	14
SUBARU	WRX	V10	05.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUBARU	XV	GT	04.17 →	3M™ 至尊鍍膜水喉	G	B+8	26	16
SUBARU	XV	G33	08.11 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUZUKI	Across	ASZ	06.20 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	16
SUZUKI	Alto	AMF	12.08 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	14
SUZUKI	Alto	MA	02.02 - 12.06	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	16
SUZUKI	Alto	EF	10.94 - 02.02	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	16
SUZUKI	Baleno	WB32,WB42	03.16 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Baleno Hatchback		04.95 - 09.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Baleno Sedan		04.95 - 09.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Baleno Wagon		08.96 - 09.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Carry	ED	10.94 - 03.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	14	14
SUZUKI	Carry	FD	03.99 - 03.09	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	16	16
SUZUKI	Carry	ED	10.85 - 03.99	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	16	16
SUZUKI	Celerio		10.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	14
SUZUKI	Escudo		05.05 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
SUZUKI	Grand Vitara		03.98 - 09.05	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
SUZUKI	Grand Vitara	JT	10.05 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
SUZUKI	Grand Vitara Cabrio		03.98 - 03.08	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	19
SUZUKI	Ignis	MF	10.16 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
SUZUKI	Ignis Hatchback		10.00 - 12.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	19	18
SUZUKI	Jimny	GJ	10.18 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	16	16
SUZUKI	Jimny	FJ	10.98 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	18	16
SUZUKI	Kizashi		10.09 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	24	20
SUZUKI	Liana Hatchback		03.01 - 04.08	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	19
SUZUKI	Liana Sedan		04.02 - 12.07	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	19
SUZUKI	S-CROSS	AKK414	01.22 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	14
SUZUKI	Splash	ASB	01.08 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	22	16
SUZUKI	Swace	AMZ	10.20 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	28	14
SUZUKI	Swift	Z	11.14 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Hatchback	EA	01.89 - 09.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Hatchback	MA	03.96 - 12.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Hatchback	MZ/EZ	11.04 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Hatchback	AZH,AZG	09.10 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Hatchback	A2L	05.17 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	19
SUZUKI	Swift Sedan	EA	01.91 - 09.95	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Sedan	MA	03.96 - 12.04	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	Swift Sedan	Z	11.04 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	20	18
SUZUKI	SX4		07.06 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	14
SUZUKI	SX4 Hatchback		05.06 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	14
SUZUKI	SX4 S-Cross		10.13 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	14
SUZUKI	SX4 Sedan		07.07 →	3M™ 極致鍍膜水喉	A	極致鍍膜水喉	26	14

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(司機)	尺寸(乘客)
SUZUKI	Vitara	LY	02.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
SUZUKI	Vitara		09.95 - 03.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
SUZUKI	Vitara	ET	01.95 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
SUZUKI	Vitara Cabrio	ET	01.95 - 03.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
SUZUKI	Wagon R+	EM	10.96 - 05.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
SUZUKI	Wagon R+	MM	05.00 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
SUZUKI	X-90		09.95 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TESLA	Model 3	5YJ3	01.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
TESLA	Model S		08.11 →	3M™ 至尊鍍膜水撥	B+C	A+2	28	18
TESLA	Model Y	5YJY	03.19 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
TESLA	Roadster		08.06 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	
TOYOTA	Alphard	H3	01.15 →	3M™ 至尊鍍膜水撥	G	B+8	30	14
TOYOTA	Alphard	TH2,NH2,GH2	01.08-12.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Auris	E18	10.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Auris	E15,JTN	10.06 - 08.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Auris	E15,NMT,S81	02.07 - 10.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Auris Touring Sports	E18	07.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Avalon		09.99 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Avensis	T27	11.08 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
TOYOTA	Avensis	T25	01.03 - 11.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Avensis	T22	10.97 - 01.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Avensis Liftback	T25	01.03 - 11.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Avensis Liftback	T22	10.97 - 01.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Avensis Verso	M2	05.01 - 11.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Avensis Wagon	T27	11.08 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
TOYOTA	Avensis Wagon	T25	01.03 - 11.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Avensis Wagon	T22	10.97 - 01.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Aygo	B4	05.14 →	3M™ 至尊鍍膜水撥	D	A+3	26	
TOYOTA	Aygo		02.05 - 12.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	
TOYOTA	Aygo X	B7	03.22 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Camry	V1	06.91 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Camry	V2	06.96 - 08.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Camry	V3	08.01 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
TOYOTA	Camry	V5	08.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
TOYOTA	Camry	V3	08.99 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
TOYOTA	Camry	V4,V40	01.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
TOYOTA	Camry	V7	04.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	Camry Wagon	V1	03.92 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Carina E Liftback	T19	02.92 - 10.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Carina E Sedan	T19	02.92 - 10.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Carina E Wagon	T19	11.92 - 10.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Celica Cabrio	T20	08.94 - 05.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	Celica Coupé	T23	08.99 - 09.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Celica Liftback	T20	11.93 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	C-HR	X1	10.16 →	3M™ 至尊鍍膜水撥	G	B+8	26	16
TOYOTA	Conquest	Carri	11.98 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
TOYOTA	Corolla	E14,E15	11.06 - 04.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Corolla	E18	06.13 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Corolla	E21	02.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Corolla	E12	10.02 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Corolla	E10	05.92 - 08.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla	E11	05.95 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla	E12	08.00 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
TOYOTA	Corolla Hatchback	E21	10.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Corolla Hatchback	E12	11.01 - 11.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Corolla Hatchback	E10	05.92 - 04.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Hatchback	E11	05.97 - 07.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Hatchback	E12,S81	11.01 - 12.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
TOYOTA	Corolla Hatchback	E12,JTD	09.02 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
TOYOTA	Corolla Liftback	E10	05.92 - 05.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Liftback	E11	05.97 - 11.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Sedan	E10	05.92 - 08.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Sedan	E11	05.95 - 08.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Verso	E12	09.01 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Corolla Verso	R1	02.04 - 02.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Corolla Wagon	E12	08.00 - 02.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Corolla Wagon	E10	05.92 - 04.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Corolla Wagon	E11	04.97 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Cressida Sedan	X8	08.88 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Dyna		01.97 - 04.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Dyna		10.00 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
TOYOTA	Echo		09.99 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
TOYOTA	Fortuner		01.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	GT86		04.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
TOYOTA	Harrier		12.97 - 02.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
TOYOTA	Harrier		02.03 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
TOYOTA	Hiace	LXH,RCH	08.95 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Hiace	LXH,RCH	08.96 - 05.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
TOYOTA	Hiace	KLH	08.01 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
TOYOTA	Hiace Van	LH,LXH,ZH	08.96 - 02.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
TOYOTA	Hiace Van	LH,ZH	08.89 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Hiace Wagon	LH,ZH	08.89 - 08.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Hiace Wagon	LH,ZH	08.96 - 02.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
TOYOTA	Highlander	GSU7, AXUH7	12.19 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	18
TOYOTA	Highlander		09.00 - 08.07	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	19
TOYOTA	Highlander		09.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	Hilux	N12,N13	06.15 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
TOYOTA	Hilux	N5/N6	08.84 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Hilux	N16/N17	08.97 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Hilux	Raider	05.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	Hilux	N15,N25,N26,N35	07.05 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	Hilux Pickup	N8...19	08.88 - 08.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Hilux Vigo	TGN16, TGN26	08.04 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	iQ		11.08 - 05.14	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Land Cruiser	J7	11.84 - 08.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
TOYOTA	Land Cruiser	J8	01.90 - 01.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
TOYOTA	Land Cruiser	J9	04.96 - 12.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	18
TOYOTA	Land Cruiser	J15	08.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	Land Cruiser	J12	09.02 - 08.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
TOYOTA	Land Cruiser	J10	01.98 - 07.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	22
TOYOTA	Land Cruiser	J20	09.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	22
TOYOTA	Land Cruiser Prado	J9	04.96 - 09.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	18
TOYOTA	Land Cruiser Prado	J15	09.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	Land Cruiser Prado	J12	08.04 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
TOYOTA	Mirai	JPD2	11.20 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	MR2 Cabrio	W3	12.99 - 05.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
TOYOTA	New Altis		07.10 - 12.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Noah/ Voxy	R70	07-13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Noah/ Voxy	R80	14-21	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Noah/ Voxy	R90	21-	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Paseo	L5	08.95 - 08.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Picnic		09.96 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Picnic		08.03 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Previa		02.00 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	18
TOYOTA	Prius	W50	11.15 →	3M™ 至尊鍍膜水撥	G	B+8	28	16
TOYOTA	Prius	W6	01.23 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	14
TOYOTA	Prius	W11	09.00 - 08.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	Prius	W20	09.03 - 03.09	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Prius	W30,W35	04.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Prius +	W40	03.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	14
TOYOTA	Proace	K0	02.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
TOYOTA	Proace	K0	02.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
TOYOTA	Proace	G9	06.13 - 01.16	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	20
TOYOTA	Proace Verso	K0	02.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
TOYOTA	Proace Verso	K0	02.16 →	3M™ 至尊鍍膜水撥	E	A+4	26	20
TOYOTA	RAV4	A3	11.05 - 11.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
TOYOTA	RAV4	A4	12.12 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	RAV4	A5	11.18 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	RAV4	A1	04.94 - 08.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	RAV4	A2	05.00 - 01.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
TOYOTA	RAV4 Cabrio	A1	11.95 - 08.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Sequoia		09.07 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
TOYOTA	Sienna		09.06 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	19
TOYOTA	Sienna		01.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
TOYOTA	Solara		09.03 - 08.08	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	19
TOYOTA	Solara		09.98 - 08.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	20
TOYOTA	Starlet	P8	12.89 - 01.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Starlet	P9	01.96 - 07.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
TOYOTA	Supra	DB	03.19 →	3M™ 至尊鍍膜水撥	B+C	A+2	22	21
TOYOTA	Tundra		11.06 →	3M™ 至尊鍍膜水撥	D	A+3	26	22
TOYOTA	Urban Cruiser	P1	01.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
TOYOTA	Venza		02.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	22
TOYOTA	Verso	R2	02.09 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	26	16
TOYOTA	Verso-S		11.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	
TOYOTA	Yaris	P9,JTD	08.05 - 07.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
TOYOTA	Yaris	P9,VNK	11.05 - 07.11	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	14
TOYOTA	Yaris	P1	01.99 - 08.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
TOYOTA	Yaris	P13	07.11 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	
TOYOTA	Yaris (FR)	P1	01.01 - 08.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
TOYOTA	Yaris Verso	P2	08.99 - 11.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
TOYOTA	Yaris Verso	P2	12.02 - 09.05	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	22	16
VOLKSWAGEN	Amarok	2H	05.12 - 10.16	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Amarok	S6, S7	06.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Amarok	2H	09.10 - 04.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Arteon	3H7	03.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
VOLKSWAGEN	Beetle	5C1,5C2	04.11 →	3M™ 至尊鍍膜水撥	B	A+6	21	21
VOLKSWAGEN	Beetle Cabriolet	5C7,5C8	01.13 →	3M™ 至尊鍍膜水撥	B	A+6	21	21
VOLKSWAGEN	Bora	1J2	06.02 - 05.05	3M™ 至尊鍍膜水撥	F	A+1	21	18
VOLKSWAGEN	Bora	1J2	09.98 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Bora Variant	1J6	06.02 - 05.05	3M™ 至尊鍍膜水撥	F	A+1	21	18

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
VOLKSWAGEN	Bora Variant	1J6	09.98 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Caddy	SBB, SBJ	09.20 →	3M™ 至尊鍍膜水撥	B	A+6	28	16
VOLKSWAGEN	Caddy	SA	06.17 →	3M™ 至尊鍍膜水撥	B	A+6	24	18
VOLKSWAGEN	Caddy	2K	11.06 - 08.10	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
VOLKSWAGEN	Caddy	2C	09.10 - 05.15	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
VOLKSWAGEN	Caddy	SA	05.15 - 05.17	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
VOLKSWAGEN	Caddy	2K	02.04 - 10.06	3M™ 至尊鍍膜水撥	F	A+1	24	18
VOLKSWAGEN	Caddy	2K	02.04 - 08.10	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	Caddy	9K9	11.95 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
VOLKSWAGEN	Caddy Pickup	9U7	06.96 - 12.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
VOLKSWAGEN	California T4	70,7D	09.90 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	California T5	7E	06.13 - 08.15	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	California T5	7E	09.09 - 05.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	California T5	7H	02.03 - 11.09	3M™ 至尊鍍膜水撥	F	A+1	24	24
VOLKSWAGEN	California T6	SG	04.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Caravelle T4	70,7D	09.90 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Caravelle T5	7E	06.13 - 08.15	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Caravelle T5	7H	02.03 - 11.09	3M™ 至尊鍍膜水撥	F	A+1	24	24
VOLKSWAGEN	Caravelle T5	7E	09.09 - 05.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Caravelle T6	SG	04.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	CC	358	11.11.12.16	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Corrado	50	09.88 - 07.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
VOLKSWAGEN	Crafter	2E	04.06 - 12.16	3M™ 至尊鍍膜水撥	D	A+3	26	24
VOLKSWAGEN	Crafter	SY, SZ	09.16 →	3M™ 至尊鍍膜水撥	B	A+6	28	26
VOLKSWAGEN	e-Golf	BE1	03.14 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Eos	1F7,1F8	05.06 - 08.15	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	e-up!	BL1	07.13 - 06.16	3M™ 至尊鍍膜水撥	B	A+6	24	16
VOLKSWAGEN	e-up!	BL2	08.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
VOLKSWAGEN	Eurovan	70	09.91 - 08.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Fox	521	04.05 - 12.12	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	14
VOLKSWAGEN	Golf Alltrack	BAS, BV5	11.14 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Golf Alltrack	CG5	11.20 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Golf II	19,1G1,1G4	02.86 - 11.92	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	18	18
VOLKSWAGEN	Golf III	1H1	11.91 - 12.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf III Cabriolet	1.00E+07	09.93 - 04.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf III Variant	1H5	07.93 - 02.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf IV	1J1	06.02 - 06.05	3M™ 至尊鍍膜水撥	F	A+1	21	18
VOLKSWAGEN	Golf IV	1J1	10.97 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf IV Cabriolet	1.00E+07	04.98 - 06.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf IV Variant	1J5	06.02 - 06.06	3M™ 至尊鍍膜水撥	F	A+1	21	18
VOLKSWAGEN	Golf IV Variant	1J5	05.99 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Golf Plus	5M1	01.05 - 05.09	3M™ 至尊鍍膜水撥	F	A+1	28	28
VOLKSWAGEN	Golf Plus	521	01.09 - 02.14	3M™ 至尊鍍膜水撥	F	A+1	28	28
VOLKSWAGEN	Golf Plus	5M1,521	01.05 - 02.14	3M™ 至尊鍍膜水撥	F	A+1	28	28
VOLKSWAGEN	Golf Sportsvan	AM1	02.14 →	3M™ 至尊鍍膜水撥	B	A+6	28	16
VOLKSWAGEN	Golf V	1K1	11.05 - 11.08	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Golf V	1K1	10.03 - 11.08	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	Golf V	1K1	10.03 - 10.05	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	Golf V Variant	1K5	05.07 - 07.09	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Golf VI	5K1	10.08 - 11.12	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Golf VI Cabriolet	511	03.11 - 05.16	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Golf VI Variant	AJ5	06.09 - 04.13	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Golf VII	5G1, BQ1	08.12 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Golf VII Variant	BAS, BV5	04.13 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Golf VIII	CD1	07.19 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Golf VIII Variant	CG5	07.19 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	ID.3	E11, E12	11.19 →	3M™ 至尊鍍膜水撥	B+C	A+2	30	30
VOLKSWAGEN	ID.4	E21	05.20 →	3M™ 至尊鍍膜水撥	B+C	A+2	28	18
VOLKSWAGEN	ID.5	E39	07.21 →	3M™ 至尊鍍膜水撥	B+C	A+2	28	18
VOLKSWAGEN	ID.7	ED2	06.23 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Jetta	162,163,AV2	02.11 →	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Jetta	1K2	12.05 - 10.10	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Jetta	1K2	01.05 - 10.10	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	Jetta	1K2	01.05 - 11.05	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	LT	2D,2H	05.96 - 04.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Lupo	6X1	06.03 - 07.05	3M™ 至尊鍍膜水撥	F	A+1	19	18
VOLKSWAGEN	Lupo	6X1	06.98 - 05.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Maggiolino (Beetle)	5C1	04.11 - 06.16	3M™ 至尊鍍膜水撥	B	A+6	21	21
VOLKSWAGEN	Multivan T4	70,7D	09.90 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Multivan T5	7E	06.13 - 08.15	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Multivan T5	7H	02.03 - 11.09	3M™ 至尊鍍膜水撥	F	A+1	24	24
VOLKSWAGEN	Multivan T5	7E	09.09 - 05.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Multivan T6	SG	04.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	New Beetle	1C1,9C1	01.98 - 12.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	New Beetle Cabriolet	1Y7	01.03 - 10.10	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat	362	08.11 - 12.14	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Passat	3G2	08.14 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
VOLKSWAGEN	Passat	3C2	03.05 - 11.10	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Passat	362	08.10 - 11.11	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Passat	3B3	11.01 - 05.05	3M™ 至尊鍍膜水撥	F	A+1	21	19

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
VOLKSWAGEN	Passat	3B2	10.96 - 11.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat	3B3	10.00 - 10.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat	35I,3A2	04.88 - 03.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat Alltrack	3G5	05.15 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
VOLKSWAGEN	Passat Alltrack	365	01.12 - 12.14	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Passat CC	357	12.11 - 05.12	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Passat CC	357	05.08 - 11.11	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Passat Variant	365	08.11 - 12.14	3M™ 至尊鍍膜水撥	B	A+6	24	19
VOLKSWAGEN	Passat Variant	3G5	08.14 →	3M™ 至尊鍍膜水撥	B	A+6	26	19
VOLKSWAGEN	Passat Variant	3C5	08.05 - 11.10	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Passat Variant	365	08.10 - 11.11	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Passat Variant	3B6	11.01 - 05.05	3M™ 至尊鍍膜水撥	F	A+1	21	19
VOLKSWAGEN	Passat Variant	3B5	01.97 - 11.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat Variant	3B6	10.00 - 10.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Passat Variant	35I,3A5	04.88 - 03.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Phaeton	3D	05.02 →	3M™ 至尊鍍膜水撥	F	A+1	24	21
VOLKSWAGEN	Polo	6R1,6C1	06.09 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
VOLKSWAGEN	Polo	AW1	06.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Polo	9N3	05.05 - 12.09	3M™ 至尊鍍膜水撥	B+C	A+2	21	19
VOLKSWAGEN	Polo	9N1	06.02 - 06.05	3M™ 至尊鍍膜水撥	F	A+1	21	19
VOLKSWAGEN	Polo	6N1	10.94 - 12.99	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
VOLKSWAGEN	Polo	6N2	07.98 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	19	19
VOLKSWAGEN	Polo	9N1	09.01 - 05.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLKSWAGEN	Polo Classic	9N4	04.05 - 02.10	3M™ 至尊鍍膜水撥	B+C	A+2	21	19
VOLKSWAGEN	Polo Classic	6V2	11.95 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
VOLKSWAGEN	Polo Playa	9V4	10.98 - 10.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
VOLKSWAGEN	Polo Sedan	612, 614	09.10 →	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	16
VOLKSWAGEN	Polo Variant	6V5	05.97 - 09.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	18
VOLKSWAGEN	Scirocco	137I38	08.08 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	19
VOLKSWAGEN	Sharan	7N1,7N2	05.10 →	3M™ 至尊鍍膜水撥	B	A+6	28	16
VOLKSWAGEN	Sharan	7M9,7M6	06.01 - 03.10	3M™ 至尊鍍膜水撥	F	A+1	28	28
VOLKSWAGEN	Sharan	7M8	09.95 - 02.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	24
VOLKSWAGEN	Sharan	7M9,7M6	04.00 - 05.01	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	28	24
VOLKSWAGEN	Taigo	C51	09.21 →	3M™ 至尊鍍膜水撥	B	A+6	26	18
VOLKSWAGEN	Taro	7A	04.89 - 03.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	16	16
VOLKSWAGEN	T-Cross	C11	12.18 →	3M™ 至尊鍍膜水撥	B	A+6	24	18
VOLKSWAGEN	Tiguan	AD1	01.16 →	3M™ 至尊鍍膜水撥	B	A+6	26	22
VOLKSWAGEN	Tiguan	BW2	03.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	22
VOLKSWAGEN	Tiguan	5N1,5N2	11.07 →	3M™ 至尊鍍膜水撥	B+C	A+2	24	21
VOLKSWAGEN	Touareg	CR7	11.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	21
VOLKSWAGEN	Touareg	7LA,7L6	11.02 - 08.07	3M™ 至尊鍍膜水撥	F	A+1	26	26
VOLKSWAGEN	Touareg	7L6	06.07 - 05.10	3M™ 至尊鍍膜水撥	F	A+1	26	26
VOLKSWAGEN	Touareg	7P5,7P6	01.10 - 03.18	3M™ 至尊鍍膜水撥	F	A+1	26	26
VOLKSWAGEN	Touran	1T2	11.06 - 05.10	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
VOLKSWAGEN	Touran	1T1	02.03 - 11.06	3M™ 至尊鍍膜水撥	F	A+1	24	18
VOLKSWAGEN	Touran	5T1	05.15 →	3M™ 至尊鍍膜水撥	B	A+6	28	16
VOLKSWAGEN	Touran	1T3	05.10 - 05.15	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
VOLKSWAGEN	Touran	1T1,1T2	02.03 - 05.10	3M™ 至尊鍍膜水撥	F	A+1	24	19
VOLKSWAGEN	Transporter T4	70,7D	09.90 - 06.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLKSWAGEN	Transporter T5	7E	06.13 - 08.15	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	Transporter T5	7H,7J	02.03 - 11.09	3M™ 至尊鍍膜水撥	F	A+1	24	24
VOLKSWAGEN	Transporter T5	7E	09.09 - 05.13	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLKSWAGEN	Transporter T6	SF,SG	04.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	24
VOLKSWAGEN	T-Roc		07.17 →	3M™ 至尊鍍膜水撥	B	A+6	26	20
VOLKSWAGEN	Up!	121I22	12.11 →	3M™ 至尊鍍膜水撥	B	A+6	24	16
VOLKSWAGEN	Vento	1H2	11.91 - 12.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	19
VOLVO	440		09.88 - 07.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	460		03.90 - 07.97	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	480	E12	08.88 - 12.96	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	740		09.90 - 07.95	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	850		09.91 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	940		09.90 - 10.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	960		08.90 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	850 Kombi		09.91 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	C30		09.06 - 12.13	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	C30		10.06 - 07.10	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	C30		08.10 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	C40	539	10.21 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
VOLVO	C70 Coupé		01.97 - 07.02	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	C70 I Cabrio		02.98 - 03.06	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	C70 II Cabrio		03.06 - 12.13	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	EX30	416	06.23 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	16
VOLVO	S40 I		09.95 - 01.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	S40 II	P11	12.03 - 12.12	3M™ 至尊鍍膜水撥	F	A+1	26	20
VOLVO	S40 II [P11]		08.05 - 12.12	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	S40 II [P11]		12.03 - 08.05	3M™ 至尊鍍膜水撥	F	A+1	26	20
VOLVO	S60 Cross Country		08.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	S60 I		08.04 - 07.09	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	S60 I		11.00 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	S60 II		11.10 - 12.18	3M™ 至尊鍍膜水撥	B+C	A+2	26	20

車廠品牌	車款	型號 MODEL CODE	年份	適用水撥款式	水撥臂及接頭款式	3M™ 水撥接頭	英寸(Inch)	英寸(Inch)
							尺寸(吋機)	尺寸(乘客)
VOLVO	S70		01.97 - 07.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	S80 I		08.04 - 07.06	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	S80 I		08.98 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	S80 II		03.06 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	S90 I		01.97 - 05.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	S90 II		03.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
VOLVO	V40 Cross Country		01.13 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	V40 I		01.95 - 08.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	V40 II		09.12 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	V50		08.05 - 12.12	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	V50		04.04 - 12.12	3M™ 至尊鍍膜水撥	F	A+1	26	19
VOLVO	V50		04.04 - 07.05	3M™ 至尊鍍膜水撥	F	A+1	26	20
VOLVO	V60		06.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	V60		09.10 - 06.15	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	V60		06.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	V60 Cross Country		08.15 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	V70 I		01.97 - 03.00	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	V70 II		08.04 - 07.07	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	V70 II		03.00 - 07.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	V70 II		08.03 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	V70 II		03.00 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	V70 III		08.07 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	V90 Cross Country		02.17 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
VOLVO	V90 I		01.97 - 07.98	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	20	20
VOLVO	V90 II		03.16 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
VOLVO	XC40		12.17 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
VOLVO	XC60 I		03.09 - 07.10	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	XC60 I		08.10 - 07.17	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	XC60 II	246	03.17 →	3M™ 至尊鍍膜水撥	B+C	A+2	26	19
VOLVO	XC70 I		08.04 - 07.07	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	XC70 I		08.02 - 07.03	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	XC70 I		08.03 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	XC70 I		08.03 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	XC70 II		04.07 - 12.16	3M™ 至尊鍍膜水撥	B+C	A+2	26	20
VOLVO	XC90 I		08.04 - 07.06	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	XC90 I		08.06 - 07.10	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	XC90 I		08.10 - 07.16	3M™ 至尊鍍膜水撥	D	A+3	24	21
VOLVO	XC90 I		10.02 - 07.04	3M™ 極致鍍膜水撥	A	極致鍍膜水撥	24	20
VOLVO	XC90 II		06.15 →	3M™ 至尊鍍膜水撥	B	A+6	24	20
Zeekr	009		11.22→	3M™ 至尊鍍膜水撥	B+C	A+2	28	16
Zeekr	7X		09.24→	3M™ 至尊鍍膜水撥	B+C	A+2	24	18
Zeekr	X		04.23→	3M™ 至尊鍍膜水撥	B+C	A+2	24	16