

3M Science.
Applied to Life.™



Presenting

3M™ Clean Sanding System

Designed with technicians and shop owners in mind.

3M™ Clean Sanding System

Smarter. Faster. Cleaner.

A clean shop can mean less rework, better cycle times, and the peace of mind that you are doing what you can to improve the shop environment. For you, your technicians and your customers.

The 3M™ Clean Sanding System is a complete sanding solution for efficiently moving through your essential surface preparation and finishing work. The system includes our dust extractor, pneumatic and/or electric random orbital sanders, mobile workstation, wide selection of quality abrasives, and personal protective equipment.



3M™ Clean Sanding System Dust Extractors

Designed to reduce dust in the air from sanding for a cleaner workspace.

- Helps shops boost productivity and efficiency by helping to reduce rework and cleanup time.
- Compact and mobile. Designed for easy, flexible use around the shop.
- Compatible with pneumatic and/or electric sanders.
- Tech-friendly design including auto on/off, antistatic hose, rubber wheels, brake locks, and LED indicator lights.
- Available in 45 L and 30 L size

Part No.	Product Description	Quantity
33761	3M™ Dust Extractor, 45 Liter, 230V, Plug Type G, L Class	1 per box
33762	3M™ Dust Extractor, 45 Liter, 230V, Plug Type G, M Class	1 per box
33756	3M™ Dust Extractor, 30 Liter, 230V, Plug Type G, L Class	1 per box
33787	3M™ Dust Extractor, 30 Liter, 230V, Plug Type G, M Class	1 per box



3M™ Clean Sanding System Tools



Durable composite cover with soft grip material, providing comfort and long life.



Variable speed adjustment.



Thumb control designed to avoid accidental speed changes.



Integrated muffler system to reduce noise and protects the muffler from breakage.



3M™ Clean Sanding System Electric Tools

With electric power you can help increase mobility without the need for compressed air.



- Brushless motor requires less maintenance, no brushes to replace.
- Multihole back-up pad and shroud for effective dust extraction.
- Keep the area small with the 75 mm size.

Part No.	Product Description	Quantity
33802	3M™ Electric Random Orbital Sander, 150 mm (6 in), 2.5 mm (3/32) Orbit, 230V, Plug Type G	1 per box
33794	3M™ Electric Random Orbital Sander, 150 mm (6 in), 5 mm (3/16) Orbit, 230V, Plug Type G	1 per box
33808	3M™ Electric Random Orbital Sander, 75 mm (3 in), 2.5 mm (3/32) Orbit, 230V, Plug Type G	1 per box

3M™ Clean Sanding System Pneumatic Tools

Use 3M™ Precision Orbital - Pneumatic sanders to efficiently sand metal, paint, filler and primer for automotive collision repair.



- Recessed aluminum lever to reduce pinch points enhancing safety and ease of use.
- 75 mm size ideal for spot repair and finishing applications.



Part No.	Product Description	Quantity
33632	3M™ Pneumatic Precision Random Orbital Sander, 150 mm, 2.5 mm Orbit	1 per box
33633	3M™ Pneumatic Precision Random Orbital Sander, 150 mm, 5 mm Orbit	1 per box
33634	3M™ Pneumatic Precision Random Orbital Sander, 150 mm, 8 mm Orbit	1 per box
33797	3M™ Pneumatic Precision Random Orbital Sander, 75 mm, 2.5 mm Orbit	1 per box
38505	3M™ Pneumatic Precision Random Orbital Sander, 75 mm, 5 mm Orbit	1 per box
33796	3M™ Pneumatic Precision Orbital Sheet Sander, 198 × 70 mm	1 per box

Technical Details

3M™ Clean Sanding System Dust Extractors

Product				
Part Number	3376	33762	33756	33787
Container capacity	45 L	45 L	30 L	30 L
Dust Class	L Class	M Class	L Class	M Class
Operating Voltage and Frequency	230 VAC - 50/60 Hz	230 VAC - 50/60 Hz	230 VAC - 50/60 Hz	230 VAC - 50/60 Hz
Power/Tot Power (max)	1200 W - 3000 W	1200 W - 3000 W	1200 W - 3000 W	1200 W - 3000 W
Power at socket (max)	1800W	1800W	1800W	1800W
Air capacity (EN 60335-2-69)	165 m³/h	165 m³/h	165 m³/h	165 m³/h
Quick connect air coupling	2	1	1	1
Max compressed airflow	1450 l/min	1450 l/min	1450 l/min	1450 l/min
Vacuum level	215 hPA	215 hPA	215 hPA	215 hPA
Automatic Filter Cleaning	Yes	Yes	No	No
Noise level	70 dB (A)	70 dB (A)	70 dB (A)	70 dB (A)
Weight	13.5 kg	13.5 kg	10.2 kg	10.2 kg

3M™ Clean Sanding System Tools

Product									
Part Number	33808	33802	33794	33797	38505	33632	33633	33634	33796
Pad Diameter/ Size	75 mm	150 mm	150 mm	75 mm	75 mm	150 mm	150 mm	150 mm	70×198 mm
Power Source	Electric	Electric	Electric	Pneumatic	Pneumatic	Pneumatic	Pneumatic	Pneumatic	Pneumatic
Voltage	220-240V	230V	230V	NA	NA	NA	NA	NA	NA
Power	350 W	350 W	350 W	NA	NA	NA	NA	NA	NA
Speed (rpm/opm)	4000-10000	4000-10000	4000-10000	12000	12000	12000	12000	12000	10000
Orbit	2.5 mm	2.5 mm	5 mm	2.5 mm	5 mm	2.5 mm	5 mm	8 mm	NA
Noise level	61.7 dBa	63.14 dBa	66.9 dBa	79.2 dBa	79.1 dBa	71.8 dBa	77.5 dBa	77.6 dBa	72.5 dBa
Vibration	1.51 m/s²	1.97 m/s²	2.7 m/s²	1.67 m/s²	1.85 m/s²	2.31 m/s²	3.41 m/s²	3.97 m/s²	3.29 m/s²
Weight	1.16 kg	1.5 kg	1.53 kg	0.66 kg	0.76 kg	0.91 kg	0.92 kg	0.96 kg	1.00 kg



Dust Extractors

33761	3M™ Dust Extractor, 33761, 45 Liter, 230V, Plug Type G, L Class, 1/Case
33762	3M™ Dust Extractor, 33762, 45 Liter, 230V, Plug Type G, M Class, 1/Case
33756	3M™ Dust Extractor, 33756, 30 Liter, 230V, Plug Type G, L Class, 1/Case
33787	3M™ Dust Extractor, 33787, 30 Liter, 230V, Plug Type G, M Class, 1/Case

Random Orbital Sanders

33797	3M™ Pneumatic Precision Random Orbital Sander, 33797, 75 mm, 2.5 mm (3/32) Orbit, Vacuum-Ready, 1 per box
38505	3M™ Precision Random Orbital Sander, 38505, 75 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33632	3M™ Precision Random Orbital Sander, 33632, 150 mm, 2.5 mm (3/32) Orbit, Vacuum-Ready, 1 per box
33633	3M™ Precision Random Orbital Sander, 33633, 150 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33634	3M™ Precision Random Orbital Sander, 33634, 150 mm, 8 mm (5/16) Orbit, Vacuum-Ready, 1 per box
33796	3M™ Pneumatic Precision Orbital Sheet Sander, 33796, 70 mm x 198 mm, Vacuum-Ready, 1 per box
33808	3M™ Electric Random Orbital Sander, 33808, 75 mm, 2.5 mm (3/32) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box
33802	3M™ Electric Random Orbital Sander, 33802, 150 mm, 2.5 mm (3/32) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box
33794	3M™ Electric Random Orbital Sander, 33794, 150 mm, 5 mm (3/16) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box

Dust Extractor Accessories

33645	3M™ Antistatic Pneumatic Hose, 33645, 5 m, 1 per box
33783	3M™ Antistatic Pneumatic Hose, 33783, 8 m, 1 per box
33790	3M™ Antistatic Pneumatic Hose, 33790, 10m, 1 per box
33646	3M™ Antistatic Electric Hose, 33646, 5 m, 1 per box
33648	3M™ Dust Extractor Filter Bag, 33648, 5/Pack
33647	3M™ Dust Extractor Filter, 33647, 2/Pack
33652	3M™ Dust Extractor Y-Connector, 33652
33765	3M™ Dust Extractor Handle Extension, 33765, 1 per box
33784	3M™ Abrasives Organizer, 33784
33770	3M™ Random Orbital Sander Adaptor for Hose Assembly 57 mm, 33770, 1 per carton, 4 per case
33771	3M™ Dust Extractor Straight Adaptor 38 mm, 33771, 1 per carton, 4 per case
33772	3M™ Dust Extractor Adaptor 29 mm, 33772, 1 per carton, 4 per case
33653	3M™ Clean Sanding System Workstation, 33653, 1 per box
33654	3M™ Clean Sanding System Workstation Extension, 33654, 1 per box

Accessories

30160	3M™ Hookit™ Low Profile Disc Back-up Pad 30160, 53 Holes, Red Foam, 10/Case
20446	3M™ Hookit™ Clean Sanding Disc Pad Hook Saver 20446, 150 mm, 20 ea/Case
35826	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35826, 178 mm x 67 mm, 24/Case
35828	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35828, 406 mm x 67 mm, 8/Case
35825	3M™ Hookit™ Dust Extraction Flexible Sanding Block 35825, 133 mm x 67 mm, 24/Case



3M United Kingdom PLC

Automotive Aftermarket
3M Centre
Cain Road
Bracknell, RG12 8HT
+44 (0)161 237 6391
aadukenquiries@mmm.com



For more information, visit us at www.3M.co.uk/dust-extraction-systems

For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3M.co.uk/aad-info

3M, Cubitron and Hookit are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2025. All rights reserved.