

# Maximize productivity with 3M solutions for 24/7 store cleanliness.



**1** 3M™ Neutral Quat Disinfectant Cleaner Concentrate 23

**2** 3M™ Neutral Cleaner Concentrate 3



**3** 3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover

**4** 3M™ Easy Trap™ Sweep & Dust Sheets

**5** 3M™ Easy Scrub Flat Mop System

**6** 3M™ Glass Cleaner and Protector Concentrate 17



**7** 3M™ Non-Acid Disinfectant Bathroom Cleaner Concentrate 15

**8** 3M™ Peroxide Cleaner Concentrate 34



**9** 3M™ Heavy Duty Multi-Surface Mark Remover Concentrate 2

**10** Scotch-Brite™ Stainless Steel Hood Degreaser Wipes with Scotchgard™ Protector



**11** 3M™ Sanitizer Concentrate 16

**12** 3M™ Industrial Degreaser Concentrate 26

**13** 3M™ Flow Control Chemical Management System

# Maintain the high standards of your convenience store with 3M Commercial Cleaning Solutions.



## 1 3M™ Neutral Quat Disinfectant Cleaner Concentrate 23

Multi-purpose, germicidal detergent and deodorant. Cleans, disinfects and deodorizes in one labor-saving step when used according to disinfection directions.



## 2 3M™ Neutral Cleaner Concentrate 3

No-rinse, low-foaming formula cleans washable hard floors and won't leave a soapy residue that can dull or soften floor finish. Fresh scent.



## 3 3M™ Sharpshooter™ Extra Strength No-Rinse Mark Remover

Light duty graffiti remover. For use on vinyl, porcelain, stainless steel, chrome and ceramic. Removes spray paint, ink, marker, crayon and lipstick from hard washable surfaces.



## 4 3M™ Easy Trap™ Sweep & Dust Sheets

Traps up to 800% more dirt, dust and sand than the professional version of a conventional flat-fringed cotton dust mops or a competitive sweeping dust cloth brand.



## 5 3M™ Easy Scrub Flat Mop System

Reduces chemical waste by up to 80% compared to using a mop and bucket. Use the squeeze-bottle at the top of the handle to dispense solution. Small, reusable bottles are quick to swap when your task calls for a different solution.



## 6 3M™ Glass Cleaner and Protector Concentrate 17

Leaves an invisible layer of protection on glass for easier cleaning after routine use. It reduces fogging on windows and mirrors with repeated use, leaving an attractive shine. Not for direct food contact surfaces, vehicles, aquariums or eyewear.



## 7 3M™ Non-Acid Disinfectant Bathroom Cleaner Concentrate 15

When used as directed, formulated to disinfect hard, non-porous surfaces such as floors, walls, metal surfaces, stainless steel surfaces, glazed porcelain, glazed ceramic tile, plastic surfaces and cabinets.



## 8 3M™ Peroxide Cleaner Concentrate 34

An all purpose, light duty, peroxide cleaner concentrate for daily use. This low odor product leaves no messy residue behind. Uses effervescing action to clean nonporous surfaces such as floors, walls, tables, chairs, countertops, bathroom fixtures, sinks, doors, shelves, tile and grout, and more.



## 9 3M™ Heavy Duty Multi-Surface Mark Remover Concentrate 2

Versatile cleaner removes most spots, stains and grease from washable surfaces. Use to remove marks from marble, aluminum, stainless steel and chrome.



## 10 Scotch-Brite™ Stainless Steel Hood Degreaser Wipes with Scotchgard™ Protector

A fast, easy, convenient way to wipe away grease on stainless steel hoods, while leaving behind a protective Scotchgard™ layer as you clean — making it easier to wipe off grease the next time.



## 11 3M™ Sanitizer Concentrate 16

EPA registered sanitizer for walls, floors and other hard, nonporous surfaces. For sanitizing food contact surfaces. Low flow for use in filling bottles.



## 12 3M™ Industrial Degreaser Concentrate 26

Removes petroleum-based grease and oil, animal fats, food soils and heavy dirt buildup. Can be used in industrial plants, transportation and auto facilities, schools, hospitals and other facilities to clean a variety of surfaces.



## 13 3M™ Flow Control Chemical Management System

This system is on average 55% more accurate at diluting chemical concentrates than the nearest competitive system when tested under laboratory conditions at water pressures ranging from 20 to 120 psi.



Commercial Branding & Transportation  
3M Center, Bldg 223-3N-20  
St. Paul, MN 55144-1000 USA  
1-800-698-4595  
3M.com/facility

For more information, please  
contact your distribution  
representative or scan QR code.



3M, Easy Trap, Scotch-Brite, Scotchgard and Sharpshooter are trademarks of 3M. Used under license in Canada. Green Seal and the Green Seal Certified mark are trademarks of Green Seal, Inc. All other trademarks are property of their respective owners. © 3M 2025. All rights reserved. 75-5100-3071-3