



# Technical Data Sheet

## Preliminary 3M™ Electrically Debondable Tape 1200-200

### Product Description

3M™ Electrically Debondable Tape 1200-200 is a single layer adhesive transfer tape (ATT) featuring an electrically debondable thin PSA. When bonded to 2 conductive surfaces, the 1200-200 is electrically debondable. The electrically debondable feature enables a clean, quick, and safe breaking of this adhesive bond to enable rework, repair, and recycling of critical components

### Product Features

- Reliable bonding strength in harsh conditions
- Quick, clean removal with low voltages
- Improved corrosivity

### Typical Physical Properties

Attribute Name	Value
Adhesive Thickness	0.2 mm
Adhesive Type	Specialty Acrylic
Tight Side Release Liner Thickness	0.075 mm
Color	White
Easy Side Release Liner Thickness	0.05 mm

### Typical Performance Characteristics

Substrate: Stainless Steel  
Test Condition: 10 mm/min

Attribute Name	Test Method	Value
Tensile Strength	ASTM D897	1.2 MPa

Substrate: Stainless Steel  
Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	1.2 N/mm <sup>1</sup>

<sup>1</sup> 300 mm/min (12 in/min)

Substrate: Stainless Steel  
Temperature: 23 °C (73 °F)

Attribute Name	Test Method	Test Condition	Value
Electrical Debond Time (Peel)	ASTM D3330	9V	120 s <sup>1</sup>
Electrical Debond Time (Pushout)	ASTM D897	30V	120 s <sup>2</sup>

<sup>1</sup> Time at indicated voltage resulting in 180° peel test falls below 0.1 N/mm

<sup>2</sup> Time at indicated voltage resulting in tensile pushout test falls below 0.3MPa

## **Application Guidelines**

The 3M™ Electrically Debondable Tape 1200-200 can be debonded by applying a low voltage across the two conductive, bonded surfaces. Current will move through the system causing debond on the low voltage side.

### **Steps to Debond**

From a power source, attach the low potential lead to the substrate that will debond, and the high potential lead to the substrate that will remain bonded.

Apply a small DC voltage, 10-30V for example, which will cause a current to flow through the system, creating a weak boundary layer at the PSA interface on the low potential side.

Afterwards, remove the power and open the bond.

## **Storage and Shelf Life**

The shelf life of 3M™ Electrically Debondable Tape 1200-200 is 12 months from the date of manufacture when stored in the original packaging materials below 40°C (104°F). It is best practice to avoid low humidity and/or high temperature storage conditions.

## **Certificate of Analysis (COA)**

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and is deemed commercially available from 3M. The COA contains the 3M specifications, test methods and test results for the products performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

## **Information**

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Warranty claims must be made within one (1) year from the date of 3M's shipment.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).