

3M Science.
Applied to Life.™

The new gold standard in abrasives

**Cut faster, last longer –
the performance leader
in 3M value abrasives**


Re-engineered 3M™ Gold Abrasives for collision repair deliver our longest cut and life – on average 30% better than previous 3M Gold and Green standard value ranges* – for a fast, consistently sharp cut, durable performance and a uniform finish.

*Based upon 3M internal automated testing




3M™ Gold Abrasive Discs

Our Gold Abrasive Discs are available in a wide range of sizes, grades and hole configurations to suit your personal preferences and needs in the body shop. 3M™ Hookit™ Attachment for fast change-out.



No hole



15-hole



Multi-hole



Multi-hole soft

3M™ Hookit™ Discs



3M™ Hookit™ Gold Abrasive Disc 288U 75mm – no hole, 50 discs/carton, 4 cartons/case											
Part No.	09210	09211	09212	09213	09214	09215	09216	09217	09218	09219	09220
Grade	80	120	150	180	220	240	320	400	500	600	800



3M™ Hookit™ Gold Abrasive Disc 288U, 150mm, 15 hole, 100 discs/carton, 4 cartons/case												
Part No.	51542	51543	51545	51546	51547	51548	51549	51551	51553	51554	51555	51556
Grade	40	80	120	150	180	220	240	320	400	500	600	800



3M™ Hookit™ Gold Abrasive Disc 288U, 150mm multi-hole, 100 discs/carton, 4 cartons/case*												
Part No.	09280	09281	09282	09283	09284	09285	09286	09287	09288	09289	09290	09291
Grade	40	80	120	150	180	220	240	320	400	500	600	800

*Aligns with 7, 15 and 17 back-up pads hole patterns

3M™ Hookit™ Soft & Easy Discs



3M™ Hookit™ Soft Gold Abrasive Disc 288U, 150mm, 15 hole, 25 discs/carton, 6 cartons/case					
Part No.	41087	41089	41090	41091	41092
Grade	320	400	500	600	800
Foam backing					



3M™ Hookit™ Soft Gold Abrasive Disc 288U, 150mm, multi-hole, 25 discs/carton, 6 cartons/case					
Part No.	41137	41139	41140	41141	41142
Grade	320	400	500	600	800
Foam backing					



3M™ Hookit™ Easy Gold Abrasive Disc 288U, 150mm, 15 hole, 50 discs/carton, 6 cartons/case					
Part No.	41095	41097	41098		
Grade	320	400	500		
Latex backing					

3M™ Gold Abrasive Sheets and Sheet Rolls

The versatile 3M™ Gold Abrasive Sheets and Sheet Rolls are excellent for manual, block or orbital sanding. They are available in various sizes and grades ready for efficient bodyshop use.



3M™ Plain Backed Sheets



3M™ Gold Abrasive Hand Sheets 288U, 229mm x 280mm – no hole, 50 sheets/carton, 5 cartons/case

Part No.	12552	12549	12547	12546	12545	12544	12543	12541	12539	12538	12537	12536
Grade	40	80	120	150	180	220	240	320	400	500	600	800

3M™ Plain Backed Sheet Rolls



3M™ Gold Sheet Roll 288U, 115mm x 50m, 2 rolls/case

Part No.	44400	44398	44397	44396	44395	44394	44393	44392
Grade	80	120	150	180	220	240	320	400

3M™ Hookit™ Sheet Rolls



3M™ Hookit™ Gold Sheet Roll 288U, 70mm x 12m, 5 rolls/case

Part No.	02768	02769	02770	02771	02772	02773	02774
Grade	80	120	150	180	220	240	320



3M™ Hookit™ Gold Sheet Roll 288U, 115mm x 12m, 3 rolls/case

Part No.	12799*	12798	12797	12795	12793	12792	12791	12790	12789
Grade	40	80	120	150	180	220	240	320	400

*40 grade roll is 8m long



3M™ Soft Hand Gold Abrasive Sheet Roll 288U, 114mm x 25m, perforated, 4 rolls/case

Part No.	40330	40331	40333	41218	41242	41243	41244	41245
Grade	150	180	240	320	400	500	600	800

Note: For all available options and replacements of existing 3M™ Gold Abrasive Products, please use QR code on back page.

Premium abrasives



3M™ Cubitron™ II Abrasives feature 3M™ Precision-Shaped Grain technology to deliver premium cut and life.

Cut rate



Disc life



Dust extraction



Advanced abrasives



3M™ Blue Abrasives use an engineered ceramic mineral blend for leading combination of performance and value.

Cut rate




Disc life



Dust extraction



Standard abrasives



3M™ Gold Abrasives are a true classic, trusted for decades, now re-engineered for better cut and longer life.

Cut rate



Disc life



Dust extraction



Scan the QR code to see:
The full range of all NEW 3M™ Gold Abrasives

Crossover to legacy 3M™ Gold 255P/216U/236U Abrasives



Discover the full 3M Clean Sanding System

Electric tools



Pneumatic tools



Dust extractors



For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3M.co.uk/aad-info



3M United Kingdom PLC
Automotive Aftermarket
3M Centre, Cain Road,
Bracknell, RG12 8HT
Phone: +44 (0)161 237 6391
aaduenquiries@mmm.com

Dust Extractors

33761	3M™ Dust Extractor, 33761, 45 Litre, 230V, Plug Type G, L Class, 1/Case
33762	3M™ Dust Extractor, 33762, 45 Litre, 230V, Plug Type G, M Class, 1/Case
33756	3M™ Dust Extractor, 33756, 30 Litre, 230V, Plug Type G, L Class, 1/Case
33787	3M™ Dust Extractor, 33787, 30 Litre, 230V, Plug Type G, M Class, 1/Case

Random Orbital Sanders

33797	3M™ Pneumatic Precision Random Orbital Sander, 33797, 75 mm, 2.5 mm (3/32) Orbit, Vacuum-Ready, 1 per box
38505	3M™ Precision Random Orbital Sander, 38505, 75 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33632	3M™ Precision Random Orbital Sander, 33632, 150 mm, 2.5 mm (3/32) Orbit, Vacuum-Ready, 1 per box
33633	3M™ Precision Random Orbital Sander, 33633, 150 mm, 5 mm (3/16) Orbit, Vacuum-Ready, 1 per box
33634	3M™ Precision Random Orbital Sander, 33634, 150 mm, 8 mm (5/16) Orbit, Vacuum-Ready, 1 per box
33796	3M™ Pneumatic Precision Orbital Sheet Sander, 33796, 70 mm x 198 mm, Vacuum-Ready, 1 per box
33808	3M™ Electric Random Orbital Sander, 33808, 75 mm, 2.5 mm (3/32) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box
33802	3M™ Electric Random Orbital Sander, 33802, 150 mm, 2.5 mm (3/32) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box
33794	3M™ Electric Random Orbital Sander, 33794, 150 mm, 5 mm (3/16) Orbit, 230V, Plug Type G, Vacuum-Ready, 1 per box