



3M Science.
Applied to Life.™

Introducing 3M™ Hookit™ Flexible Foam Abrasives in sheets —

Versatility at its finest.

**Highly flexible foam backed abrasive
which conforms to irregular surfaces**

- Available in sheets and discs
- Excellent dust and water control to help ensure a clean sanding environment
- Delivers a uniform, consistent finish with excellent cut

3M™ Hookit™ Flexible Foam Abrasive Sheets



The soft foam construction conforms to irregular surfaces, ensuring a uniform and consistent finish, especially around panel edges and corners.


These innovative sanding sheets are designed for use by hand or with a sheet sander, offering versatility for blending, primer finishing, and scuffing applications.

The perforated double sheet can be folded in half to enhance grip and control of the abrasive.




139 mm x 172 mm 10 Sheets/Carton 6 Cartons/Case	
Grade	3M Part No.
P400	33531
P600	33532
P800	33533
P1000	33534
P1200	33535
P1500	33536
P2000	33537

3M™ Hookit™ Flexible Foam Abrasive Discs



Flexible and durable, provides sustained cutting performance and an excellent finish, whether used wet or dry.



3M™ Hookit™ Flexible Foam Abrasive Discs combine flexible aluminum oxide abrasives with a soft foam backing to create a high performing, versatile blending abrasive for wet or dry use by hand or machine.

Grade	150 mm 20 Discs/Carton 4 Cartons/Case
	3M Part No.
P400	33538
P600	33539
P800	33540
P1000	33541
P1200	33542
P1500	33543
P2000	33544

Top Reasons to Choose 3M™ Flexible Foam Abrasives

▼


Hundreds of laser perforated holes mean excellent dust and water control when used wet or dry creating a clean sanding environment.

▼

Flexible and long lasting, delivering an excellent finish.

▼

Product has a very good initial and sustained cut for use on clear coats, paint, primer and plastics.



Recommended Grades for Use

Grade	Applications
P400	Final DA primer refinement before 2K paint application - Plastic bumper sanding - Stone chip sanding - prep for base coat and clear coat application
P600	Final primer sanding for critical colors and refining previous sanding marks. (water-based base coat)
P800	Final primer sanding for critical colours and blending
P1000	Blending/Matting (while retaining paint structure/texture)
P1200	Preparation for clear coat
P1500	Defect removal - Paint Rectification
P2000	Minor defect removal - Paint Rectification



3M Automotive Aftermarket Division Australia
Building A, 1 Rivett Rd North Ryde, NSW, 2113
Phone 136-136

3M Automotive Aftermarket Division New Zealand
94 Apollo Drive Rosedale,
Albany North Shore City Auckland 0632
Phone 0800 362 886

For additional information, including important safety and warranty details on 3M Automotive Aftermarket products, please [contact us](#).

Hookit and 3M are trademarks of 3M Company.
© 3M 2025. All rights reserved.