



Technical Data Sheet

IS1 Industrial Sealing Tape



[Additional Info](#)

Product Description

3M™ IS1 Industrial Sealing Tape is a non-permeable membrane tape with an aggressive adhesive that sticks to a variety of substrates. This product uses a specially formulated acrylic adhesive that sticks and stays stuck at a wider range of temperatures than many traditional tapes. The proprietary film backing seals around rivets, screws, staples, and nails to prevent moisture intrusion. This film is also tough, resisting punctures and tears, yet is flexible enough to be tightly tucked into corners.

Product Features

- Can be applied to substrates from 0° to 150°F (-18° to 66°C)
- Compatible with most sealants: Rubberized Asphalt, Polyurethane, Silicone and Hybrid sealants
- Great adhesion to anodized aluminum, rigid vinyl, and plywood without the need for a primer
- Seals around screws, nails, staples, and rivets to prevent moisture intrusion.
- UV Resistance up to 12 months

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		White
Adhesive Type		Acrylic
Backing		Multi-Layer Film
Liner		Polycoated Kraft
Backing Thickness	ASTM D3652	0.13 mm
Total Tape Thickness	ASTM D3652	0.25 mm
Liner Thickness		0.16 mm

Attribute Name	Test Method	Environmental Condition	Test Condition	Value
Water Vapor Transmission	ASTM E96		Wet Cup	4.90 ng/s/m ² /Pa
Water Vapor Transmission	ASTM E96		Dry Cup	5.59 ng/s/m ² /Pa
Nail Sealability	ASTM D1970	127 mm(5 inches) water head after 3 days		Dry/Pass

Typical Performance Characteristics

Attribute Name	Test Method	Dwell Time	Temperature	Substrate	Value
180° Peel Adhesion	ASTM D3330	20 min	23 °C	Stainless Steel	57 N/100mm ¹
Tensile Strength	ASTM D3759				385 N/100mm
Elongation at Break	ASTM D882				>700 %
Temperature Use Range					-40 - 116 °C

¹ 300 mm/min (12 in/min)

Application Examples

- Sealing around fasteners for exterior panels, preventing corrosion and water intrusion for busses, trucks, and RVs
- Seaming underneath roof joints, windows, and moon roofs
- Gas/fume barrier for interiors
- Sealing interior joints of HVAC or electrical enclosures
- Helps prevent water intrusion on signage

Storage and Shelf Life

Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Standard Roll Length	33 m

Information

Important Information: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Centre
Cain Rd, Binfield, Bracknell RG12 8HT, United Kingdom
3m.co.uk/iatd

3M is a trademark of 3M Company.
©3M 2026 (1/26)