



Technical Data Sheet

Effective: 01/01/2026 Supersedes: New

Automotive Aftermarket Division

3M™ Hookit™ Blue Net Abrasives

1) Part Numbers

Discs		Sheet Rolls	
Part Number	Grit Grade	Part Number	Grit Grade
Size: 75 mm (3 in)		Size: 70 mm x 10 m (2.75 in x 10.9 yd)	
36449	80	36462	80
36450	120	36463	120
36451	50	36464	150
36452	180	36465	180
36453	220	36466	220
36454	240	36467	240
36455	320	36468	320
36456	400	36469	400
Size: 125 mm (5 inch)		Size: 115 mm x 10 m (4.5 inch x 10.9 yards)	
36435	80	36470	80
36436	120	36471	120
36437	150	36472	150
36438	180	36473	180
36439	220	36474	220
36440	240	36475	240
36441	320	36476	320
36442	400	36477	400
Size: 150 mm (6 inch)			
36420	80		
36421	120		
36422	150		
36423	180		
36424	220		
36425	240		
36426	320		
36427	400		



Technical Data Sheet

Effective: 01/01/2026 Supersedes: New

2) Description and Applications

The new and improved 3M™ Hookit™ Blue Net Abrasives are a proprietary abrasive product designed to deliver exceptional abrasive performance with increased robustness and high levels of dust extraction when used with a dust extraction system.

Grade	Applications
80	General stock removal. Used to clean the repair area and remove all loose paint particles or rust. Initial filler shaping.
120	Used to clean the repair area and remove all loose paint particles or rust. Filler sanding.
150	Used to clean the repair area and remove all loose paint particles or rust. Filler sanding.
180	Feather edge around the repair area.
220	Feather edge around the repair area. Filler refinement
240	Surface refinement. Filler shaping.
320	Primer refinement before paint application. Surface preparation for sealer

3) Physical Properties

Note: the following technical information and data should be considered representative or typical only and should not be used for specification

Backing	Net with integrated loops
Mineral	3M™ Precision Shaped Grain and Aluminium Oxide blend
Bonding	Resin Bond
Colour	Blue
Grades	80 to 400

4) Directions for Use

Product can be used on a tool or by hand. Product should be used dry.

For best results use in combination with a dust extraction system. Product does not require specific hole alignment.



Technical Data Sheet

Effective: 01/01/2026 Supersedes: New

5) **Storage**

Product shall have a shelf life of 5 years from date of manufacture when stored in original unopened containers at standard environmental conditions.

Storage conditions: Store at room temperature 18-23 °C (65-75 °F). Rotate stock on a “first-in-first-out” basis.

6) **Safety**

3M™ Hookit™ Blue Net Abrasives are designed FOR PROFESSIONAL INDUSTRIAL USE ONLY.

7) **Disclaimer**

All statements, technical information and recommendations are based on tests we believe to be reliable as at the date of hereof, but the accuracy or completeness thereof is not guaranteed. Please ensure before using the product that it is suitable for your intended use. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, other than for fraudulent misrepresentation, 3M expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information.



Technical Data Sheet

Effective: 01/01/2026 Supersedes: New

For Additional Health and Safety Information

3M United Kingdom plc Automotive Aftermarket 3M Centre, Cain Road, Bracknell, RG12 8HT Tel: +44 (0)161 237 6391 aadukenquiries@mmm.com www.3Mbodyshop.co.uk	3M Ireland Limited Automotive Aftermarket The Iveagh Building Carrickmines Park Carrickmines , Dublin 18 Tel: +353 12160301 aadukenquiries@mmm.com www.3Mbodyshop.co.uk	3M Denmark a/s Automotive Aftermarket Hannemanns Allé 53 2300 København S Tel: +45 43480100 aadukenquiries@mmm.com www.3MAuto.dk
3M Finland, Suomen 3M Oy Autotuotteet Keilaniementie 1 02151 Espoo Tel: 09 5252 1 aadukenquiries@mmm.com www.3M.fi/autotuotteet	3M Svenska AB Automotive Aftermarket Herrjärva torg 4 170 67 Solna Tel: 08-922100 aadukenquiries@mmm.com www.3M.se/bileftermarkad	3M Norge AS Automotive Aftermarket Kanalveien 2 2004 Lillestrøm Tel: 06384 aadukenquiries@mmm.com www.3m.no/auto
3M Latvija K.Ulmana 5 Riga, LV-1004 Tel: +371 67066120 aadukenquiries@mmm.com www.3m.lv	3M Eesti OU Pärnu mnt. 158 11317 Tallinn Tel: +372 6 115 902 aadukenquiries@mmm.com www.3m.ee	3M Lietuva A.Goštauto str. 40 A LT-01112 Vilnius Tel: +370 5 2160780 aadukenquiries@mmm.com www.3m.lt

3M and Hookit are the trademarks of 3M Company, © 3M 2026, All rights reserved.