

## Recommended digital printers for traffic signs

A robust portfolio of printers, giving you the flexibility to choose the ultimate printing solution for your business.



**Durst Rho 163  
TS | HS**



**EFI H1625-RS**



**Canon Colorado  
M-Traffic**



**HP Latex  
830/830W**



**HP Latex  
730/730W**

<b>Productivity</b>	275 ft <sup>2</sup> /hr, 25 m <sup>2</sup> /hr 550 ft <sup>2</sup> /hr, 50 m <sup>2</sup> /hr	200 ft <sup>2</sup> /hr, 18 m <sup>2</sup> /hr	165 ft <sup>2</sup> /hr, 15.3m <sup>2</sup> /hr	145 ft <sup>2</sup> /hr, 13.5 m <sup>2</sup> /hr	124 ft <sup>2</sup> /hr, 11.5 m <sup>2</sup> /hr
<b>Production</b>	Hybrid	Hybrid	Roll-to-Roll	Roll-to-Roll	Roll-to-Roll
<b>Inks</b>	3M™ Piezo InkJet 8900UV Series	3M™ Piezo InkJet 8900UV Series	Canon UVgel 540-R	HP Series 873	HP Series 832
<b>Ink Volume</b>	3L	1 L (2 bottle/case)	1L	3L	1L
<b>RIP Software</b>	Caldera GrandRIP+	EFI Fiery XF RIP	SAi Flexi COMPLETE – 3M Traffic Edition RIP	SAi Flexi COMPLETE – 3M Traffic Edition RIP	SAi Flexi COMPLETE – 3M Traffic Edition RIP
<b>Sheeting Compatibility</b>	<p><a href="#">3M™ Diamond Grade™ DG3 Digital Reflective Sheeting Series 4000UDS</a></p> <p><a href="#">3M™ High Intensity Prismatic Digital Reflective Sheeting Series 3930UDS</a></p> <p><a href="#">3M™ Diamond Grade™ Fluorescent Work Zone Digital Sheeting Series 3924SUDS</a></p> <p><a href="#">3M™ Advanced Flexible Engineer Grade Reflective Sheeting Series 7310</a></p>	<p><a href="#">3M™ Diamond Grade™ DG3 Digital Reflective Sheeting Series 4000UDS</a></p> <p><a href="#">3M™ High Intensity Prismatic Digital Reflective Sheeting Series 3930UDS</a></p> <p><a href="#">3M™ Diamond Grade™ Fluorescent Work Zone Digital Sheeting Series 3924SUDS</a></p> <p><a href="#">3M™ Advanced Flexible Engineer Grade Reflective Sheeting Series 7310</a></p>	<p><a href="#">3M™ Diamond Grade™ DG3 Digital Reflective Sheeting Series 4000UDS</a></p> <p><a href="#">3M™ High Intensity Prismatic Digital Reflective Sheeting Series 3930UDS</a></p> <p><a href="#">3M™ Diamond Grade™ Fluorescent Work Zone Digital Sheeting Series 3924SUDS</a></p> <p><a href="#">3M™ Advanced Flexible Engineer Grade Reflective Sheeting Series 7310</a></p>	<p><a href="#">3M™ Diamond Grade™ DG3 Digital Reflective Sheeting Series 4000 and 4000UDS</a></p> <p><a href="#">3M™ High Intensity Prismatic Digital Reflective Sheeting Series 3930 and 3930UDS</a></p> <p><a href="#">3M™ Diamond Grade™ Fluorescent Work Zone Digital Sheeting Series 3924S and 3924SUDS</a></p>	<p><a href="#">3M™ Diamond Grade™ DG3 Digital Reflective Sheeting Series 4000 and 4000UDS</a></p> <p><a href="#">3M™ High Intensity Prismatic Digital Reflective Sheeting Series 3930 and 3930UDS</a></p> <p><a href="#">3M™ Diamond Grade™ Fluorescent Work Zone Digital Sheeting Series 3924S and 3924SUDS</a></p>
<b>3M™MCS™ Warranty for Traffic</b>	Yes	Yes	Yes	Yes	Yes

