



Value focused. Performance ready.

Introducing

3M™ PPS™ Basic Series Lid and Liner Kit

3M™ PPS™ Basic Series Lid and Liner Kit delivers dependable spraying performance with value focus.

Designed to work seamlessly with 3M™ PPS™ Series 2.0 Hard Cups, it offers smooth fluid flow, built-in full-diameter filtration, and a reusable collar for practical, day-to-day efficiency.

Available in standard and large sizes, it provides a reliable solution for paint, primer, and coating applications while maintaining compatibility with existing 3M™ PPS™ 2.0 adapters and the 3M™ Performance Spray Gun.

3M™ PPS™ Basic Series Features

- Value-line Lid and Liner Kits with the trusted design from 3M™PPS™ Spray Cup Systems
- Kit includes 50 lids, 50 liners, 1 collar, 16 sealing plugs
- Available in standard (650 ml / 22 oz) and large (850 ml / 28 oz)
- Opaque black lid
- Full diameter filter mesh (125 micron & 200 micron)
- Quarter-turn easy-lock re-usable collar (1 in every kit)
- Compatible with 3M™ Performance Spray Gun and all 3M™ PPS™ Series 2.0 Adapters
- Must be used with 3M™ PPS™ Series 2.0 Hard Cup (not included in kit)



3M™ PPS™ Basic Series Lid and Liner Kit



Part Number	Size	Volume	Filter	Content
PBS125	Standard	22 oz / 650 ml	125 micron	50 lids, 50 liners, 16 sealing plugs, 1 re-useable collar
PBS200	Standard	22 oz / 650 ml	200 micron	
PBL125	Large	28 oz / 850 ml	125 micron	
PBL200	Large	28 oz / 850 ml	200 micron	

3M™ PPS™ Basic Series Collar



Part Number	Size	Content
PBC005	Std / Large	5 re-useable collars/pack, 4 packs/case

3M™ PPS™ Series 2.0 Hard Cup



Part Number	Size	Volume	Content
26001	Standard	22 oz / 650 ml	2 Cups/Bag, 4 Bags/Case
26023	Large	28 oz / 850 ml	

3M™ PPS™ Series 2.0 Systems - Features at a glance

Features	3M™ PPS™ Series 2.0 Spray Cup System	3M™ PPS™ Series 2.0 Vented Spray Cup System	3M™ PPS™ Basic Series Lid + Liner Kits
Secure 4-point wide spout spray gun connection	✓	✓	✓
Compatible with 3M™ Performance Spray Gun	✓	✓	✓
125 and 200 micron filter	✓	✓	✓
Full diameter filter	✓	✓	✓
Compatible with 3M™ PPS™ Series 2.0 Dispensers and adapters	✓	✓	✓
New hard cup(s) in every kit	✓	✓	Only sold separately
Locking collar part of each lid	✓	✓	
Full range of sizes	✓	✓	Only Large and Standard
Pressure Cup H/O compatible	✓		✓
Transparent lid	✓	✓	
Sealing Plugs per kit	32	32	16



Automotive Aftermarket Division
3M Center
Building 223-4S-04
St. Paul, MN 55144-1000
1-877-666-2277

For additional information, including important safety and warranty information, regarding 3M Automotive Aftermarket Products, please visit: www.3MCollision.com/info

For industrial/occupational use only. Not for consumer sale or use.

3M and PPS are trademarks of 3M Company. All other trademarks are property of their respective owners. Please recycle.
© 3M 2026. All rights reserved. 60-4405-0305-4