



SCOTT™
Fire & Safety

3M™ Scott™ Air-Pak™ SCBA NFPA 1970, 2025 Edition Specifications & Ordering Information



Reference Guide

Technical Data

Facepiece	
3M™ Scott™ AV-3000 HT Facepiece	
Weight	1.59 lbs (0.72 kg)
Construction	Seal - Polyisoprene / EPDM blend; Headnet - Para-Aramid; Harness Straps - Polyaramid / polybenzimidazole fiber blend (commonly referred to as PBI® Gold)
3M™ Scott™ Vision C5 Facepiece	
Weight	1.53 lbs (0.69 kg)
Construction	Seal - Polyisoprene / EPDM blend; Headnet - Para-Aramid; Harness Straps - Polyaramid / polybenzimidazole fiber blend (commonly referred to as PBI® Gold)
Backframe	
3M™ Scott™ Air-Pak™ XD SCBA	
Weight	Backframe 1.63 lbs (0.73 kg)
	Backframe and Padded Harness* 4.26 lbs (1.93 kg)
Construction	Stainless Steel 300 Series
3M™ Scott™ Air-Pak™ X3 Pro SCBA	
Weight	Backframe 1.61 lbs
	Backframe & Padded Harness* 4.76 lbs
Construction	Heat-treated 6061-T6 Aluminum alloy
Harness	
3M™ Scott™ Air-Pak™ XD SCBA	
Construction	Outer Shell—Polybenzimidazole blend (commonly referred to as Armor AP™) Webbing—Kevlar™/Nomex
3M™ Scott™ Air-Pak™ X3 Pro SCBA	
Construction	Outer Shell—Polybenzimidazole blend (commonly referred to as Armor AP™) Webbing—Kevlar™/Nomex
Regulator	
3M™ Scott™ E-Z Flo+ Regulator	
Weight ⁺	0.82 lbs. (0.37 kg)
Dimension	Low-pressure supply line - 0.575 in. OD (14.61 mm); 0.25 in. ID (6.35 mm)
3M™ Scott™ E-Z Flo C5 Regulator	
Weight ⁺	0.94 lbs. (0.42 kg)
Dimension	Low-pressure supply line - 0.575 in. OD (14.61 mm); 0.25 in. ID (6.35 mm)
* Includes regulator holder	
+ Includes quick disconnect hose (plug) and Heads-Up Display (HUD)	

PBI Gold is a registered trademark of PBI Performance Products, Inc.

Armor AP is a trademark of Safety Components, Inc.

Kevlar and Nomex are registered trademarks of DuPont de Nemours, Inc.

Reference Guide

Cylinder and Valve Assemblies

Cylinder and Valve Assemblies							
Part Number	Pressure (psig)	Duration (minutes)	Dimensions (L in. x W in.)	Air Capacity (ft ³ / l ³)	Water Volume (in ³ / l ³)	Weight* (lb / kg)	DOT/TC Exemption
Carbon-Wrapped							
804721-01	4500	30	21.50 × 5.44	45 / 1274	285 / 4.7	11.08 / 5.03	SP-10915-4500 / SU 5134-310
200128-01**	4500	30	21.50 × 5.44	45 / 1274	285 / 4.7	11.40 / 5.17	SP-10915-4500 / SU 5134-310
804722-01	4500	45	23.40 × 6.26	65 / 1841	418 / 6.8	14.99 / 6.80	SP-10915-4500 / SU 5134-310
200129-01**	4500	45	23.40 × 6.26	65 / 1841	418 / 6.8	15.31 / 6.94	SP-10915-4500 / SU 5134-310
804723-01	4500	60	24.79 × 6.90	87 / 2464	550 / 9.0	19.19 / 8.70	SP-10915-4500 / SU 5134-310
200130-01**	4500	60	24.79 × 6.90	87 / 2464	550 / 9.0	19.51 / 8.85	SP-10915-4500 / SU 5134-310
200930-01	5500	30	22.20 × 4.94	45 / 1274	233 / 3.8	9.99 / 4.53	SP-15136-5500 / SU-10350-379
200967-01**	5500	30	22.20 × 4.94	45 / 1274	233 / 3.8	10.30 / 4.67	SP-15136-5500 / SU-10350-379
200969-01	5500	45	22.22 × 6.00	66 / 1869	349 / 5.7	13.76 / 6.24	SP-15136-5500 / SU-10350-379
200970-01**	5500	45	22.22 × 6.00	66 / 1869	349 / 5.7	14.06 / 6.38	SP-15136-5500 / SU-10350-379
200972-01	5500	60	24.53 × 6.53	87 / 2464	465 / 7.6	17.36 / 7.87	SP-15136-5500 / SU-10350-379
200973-01**	5500	60	24.53 × 6.53	87 / 2464	465 / 7.6	17.67 / 8.01	SP-15136-5500 / SU-10350-379
200975-01	5500	75	25.51 × 7.15	111 / 3143	581 / 9.5	21.62 / 9.81	SP-15136-5500 / SU-10350-379
200976-01**	5500	75	25.51 × 7.15	111 / 3143	581 / 9.5	21.93 / 9.95	SP-15136-5500 / SU-10350-379
Carbon-Wrapped, Short & Stubby							
804722-01A	4500	45	21.30 × 6.79	65 / 1841	416 / 6.8	15.32 / 6.9	SP-10915-4500 / SU 5134-310
200129-01A**	4500	45	21.30 × 6.79	65 / 1841	416 / 6.8	15.64 / 7.09	SP-10915-4500 / SU 5134-310
Carbon-Wrapped ST7							
804721-11	4500	30	21.50 × 5.47	45 / 1274	285 / 4.6	11.08 / 5.03	SP-10915-4500 / SU 5134-310
200128-11**	4500	30	21.50 × 5.47	45 / 1274	285 / 4.7	11.40 / 5.17	SP-10915-4500 / SU 5134-310
804722-11	4500	45	23.40 × 6.29	65 / 1841	418 / 6.8	14.99 / 6.80	SP-10915-4500 / SU 5134-310
200129-11**	4500	45	23.40 × 6.29	65 / 1841	418 / 6.8	15.31 / 6.94	SP-10915-4500 / SU 5134-310
804723-11	4500	60	24.70 × 6.93	87 / 2464	550 / 9.0	19.19 / 8.70	SP-10915-4500 / SU 5134-310
200130-11**	4500	60	24.70 × 6.93	87 / 2464	550 / 9.0	19.51 / 8.85	SP-10915-4500 / SU 5134-310
Carbon-Wrapped 30-Year							
804721-35	4500	30	21.50 × 5.49	45 / 1274	285 / 4.6	11.48 / 5.21	SP-14232-4500
200128-35**	4500	30	21.50 × 5.49	45 / 1274	285 / 4.6	11.80 / 5.35	SP-14232-4500
804722-35	4500	45	23.40 × 6.31	65 / 1841	418 / 6.8	15.84 / 7.18	SP-14232-4500
200129-35**	4500	45	23.40 × 6.31	65 / 1841	418 / 6.8	16.16 / 7.33	SP-14232-4500
804723-35	4500	60	24.75 × 7.00	87 / 2464	550 / 9.0	20.49 / 9.29	SP-14232-4500
200130-35**	4500	60	24.75 × 7.00	87 / 2464	550 / 9.0	20.81 / 9.44	SP-14232-4500

* Nominal weight of charged cylinder to specified pressure

** Snap-Change Cylinder Valve

Reference Guide

3M™ Scott™ Air-Pak™ XD SCBA



Replacement Parts

3M™ Scott™ Air-Pak™ XD SCBA

1	Backframe	
	Backframe Assembly, XD	201847-01
2	Harness Components	
	Air-Pak™ XD SCBA	
	Waist Belt, Male	78-8151-3123-6
	Waist Belt, Female	78-8151-3122-8
	Cylinder Retention Assembly	78-8151-5068-1
	Waist-to-Shoulder Strap	78-8151-3121-0
	Shoulder Pad/Strap Assembly	201609-11
	Regulator Holder	201649-01
	UEBSS Pouch	201611-09
	Air-Pak™ XD SCBA, Padded Harness	
	Waist Pad, Padded, Spring Clips	201843-01
	Waist Pad, Padded, Parachute	201843-11
	Shoulder Harness & Strap Assembly, Padded, Spring Clips	201842-01
	Shoulder Harness & Strap Assembly, Padded, Parachute	201842-11
	Air-Pak™ XD SCBA, Unpadded Harness	
	Waist Pad, Unpadded, Spring Clips	201843-02
	Waist Pad, Unpadded, Parachute	201843-12
	Shoulder Harness & Strap Assembly, Padded, Spring Clips	201842-02
	Shoulder Harness & Strap Assembly, Padded, Parachute	201842-12
3	Personal Alert Safety System (PASS)	
	Battery Cover Assembly	70-0020-0962-2
	Battery Cover Screw	78-8151-2956-0
	Battery Cover Screw O-ring	31001262
	Battery Cover Seal	31001287
	Battery Cover E-Clip	31001290
4	Cylinder Valve	
	4500 psig Cylinder Valve, CGA	804098-01
	5500 psig Cylinder Valve, CGA	804098-02
	Seal Replacement Kit	200286-01
	Safety Device Kit, 4500 psig	26954-01
	Safety Device Kit, 5500 psig	26954-03

Regulator Assembly (not shown)	
E-Z Flo C5 Regulator	
Regulator, Continuous, Snap-Change	201650-07
Regulator, Continuous, CGA	201650-06
Regulator, Quick Disconnect Hose, Rectus	201650-05
Regulator Gasket	10005368
E-Z Flo+ Regulator	
Regulator, Continuous, Snap-Change	200077-67
Regulator, Continuous, CGA	200077-68
Regulator, Quick Disconnect Hose, Rectus	200077-60
Regulator Gasket	10005368
Facepiece Assembly (not shown)	
Vision C5 Facepiece	
See pages 8-9	
AV-3000 HT	
See pages 10-11	
High Pressure Hose Assembly (not shown)	
4500 & 5500 psig Hose & Coupling Assembly	200922-02
Nipple Seal O-Ring	57264-00
Retaining Screw, Nipple Seal O-Ring	10000113

Reference Guide

3M™ Scott™ Air-Pak™ X3 Pro SCBA



Replacement Parts

3M™ Scott™ Air-Pak™ X3 Pro SCBA

1	Backframe and Harness Assembly	
	Air-Pak™ X3 Pro SCBA, Parachute Buckles	201615-23
2	Harness Components	
	Air-Pak™ X3 Pro SCBA, Parachute Buckles	
	Waist Belt, Male	201608-01
	Waist Belt, Female	201608-02
	Cylinder Retention Assembly	201180-01
	Waist-to-Shoulder Strap	31003739
	Waist Pad Assembly	201610-11
	Shoulder Pad/Strap Assembly	201609-11
	Regulator Holder	201649-01
	UEBSS Pouch	201611-02
3	Personal Alert Safety System (PASS)	
	Battery Cover Assembly	201163-01
	Battery Cover Screw	31001288
	Battery Cover Screw O-ring	31001262
	Battery Cover Seal	31001287
	Battery Cover E-Clip	31001290
4	Cylinder Valve	
	4500 psig Cylinder Valve, CGA	804098-01
	5500 psig Cylinder Valve, CGA	804098-02
	Seal Replacement Kit	200286-01
	Safety Device Kit, 4500 psig	26954-01
	Safety Device Kit, 5500 psig	26954-03
	4500 psig Cylinder Valve, Snap-Change	805783-01
	5500 psig Cylinder Valve, Snap-Change	805783-02

Regulator Assembly (not shown)	
E-Z Flo C5 Regulator	
Regulator, Continuous Hose, Snap-Change	201650-07
Regulator, Continuous Hose, CGA	201650-06
Regulator, Quick Disconnect Hose, Rectus	201650-05
Regulator Gasket	10005368
E-Z Flo+ Regulator	
Regulator, Continuous Hose, Snap-Change	200077-67
Regulator, Continuous Hose, CGA	200077-68
Regulator, Quick Disconnect Hose, Rectus	200077-60
Regulator Gasket	10005368
Facepiece Assembly (not shown)	
Vision C5 Facepiece	
See pages 8-9	
AV-3000 HT	
See pages 10-11	
High Pressure Hose Assembly (not shown)	
4500 & 5500 psig Hose & Coupling Assembly	200922-02
Nipple Seal O-Ring	57264-00
Retaining Screw, Nipple Seal O-Ring	10000113

Replacement Parts

3M™ Scott™ Vision C5 Facepiece



Replacement Parts

3M™ Scott™ Vision C5 Facepiece

Facepiece Assembly

3M™ Scott™ Vision C5 Facepiece

Vision C5, Small Facesal, 4-Strap	FP1S400000000000
Vision C5, Medium Facesal, 4-Strap	FP1M400000000000
Vision C5, Large Facesal, 4-Strap	FP1L400000000000
Vision C5, Small Facesal, 5-Strap	FP1S500000000000
Vision C5, Medium Facesal, 5-Strap	FP1M500000000000
Vision C5, Large Facesal, 5-Strap	FP1L500000000000
Nosecup Assembly, Small	201484-01
Nosecup Assembly, Medium	201486-01
Nosecup Assembly, Large	201488-01
Inhalation Valve	31002788
Temple Tab, Left	201491-01
Temple Tab, Right	201500-01
Sizing Stud, Small	31003603
Sizing Stud, Medium	31003602
Sizing Stud, Large	31003601
Headnet Buckle, Gen 1	201502-02
Headnet Buckle, Gen 2	78-8151-6243-9
Headnet Buckle with D-ring, Gen 1	201502-01
Headnet Assembly, Small, Gen 1*	201496-03
Headnet Assembly, Medium, Gen 1*	201496-02
Headnet Assembly, Large, Gen 1*	201496-01
Headnet Assembly, Small, 4-Strap, Gen 2*	78-8151-6291-8
Headnet Assembly, Medium, 4-Strap, Gen 2*	78-8151-6292-6
Headnet Assembly, Large, 4-Strap, Gen 2*	78-8151-6293-4
Headnet Assembly, Small, 5-Strap, Gen 2*	70-0020-1033-1
Headnet Assembly, Medium, 5-Strap, Gen 2*	70-0020-1034-9
Headnet Assembly, Large, 5-Strap, Gen 2*	70-0020-1035-6
Stirrup Assembly, Small, 5-Strap, Gen 2**	70-0020-1036-4
Stirrup Assembly, Medium, 5-Strap, Gen 2**	70-0020-1063-8
Stirrup Assembly, Large, 5-Strap, Gen 2**	70-0020-1064-6
Temple Strap, Gen 1	804178-05
Temple Strap, Gen 2	78-8151-6287-6
Neck Strap, Gen 1	804178-03
Neck Strap, Gen 2	78-8151-6286-8
Accessory Neck Strap	201682-01

*Includes headnet, temple and neck straps

**Includes stirrup, buckle, and sizing stud

Replacement Parts

3M™ Scott™ AV-3000 HT Facepiece



Replacement Parts

3M™ Scott™ AV-3000 HT Facepiece

Facepiece Assembly	
3M™ Scott™ AV-3000 HT Facepiece	
AV-3000 HT, 5-strap, Small	201215-01
AV-3000 HT, 5-strap, Medium	201215-02
AV-3000 HT, 5-strap, Large	201215-03
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Small	201215-04
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Medium	201215-05
AV-3000 HT w/ RT Comm Bracket (Open), 5-Strap, Large	201215-06
AV-3000 HT, 4-Strap, Small	201215-21
AV-3000 HT, 4-Strap, Medium	201215-22
AV-3000 HT, 4-Strap, Large	201215-23
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Small	201215-27
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Medium	201215-28
AV-3000 HT w/ RT Comm Bracket (Open), 4-Strap, Large	201215-29
Fenestra Lens	201134-01
Head Harness Assembly, 5-Strap*	200803-01
Temple Strap, 5-Strap**	804178-02
Neck Strap, 5-Strap	804176-02
Head Harness Assembly, 4-Strap, Small	201467-01
Head Harness Assembly, 4-Strap, Medium/Large	201467-02
Temple Strap, 4-Strap	804178-03
Neck Strap, 4-Strap	804176-03
Nosecup Assembly, Small	201126-02
Nosecup Assembly, Medium	201127-02
Nosecup Assembly, Large	201128-02
Sizing Dot, Small (Green)	31003407
Sizing Dot, Medium (Black)	31003408
Sizing Dot, Large (Red)	31003409

*Includes the temple strap sewn into the head harness

**Replacement of the temple strap on AV-3000 HT, 5-Strap products produced after August 2015 will require replacement of head harness assembly (200803-01)

SCBA Weights

3M™ Scott™ Air-Pak™ XD SCBA (Padded Harness) with 3M™ Scott™ E-Z Flo+ Regulator						
	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)
4500 psig, 45-min (Carbon Cylinder)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)
4500 psig, 60-min (Carbon Cylinder)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)
5500 psig, 30-min (Carbon Cylinder)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)
5500 psig, 45-min (Carbon Cylinder)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)
5500 psig, 60-min (Carbon Cylinder)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)
3M™ Scott™ Air-Pak™ XD SCBA (Unpadded Harness) with 3M™ Scott™ E-Z Flo+ Regulator						
	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.6 (11.61)	25.89 (11.74)	27.08 (12.28)	25.6 (11.61)	25.89 (11.74)	27.08 (12.28)
4500 psig, 45-min (Carbon Cylinder)	29.5 (13.38)	29.79 (13.51)	30.98 (14.05)	29.5 (13.38)	29.79 (13.51)	30.98 (14.05)
4500 psig, 60-min (Carbon Cylinder)	33.7 (15.28)	33.99 (15.41)	35.18 (15.95)	33.7 (15.28)	33.99 (15.41)	35.18 (15.95)
5500 psig, 30-min (Carbon Cylinder)	24.5 (11.11)	24.79 (11.24)	25.98 (11.78)	24.5 (11.11)	24.79 (11.24)	25.98 (11.78)
5500 psig, 45-min (Carbon Cylinder)	28.3 (12.83)	28.59 (12.96)	29.78 (13.50)	28.3 (12.83)	28.59 (12.96)	29.78 (13.50)
5500 psig, 60-min (Carbon Cylinder)	31.9 (14.46)	32.19 (14.60)	33.38 (15.14)	31.9 (14.46)	32.19 (14.60)	33.38 (15.14)
3M™ Scott™ Air-Pak™ XD SCBA (Padded Harness) with 3M™ Scott™ E-Z Flo C5 Regulator						
	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.90 (11.75)	26.19 (11.87)	27.39 (12.42)	25.90 (11.75)	26.19 (11.87)	27.39 (12.42)
4500 psig, 45-min (Carbon Cylinder)	29.80 (13.51)	30.09 (13.64)	31.29 (14.19)	29.80 (13.51)	30.09 (13.64)	31.29 (14.19)
4500 psig, 60-min (Carbon Cylinder)	34.00 (15.42)	34.29 (15.55)	35.49 (16.09)	34.00 (15.42)	34.29 (15.55)	35.49 (16.09)
5500 psig, 30-min (Carbon Cylinder)	24.80 (11.24)	25.09 (11.38)	26.29 (11.92)	24.80 (11.24)	25.09 (11.38)	26.29 (11.92)
5500 psig, 45-min (Carbon Cylinder)	28.60 (12.97)	28.89 (13.10)	30.09 (13.64)	28.60 (12.97)	28.89 (13.10)	30.09 (13.64)
5500 psig, 60-min (Carbon Cylinder)	32.20 (14.60)	32.49 (14.73)	33.69 (15.28)	32.20 (14.60)	32.49 (14.73)	33.69 (15.28)
3M™ Scott™ Air-Pak™ XD SCBA (Unpadded Harness) with 3M™ Scott™ E-Z Flo C5 Regulator						
	Pak-Tracker			SEMS 3.0		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)	25.72 (11.66)	26.01 (11.79)	27.20 (12.33)
4500 psig, 45-min (Carbon Cylinder)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)	29.62 (13.43)	29.91 (13.56)	31.10 (14.10)
4500 psig, 60-min (Carbon Cylinder)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)	33.82 (15.34)	34.11 (15.47)	35.30 (16.01)
5500 psig, 30-min (Carbon Cylinder)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)	24.62 (11.16)	24.91 (11.29)	26.10 (11.83)
5500 psig, 45-min (Carbon Cylinder)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)	28.42 (12.89)	28.71 (13.02)	29.90 (13.56)
5500 psig, 60-min (Carbon Cylinder)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)	32.02 (14.52)	32.31 (14.65)	33.50 (15.19)

*Includes a standard low pressure hose, standard waist belt, no buddy breathing option, and no airline option
Nominal weights in lbs. (kg) with fully charged cylinder

3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA) with 3M™ Scott™ E-Z Flo+ Regulator						
	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.77 (11.69)	26.06 (11.82)	27.25 (12.36)	25.77 (11.69)	26.06 (11.82)	27.25 (12.36)
4500 psig, 45-min (Carbon Cylinder)	29.70 (13.47)	29.99 (13.60)	31.18 (14.14)	29.70 (13.47)	29.99 (13.60)	31.18 (14.14)
4500 psig, 60-min (Carbon Cylinder)	33.98 (15.41)	34.27 (15.54)	35.46 (16.08)	33.98 (15.41)	34.27 (15.54)	35.46 (16.08)
5500 psig, 30-min (Carbon Cylinder)	24.95 (11.32)	25.24 (11.45)	26.43 (11.99)	24.95 (11.32)	25.24 (11.45)	26.43 (11.99)
5500 psig, 45-min (Carbon Cylinder)	28.66 (13.00)	28.95 (13.13)	30.14 (13.67)	28.66 (13.00)	28.95 (13.13)	30.14 (13.67)
5500 psig, 60-min (Carbon Cylinder)	32.37 (14.68)	32.66 (14.81)	33.85 (15.35)	32.37 (14.68)	32.66 (14.81)	33.85 (15.35)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A
3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA) with 3M™ Scott™ E-Z Flo C5 Regulator						
	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.89 (11.74)	26.18 (11.87)	27.37 (12.41)	25.89 (11.74)	26.18 (11.87)	27.37 (12.41)
4500 psig, 45-min (Carbon Cylinder)	29.82 (13.53)	30.11 (13.66)	31.30 (14.20)	29.82 (13.53)	30.11 (13.66)	31.30 (14.20)
4500 psig, 60-min (Carbon Cylinder)	34.10 (15.47)	34.39 (15.60)	35.58 (16.14)	34.10 (15.47)	34.39 (15.60)	35.58 (16.14)
5500 psig, 30-min (Carbon Cylinder)	25.07 (11.37)	25.36 (11.50)	26.55 (12.04)	25.07 (11.37)	25.36 (11.50)	26.55 (12.04)
5500 psig, 45-min (Carbon Cylinder)	28.78 (13.05)	29.07 (13.18)	30.26 (13.72)	28.78 (13.05)	29.07 (13.18)	30.26 (13.72)
5500 psig, 60-min (Carbon Cylinder)	32.49 (14.74)	32.78 (14.87)	33.97 (15.41)	32.49 (14.74)	32.78 (14.87)	33.97 (15.41)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A
3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change) with 3M™ Scott™ E-Z Flo+ Regulator						
	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.38 (11.51)	25.67 (11.64)	26.86 (12.18)	25.38 (11.51)	25.67 (11.64)	26.86 (12.18)
4500 psig, 45-min (Carbon Cylinder)	29.31 (13.29)	29.60 (13.43)	30.79 (13.97)	29.31 (13.29)	29.60 (13.43)	30.79 (13.97)
4500 psig, 60-min (Carbon Cylinder)	33.59 (15.24)	33.88 (15.37)	35.07 (15.91)	33.59 (15.24)	33.88 (15.37)	35.07 (15.91)
5500 psig, 30-min (Carbon Cylinder)	24.56 (11.14)	24.85 (11.27)	26.04 (11.81)	24.56 (11.14)	24.85 (11.27)	26.04 (11.81)
5500 psig, 45-min (Carbon Cylinder)	28.27 (12.82)	28.56 (12.95)	29.75 (13.49)	28.27 (12.82)	28.56 (12.95)	29.75 (13.49)
5500 psig, 60-min (Carbon Cylinder)	31.98 (14.51)	32.27 (14.64)	33.46 (15.18)	31.98 (14.51)	32.27 (14.64)	33.46 (15.18)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A
3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change) with 3M™ Scott™ E-Z Flo C5 Regulator						
	Pak-Tracker			SEMS II Pro		
	Standard*	w/ QD Hose	w/ UEBSS	Standard*	w/ QD Hose	w/ UEBSS
4500 psig, 30-min (Carbon Cylinder)	25.50 (11.57)	25.79 (11.70)	26.98 (12.24)	25.50 (11.57)	25.79 (11.70)	26.98 (12.24)
4500 psig, 45-min (Carbon Cylinder)	29.43 (13.35)	29.72 (13.48)	30.91 (14.02)	29.43 (13.35)	29.72 (13.48)	30.91 (14.02)
4500 psig, 60-min (Carbon Cylinder)	33.71 (15.29)	34.00 (15.40)	35.19 (15.96)	33.71 (15.29)	34.00 (15.40)	35.19 (15.96)
5500 psig, 30-min (Carbon Cylinder)	24.68 (11.19)	24.97 (11.33)	26.16 (11.86)	24.68 (11.19)	24.97 (11.33)	26.16 (11.86)
5500 psig, 45-min (Carbon Cylinder)	28.39 (12.88)	28.68 (13.01)	29.87 (13.55)	28.39 (12.88)	28.68 (13.01)	29.87 (13.55)
5500 psig, 60-min (Carbon Cylinder)	32.10 (14.56)	32.39 (14.69)	33.58 (15.23)	32.01 (14.52)	32.39 (14.69)	33.58 (15.23)
5500 psig, 75-min (Carbon Cylinder)	N/A	N/A	N/A	N/A	N/A	N/A

Certification/Warranty

NIOSH Approvals

3M™ Scott™ Air-Pak™ XD SCBA

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
4500 psig (300 BAR) Models	TC-13F-1343CBRN TC-13F-1349CBRN TC-13F-1355CBRN TC-13F-1361CBRN	TC-13F-1344CBRN TC-13F-1350CBRN TC-13F-1356CBRN TC-13F-1362CBRN	TC-13F-1345CBRN TC-13F-1351CBRN TC-13F-1357CBRN TC-13F-1363CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-1346CBRN TC-13F-1352CBRN TC-13F-1358CBRN TC-13F-1364CBRN	TC-13F-1347CBRN TC-13F-1353CBRN TC-13F-1359CBRN TC-13F-1365CBRN	TC-13F-1348CBRN TC-13F-1354CBRN TC-13F-1360CBRN TC-13F-1366CBRN	N/A

3M™ Scott™ Air-Pak™ X3 Pro SCBA (CGA)

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
4500 psig (300 BAR) Models	TC-13F-1287CBRN TC-13F-1301CBRN TC-13F-1315CBRN TC-13F-1329CBRN	TC-13F-1289CBRN TC-13F-1303CBRN TC-13F-1317CBRN TC-13F-1331CBRN	TC-13F-1291CBRN TC-13F-1305CBRN TC-13F-1319CBRN TC-13F-1333CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-1293CBRN TC-13F-1307CBRN TC-13F-1321CBRN TC-13F-1335CBRN	TC-13F-1295CBRN TC-13F-1309CBRN TC-13F-1323CBRN TC-13F-1337CBRN	TC-13F-1297CBRN TC-13F-1311CBRN TC-13F-1325CBRN TC-13F-1339CBRN	TC-13F-1299CBRN TC-13F-1313CBRN TC-13F-1327CBRN TC-13F-1341CBRN

3M™ Scott™ Air-Pak™ X3 Pro SCBA (Snap-Change)

Model	30 Minutes	45 Minutes	60 Minutes	75 Minutes
4500 psig (300 BAR) Models	TC-13F-1288CBRN TC-13F-1302CBRN TC-13F-1316CBRN TC-13F-1330CBRN	TC-13F-1290CBRN TC-13F-1304CBRN TC-13F-1318CBRN TC-13F-1332CBRN	TC-13F-1292CBRN TC-13F-1306CBRN TC-13F-1320CBRN TC-13F-1334CBRN	N/A
5500 psig (379 BAR) Models	TC-13F-1294CBRN TC-13F-1308CBRN TC-13F-1322CBRN TC-13F-1336CBRN	TC-13F-1296CBRN TC-13F-1310CBRN TC-13F-1324CBRN TC-13F-1338CBRN	TC-13F-1298CBRN TC-13F-1312CBRN TC-13F-1326CBRN TC-13F-1340CBRN	TC-13F-1300CBRN TC-13F-1314CBRN TC-13F-1328CBRN TC-13F-1342CBRN

Warranty

3M™ Scott™ Air-Pak™ SCBA

SCBA (Including electronics and pressure reducer) - As Long As You Own It

3M™ Scott™ Vision C5 Facepiece

Facepiece (less electronics) - As Long As You Own It

Radio Direct Interface (RDI) - 5 Years

Rechargeable Battery and Battery Charger - 3 years

See published warranty statements for further details

Accessories / Options	
Supply Hose	
Hansen	30010-XXX*
Schrader	30020-XXX*
Hansen HK	26369-XXX*
Foster	26370-XXX*
Extended Duration Airline Adapter (Rectus compatible)	
Hansen	201729-01
Foster	201729-02
Hansen HK	201729-03
Schrader	201729-04
Chest Strap	
Universal (Compatible with Air-Pak XD** and Air-Pak X3 Pro SCBA)	201612-01
Waist Belt Extension	
Air-Pak™ X3 Pro SCBA	201614-01
Air-Pak™ XD SCBA	805088-01
Carrying Case	
Hard Plastic	804497-01
Soft Canvas	10009324
Tool Adapter***	
Snap-Change	200388-01
Facepiece	
Storage Bag, Fleece	805534-01
Neck Strap Accessory, AV-3000 HT	804088-02
Neck Strap Accessory, Vision C5	201682-01
Communications Bracket, AV-3000 HT, Open, Right	201210-01
Communications Bracket, AV-3000 HT, Open, Left	201210-02
Mask Hook	804594-01
Eyeglass Kit	
Standard	805753-01
Wire Frame, 52mm, AV-3000 HT	200372-52F
Wire Frame, 60mm, AV-3000 HT	200372-60F
Wire Frame, 52mm, Vision C5	200372-52FC5
Wire Frame, 60mm, Vision C5	200372-60FC5

*XXX denotes length up to 150 ft. Please contact 3M Scott Fire & Safety for more information.

**Chest strap is only compatible with the Air-Pak XD with Padded Harness

***Accommodates 2216 psig, 4500 psig, and 5500 psig Snap-Change cylinders.



3M PSD products are occupational use only.

Personal Safety Division

3M Scott Fire & Safety
Monroe Center, P.O. Box 569
Monroe, NC 28110

Phone: 1-800-247-7257
Email: 3msupport.scott.us@mmm.com
Web: 3M.com/ScottFire
3M.ca/ScottFire

3M, Scott, and Air-Pak are trademarks of 3M. Used under license in Canada. All other trademarks are property of their respective owner. © 2026, 3M. All rights reserved.