

OEM Match made easy

Help save time and effort with
the 3M™ OEM Match Family
of seam sealer solutions

The 3M™ OEM Match Family of seam sealing products are engineered to help technicians of all skill levels more easily replicate the appearance and function of a vehicle's original factory seam sealer.

The system includes our line of seam sealer matching tips and the 2K 3M™ OEM Match Epoxy Seam Sealer in 4 colours – allowing you to replicate the most common OEM seams with one simple application.

Whether you are a novice or seasoned expert, the 3M™ OEM Match Family is designed to make replicating OEM seam sealer easy.



3M™ OEM Match Wing Tip

Helps technicians quickly replicate OEM seams on door skins and hem flanges.

Tip and wing can be trimmed to adjust the size and position of the seam sealer.




Part no.	Product name	Fitting	Packed as
33992	3M™ OEM Match Wing Nozzle 1K Tip	1K Seam Sealer Cartridges (MSP or Polyurethane)	10 nozzles/pack 5 packages/case
33997	3M™ OEM Match Wing Nozzle 2K Tip	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)	10 nozzles/pack 5 packages/case

3M™ OEM Match Ripple Tip

Helps technicians quickly replicate OEM seam sealer textures including caterpillar and lasagna beads.

Width, texture, and height can be controlled by angling nozzle and adjusting air pressure during application.



Part no.	Product name	Fitting	Packed as
33994	3M™ OEM Match Ripple 1K Tip	1K Seam Sealer Cartridges (MSP or Polyurethane)	10 nozzles/pack 5 packages/case
33995	3M™ OEM Match Adjustable Ripple 2K Tip	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)	10 nozzles/pack 5 packages/case

3M™ OEM Match Wide Stream Tip

Helps technicians quickly match OEM seams for smooth or wide applications.

Tip can be trimmed to the required size to match the look of factory-applied materials.



Part no.	Product name	Fitting	Packed as
33993	3M™ OEM Match Wide Stream 1K Tip	1K Seam Sealer Cartridges (MSP or Polyurethane)	10 nozzles/pack 5 packages/case
33998	3M™ OEM Match Wide Stream 2K Tip	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)	10 nozzles/pack 5 packages/case

3M™ OEM Match Spray Tip

Spray multiple patterns to help match OEM seams with simple applicator adjustments.

The 3M™ OEM Match Air Supply Kit, paired with the OEM Match Sprayable Tips, allows technicians to convert pneumatic applicators to spray many 1K and 2K seam sealer products.



Part no.	Product name	Fitting	Packed as
33991	3M™ OEM Match Sprayable 1K Tip	1K MSP Seam Sealer Cartridges	10 nozzles/pack 5 packages/case
33996	3M™ OEM Match Sprayable 2K Tip	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)	10 nozzles/pack 5 packages/case
33999	3M™ OEM Match Air Supply Kit	Can be fitted to all 3M™ Pneumatic Applicators to allow spray application of seam sealers	10 kits/case

3M™ OEM Match Family overview

3M offers professional grade seam sealers, nozzles, tips and applicators to allow technicians of all skill levels to easily replicate OEM seams. The 3M™ OEM Match family joins the full line of 3M™ Seam Sealers to give shops a full toolset to meet the demands of OEM procedures.

	Part no.	Product name	Quantity	Use with/for
Nozzles and applicators	PN09930	3M™ Performance Pneumatic Applicator	1 per case	Pneumatic Applicator for 200 ml 2K material cartridges
	PN08012	3M™ Flexible Package Pneumatic Applicator	1 per case	Pneumatic Applicator – For smooth application of 310mL and 290mL cartridges
	PN08014	3M™ Manual Applicator	1 per case	Manual Gun for Cartridge and Sachet, High Power Version
	PN08193	3M™ Static Mixing Nozzle	6 nozzles/bag, 6 bags/case	Static Mixing Nozzle for 200 ml 2K materials
	PN08206	3M™ OEM Seam Sealer Tip Adapter	6 tips/bag, 6 bags/carton	1K Material flexpack adapter
2K Sealers	PN08524	3M™ OEM Match Epoxy Seam Sealer, White, 200 ml Cartridge	6 per case	► Used in combination with 3M™ OEM Match tips to help replicate some robotically applied OEM seam sealers at the factory ► Caulkable, toolable, brushable, and sprayable ► Non-sagging formula designed for easy to manipulate tooling and texture on vertical and horizontal surfaces ► Adheres to properly prepared bare metal and primed surfaces ► Set and ready to paint after 15 minutes. Fast curing seam sealers reduce potential for rework and allow greater throughput in the body shop
	PN08526	3M™ OEM Match Epoxy Seam Sealer, Gray, 200 ml Cartridge	6 per case	
	PN08522	3M™ OEM Match Epoxy Seam Sealer, Beige, 200 ml Cartridge	6 per case	
	PN08528	3M™ OEM Match Epoxy Seam Sealer, Black, 200 ml Cartridge	6 per case	
	PN05887	3M™ EZ Sand Multi Purpose Repair Material, 200 ml	6 per case	2-part flexible epoxy material used for matching OEM seam sealers
1K Polyurethane Sealers	PN08787	3M™ Polyurethane Seam Sealer, White, 310 ml, Sachet	12 per case	► 1-part high solids urethane material ideal for sealing seams and joints ► Adheres well to bare metal, primed metal and painted surfaces ► Can be smoothed to a featheredge and/or brushed ► Tack free and paintable after 30-45 minutes ► Permanently flexible ► Isocyanate free
	PN08782	3M™ Polyurethane Seam Sealer, Grey, 310 ml, Sachet	12 per case	
	PN08684	3M™ Polyurethane Seam Sealer, Grey, 310 ml, Cartridge	12 per case	
	PN08694	3M™ Polyurethane Seam Sealer, Black, 310 ml, Cartridge	12 per case	
	PN08689	3M™ Polyurethane Seam Sealer, White, 310 ml, Cartridge	12 per case	
1K MSP Sealers	PN08851	3M™ MS Sprayable Seam Sealer, Grey, 290 ml, Cartridge	12 per case	► Heavy-bodied, general purpose, moisture-curing seam sealer for interior and exterior body joints ► Adheres well to properly prepared primer, paint, and bare metal surfaces (except acrylic lacquer) ► Can be caulked or sprayed, allows for painting almost immediately after being applied (wet-on-wet)
	PN08855	3M™ MS Caulkable Sealer, White, 290 ml, Cartridge	12 per case	
	PN50740	3M™ Multi-Purpose Seam Sealer, Beige, 310 ml, Cartridge	9 per case	

	Part no.	Product name	Quantity	Fitting
3M™ OEM Match Nozzles	PN33992	3M™ OEM Match Wing Nozzle 1K Tip	10 nozzles/pack 5 packs/case	1K MSP or Polyurethane Seam Sealer in Cartridge
	PN33993	3M™ OEM Match Wide Stream 1K Tip	10 nozzles/pack 5 packs/case	1K MSP or Polyurethane Seam Sealer in Cartridge
	PN33994	3M™ OEM Match Ripple 1K Tip	10 nozzles/pack 5 packs/case	1K MSP or Polyurethane Seam Sealer in Cartridge
	PN33991	3M™ OEM Match Sprayable 1K Tip	10 nozzles/pack 5 packs/case	1K MSP Seam Sealer in Cartridge
	PN33997	3M™ OEM Match Wing Nozzle 2K Tip	10 nozzles/pack 5 packs/case	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)
	PN33998	3M™ OEM Match Wide Stream 2K Tip	10 nozzles/pack 5 packs/case	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)
	PN33995	3M™ OEM Match Adjustable Ripple Tip 2K	10 nozzles/pack 5 packs/case	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)
	PN33996	3M™ OEM Match Sprayable 2K Tip	10 nozzles/pack 5 packs/case	3M™ Static Mixing Nozzles for 2K products (PN 08193) 3M™ OEM Seam Sealer Tip Adapter for 1K Flexpack Sealers (PN 08206)
	PN33999	3M™ OEM Match Air Supply Kit	10 kits/case	Fits to all 3M™ Pneumatic Applicators to allow spray application of seam sealers



Automotive Aftermarket Division

3M United Kingdom PLC

3M Centre
Cain Road
Bracknell, RG12 8HT
www.3M.co.uk

3M Ireland Ltd

Ella House
39-43 Merriion Square, Dublin 2
D02 NP96, Ireland
www.3Mireland.ie

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3Ms option, replacement of the 3M product or refund of the purchase price.



Find out more about
3M™ OEM Match Family

© 3M 2026. All rights reserved. 3M is a trademark of 3M Company. OMG2232406