

3M[™] Polishing Films Series 291X, 298X, 491X, 498X, 591X and 598X

Product Description

3M[™] Polishing Films Series 291X, 298X, 491X, 498X, 591X and 598X are comprised of micron graded mineral that has been coated onto a fibrous polyester film backing. These films break down into a slurry during use with water for polishing MT style, multi-fiber ferrules. These films are available as plain backing or with pressure sensitive adhesive (PSA) backing.

Applications

MT style, multi-fiber optic connector optic connector polishing and wafer edge cleaning.

Key Features

- Enables better control of fiber protrusion
- Can help improve process throughput
- Precision construction results in fewer rejects
- Can helps reduce slurry mess and contamination on fixtures and machines
- Can helps reduce equipment maintenance costs

Product Construction/Material Description

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product ID	uct ID Product ID		Micron Grade	
(plain back)	(PSA back)	Mineral	(nominal)	Color
291X	298X	Aluminum Oxide	0.5	Pink
			1.0	Light Green
491X	498X	Silicon Carbide	3.0	Gray
591X	598X	Cerium Oxide	0.5	Light Orange

Converted Forms

- Sheets, discs and rolls.
- Maximum width 22 inches.

Backing

• Fibrous film

3M[™] Polishing Films 291X, 298X, 491X, 498X, 591X and 598X

Storage and Shelf Life

The shelf life of 3M[™] Polishing Films 291X, 491X and 591X is 5 years from the date of manufacture when stored in the original packaging materials and stored at 10°C - 30° C (50°F - 86°F) and 30-60% relative humidity.

The shelf life of 3M[™] Polishing Films 298X, 498X and 598X is 24 months from the date of manufacture when stored in the original packaging materials and stored at 10°C - 30° C (50°F - 86°F) and 30-60% relative humidity.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains references to the 3M specifications, test method names, and test results for the product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

Safety Data Sheet: Consult Safety Data Sheet before use.

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product in accordance with all applicable instructions and with appropriate safety equipment, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification on the Certificate of Analysis, which is established when the product is manufactured and deemed commercially available and is provided at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement or repair of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by applicable law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: For industrial use only. Not intended, labeled or packaged for consumer sale or use.



Electronics Materials Solutions Division 3M Center, Building 223-3S-32 St. Paul, MN 55144-1000 1-800-251-8634 phone 1-651-778-4244 fax www.3M.com/electronics

3M is a trademark of 3M Company. Please recycle. ©3M 2023. All rights reserved. 60-5002-0036-9