



Product Change Notice:

3M™ Shielded/Jacketed, Flat Cable Series 3517

.050" 28 AWG Stranded, PVC/PVC

Date: April 6, 2004

Issue Number: 527

To: 3M Electronic Solutions Division Global Copy List
3M Electronic Solutions Division Distribution List
3M Electronic Solutions Manufacturing Rep Firm List
Mara Guzman, 3M EMD

Product: 3M Shielded/Jacketed, Flat Cable Series 3517, .050" 28 AWG Stranded, PVC/PVC

TS0069

3517/09(100')	80400007615	3517/30(100')	80400007441
3517/09(100'SF)	80400007250	3517/34(100')	80400007466
3517/10(100')	80400007276	3517/34(100'SF)	80400007458
3517/10(100'SF)	80400007268	3517/36(100')	80400007482
3517/14(100')	80400007300	3517/36(100'SF)	80400007474
3517/14(100'SF)	80400007292	3517/37(100')	80400007508
3517/15(100')	80400007326	3517/37(300'SF)	80400007490
3517/15(100'SF)	80400007318	3517/40(100')	80400007524
3517/16(100')	80400007342	3517/40(100'SF)	80400007516
3517/16(100'SF)	80400007334	3517/40MJ(100')	80400013605
3517/20(100')	80400007367	3517/50(100')	80400007565
3517/20(100'SF)	80400007359	3517/50(100'SF)	80400007540
3517/24(100')	80400007383	3517/50(300')	80400007532
3517/24(100'SF)	80400007375	3517/50(300'SF)	80400007557
3517/25(100')	80400007409	3517/60(100')	80400007581
3517/25(100'SF)	80400007391	3517/60(100'SF)	80400007573
3517/26(100')	80400007433	3517/64(100')	80400007607
3517/26(100'SF)	80400007425	3517/64(100'SF)	80400007599
3517/26EB(100')	80400016442		

Enhancement:

3M is pleased to announce the 3M™ Shielded/Jacketed, Flat Cable Series 3517 is now RoHS Compliant.

3M's intent is to offer products that allow our customers to be in compliance with the European Union RoHS (Restriction of Hazardous Substances) and WEEE (Waste, Electrical and Electronic Equipment) directives. This change does not affect the form, fit or function of the cable, therefore product numbers and stock numbers will remain unchanged. The description, as well as the factory run number, will be updated to include "RC" for RoHS Compliant.

The Shielded/Jacketed, Flat Cable Series 3517 is available in standard lengths of 100 feet with a minimum order quantity of one roll.

No new literature will be issued at this time. Please use the latest electronic revision of TS-0069 which lists the RoHS and WEEE compliance in the Features and Benefits section.

Actions Required:

- Please notify customers of this enhancement.

Thank you for your continued support of 3M products.

Please direct all correspondence on this matter to :

Jeff Bullion

Copper Product Marketing

Phone: 512-984-5982

Email: jbullion@mmm.com

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electronic Solutions Division

6801 River Place Blvd.

Austin, TX 78726-9000

www.3M.com/interconnects

© 3M 2004