



PELTOR™
Protection & Communication

Keep Connected, Working and Engaged.

Conduct all your business from inside your headset. You can clearly hear incoming callers in your headset by connecting one or two devices using Bluetooth® technology. By using the noise-cancelling boom microphone, you can speak to others at a normal volume even in noisy environments and they can hear you without the surrounding noise interfering with your conversation.

WS™ ALERT™ X+

Large buttons and voice-guided menus

Push-to-Listen function

Ambient Listening Microphones

Noise-cancelling speech microphone

Stainless steel

Partly produced with recycled plastic

USB-C charging jacket with built-in rechargeable Lithium-Ion Battery



Qualcomm®
aptX™ HD

3M™ Connected Equipment App

Control your PELTOR™ Headset through your phone or tablet. The app gives you access to all settings in an easy-to-use interface.

The mobile app simplifies the setup process, allows you to customize your audio experience, and monitor the power status of your headset. If there is a new firmware update available, you can get it via the mobile app (OTA).



Features and functions for WS ALERT Series



PTL - Push-To-Listen function

You can pause streaming quickly and turn on the environmental listening with a double press.

Multifunction Button

Can be customized to be used for different pre-defined features in the 3M Connected Equipment app, such as Bluetooth, Mute Microphone, streaming profiles, Time, APS (Audio Pan Setting).

Ambient Listening Microphones

In low noise, ambient microphones help you hear oncoming vehicles, alerts, and other warning signals when needed and when it's loud helps provide hearing protection.

WAP - Work Audio Profiles

New advanced ambient listening types that allow access to a variety of gain settings, but with frequency shaping, to promote auditory performance in different work environments.

Solar Powered Headband - Powerfoyle

By using the surrounding light to power your headset, it reduces the need of disposable batteries. Innovative light charging material transforming indoor and outdoor light into clean, continuous energy.

Qualcomm® aptX™ HD Adaptive audio

Qualcomm® aptX™ HD Adaptive audio supports robust, high resolution Bluetooth wireless audio.

APS - Audio Pan Setting

Bluetooth®

Bluetooth® MultiPoint technology for connection to one or two external devices for hands-free talk and streaming. Simultaneous, seamless connection to Bluetooth® devices allows for flexibility and mobility.

USB-C charging jack

Built-in rechargeable Lithium-Ion Battery.

Noise-cancelling speech microphone

Helps provide clear communication, in noisy environments.

OTA - Over the air

Over The Air firmware updates help prolong the product lifetime.

3M Connected Equipment App

Control your PELTOR™ Headset through your phone or tablet. The app gives you access to all settings in an easy-to-use interface.

Large buttons and voice-guided menus

No need to remove the headset for any adjustments. Voice confirmation after setting adjustments, including "low battery" voice alert.

Pod and Music mode

Adapt your listening experience with two different streaming settings for pod and music.

Stainless steel

The headset features long-lasting, stainless steel wire bands that can help provide consistent wear experience.

Approved hearing Protection

Complies with Australian/New Zealand Standard AS/NZS 1270:2002.



	3M™ PELTOR™ WS™ ALERT™ X+	3M™ PELTOR™ WS™ ALERT™ XPV
PTL - Push-To-Listen	✓	✓
Multifunction Button	—	✓
Ambient Listening	✓	✓
WAP - Work Audio Profiles	—	✓
Self charging technology	—	✓
Qualcomm™ aptX™ HD	✓	✓
Bluetooth®	Bluetooth® 5.2 Multipoint Technology	Bluetooth® 5.2 Multipoint Technology
USB-C charging jack	USB-C (Built-in Li-Ion Battery)	USB-C (Built-in Li-Ion Battery)
Noise-cancelling boom microphone	✓	✓
OTA - Over the Air Firmware Updates	✓	✓
Available as helmet attachment	✓	—

3M PSD Products are Occupational Use Only.

Product and Content accurate at the time of publication. Products and product information is subject to change. Application images may show product not available in ANZ. Note: 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence or fraudulent misrepresentation

© 3M 2026. All rights reserved. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by 3M Company is under license. Qualcomm aptX is a product of Qualcomm Technologies, Inc. and/or its subsidiaries. Qualcomm is a trademark of Qualcomm Incorporated, registered in the United States and other countries. aptX is a trademark of Qualcomm Technologies International, Ltd., registered in the United States and other countries. The Powerfoyle™ wordmark and logos are registered trademarks owned by Exeger Operations AB. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. 3M, PELTOR, WS and ALERT are trademarks of 3M Company.



3M Australia Pty Ltd
Personal Safety Division
 Bldg A, 1 Rivett Road
 North Ryde NSW 2113
 Customer Service: 1300 363 565
 Email: 3msupport.safety.au@mmm.com
 Web: www.3M.com/au/ppesafety

3M New Zealand Ltd
Personal Safety Division
 94 Apollo Drive, Rosedale
 Auckland 0632
 Customer Service: 0800 252 627
 Email: 3msupport.safety.nz@mmm.com
 Web: www.3M.com/nz/ppesafety