

Parts List

3M-Matic™ 8000af-8000af3

Type 32600

Adjustable Case Sealer

Serial #: _____
For reference, record machine serial number here.

Important Safety Information

BEFORE INSTALLING OR OPERATING THIS EQUIPMENT
Read, understand and follow all safety and operating instructions.

Spare Parts

It is recommended you immediately order the spare parts listed in the “Spare Parts/Service Information” section. These parts are expected to wear through normal use, and should be kept on hand to minimize production delays.


Replacement Parts and Service Information

To Our Customers:

This is the 3M-Matic™/AccuGlide™/Scotch® equipment you ordered.
It has been set up and tested in the factory with Scotch® tapes.
If any problems occur when operating this equipment and you desire a service call or phone consultation, call, write, or fax the appropriate number listed below.

Included with each machine is an Instructions and Parts List Manual.

Service, replacement parts, and additional manuals available direct from:



Order parts by part number, part description, and quantity required.
Also, when ordering parts or additional manuals, include model/machine name, machine type, and serial number that are located on the identification plate.

Replacement Parts and Service Information

To Our Customers:

This is the 3M-Matic™/AccuGlide™/Scotch® equipment you ordered.
It has been set up and tested in the factory with Scotch® Tapes.

Included with each machine is an Instructions and Parts List Manual.

Technical Assistance / Replacement Parts and Additional Manuals:



For technical assistance, contact our help line at 1-800-328-1390.
Provide the customer support coordinator with the model/machine name,
machine type, and serial number that are located on the identification plate
(For example: Model 8000fa-8000af3 - Type 32600 - Serial Number 13282)

To order replacement parts, contact us:

CSPD division of Combi Packaging Systems LLC.
6299 Dressler Rd. NW
North Canton, OH 44720
store.combi.com/CSPD/PublicStore/

1-800-344-9883 Fax: 1-877-847-5883
e-mail: CSPD-CSR@combi.com
www.combi.com

Identification Plate

	3M Company - St. Paul MN 55144 USA 3M - Matic™	Elec. Drawing Schéma électrique 	Conforms to / Conforme à la norme UL 963 Certified to / Certifié selon la norme CSA 22.2 No 68 Indoor Industr. use only / Utilisation industrielle intérieure seulement Control No / Numéro de contrôle 4000563				 Intertek
	Model / Modèle 	Part Number / Numéro de pièce 	VAC / V.c.a. 	Hertz 	Ampère 	Compressed Air/Air Comprimé 	
Type 	Serial Number/Numero de série 	Yr/Année 	Phase 	Watts 	Volume 		

Minimum billing on replacement part orders will be \$50.00

Replacement part information and pricing available on request

There is a 15% restocking fee (per order) on returned parts

Note: Outside of the United States, for replacement parts and ordering information please contact your local /regional 3M or 3M representative.

2. General Information *(continued)*

2.3 Warranty

Equipment Warranty and Limited Remedy: THE FOLLOWING WARRANTY IS MADE IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, THE IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE AND ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, A CUSTOM OR USAGE OF TRADE:

3M sells its 3M-Matic™ 8000af-8000af3 Adjustable Case Sealer, Type 32600 with the following warranties:

1. The drive belts and the taping head knives, springs and rollers will be free from all defects for ninety (90) days after delivery.
2. All other taping head parts will be free from all defects for three (3) years after delivery.
3. All other parts will be free from all defects for two (2) years after delivery.


If any part is proved to be defective within its warranty period, then the exclusive remedy and 3M's and seller's sole obligation shall be, at 3M's option, to repair or replace the part, provided the defective part is returned immediately to 3M's factory or an authorized service station designated by 3M. A part will be presumed to have become defective after its warranty period unless the part is received or 3M is notified of the problem no later than five (5) calendar days after the warranty period. If 3M is unable to repair or replace the part within a reasonable time, then 3M at its option, will replace the equipment or refund the purchase price. 3M shall have no obligation to provide or pay for the labor required to install the repaired or replacement part. 3M shall have no obligation to repair or replace (1) those parts failing due to operator misuse, carelessness, or due to any accidental cause other than equipment failure, or (2) parts failing due to non-lubrication, inadequate cleaning, improper operating environment, improper utilities or operator error.

Limitation of Liability: 3M and seller shall not be liable for direct, indirect, special, incidental or consequential damages based upon breach of warranty, breach of contract, negligence, strict liability or any other legal theory.

The foregoing Equipment Warranty and Limited Remedy and Limitation of Liability may be changed only by a written agreement signed by authorized officers of 3M and seller.

Contents: 8000af-8000af3 Adjustable Case Sealer

- (1) 8000a-8000a3 Adjustable Case Sealer, Type 32600
- (1) Tool and Spare Parts Kit
- (1) Instruction and Parts Manual



Assemblées




Figure 23008

Figure 23008

Ref. No.	3M Part No.	Description
23008-1	78-8055-0640-5	Spacer
23008-2	78-0025-0928-5	Track-cable
23008-3	78-8137-7853-3	Cover-housing
23008-4	78-0025-3156-0	Housing-cable
23008-5	78-0025-3157-8	Bracket-cable track (upper)
23008-6	M8x20 SHCS	Screw-M8x20 shcs
23008-7	M8 WSHR	Washer-M8 plain
23008-8	M5 WSHR	Washer-M5 plain
23008-9	M5X25 HHCS	Screw-M5x25 hhcs
23008-10	M5X12 HHCS	Screw-M5x12 hhcs
23008-11	M4-WSHR FEND	Washer-M4 fender
23008-12	M4X10 HHCS	Screw-M4x10 hhcs
23008-13	78-8060-7758-8	Grommet




Figure 23017




Figure 23017




Figure 23017

Figure 23017

Ref. No.	3M Part No.	Description
23017-1	78-0025-0764-4	Bracket 66×30×40 th=3 skid
23017-2	78-8052-6676-0	Clamp - outer
23017-3	78-8052-6677-8	Clamp - inner
23017-4	M8 WSHR	Washer-m8 plain
23017-5	M8×16 SHCS	Screw-m8×16 SHCS
23017-6	M5X12 PHBHCS	Screw-m5×12 PHBHCS
23017-7	78-8137-8609-8	Rear conveyor plate assy 8000af
23017-8	78-8137-8610-6	Conveyor - rear plate 8000af
23017-9	78-8060-7693-7	Roller-32×38
23017-10	78-8052-6694-3	Shaft - roller 8mm x 128mm
23017-11	78-8010-7163-6	Screw - hex hd, m5 × 10
23017-12	78-8137-8611-4	Conveyor assy - right 8000af
23017-13	78-8137-8613-0	Right conveyor pan 8000af
23017-14	M6 WSHR	Washer-m6 plain
23017-15	M6X12 HHCS	Screw- m6×12 HHCS special
23017-16	78-8137-8612-2	Conveyor assy - left 8000af
23017-17	78-8137-8614-8	Left conveyor pan 8000af
23017-18	78-8076-4771-0	Pin d=8 l=133
23017-19	78-8060-8035-0	E-ring - 7din6799 .25"
23017-20	78-0025-3373-1	Center conveyor assy
23017-21	78-8052-6694-3	Shaft - roller 8mm x 128mm
23017-22	78-8137-8608-0	Central conveyor panel welded 8000af
23017-23	78-8054-8857-0	Shaft - 8×43mm 120af (6227-29)
23017-24	78-8076-4766-0	Shaft - roller 8mm x 128mm
23017-25	M5X10 HHCS	Screw-m5×10 HHCS
23017-26	78-8076-4701-7	Plug hole x d525 /32×2 series 3m
23017-27	78-8137-8615-5	Cover plate left side 800af
23017-28	M6 WSHR	Washer-m6 plain
23017-29	M6X12 SHCS	Screw-m6×12 SHCS
23017-30	M4X10 HHCS	Screw-m4×10 HHCS
23017-31	M6X16 SHCS	Screw-m6×16 SHCS
23017-32	M6X10 PHBHCS	Screw-m6×10 PHBHCS
23017-33	M6 HEX NUT	Nut-M6 hex
23017-34	M8 WSHR FEND	Washer-M8 fender
23017-35	M4-WSHR FEND	Washer-M4 fender
23017-36	78-0025-3463-0	Plate-cover
23017-37	78-0025-3465-5	Support-lower assembly
23017-38	78-8076-4890-8	Fitting - 90 degree elbow, 6mm
23017-39	78-8137-8605-6	Support-lower left assembly
23017-40	78-8060-7722-4	Spacer-l=144
23017-41	78-8091-0696-2	Spacer
23017-42	78-8137-8604-9	Support-lower right assembly
23017-43	M6 WSHR	Washer-M6 plain
23017-44	M6X12 HHCS	Screw- M6×12 HHCS special
23017-45	M6×25 SHCS	Screw-M6×25 SHCS
23017-46	M5 WSHR	Washer-M5 plain

Figure 23017

Ref. No.	3M Part No.	Description
23017-47	78-8032-0382-3	Screw - soc hex hd, M5 × 16
23017-48	M6X16 HHCS	Screw-M6×16 HHCS
23017-49	M8×20 SHCS	Screw-M8×20 SHCS
23017-50	M8 WSHR	Washer-M8 plain
23017-51	M8×16 SHCS	Screw-M8×16 SHCS
23017-52	M8 HEX-L	Nut-M8 hex locking
23017-53	26-1005-6859-6	Nut - self-locking, M5 vc
23017-54	78-8137-8606-4	Support - valve assy, flap folder 8000af
23017-55	78-8054-8857-0	Shaft - 8×43mm 120af (6227-29)
23017-56	78-8076-4779-3	Support - actuator assy
23017-57	M5 WSHR	Washer-M5 plain
23017-58	M5X10 HHCS	Screw-M5×10 HHCS
23017-59	26-1005-6859-6	Nut - self-locking, M5 vc
23017-60	M6X35 SHCS	Screw-M6×35 SHCS
23017-61	26-1002-3866-1	Screw - flat hd, hex dr, M5 × 10
23017-62	M4X35 SHCS	Screw-M4×35 SHCS
23017-63	78-8054-8758-0	Spacer - valve holder
23017-64	78-8059-5607-1	Plate-threaded
23017-65	78-80548757-2	Pin - spring holder
23017-66	78-8076-4774-4	Spring - bed switch
23017-67	78-8055-0746-0	Link - front actr 120af black
23017-68	78-8055-0747-8	Link - rear actr 120af black
23017-69	78-8054-8858-8	Spacer d=8-M5 l=26
23017-70	78-8076-4780-1	Guide - right, actuator
23017-71	78-8076-4781-9	Guide - left, actuator
23017-72	78-8076-4782-7	Cam for flap closer 8000af
23017-73	78-8076-4783-5	Plate for cam
23017-74	26-1005-6358-9	Valve-roller 3 way 2position
23017-75	26-1002-4955-1	Screw-self tapping 8px18
23017-76	78-8119-8554-4	Adhesive rubber (1 meter)
23017-77	78-8076-4772-8	Support assy w/cam-gate
23017-78	78-8054-8857-0	Shaft - 8×43mm 120af (6227-29)
23017-79	78-8054-8858-8	Spacer d=8-M5 l=26
23017-80	26-1005-6358-9	Valve-roller 3 way 2position
23017-81	78-8076-4773-6	Support assy - cam, gate
23017-82	78-8054-8758-0	Spacer - valve holder
23017-83	78-80548757-2	Pin - spring holder
23017-84	78-8076-4774-4	Spring - bed switch
23017-85	26-1002-4955-1	Screw-self tapping 8px18
23017-86	78-8055-0746-0	Link - front actr 120af black
23017-87	78-8055-0747-8	Link - rear actr 120af black
23017-88	78-8119-8554-4	Adhesive rubber (1 meter)
23017-89	78-8076-4775-1	Support assy - cam
23017-90	M4X35 SHCS	Screw-M4×35 SHCS
23017-91	M5 WSHR	Washer-M5 plain
23017-92	26-1005-6859-6	Nut - self-locking, M5 vc
23017-93	M5X10 HHCS	Screw-M5×10 HHCS

Figure 23017

Ref. No.	3M Part No.	Description
23017-94	26-1002-3866-1	Screw - flat hd, hex dr, M5 × 10
23017-95	M5X30 SHCS	Screw-M5×30 SHCS
23017-96	78-8076-4777-7	Cam-short
23017-97	78-8076-4776-9	
23017-98	78-8076-4751-2	Bearing support - gate
23017-99	26-1000-6036-2	Bearing 6003-2rs ntn skf
23017-100	78-0025-3478-8	Bearing support for gate
23017-101	78-8076-4752-0	Gate assy
23017-102	78-8076-4753-8	Spacer - gate
23017-103	78-8076-4754-6	Washer-special d=6.5
23017-104	78-8076-4755-3	Support - cylinder, gate
23017-105	78-0025-3483-8	Bracket for gate cylinder
23017-106	78-0025-3486-1	Bushing
23017-107	78-0025-3487-9	Screw-M8×80 HHCS
23017-108	78-8076-4757-9	Bumper
23017-109	78-8076-4756-1	Shaft - cylinder, gate
23017-110	78-8056-3965-1	Ring - 8 din 6799 (e clip 8mm)
23017-111	78-8076-4902-1	Ball joint cq2
23017-112	78-8076-4901-3	Air cylinder ecq 2b 40-25
23017-113	78-8076-4903-9	Hinge - cylinder /40
23017-114	78-8076-4904-7	Ext-conical ra016 1/8"
23017-115	78-8013-9935-9	Valve-quick exhaust
23017-116	78-8137-3668-9	Screw-M5×65 SHCS
23017-117	78-8076-4897-3	Kqh male connector - one-touch fittings male connector
23017-118	78-8137-8603-1	Bed assy
23017-119	78-0025-3342-6	Painted welded bed 8000af-3M
23017-120	78-0025-3344-2	Leg reinforcement 200a-700a-700r 3M
23017-121	78-0025-0862-6	Fixed door bracket
23017-122	M5X12 SHCS	Screw-M5×12 SHCS
23017-123	M6 WSHR	Washer-M6 plain
23017-124	M6X12 HHCS	Screw- M6×12 HHCS special
23017-125	M6X12 SHCS	Screw-M6×12 SHCS
23017-126	M8 WSHR FEND	Washer-M8 fender
23017-127	M8×16 SHCS	Screw-M8×16 SHCS
23017-128	M5 WSHR FEND	Washer-M5 fender
23017-129	78-8032-0382-3	Screw - soc hex hd, M5 × 16
23017-130	78-8028-8208-0	Screw - self tap 6p x 9.5
23017-131	78-0025-3488-7	Cap-black
23017-132	78-0025-3353-3	Reinforcement lower part of the bed 800af/3M
23017-133	78-0025-3472-1	Sliding leg assembly 3M
23017-134	78-8060-8480-8	Pad - foot
23017-135	78-8055-0867-4	Screw - hex hd, M8 × 30
23017-136	78-8017-9318-9	Washer-plain 8mm
23017-137	26-1003-7963-0	Screw - soc hd, M8 × 16
23017-138	78-8060-8481-6	Label-leg ruler
23017-139	78-8017-9313-0	Nut - self-locking, M8
23017-140	78-0025-2071-2	Bracket - shipping

Figure 23017

Ref. No.	3M Part No.	Description
23017-141	78-0025-3393-9	Leg - inner w/inserts
23017-142	78-8028-8208-0	Screw - self tap 6p x 9.5
23017-143	78-8114-4966-5	Cap - dp-1093 /28
23017-144	78-8060-7886-7	Screw - hex.hd.M6×16 special
23017-145	78-0025-3488-7	Cap-black
23017-146	78-8070-1630-4	Label - cam (2''-27'')
23017-147	78-8137-8577-7	Support - electric box assy
23017-148	78-8060-7758-8	Grommet
23017-149	78-0025-3490-3	Grommet
23017-150	78-8094-6406-4	Rubber cable for hole / 38
23017-151	78-8137-8567-8	Front lock support 8000af-3M
23017-152	78-8076-4932-8	Stop - female latch
23017-153	M6 WSHR FEND	Washer-M6 fender
23017-154	M5 WSHR FEND	Washer-M5 fender
23017-155	26-1005-5316-8	Screw - flat hd hex dr, M5 × 16
23017-156	26-1005-6859-6	Nut - self-locking, M5 vc
23017-157	78-8137-0816-5	Bracket - door latch - rear




Figure 23018

Figure 23018

Ref. No.	3M Part No.	Description
23018-1	78-8091-0766-3	Spacer - drive
23018-2	78-8054-8577-4	Washer-special 6.5×30×5 w/countersink
23018-3	78-8137-8694-0	Drive-motorized assy r/h
23018-4	78-8137-8625-4	Guide - lower, r/h 8000af
23018-5	78-0025-3379-8	Lower right guide assy 8000af
23018-6	78-0025-3380-6	Lower right guide 800af
23018-7	M10X20 HHCS	Screw-M10×20 HHCS
23018-8	78-8060-8014-5	Pulley assembly d=102 l=112 idle
23018-9	78-8052-6710-7	Roller - idler
23018-10	78-8137-8238-6	Pulley
23018-11	78-8070-1530-6	Bearing-6205 2rs
23018-12	78-8054-8913-1	Pin d=M8-16-24.5-25-30 l=112
23018-13	12-7997-0272-0	Snap ring-ext. 25 stainless steel
23018-14	78-8076-4862-7	Driving pulley ass.800af-3M
23018-15	78-8076-5442-7	Flange-assy w/nuts
23018-16	78-8114-4709-9	Flange-bearing support
23018-17	26-1000-4350-9	Bearing-6002 2rs
23018-18	78-8137-7936-6	Nutsert-M6 galvanized
23018-19	78-8137-3777-8	Drive pulley-assy d=103 l=101
23018-20	78-8052-6713-1	Ring-polyurethane friction
23018-21	78-0025-3433-3	Pulley-assy w/shaft
23018-22	5X5X12 KEY	Key-5×5×12
23018-23	78-8054-8877-8	Washer-5.5×20×4 w/countersink
23018-24	M5X12 FSHCS	Screw-M5×12 FSHCS
23018-25	78-8076-5439-3	Flange assy 800af
23018-26	78-8137-7946-5	Bearing-2202 2rs
23018-27	78-8137-7945-7	Support-bearing
23018-28	78-8137-7936-6	Nutsert-M6 galvanized
23018-29	5X5X12 KEY	Key-5×5×12
23018-30	78-8057-5834-5	Washer-lock
23018-31	78-8057-5835-2	Washer-centering (lock nut)
23018-32	M6X12 HHCS	Screw- M6×12 HHCS special
23018-33	78-8091-0757-2	Extension - gearmotor (800af)
23018-34	78-8054-8910-7	Spacer - hexagonal
23018-35	78-8137-8626-2	Guide - upper, r/h 8000af
23018-36	78-8091-0500-6	Bushing - sidedrive
23018-37	78-0025-3435-8	Guide-upper right assy 8000af
23018-38	78-0025-3436-6	Guide-upper right
23018-39	M6 WSHR	Washer-M6 plain
23018-40	M4 WSHR	Washer-M4 plain
23018-41	M4X12 PHBHCS	Screw-M4×12 phbhcs
23018-42	M5X12 SHCS	Screw-M5×12 SHCS
23018-43	M6×20 SHCS	Screw-M6×20 SHCS
23018-44	M8 WSHR	Washer-M8 plain
23018-45	M8 HEX NUT	Nut-M8 hex
23018-46	M10 WSHR	Washer-M10 plain

Figure 23018

Ref. No.	3M Part No.	Description
23018-47	M10 HEX NUT	Nut-M10 hex locking
23018-48	M6×25 SHCS	Screw-M6×25 SHCS
23018-49	78-8076-4933-6	Chain- 3/8 52 links
23018-50	78-8137-8627-0	Cover-drive r/h 8000af
23018-51	78-0025-0602-6	Bracket-drive exit
23018-52	26-1002-4955-1	Screw-self tapping 8px18
23018-53	26-1002-5753-9	Screw - self tapping
23018-54	78-8060-7996-4	Roller-belt
23018-55	78-8060-7995-6	Pin roller
23018-56	78-8137-8629-6	Plate-pin stop r/h top rear
23018-57	78-0025-3437-4	Plate-pin stop r/h front
23018-58	78-8137-8631-2	Plate-pin stop r/h bottom rear
23018-59	78-8091-0764-8	Cover-chain 8000af right
23018-60	78-8054-8903-2	Block - belt
23018-61	78-8054-8904-0	Screw - belt adjustment
23018-62	78-8137-8632-0	Plate-belt tensioner 8000af
23018-63	78-8094-6109-4	Support - gearmotor (800af)
23018-64	78-8070-1522-3	Gearmotor - 115v,60hz,bodine w/cap 1/6hp
23018-65	26-1011-8828-7	Capacitor-15 mf 300v
23018-66	78-8070-1523-1	Screw - 1/4 - 28 × 1/2 SHCS
23018-67	78-8137-0932-2	Tensioner-right
23018-68	78-8076-4865-0	Belt - 800af
23018-69	78-8137-0935-5	Sprocket-3/8" z20
23018-70	78-8137-0934-8	Sprocket-3/8" z-17
23018-71	78-8076-4532-6	Cord grip-pg11
23018-72	78-8060-7877-6	Plug housing-vertical
23018-73	78-8060-7875-0	Plug-male 3p+t
23018-74	78-8134-1975-7	Cable-3g 1.5ul/csa
23018-75	78-8060-7886-7	Screw - hex.hd.M6×16 special

Figure 16076




Figure 23019

Figure 23019

Ref. No.	3M Part No.	Description
23019-1	78-8137-8695-7	L/h motorized belt assy 8000af 115v
23019-2	78-8060-8014-5	Pulley assembly d=102 l=112 idle
23019-3	78-8052-6710-7	Roller - idler
23019-4	78-8137-8238-6	Pulley
23019-5	78-8070-1530-6	Bearing-6205 2rs
23019-6	78-8054-8913-1	Pin d=M8-16-24.5-25-30 l=112
23019-7	12-7997-0272-0	Snap ring-ext. 25 stainless steel
23019-8	78-8076-4862-7	Driving pulley ass.800af-3M
23019-9	78-8076-5442-7	Flange-assy w/nuts
23019-10	78-8114-4709-9	Flange-bearing support
23019-11	26-1000-4350-9	Bearing-6002 2rs
23019-12	78-8137-7936-6	Nutsert-M6 galvanized
23019-13	78-8137-3777-8	Drive pulley-assy d=103 l=101
23019-14	78-8052-6713-1	Ring-polyurethane friction
23019-15	78-0025-3433-3	Pulley-assy w/shaft
23019-16	5X5X12 KEY	Key-5×5×12
23019-17	78-8054-8877-8	Washer-5.5×20×4 w/countersink
23019-18	M5X12 FSHCS	Screw-M5×12 FSHCS
23019-19	78-8137-8696-5	Guide - lower l/h
23019-20	78-0025-3440-8	Lower right guide assy 8000af
23019-21	78-0025-3441-6	Lower left guide 800af
23019-22	M10X20 HHCS	Screw-M10×20 HHCS
23019-23	78-0025-0601-8	Cover-drive l/h 8000af
23019-24	78-0025-0602-6	Bracket-drive exit
23019-25	26-1002-4955-1	Screw-self tapping 8px18
23019-26	5X5X12 KEY	Key-5×5×12
23019-27	M6 WSHR	Washer-M6 plain
23019-28	M4 WSHR	Washer-M4 plain
23019-29	M4X12 PHBHCS	Screw-M4×12 phbhcs
23019-30	M5X25 SHCS	Screw-M5×25 SHCS
23019-31	M6×20 SHCS	Screw-M6×20 SHCS
23019-32	M8 WSHR	Washer-M8 plain
23019-33	M8 HEX NUT	Nut-M8 hex
23019-34	M10 WSHR	Washer-M10 plain
23019-35	M10 HEX NUT	Nut-M10 hex locking
23019-36	M6×25 SHCS	Screw-M6×25 SHCS
23019-37	26-1002-5753-9	Screw - self tapping
23019-38	78-8060-7996-4	Roller-belt
23019-39	78-8060-7995-6	Pin roller
23019-40	78-0025-3442-4	Plate-pin stop l/h front
23019-41	78-0025-0600-0	Plate-pin stop l/h top rear
23019-42	78-8137-8698-1	Plate-pin stop l/h bottom rear
23019-43	78-8076-4865-0	Belt - 800af
23019-44	78-8091-0765-5	Cover-chain 8000af left
23019-45	78-8137-8632-0	Plate-belt tensioner 8000af
23019-46	78-8054-8903-2	Block - belt

Figure 23019

Ref. No.	3M Part No.	Description
23019-47	78-8054-8904-0	Screw - belt adjustment
23019-48	78-8054-8910-7	Spacer - hexagonal
23019-49	M6X12 HHCS	Screw- M6×12 HHCS special
23019-50	78-8094-6109-4	Support - gearmotor (800af)
23019-51	78-8091-0757-2	Extension - gearmotor (800af)
23019-52	78-8076-5439-3	Flange assy 800af
23019-53	78-8137-7946-5	Bearing-2202 2rs
23019-54	78-8137-7945-7	Support-bearing
23019-55	78-8137-7936-6	Nutsert-M6 galvanized
23019-56	78-8076-4933-6	Chain- 3/8 52 links
23019-57	78-8057-5835-2	Washer-centering (lock nut)
23019-58	78-8057-5834-5	Washer-lock
23019-59	78-8070-1522-3	Gearmotor - 115v,60hz,bodine w/cap 1/6hp
23019-60	26-1011-8828-7	Capacitor-15 mf 300v
23019-61	78-8137-0933-0	Tensioner - pulley l/h
23019-62	78-8137-0935-5	Sprocket-3/8" z20
23019-63	78-8137-0934-8	Sprocket-3/8" z-17
23019-64	78-8076-4532-6	Cord grip-pg11
23019-65	78-8060-7877-6	Plug housing-vertical
23019-66	78-8060-7875-0	Plug-male 3p+t
23019-67	78-8134-1975-7	Cable-3g 1.5ul/csa
23019-68	78-8137-8697-3	Guide-upper l/h
23019-69	78-0025-3438-2	Guide-upper left assy 8000af
23019-70	78-0025-3439-0	Guide-upper left
23019-71	M10X20 HHCS	Screw-M10×20 HHCS
23019-72	78-8091-0500-6	Bushing - sidedrive
23019-73	78-8060-7886-7	Screw - hex.hd.M6×16 special
23019-74	78-8070-1523-1	Screw - 1/4 - 28 × 1/2 SHCS
23019-75	78-8091-0766-3	Spacer - drive
23019-76	78-8054-8577-4	Washer-special 6.5×30×5 w/countersink




Figure 23020

Figure 23020

Ref. No.	3M Part No.	Description
23020-1	78-0025-0883-2	Column assy 8000af
23020-2	26-1005-5316-8	Screw - flat hd hex dr, M5 × 16
23020-3	M6 WSHR	Washer-M6 plain
23020-4	M6X16 HHCS	Screw-M6×16 HHCS
23020-5	M4X10 HHCS	Screw-M4×10 HHCS
23020-6	M8 WSHR FEND	Washer-M8 fender
23020-7	M8×16 SHCS	Screw-M8×16 SHCS
23020-8	M8 WSHR	Washer-M8 plain
23020-9	M6X16 SHCS	Screw-M6×16 SHCS
23020-10	M6 WSHR FEND	Washer-M6 fender
23020-11	M4 WSHR	Washer-M4 plain
23020-12	78-8137-8693-2	Sliding column assy
23020-13	78-8059-5625-3	Bearing 6001-2rs
23020-14	26-1000-4350-9	Bearing-6002 2rs
23020-15	M6×20 SHCS	Screw-M6×20 SHCS
23020-16	M6X8 SS	Set screw-M6×8
23020-17	78-8054-8586-5	Roll pin-4×30
23020-18	78-0025-3512-4	Sliding column with ins.
23020-19	78-0025-3513-2	Weldment- sliding column
23020-20	M4X25 SHCS	Screw-M4×25 SHCS
23020-21	78-8076-4815-5	Screw for bearing 6001
23020-22	78-8076-4816-3	Bushing - eccentric
23020-23	78-8137-8545-4	Lead screw
23020-24	78-8054-8968-5	Nut-special
23020-25	78-8054-8585-7	Collar
23020-26	78-8054-8584-0	Bearing-thrust 30mm od 51103
23020-27	78-8054-8583-2	Bushing
23020-28	78-8060-8497-2	Bushing-lead screw w/ss threads
23020-29	78-8060-8498-0	Bushing - inner column
23020-30	78-8060-8499-8	Sprocket - 3/8, z=13 bore=12mm 800a
23020-31	78-0025-3519-9	Fixed column assy
23020-32	M5X12 PHBHCS	Screw-M5×12 phbhcs
23020-33	M8 WSHR FEND	Washer-M8 fender
23020-34	M8×16 SHCS	Screw-M8×16 SHCS
23020-35	M6X12 BSHHCS	Screw-6×12 BSHHCS
23020-36	78-8137-8598-3	(c) fixed column comp. painted 8000af
23020-37	78-8054-8970-1	Plate-lead nut spring
23020-38	78-8054-8997-4	Spring (3871-55)
23020-39	78-8091-0551-9	Nut - lead screw
23020-40	78-8060-8493-1	Plate - nut stop
23020-41	78-8076-4812-2	Plug - outer column
23020-42	78-8060-8490-7	Plate - column mounting
23020-43	78-8076-4811-4	Guide-outer column
23020-44	78-0025-3520-7	Crossbeam chain group
23020-45	M6 WSHR FEND	Washer-M6 fender
23020-46	M6 HEX NUT-L	Nut-M6 hex locking

Figure 23020

Ref. No.	3M Part No.	Description
23020-47	78-8137-8547-0	Crossmember - 8000af
23020-48	78-8070-1503-3	Roller - chain tensioning
23020-49	78-8060-7878-4	Idler screw (3871-31)
23020-50	78-8076-4818-9	Chain - longer for 24" width mod
23020-51	78-8060-8491-5	Cap - column
23020-52	78-8137-8665-0	Cap-column top
23020-53	78-8137-8600-7	Cover-chain crossbeam
23020-54	78-8070-1506-6	Cover-screw
23020-55	78-8060-8073-1	Washer-special 5.5×15 w/countersink
23020-56	78-0025-3522-3	Spacer
23020-57	78-8137-8666-8	Set square stop columns 8000af
23020-58	78-8137-8622-1	Crank assy / manovella mt.64 as-10×10




Figure 23021

Figure 23021

Ref. No.	3M Part No.	Description
23021-1	78-8076-4825-4	Frame - upper, left
23021-2	78-0025-3503-3	Cover-upper support lt
23021-3	78-8070-1555-3	Thumb screw M8
23021-4	78-8060-8087-1	Screw - M5 × 10
23021-5	M5 WSHR FEND	Washer-M5 fender
23021-6	M5X20 SHCS	Screw-M5×20 SHCS
23021-7	78-8076-4823-9	Cover - rear
23021-8	78-8076-4824-7	Frame - upper, right
23021-9	78-0025-3502-5	Cover-upper support rt




Figure 23022

Figure 23022

Ref. No.	3M Part No.	Description
23022-1	M8 WSHR	Washer-M8 plain
23022-2	M8X20 HHCS	Screw-M8×20 HHCS
23022-3	M8×20 SHCS	Screw-M8×20 shcs
23022-4	M8×16 SHCS	Screw-M8×16 shcs
23022-5	M8 WSHR FEND	Washer-M8 fender
23022-6	M6X16 HHCS	Screw-M6×16 HHCS
23022-7	M6 WSHR FEND	Washer-M6 fender
23022-8	78-8137-7900-2	Compression roller assembly
23022-9	78-8076-4631-6	Screw - M10 × 35
23022-10	78-8070-1549-6	Knob - vtr-b-M10
23022-11	78-8017-9074-8	Washer - nylon 10.5m/18×1 (15mm)
23022-12	78-8076-4632-4	Cap - support
23022-13	78-8076-4630-8	Plate - tube, roller
23022-14	78-8137-7901-0	Support - compression roller
23022-15	78-8076-4628-2	Roller - compression
23022-16	78-8076-4629-0	Shaft - roller
23022-17	26-1003-5841-0	Screw - M8 × 16
23022-18	78-8017-9318-9	Washer-plain 8mm
23022-19	78-0025-3491-1	Support-tube
23022-20	78-0025-3492-9	Bracket-support tube rt
23022-21	78-0025-3493-7	Bracket-support tube lt
23022-22	78-8137-8601-5	Support – upper head
23022-23	78-8052-6652-1	Cap - end
23022-24	78-8114-4786-7	Slide - 800af




Figure 23023

Figure 23023

Ref. No.	3M Part No.	Description
23023-1	78-8114-4713-1	Flap folder assy
23023-2	78-8114-4791-7	Block - side flap folder 800af
23023-3	78-8114-4792-5	Plate - side flap folder
23023-4	78-8114-4714-9	Right side galvanized flaps closer
23023-5	78-8114-4715-6	Left galvanized side flaps closer
23023-6	78-8076-4546-6	Knob complete
23023-7	78-8114-4696-0	Spacer - cylinder
23023-8	78-8076-4665-4	Indicator - visual (7357-57)
23023-9	M8 WSHR	Washer-M8 plain
23023-10	M6X20 SS	Set screw-M6×20 ss
23023-11	M8X60 HHCS	Screw-M8×60 HHCS
23023-12	M12 WSHR	Washer-M12 plain
23023-13	M8 HEX-L	Nut-M8 hex locking
23023-14	78-0025-3523-1	Elbow
23023-15	78-0025-3524-9	Flaps closer support assy
23023-16	M6 WSHR	Washer-M6 plain
23023-17	M6×20 SHCS	Screw-M6×20 SHCS
23023-18	M6X16 HHCS	Screw-M6×16 HHCS
23023-19	M6 HEX NUT-L	Nut-M6 hex locking
23023-20	78-8056-3965-1	Ring - 8 din 6799 (e clip 8mm)
23023-21	M8 WSHR FEND	Washer-M8 fender
23023-22	M8 HEX-L	Nut-M8 hex locking
23023-23	M8×20 SHCS	Screw-M8×20 SHCS
23023-24	78-8060-8087-1	Screw - M5 × 10
23023-25	78-8137-8542-1	Flap folder support with inserts
23023-26	78-8076-4832-0	Plate - box guide
23023-27	78-8137-8624-7	Flap folder - front, 8000af
23023-28	78-8076-4833-8	Flat sliding w/ins.800af
23023-29	78-8076-4840-3	Cover - 800af (6419-33)
23023-30	78-8076-4830-4	Cover - flap fold support 800af 6419-32
23023-31	78-8076-4831-2	Pin - air cylinder 12mm dia x 100mm lg
23023-32	78-8091-0740-8	Supp. for hexagonal key 800af mod.29400
23023-33	78-0025-3533-0	Kicker assy
23023-34	78-8137-8543-9	Kicker arm assy
23023-35	78-8114-4711-5	Shaft – support, hex
23023-36	78-8114-4712-3	Spacer - bearing
23023-37	78-8114-4710-7	Washer – support
23023-38	78-8114-4709-9	Flange-bearing support
23023-39	78-8137-8544-7	Cap-kicker assy
23023-40	M4 WSHR	Washer-M4 plain
23023-41	M6X12 SHCS	Screw-M6×12 SHCS
23023-42	78-0025-3535-5	Screw-M4×8 BSHCS
23023-43	26-1000-4350-9	Bearing-6002 2rs
23023-44	78-8060-7758-8	Grommet
23023-45	78-0025-3536-3	Kicker cylinder assy
23023-46	78-8137-8556-1	Pneum. drives 120s40125cn 800af
23023-47	78-8137-8337-6	Pneumatic components (6323003)
23023-48	78-8137-8551-2	Regulator - flux mrf
23023-49	78-8057-5747-9	Mount - cylinder rod end




Figure 23024

Figure 23024

Ref. No.	3M Part No.	Description
23024-1	78-0025-3444-0	Centering assembly
23024-2	78-8091-0743-2	Arm assembly - rear, r/h
23024-3	78-8076-4791-8	Bushing - arm assy
23024-4	78-0025-3451-5	Right rear arm
23024-5	78-8091-0744-0	Arm assembly - rear, l/h
23024-6	78-0025-3452-3	Left rear arm
23024-7	78-8076-4791-8	Bushing - arm assy
23024-8	M10 WSHR	Washer-M10 plain
23024-9	M10 HEX NUT	Nut-M10 hex locking
23024-10	78-8054-8586-5	Roll pin-4×30
23024-11	78-8076-4803-1	Set screw-M5×8
23024-12	78-8076-4796-7	Screw-M10×80 SHCS
23024-13	26-1005-5316-8	Screw - flat hd hex dr, M5 × 16
23024-14	78-8091-0741-6	Arm assembly - front, r/h
23024-15	78-0025-3453-1	Right front arm
23024-16	78-8076-4791-8	Bushing - arm assy
23024-17	78-8091-0742-4	Arm assembly -front, l/h
23024-18	78-0025-3457-2	
23024-19	78-8076-4791-8	Bushing - arm assy
23024-20	78-8060-7521-0	
23024-21	78-8060-7534-3	Washer-nylon
23024-22	78-8076-4754-6	Washer-special d=6.5
23024-23	78-8060-7886-7	Screw - hex.hd.M6×16 special
23024-24	78-8076-4799-1	
23024-25	78-8137-8621-3	Plate-centering arm (left)
23024-26	78-8076-4805-6	Bracket-centering (top) w/bushing
23024-27	78-8060-7984-0	Washer - belleville
23024-28	78-8137-8622-1	Crank assy / manovella mt.64 as-10×10
23024-29	78-8076-4795-9	Spacer
23024-30	78-8076-4793-4	Ball joint - (right hand threads)
23024-31	78-8076-4792-6	Bar - coupling
23024-32	78-8076-4794-2	Ball joint - (left hand threads)
23024-33	78-0025-3460-6	Spacer
23024-34	78-0025-3461-4	Chain assembly
23024-35	78-8054-8787-9	Chain link
23024-36	78-8054-8785-3	Rod - threaded right/left
23024-37	78-8054-8786-1	Chain connector
23024-38	78-8054-8784-6	Block - chain
23024-39	78-8054-8783-8	Washer - special
23024-40	78-8054-8788-7	Chain connector
23024-41	78-8060-7520-2	Screw - M3×20
23024-42	78-8060-7519-4	Screw - M3×25 vcl
23024-43	M6 HEX NUT	Nut-M6 hex
23024-44	M3 HEX-L	Nut-M3 hex locking
23024-45	78-8076-4798-3	Chain 3/8"pitch, 47 pitch
23024-46	78-8056-3945-3	E-ring - M4




Figure 23025

Figure 23025

Ref. No.	3M Part No.	Description
23025-1	78-8060-7873-5	Plug-female 3p+t
23025-2	78-8060-7876-8	Cover-plug
23025-3	M5X12 PHBHCS	Screw-M5×12 phbhcs
23025-4	78-8028-8208-0	Screw - self tap 6p x 9.5
23025-5	M6X16 SHCS	Screw-M6×16 SHCS
23025-6	M4 WSHR	Washer-M4 plain
23025-7	M4X25 SHCS	Screw-M4×25 SHCS
23025-8	78-8137-8576-9	Box-electrical system
23025-9	78-8137-0796-1	Plug-hole pg11
23025-10	78-8094-6384-3	Clamp - vgpe 4/6
23025-11	78-0025-3539-7	Coil - low tension
23025-12	78-0025-3538-9	Switch - 4-6,3 a
23025-13	78-0025-3540-5	Panel cover
23025-14	78-0025-3541-3	Switch-rotary
23025-15	78-0025-3542-1	Spacer
23025-16	78-8137-0607-0	Cord grip
23025-17	78-8129-6469-6	Nut-cord grip M20×1.5
23025-18	78-8060-7873-5	Plug-female 3p+t
23025-19	78-0025-3543-9	Plug housing
23025-20	78-0025-3151-1	Rail-din
23025-21	78-8028-7909-4	Cable power type sjt
23025-22	78-0025-3544-7	Electrical box
23025-23	78-0025-3545-4	Fuse holder
23025-24	78-0025-0920-2	Power supply
23025-25	78-8091-0412-4	Terminal - 1492-j3 grey
23025-26	78-0025-3547-0	Terminal - fuse
23025-27	78-0025-3548-8	Contactor - 24vdc
23025-28	78-0025-3549-6	Relay
23025-29	78-0025-3550-4	Transformer - 50va 0-115v 0-24v
23025-30	78-0025-3552-0	Clamp
23025-31	78-8076-4532-6	Cord grip-pg11
23025-32	78-8060-7877-6	Plug housing-vertical
23025-33	78-8060-7875-0	Plug-male 3p+t
23025-34	78-0025-0680-2	Panel-support assy
23025-35	78-0025-3553-8	Adapter plate assy
23025-36	78-0025-3557-9	Spacer
23025-37	78-0025-3558-7	Push button panel 8000af
23025-38	78-8137-8080-2	Housing - white
23025-39	78-8137-8079-4	Push button - start/stop
23025-40	78-8137-8081-0	Contact block - M22-k10, 1no, eaton
23025-41	78-8137-8082-8	Light unit - M22-led-white
23025-42	78-8137-8085-1	Contact block - M22-k01, 1nc, eaton
23025-43	78-8137-8084-4	Fixing adapter - M22-a
23025-44	78-8137-8422-6	Switch - selector
23025-45	78-8137-0607-0	Cord grip
23025-46	78-8129-6469-6	Nut-cord grip M20×1.5

Figure 23025

Ref. No.	3M Part No.	Description
23025-47	78-8137-8578-5	Plate holder - d22 ptar22
23025-48	78-0025-3543-9	Plug housing
23025-49	78-0025-3555-3	Plug-male
23025-50	78-0025-3556-1	Plug-female





Figure 23026

Figure 23026

Ref. No.	3M Part No.	Description
23026-1	78-8137-8618-9	Ext. roll holder support 8000af
23026-2	78-8137-8619-7	Support 3 rollers external 8000af
23026-3	78-8076-5028-4	Shaft - roller (7359-87)
23026-4	78-8076-5030-0	Roller - knurled
23026-5	78-8076-5031-8	Shaft - roller
23026-6	78-8076-5032-6	Roller - knurled, 110.5 mm
23026-7	26-1000-0010-3	Washer - flat, M6 × 11.8 × 1.6
23026-8	78-8032-0375-7	Screw - hex hd, M6 × 16
23026-9	78-8114-4717-2	Bracket assembly
23026-10	78-8076-5033-4	Bracket-arm 3 rollers 800af 700rks
23026-11	78-8114-4718-0	Shaft
23026-12	78-8114-4719-8	Roller
23026-13	M6 WSHR	Washer-M6 plain
23026-14	M6X12 HHCS	Screw- M6×12 hhcs special
23026-15	M6X16 SHCS	Screw-M6×16 SHCS
23026-16	M6 WSHR FEND	Washer-M6 fender
23026-17	78-0025-3559-5	Upper outboard taping assy
23026-18	78-8137-8634-6	Tape drum arm assy
23026-19	78-8070-1568-6	Cap - bracket
23026-20	78-0025-3154-5	Tape drum assy 2"
23026-21	78-8017-9169-6	Nut - M18 × 1
23026-22	78-8098-8814-8	Tape drum assy w/shaft 2"
23026-23	78-8098-8827-0	Tape drum sub assembly - 2 inch
23026-24	78-8098-8749-6	Drum-tape 2"
23026-25	78-8098-8817-1	Spring-leaf 2"
23026-26	78-8098-8816-3	Latch - tape drum
23026-27	26-1002-6167-1	Screw - self tapping
23026-28	78-8076-4519-3	Shaft-tape drum 2"
23026-29	78-8060-8172-1	Washer - friction
23026-30	78-8052-6271-0	Washer - tape drum
23026-31	78-8100-1048-4	Spring - core holder
23026-32	26-1004-5510-9	Washer - plain, M10 × 20 × 2.5
23026-33	78-8017-9077-1	Nut - self locking, M10 × 1




Figure 23027

Figure 23027

Ref. No.	3M Part No.	Description
23027-1	78-0025-0882-4	Guarding assy. 8000af
23027-2	78-0025-0865-9	Bumper d24.5-11.5 sp.14.5
23027-3	78-8137-8557-9	Assembly upright with e-stop 8000af opening
23027-4	78-8137-8558-7	Guarding upright support w/ins. 8000af
23027-5	78-8137-8559-5	Cap for tubular 100×40 black - 8000af-3M
23027-6	78-8137-8565-2	Bracket-guarding emergency button 8000af-3M
23027-7	78-8137-8560-3	Guarding support bracket
23027-8	78-8129-6293-0	Hinge - elesa
23027-9	78-8060-7807-3	Handle M443/110
23027-10	78-8137-8563-7	Guarding rear door lock 8000af-3M
23027-11	78-8076-4931-0	Stop - male latch
23027-12	78-8137-8540-5	Guarding door w/inserts 8000af-3M
23027-13	78-8137-8623-9	Interlock bracket 8000af
23027-14	78-8137-8569-4	Photocell support 8000af-3M
23027-15	78-8137-0810-0	Fixed panel w/ins 800af -3M
23027-16	78-8137-0822-5	Front locking plate 800af-3M
23027-17	78-8137-0821-7	Guarding crossbeam 800af 3M
23027-18	78-8137-8564-5	Guarding door stop 8000af-3M
23027-19	78-0025-0863-4	Guarding door bracket-verticle
23027-20	78-0025-0864-2	Door lock bracket-Interlock
23027-21	78-0025-0866-7	Door 1200 × 641 w/ ins.
23027-22	M3 WSHR	Washer-M3 Plain
23027-23	M3 HEX-L	Nut-M3 HEX Locking
23027-24	M3X12 SHCS	Screw-M3X12 SHCS
23027-25	78-8076-5057-3	Reflector - Omron E39-R1
23027-26	78-8137-7972-1	Photocell-Polarized M18 PNP 3MT
23027-27	M6X25 FSHCS	Screw-M6X25 FSHCS
23027-28	M8 WSHR	Washer-M8 Plain
23027-29	M8 WSHR FEND	Washer-M8 Fender
23027-30	M8×20 SHCS	Screw-M8X20 SHCS
23027-31	M6 WSHR FEND	Washer-M6 Fender
23027-32	M6×20 SHCS	Screw-M6X20 SHCS
23027-33	M6 WSHR	Washer-M6 Plain
23027-34	M5 WSHR	Washer-M5 Plain
23027-35	M5X12 SHCS	Screw-M5X12 SHCS
23027-36	78-8032-0382-3	Screw - Soc Hex Hd, M5 × 16
23027-37	M5 WSHR FEND	Washer-M5 Fender
23027-38	M5X12 FSHCS	Screw-M5X12 FSHCS
23027-39	26-1005-5316-8	Screw - Flat Hd Hex Dr, M5 × 16
23027-40	26-1005-6859-6	Nut - Self-Locking, M5 VC
23027-41	M6X16 SHCS	Screw-M6X16 SHCS
23027-42	M10 WSHR	Washer-M10 Plain
23027-43	M10 HEX NUT	Nut-M10 HEX Locking
23027-44	78-0025-3564-5	Screw-M10X35 SHCS
23027-45	78-8076-4929-4	Safety Interlock 800af AZ15ZVR
23027-46	78-8133-9241-8	Cord Grip - M16 × 1.5

Figure 23027

Ref. No.	3M Part No.	Description
23027-47	78-0025-3364-0	M5×16 One-Way pan head screw
23027-48	M5X25 SHCS	Screw-M5X25 SHCS




Figure 23036

Figure 23036

Ref. No.	3M Part No.	Description
23036-1	26-1005-6890-1	Muffler - bronze 1/8"
23036-2	78-0025-3523-1	Elbow
23036-3	78-0025-3565-2	Elbow
23036-4	78-8060-7651-5	Fr - distributor block
23036-5	78-8060-7690-3	Cap - b-1/8 inch
23036-6	78-8076-4679-5	Junction t intermediate 31040400
23036-7	78-8076-4886-6	Obs - use pn0190023 - muffler 1/4"
23036-8	78-8076-4889-0	Kqh male connector - one-touch fittings male connector
23036-9	78-8076-4890-8	Fitting - 90 degree elbow, 6mm
23036-10	78-8076-4891-6	Kqh male connector - one-touch fittings male connector
23036-11	78-8076-4897-3	Kqh male connector - one-touch fittings male connector
23036-12	78-8076-4898-1	Kqt union tee - 6 x 6 x 6mm
23036-13	78-8076-4899-9	Kqr plug-in reducer - one-touch fittings plug-in reducer
23036-14	78-8091-0313-4	Ftg - elbow 3199.08.10
23036-15	78-8137-7954-9	Regulator - centering assembly
23036-16	26-1005-6901-6	Fitting - dir.m.cil.31010613
23036-17	78-8055-0756-9	Union rotating mr41-6-14 (elbow 1/4 x 6mm)
23036-18	78-8137-7702-2	Regulator sy1 1/4 08
23036-19	78-8137-8140-4	Brkt - air pressure regulator, 7000r
23036-20	78-8137-8249-3	Air pressure assembly - 24vdc
23036-21	78-8054-8838-0	Guage - air (6236-15)
23036-22	26-1005-6897-6	Hose connector ra030 9-1/4"(6236-18) vc
23036-23	78-8060-7900-6	Union - ra022 1/4"-1/4"
23036-24	78-8119-8615-3	Male elbow g1/4-10 31991013 legris
23036-25	78-8137-7704-8	Silencer mwspl-f 1/8
23036-26	78-8137-7957-2	Valve - manual v3v sy1
23036-27	78-0025-0620-8	Connector
23036-28	78-8137-8252-7	Filter - regulator fr sy1
23036-29	78-8137-7701-4	Coil - 22 ø8 ba 2w-24vdc ur
	78-8137-8589-2	Air supply solenoid cable
23036-30	78-8137-6395-6	Filter - regulator fr sy1 20 08 ra
23036-31	78-8137-8250-1	Special pressure switch sy no bushes
23036-32	78-8137-8251-9	Coupler
23036-33	78-8137-8552-0	Pneumatic valve pnv35pnb00 - 7020011200
23036-34	78-8137-8553-8	Elbow-one-touch fitting kq2l08-03s smc
23036-35	78-8137-8554-6	Pneumatic valve pnv23pnsnc - 7010010200
23036-36	78-8137-8555-3	In-line flow regulator ø6
23036-37	M4 HEX-L	Nut-M4 hex-l
23036-38	M4 WSHR	Washer-M4 plain
23036-39	M4X35 SHCS	Screw-M4x55 SHCS
23036-40	M4X55 SHCS	Screw-M4x55 SHCS
23036-41	M5 WSHR	Washer-M5 plain
23036-42	M5X25 SHCS	Screw-M5x25 SHCS

