



Choose the right floor pad for the job.

Maintenance Operation	Equipment Speed	First Choice		Alternate Choices			
Stripping To remove finish, sealer and contaminants from the floor surface.	Rotary or Automatic Low Speed 175–600 RPM		3M™ High Productivity Pad 7300 Our most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping.		3M™ Black Stripper Pad 7200 For consistent, proven performance, with a longer pad life. 75% more aggressive than the nearest competitor pad.		3M™ Brown Stripper Pad 7100 A conformable stripping pad for uneven floors. Effectively strips 2–4 coats of existing finishes.
Scrubbing To provide a fresh new surface for finishing.	Rotary or Automatic Low Speed 175–600 RPM		Scotch-Brite™ Surface Preparation Pad Heavy-duty scrubbing for top coat removal prior to recoating.		Scotch-Brite™ Surface Preparation Pad Plus Long-lasting, high performance scrubbing pad. Open fibers for less clogging and no backer pad is required.		3M™ Blue Cleaner Pad 5300 Heavy-duty scrubbing of floors.
Cleaning To remove light soil and other contaminants.	Rotary or Automatic Low Speed 175–600 RPM		Scotch-Brite™ Clean & Shine Pad 2-in-1 daily cleaning pad for low-speed scrubbers that gradually increases shine with repeated use.		3M™ TopLine Autoscrubber Pad 5000 Open construction resists clogging for improved cleaning. Ideal for heavily trafficked/soiled conditions or in conjunction with a high-frequency burnishing program.		3M™ Red Buffer Pad 5100 For everyday cleaning and light scrubbing. Removes light soil, scuff marks and black heel marks.
Buffing To remove scuffs and black heel marks and enhance floor appearance.	Rotary Low Speed 175–600 RPM		3M™ White Super Polish Pad 4100 Ideal for removing soil and scuff marks with minimal dulling. Also used to polish wood floors.		3M™ Red Buffer Pad 5100 Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.		
Burnishing To remove scuffs and marks, repair finish and improve gloss and image clarity.	Electric, Battery, Propane Ultra High Speed 1500 RPM & Above		3M™ Eraser Burnish Pad 3600 Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes and high traffic areas. Excellent durability and minimal finish removal.		3M™ Natural Blend Tan Pad 3500 Removes marks and scuffs while polishing harder finishes and high-traffic surfaces. Blend of natural and synthetic fibers.		3M™ Tan Burnish Pad 3400 Produces good gloss improvement while removing scuffs and marks. Exceptional durability and life. Ideal for harder finishes and high traffic conditions.
Best Gloss	Electric, Battery, Propane Ultra High Speed 1500 RPM & Above		3M™ Tan Burnish Pad 3400 Produces good gloss improvement while removing scuffs and marks. Exceptional durability and life. Ideal for harder finishes and high traffic conditions.		3M™ Natural Blend White Pad 3300 Provides consistent high gloss while minimizing swirl marks for a wide variety of finishes and traffic conditions. Blend of natural and synthetic fibers.		
Soft Finish	Electric, Battery, Propane Ultra High Speed 1500 RPM & Above		3M™ Sky Blue Hi-Performance Burnish Pad 3050 Restores gloss to dull floors. Use for frequent burnishing with less dust, point buildup and burning.		3M™ Aqua Burnish Pad 3100 Good gloss improvement with exceptional durability and life. The soft finish problem solver.		
Stone Floor Conditioning To clean and condition worn and dull stone floors.	Rotary, Automatic, Electric, Battery or Propane Low to Ultra High Speed 175–1500 RPM & Above		Scotch-Brite™ Sienna Diamond Floor Pad Plus Diamond-coated floor pad for cleaning and conditioning worn and dull marble, terrazzo and polished concrete flooring.	Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.			
Stone Floor Polishing To clean and polish stone floors with medium shine in good condition.	Rotary, Automatic, Electric, Battery or Propane Low to Ultra High Speed 175–1500 RPM & Above		Scotch-Brite™ Purple Diamond Floor Pad Plus Diamond-coated floor pad for cleaning and polishing marble, and polished concrete flooring.				

© 3M 2026. All rights reserved. 3M and Scotch-Brite are trademarks of 3M. Used under license in Canada. Please recycle. 78-8134-0533-3 (Rev. 07/2026)