



Science.
Applied to Life.™



Robust masking performance

Now featuring  30% recycled content

The 3M™ Plastic Sheetting offering now incorporates 30% recycled content with tear resistance, easy handling and masking performance collision repair professionals can depend on.

Combined with 3M™ Masking Tapes and Specialty Tapes, it is part of a complete masking solution designed to support efficient repair workflows and consistent results.

One system. One workflow. Trusted 3M performance.

3M™ Purple Premium Moisture-Resistant Plastic Sheet

Delivers high-precision masking with excellent cling, moisture protection, and clean cutting for top-tier refinishing results

- *Moisture-resistant layer helps prevent ghosting and imprinting*
- *Excellent cling for fast, precise placement*

Part no.	Colour	Dimensions	Rolls/Case
5097R	Purple	5 m x 75 m (16 ft x 246 ft)	1

Contains 30% Pre-Consumer Recycled Content



Moisture Resistance

3M™ Advanced Plastic Sheet

Provides fast, reliable coverage with strong overspray adhesion and durability for efficient repair workflows

- *Robust and more puncture resistant*
- *Designed to allow repositioning of masking tape without tearing*

Part no.	Colour	Dimensions	Rolls/Case
8011R	Clear	5 m x 120 m (16 ft x 393 ft)	1
8013R	Clear	6 m x 80 m (19 ft x 262 ft)	1
8017R	Clear	4 m x 120 m (13 ft x 393 ft)	1

Contains 30% Post-Consumer Recycled Content



Robustness

3M™ Standard Plus Plastic Sheet

Ensures dependable masking with good cling, easy handling, and consistent performance for routine body shop tasks

- *Easy to cut for better handling around body contour*
- *Very good overspray retention for reliable results*

Part no.	Colour	Dimensions	Rolls/Case
5067R	Clear	4 m x 150 m (13 ft x 492 ft)	1
5068R	Clear	4 m x 80 m (13 ft x 262 ft)	1
5101R	Clear	5 m x 120 m (16 ft x 393 ft)	1

Contains 30% Post-Consumer Recycled Content



Easy Cutting

Choose your 3M™ Plastic Sheeting

	Thickness	Robustness	Cutability	Clinging Power	Tape repositioning	Moisture resistance
3M™ Purple Premium Moisture-Resistant Plastic Sheeting	● ● ● ● ●	● ● ● ● ●	● ● ● ● ●	● ● ● ● ●	● ● ● ● ●	✓
3M™ Advanced Plastic Sheeting	● ● ● ● ○	● ● ● ● ○	● ● ● ● ○	● ● ● ● ○	● ● ● ● ○	✗
3M™ Standard Plus Plastic Sheeting	● ● ● ● ○	● ● ● ○ ○	● ● ● ○ ○	● ● ● ○ ○	● ● ● ○ ○	✗

Complete the masking workflow

3M Masking Tapes and Specialty Tapes are designed to work alongside 3M Plastic Sheeting to help support efficient preparation, clean paint lines and high-quality finishing results.

Select the right 3M™ Masking Tape to get the job done

3M™ Performance Green Masking Tape 233+

A premium all-around masking tape with superior conformability and excellent clean removal

Part no.	Dimensions	Rolls/Sleeve	Rolls/Carton
26343	3 mm x 55 m (1/8 in x 60 yds)	12	144
26344	6 mm x 55 m (1/4 in x 60 yds)	12	96
26332	12 mm x 55 m (1/2 in x 60 yds)	12	48
26334	18 mm x 55 m (3/4 in x 60 yds)	12	48
26336	24 mm x 55 m (1 in x 60 yds)	6	24
26338	36 mm x 55 m (1 1/2 in x 60 yds)	4	16
26340	48 mm x 55 m (2 in x 60 yds)	3	12
26341	72 mm x 55 m (3 in x 60 yds)	2	8
44608	96 mm x 55 m (3 3/4 in x 60 yds)	2	8

3M™ Performance Yellow Masking Tape 388N

A balanced all-around masking tape with excellent stick and stay

Part no.	Dimensions	Rolls/Sleeve	Rolls/Carton
06652	18 mm x 55 m (3/4 in x 60 yds)	12	48
06653	24 mm x 55 m (1 in x 60 yds)	9	36
06654	36 mm x 55 m (1 1/2 in x 60 yds)	6	24
06656	48 mm x 55 m (2 in x 60 yds)	6	24

3M™ Automotive Masking Tape 2308

A cost-effective masking tape good for everyday use

Part no.	Dimensions	Rolls/Sleeve	Rolls/Carton
06545	18 mm x 55 m (3/4 in x 60 yds)	12	48
06547	36 mm x 55 m (1 1/2 in x 60 yds)	6	24
06548	48 mm x 55 m (2 in x 60 yds)	6	24

Comparing 3M™ Masking Tapes

	Adhesion	Conformability	Sliver resistance	Clean removal	Humidity resistance	UV resistance (3 Days)
3M™ Performance Green Masking Tape 233+	● ● ● ● ○	● ● ● ● ●	● ● ● ● ●	● ● ● ● ●	● ● ● ● ○	✓
3M™ Performance Yellow Masking Tape 388N	● ● ● ● ○	● ● ○ ○ ○	● ● ● ● ○	● ● ● ● ○	● ● ● ● ○	✓
3M™ Automotive Masking Tape 2308	● ● ○ ○ ○	● ● ○ ○ ○	● ● ○ ○ ○	● ● ● ● ○	● ● ● ○ ○	✗


3M™ Specialty Tapes

Designed to help create smooth transitions and professional finish quality.

3M™ Soft Edge Foam Masking Tape

Foam tape eliminates hard paint lines in jamb areas, helps reduce rework, and offers a more simplified application compared to masking with conventional tape

Part no.	Product name	Dimensions	Rolls/Case
50421	Soft Edge Foam Tape PLUS	21 mm x 49 m (0.82 in x 53.5 yds)	1
09678	Soft Edge Foam Tape	13 mm x 50 m (0.51 in x 54.68 yds)	1
09973	Soft Edge Foam Tape	19 mm x 35 m (0.74 in x 38.3 yds)	1



3M™ Smooth Transition Tape

An easy-to-use tape designed to help virtually eliminate rework caused by hard paint lines and create smooth transitions to existing finishes

Part no.	Colour	Dimensions	Rolls/Case
06800	Clear	6.35 mm x 9 m (1/4 in x 9.8 yds)	1



3M™ Perforated Trim Masking Tape

Features a rigid band along one edge that slips gently behind mouldings, lifting them slightly away from the body allowing paint to flow beneath

Part no.	Insert depth	Dimensions	Rolls/Case
06345	5 mm	50.8 mm x 10 m (2 in x 10.94 yds)	6
06347	7 mm	50.8 mm x 10 m (2 in x 10.94 yds)	6
06349	10 mm	50.8 mm x 10 m (2 in x 10.94 yds)	6
06348	15 mm	50.8 mm x 10 m (2 in x 10.94 yds)	6



Better together: Build a complete 3M™ Masking System

3M™ Plastic Sheeting, Masking Tapes and Specialty Tapes are designed to work together to help create a more efficient masking workflow—from vehicle coverage and edge definition to smooth paint transitions.



Cover

Protect the vehicle with 3M™ Plastic Sheeting



Define

Secure the perimeter with 3M™ Masking Tapes



Refine

Mask critical detail areas with 3M™ Specialty Tapes



Finish

Achieve consistent masking results across the repair process

One system. One workflow. Trusted performance.

The masking process may be the most overlooked step of refinishing—yet it is the most time consuming. If done properly with the correct tools and products, it can greatly reduce rework.

By choosing a complete 3M masking system designed to work together across every stage of the process, collision repair professionals can achieve efficient preparation, reliable application, and high-quality results.

Made to fit the way you mask

In busy collision repair environments, masking materials need to be easy to handle and tough enough for real application demands.

Robustness, cutability and tear resistance all play an important role.



With 3M™ Plastic Sheetting, Masking Tapes and Specialty Tapes, collision repair professionals can work with products designed to handle repositioning, help reduce overspray risk and support a professional finish.



Automotive Aftermarket Division

3M Canada

P.O. Box 5757

London, ON N6A 4T1

Phone 1-877-666-2277

Web www.3MCollision.ca

Limited Warranty & Limitation of Liability: 3M warrants this product will meet 3M specifications at the time of 3M shipment. Except as required by applicable law, 3M MAKES NO OTHER WARRANTIES OR CONDITIONS INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If there is a breach of this warranty, your exclusive remedy shall be product replacement or repair, or refund of purchase price. 3M will not be liable for any direct, indirect, special, incidental, or consequential damage related to the product.

For industrial/occupational use only. Not for consumer sale or use.

3M is a trademark of 3M Company. All other trademarks are property of their respective owners. Please recycle. © 3M 2026. All rights reserved. 60-440 5-0309-6