



3M™ Endorsed Architectural Finishes Installer Advanced Training with final exam

You can expect theoretical and practical content on the installation of architectural films. You will gain an insight into the 3M product portfolio in this area, and, under the guidance of our experienced, certified trainer, you will become intensively familiar with both the handling of the material and the necessary framework conditions for projects.

Prerequisites for participation:

- Experienced, active film installer in the field of PVC films (with at least 2 years of professional experience), especially with architectural films
- Traders or employed by a specialist company
- Large-area installation is practiced, especially the handling of full material widths
- Basic film knowledge (product properties and differentiation, application knowledge, understanding and effects of external influencing factors) is available

Learning objectives:

- Adhesive properties and surface science
- Surface preparation
- Requirements for installation
- Required tools and auxiliary materials
- Application on flat substrates
- Impact bonding
- Application to edges
- Inside corner/ outside corner
- Cylinder installation
- Learning and understanding the different application methods
- Selection of suitable materials for the requirements of the project

Each participant receives the 3M™ Endorsed Architectural Finishes Installer certificate upon successful completion of the assessment.

Successful completion of the assessment is a prerequisite for 3M Select certification of your company. In addition, a company audit of the specialist company is required in all cases.

Training duration:

Start: 1st day, at 9.00 a.m.

End: 3rd day, approx. 5 p.m.

Training program:

Day 1: Theory and trainer demo in the morning, practice in the afternoon

Day 2: Practice, start of the practical assessment

Day 3: Theoretical and practical assessment

In the first two days you will learn the correct application of the 3M™ DI-NOC™ surface finish. Special techniques will be demonstrated for the complete installation of wall panels, furniture and other interior design elements.

The course also includes facts worth knowing about the key benefits of 3M™ interior design solutions, which offer you strong sales arguments

Trained range of films:

Different versions of the 3M™ DI-NOC

Please note:

The training is aimed at employees of specialist companies in the film installation sector.

Maximum number of participants 4 persons per training date; guaranteed implementation from 3 participants.

We ask you to pay the invoice up to 14 days before the start of the event. All registrations from participants who have not paid by 14 days before the start of the event will be cancelled and reassigned.

Cancellation free of charge up to 14 days before the start of the event. After that 100% of the costs will be charged.

