



3M™ Endorsed Paint Protection Installer Training with final assessment (Module 2)

The certification training course checks whether the participant has the theoretical knowledge and practical skills to carry out vehicle wrapping with 3M™ paint protection films for their customers in accordance with 3M standards.

This means that the participant:

- demonstrates achievement of the learning objectives of the 3M™ Endorsed Paint Protection Film Installer Advanced Training course
- the objects are installed in the highest quality and within the specified time
- can influence the choice of products and decide correctly on their use (written test)

This is followed by an individual feedback meeting in which the results are discussed, strengths and weaknesses are analysed and suggestions for improvement are made.

Prerequisites for participation:

- Participation in the 3M™ Endorsed Paint Protection Film Installer Advanced Training (recommended interval to certification at least 3 months)
- Experienced installers who know and use the trained 3M products
- Film knowledge and installation guidelines according to 3M specifications
- Knowledge of the assessment criteria and requirements for certification
- Willingness to take the practical test, which is a prerequisite for successful 3M Endorsed Installer certification

Learning objectives:

The aim is to test your know-how in the installation of 3M™ paint protection films in accordance with specified 3M standards.

Each participant receives the 3M™ Endorsed Paint Protection Installer certificate after successfully completing the assessment.

Successful completion of installer assessment is a prerequisite for 3M Select certification of your company. In addition, a company audit of the specialist company is required in all cases.

Training duration:

Start: 1st day, at 9.00 a.m.
End: 2nd day, approx. 4.00 p.m.

Training program:

Day 1: Opportunity to practice, start of the practical assessment at midday

Day 2: Written test, continuing with practical assessment

Review of the most important information on the materials used and practical exercises in preparation for the practical test.

Trained range of films:

- 3M™ Scotchgard™ Paint Protection Film Pro Series 200
- 3M™ Paint Protection Film Series 150
- 3M™ Paint Protection Film Series 100

ATTENTION!

Participants receive tools, theoretical teaching materials and intensive training in application techniques exclusively in Module 1 (advanced training).

Please note:

The training is aimed at employees of specialist companies in the film installation sector.

Maximum number of participants 4 persons per training date; guaranteed implementation from 3 participants.

We ask you to pay the invoice up to 14 days before the start of the event. All registrations from participants who have not paid by 14 days before the start of the event will be cancelled and reassigned.

Cancellation free of charge up to 14 days before the start of the event. After that 100% of the costs will be charged.

