

# **3M Spark Arrest Cover GVP-146**

*ATTENTION: NEW PRODUCT*  
*(For Use in Grinding and Welding Operations)*

The 3M™ Spark Arrest Cover GVP-146 is available for use with the 3M™ Belt-Mounted PAPR Assemblies GVP-1 and GVP-CB. It is designed for GVP users who challenge their systems in heavy grinding and welding operations. The cover is made to fit all GVP cartridges during PAPR use and helps protect the blower unit from sparks and metal slag during grinding and welding operations. The cover is made of black suede leather and is sold one per bag.



**3M™ Spark Arrest Cover GVP-146**

## Other Important Information

- Made of durable black leather suede.
- Does not affect the airflow of the GVP-100 blower.
- Works with any GVP cartridge.
- Intended use is only for the GVP-1 and GVP-CB assemblies.
- Can be used with the following belts:
  - GVP-127 web waist belt
  - CB-1000 comfort belt
- Not intended to protect the unit from fire.
- Can be applied while the GVP-100 blower is mounted on the belt.
- Not for use with the GVP-117 vinyl waist belt or GVP-119 shower cover.

For more details regarding the GVP-146, please contact your local 3M Occupational Health and Environmental Safety Division distributor or visit the 3M website ([www.3M.com/occsafety](http://www.3M.com/occsafety)).