


3M™ Acrylic Foam Tape 5356

Technical Data Sheet



Description

3M™ Acrylic Foam Tape 5356 is a 1.52 mm (0.060 in) thick, gray, double-coated acrylic foam tape used for the attachment of a variety of automotive exterior trim parts.


Product features of 3M AFT 5356 include:

- Unique foam core that provides stress relaxation when high application loads are encountered, while maintaining tight bond-line aesthetics under normal conditions.
- Bonds to a variety of automotive substrates.
- Provides high final adhesion and peel strength.

3M AFT 5356 is thicker than other acrylic foam tapes and is used where there is greater mismatch between the trim part and the sheet metal of the vehicle. The acrylic foam core has unique viscoelastic properties that allow it to elongate and relax when put under load, thereby minimizing stress on the adhesive bond line. 3M AFT 5356 has AR7 adhesive on both sides of the product for a high level of adhesion to both the automotive paint and the exterior trim part. Since product performance will depend on actual conditions within a specific application, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular material purpose and suitable for the user's method of application.

Typical applications for 3M AFT 5356 include attachment of body side moldings, claddings, roof ditch moldings, wheel flares, and tailgate appliqués.

Product Construction



Liner Options

See the technical update “[3M™ Acrylic Foam and Acrylic Plus Tapes: Product Constructions](#)” for liner and tabbing information.




Physical Properties

5356	
Thickness Range	1.52 mm ±0.15 mm (0.060 in ±0.006 in)
Density Range	688 kg/m ³ ±80 kg/m ³ (43 lb/ft ³ ±5 lb/ft ³)

Performance Properties

Typical performance of 3M™ Acrylic Foam Tape 5356 is shown below. Peel and shear values depend on plastic substrate characteristics and/or paint composition. These values are for reference only.


Breakaway and Continuous Peel

 <p>Test Bar Painted Panel</p>	72 hrs at 22°C (72°F)	Breakaway Peel	133 N/12.7 mm	(30 lbs/.5 in)
		Continuous Peel	67 N/12.7 mm	(15 lbs/.5 in)
 <p>Breakaway</p>	72 hrs at 70°C (158°F)	Breakaway Peel	155 N/12.7 mm	(35 lbs/.5 in)
		Continuous Peel	75 N/12.7 mm	(17 lbs/.5 in)
 <p>Continuous Peel</p>	72 hrs at 38°C /100% RH (100°F/100%RH)	Breakaway Peel	111 N/12.7 mm	(25 lbs/.5 in)
		Continuous Peel	58 N/12.7 mm	(13 lbs/.5 in)

Breakaway and continuous peel tests are run with 12.7 mm (0.5 in) wide tape on PVC test bars. Tests were run on base coat/clear coat paint at a separation rate of 305 mm/min (12 in/min).

Static Shear

Exceeds 100 hours at 70°C (158°F). Static shear tests are run with 12.7 mm (0.5 in) wide by 50.8 mm (2 in) long tape on PVC test bars, 6.8 kg (15 lbs) roll-down against stainless steel. Static weight is 250 gm (0.55 lbs).



Shelf Life

36 months from date of manufacture when stored at 4°C–38°C (40°F–100°F) and 0–95% relative humidity (RH). The optimum storage conditions are 22°C (72°F) and 50% relative humidity.

Regulatory Information

Please refer to the product label and Safety Data Sheet (SDS) for health and safety information before using. Observe proper handling precautions as outlined in the SDS, which is available on request or at www.3M.com/msds.

The product is published as a material entry and is available for access on www.mdssystem.com. For product IMDS I.D. number, email requests to 3M-IMDSrequest@mmm.com.

Contact Information

The information provided in this technical document is intended as a guide for this product. For more information or help in selecting a 3M product for an application, please contact your 3M technical service representative or call 1-800-328-1684.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive and Aerospace Solutions Division

3M Center
St. Paul, MN 55144-1000
1-800-328-1684
3M.com/autosolutions

3M is a trademark of 3M Company. Please recycle.
Printed in USA. © 3M 2020. All rights reserved.