3M[™] Adhesion Promoter K500

Technical Data Sheet



Description

3M[™] Adhesion Promoter K-500 is a liquid adhesion promoter used for most EPDM, polypropylene, chlorinated rubbers, ABS, AES compounds and certain PET/PBT blends. 3M Adhesion Promoter K-500 is a moisture cured system that is specifically formulated to be used with 3M™ Acrylic Foam and Acrylic Plus Tapes for automotive applications. Because substrate formulations and surface energies for these materials may vary, each application should be tested for compatibility.

Physical Properties

Components	Toluene; chlorinated polypropylene; isocyanic acid, methylene di-p-phenylene ester; isocyanic acid, polymethylene polyphenylene ester; molecular sieves
Solids	Approximately 8%
Color	Straw
Flashpoint	4.4°C (40° F)
Coverage	75 m² (800 ft²) per gallon (Based on 0.002 inch wet
	coating thickness)
Net Weight	880 grams per liter

Equipment

3M adhesion promoter K-500 can be applied by a gravity feed wipe, knurled roller, and felt-tipped applicator or other similar type applicator. Applicator heads should be cleaned or replaced regularly.

Surface Preparation

The bonding surface should be clean and dry. Contaminated surfaces should be cleaned with an appropriate solvent* such as isopropyl alcohol. Observe precautions for solvent handling.

Application

Shake well before using. Apply a thin, uniform coating of the 3M[™] Adhesion Promoter K500 to the bonding surface, using the minimum amount that will fully coat the surface. A wet coating thickness of approximately 0.002 inch (0.05 mm) or less is recommended. Although this is usually accomplished in less than one minute, allowing 10 minutes yields the ultimate adhesion. For best results apply tape within 30 minutes after application of adhesion promoter. Be sure the primed surface remains free from contaminants prior to laminating the tape.

Clean-Up

3M Adhesion Promoter K500 can be cleaned up with acetone solvents*. Vigorous scrubbing may be required.

*Note: When using solvents for cleanup, use the precautionary measures recommended in the SDS and/or label for the solvent.

Shelf Life

Shelf life is 2 years from date of manufacturing when stored in the original container. Transfer only small amounts for 8 to 12 hours of production into other vessels. Return the original tightly sealed container to storage to avoid moisture contamination. Although room temperature storage is acceptable, refrigerated storage at 1.7° to 7.2° C (35° to 45° F) is recommended.

Regulatory Information

Observe proper handling precautions as outlined in the Safety Data Sheet (SDS), which is available on request. The website address for 3M SDSs is http://www.3m.com/3M/en_US/company-us/SDS-search/.

Contact Information

The information provided in this technical document is intended as a guide for this product. For more information or help in selecting a 3M product for an application, please contact your 3M technical service representative or call 1-800-328-1684.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive & Aerospace Solutions Division 3M Center St. Paul, MN 55144-1000 Phone 1-800-328-1684 Web www.3M.com/autosolutions K500_US Issue date: 1/2019 Revision: 03

3M is a trademark of 3M Company © 3M 2019. All rights reserved.