



Science.
Applied to Life.™




3M™ Durable Labels - Quick Cuts Program

- 2-Day Precision Roll Program
- 7-Day Half Master Program
- 2-Day Pre-Slit Program

Get the speed, flexibility and service you need.

3M's Quick Cuts Service Program includes our collection of go-to durable label materials, designed to suit most applications. These products utilize both solvent and solventless adhesive technologies as well as a range of facestocks and topcoats to ensure a speedy solution to your labeling challenges.



2-Day Pre-Slit Program

- Pre-slitted stocked 6" wide rolls
- Shipped within 48 hours

Half Master Program

- 27" wide, custom-slitted rolls at 1,668 ft
- No up-charge
- Optimized for UV inkjet and flexographic printing
- Solvent and solventless portfolio offering

2-Day Precision Roll Program

- Custom-slitted widths
- No up-charge
- Roll length of 1,668 ft

Speed, flexibility and service to help you succeed.



3M's Quick Cuts Service Program offers a wide array of standard and specialty label materials in sizes to meet your requirements and deadlines.

Program Advantages:

- Less inventory – Smaller roll offerings with materials that work across a variety of print technologies
- Less waste – Purchase materials at the size you need them
- Consistent quality – Run material immediately without concern for customer return
- Robust offering – Variety of facestock types with solvent or solventless adhesives available to suit every application

Talk to your representative today and discover the exceptional speed, value and convenience of 3M Durable Labels - Quick Cuts Program. Call 1-800-328-1681 or visit 3M.com/converter.

You save time, money and effort while meeting your customers' needs more efficiently and effectively.

➤ 2-Day Precision Roll Program

- Custom-slit widths
- No up-charge
- Roll length of 1,668 ft

➤ Half Master Program

- 27" wide, custom-slit rolls at 1,668 ft
- No up-charge
- Optimized for UV inkjet and flexographic printing
- Solvent and solventless portfolio offering

➤ 2-Day Pre-Slit Program

- Pre-slit stocked 6" wide rolls
- Shipped within 48 hours

2 Day Precision

Product	SKU	Facestock	Color	Adhesive (mils)	Liners (mils)	Agency Approvals
Label Stocks						
7871	7100013219	Polyester	White, Gloss	350	55# DK	UL, CSA
7816	7100012299	Polyester	White, Gloss	310	55# DK	UL, CSA
7872	7100072952	Polyester	Platinum	350	55# DK	UL, CSA
7868	7100072949	Polyester	White, Gloss	350	55# DK	UL, CSA
7871V*	7100205443	Polyester	White, Gloss	350	55# DK	UL, CSA
7816V*	7100205444	Polyester	White, Gloss	310	55# DK	UL, CSA
7872V*	7100204071	Polyester	Platinum	350	55# DK	UL, CSA
7868V*	7100204070	Polyester	White, Gloss	350	55# DK	UL, CSA
Overlaminates						
7730FL	7100156910	Polyester	Clear, Gloss	400	PET	UL, CSA

* Optimized for analog and digital print systems!

7 Day Half Master


Product	SKU	Facestock	Color	Adhesive (mils)	Liners (mils)	Agency Approvals
Label Stocks						
7815	7100133084	Polyester	White, Matte	310	50# SC	UL, CSA
7381/7866	7100133077	Tamper Indicating	White, Gloss (VOID)	300	55# DK	UL, CSA
7818	7100156911	Polyester	Silver, Matte	310	55# DK	UL, CSA
7350/7861	7100133079	Polyester	Clear, Gloss	300	55# DK	UL, CSA
FP0862	7100133076	Polypropylene	Clear	R3500	50# SC	
FP016902	7100304015	Polypropylene	White	R3500	50# SC	
7875	7100072955	Polyester	Platinum	310	55# DK	UL, CSA
7876	7100303306	Polyester	Clear, Gloss	350	55# DK	UL, CSA
7600	7100303307	Vinyl	White, Gloss	500	43# DK	
7777	7100303308	Polypropylene	White	Permanent Acrylic	50# SC	UL, CSA
FMV02	7100303309	Tamper Indicating	Silver, Bright (VOID)	P1410	50# SC	UL, CSA
FV0322	7100303310	Vinyl	White	P1212	50# SC	UL, CSA
7776	7100072933	Polypropylene	White	310	55# DK	UL, CSA
OFM2902	7100304014	Polyester	Silver, Brushed	P1400	50# SC	UL
OFM3102	7100303304	Polyester	Clear, Gloss	P1400	50# SC	UL
7875V*	7100204072	Polyester	Platinum	310	55# DK	UL, CSA
7331V*	7100303311	Polyester	White, Gloss	300	55# DK	UL, CSA
7876V*	7100303312	Polyester	Clear, Gloss	350	55# DK	UL, CSA
7350V*	7100204069	Polyester	Clear, Gloss	300	55# DK	UL, CSA
OFM2802	7100304495	Polyester	Silver, Bright	P1400	50# SC	UL
OFM03402	7100307291	Polyester	White, Gloss	P1400	50# SC	UL
OFV0202	7100304013	Vinyl	White	P1400	50# SC	UL, CSA
Overlaminates						
7735FL	7100133078	Acrylate	Clear, UV	400	PET	UL, CSA
FM011	7100304016	Polyester	Clear, Gloss	P1212	40# SC	UL
7733FL	7100303305	Polyester	Clear, Gloss	400	PET	UL

* Optimized for analog and digital print systems!

2 Day Pre-Slit

Product	SKU	Facestock	Color	Adhesive (mils)	Liners (mils)	Agency Approvals
Label Stocks						
7613T	7000122390	Destructible Vinyl	White	350	55# DK	UL, CSA
7883	7000123332	Polyester	Silver, Matte	300	55# DK	UL, CSA
7331	7000123824	PET	White, Gloss	300	55# DK	UL, CSA
7381/7866	7100024661	Tamper Indicating	White, Gloss (VOID)	300	55# DK	UL, CSA
7880	7000123831	Polyester	White, Matte	300	55# DK	UL, CSA
7810	7000048836	PET	White, Matte	300	50# SC	UL, CSA
7818	7000028897	PET	Silver, Matte	310	55# DK	UL, CSA
7813	7000048569	PET	Silver, Matte	300	55# DK	UL, CSA
7246	7010295703	PET	White, Matte	350	40# Densified Glassine	UL
3812	7010335420	Destructible Urethane	White, Matte	350	Glassine	
3921	7000123567	Acrylate	White, Matte	150	55# DK	UL, CSA
FMV02	7100024309	Tamper Indicating	Silver, Bright (VOID)	P1410	50# SC	
FL02N	7100139317	Polycarbonate	Clear, Velvet Clear	P1212	PET	UL
7380	7000123455	Tamper Indicating	White, Matte (VOID)	300	55# DK	UL, CSA
7323	7100016684	PET	Silver, Bright	300	55# DK	UL, CSA
7815	7000028938	PET	White, Matte	310	50# SC	UL, CSA
7247	7010375556	PET	Silver, Matte	350	40# Densified Glassine	UL
7222	7000122368	PET	Silver, Matte	300	55# DK	UL, CSA
7000	7010372143	Paper	White, High Gloss	320	43# DK	
7881	7000048466	Polyester	Clear, Matte	300	55# DK	UL, CSA
7384	7000122395	Tamper Indicating PET	Silver, Bright (VOID)	300	55# DK	UL, CSA
Overlaminates						
7745FL	7000123720	Polyester	Clear, Matte	400	PET	UL, CSA

The programs to help you keep pace with customer demands.




2-Day Pre-Slit Program

- Pre-slitted stocked 6" wide rolls
- Shipped within 48 hours



Half Master Program

- 27" wide, custom-slitted rolls at 1,668 ft
- No up-charge
- Optimized for UV inkjet and flexographic printing
- Solvent and solventless portfolio offering



2-Day Precision Roll Program

- Custom-slit widths
- No up-charge
- Roll length of 1,668 ft

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Converter Markets
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000

Phone 800-422-8116
Web 3M.com/converter

Please recycle. Printed in USA © 3M 2023. All rights reserved. 3M is a trademark of 3M. Acylar is a 3M trademark for acrylic. Lexan is a registered trademark of General Electric Company. 70-0711-1360-2