



Science.
Applied to Life.™

**Make your image last and
gain customer confidence fast.**

2-Day Precision Roll Program
2-Day Pre-Slit Program
Mini-Master Program

Get the speed, flexibility and service you need.

2-Day Pre-Slit Program

- ▶ Pre-slit stocked 4.5" or 6" rolls
- ▶ Shipped within 48 hours

Mini-Master Program

- ▶ Custom-slit, full web width master rolls
- ▶ Additional up-charge
- ▶ Roll length short as 400 ft.

2-Day Precision Roll Program

- ▶ Custom-slit widths
- ▶ No up-charge
- ▶ Roll length of 1,668 ft.

← 2.5" →

Speed, flexibility and service to help you succeed.



In today's fast-paced converting marketplace, you've got to react quickly and smoothly to keep pace with your customers' changing needs. To best meet customer needs for short runs or specialized materials, you'll want more cost-effective options than a full master of label materials.

3M™ Performance Label Material Fast Track Service Programs offer a wide array of standard and specialty label materials in sizes to meet your requirements and your deadlines.

Program Advantages:

- ▶ Less inventory — less cash tied up in inventory and less inventory to manage with no need to stock multiple widths
- ▶ Less waste — buy only the material you need when you need it
- ▶ Faster turnaround — roll delivered faster to you can mean faster turnaround to your customer
- ▶ First run assurance — confidently run material for the first time without worry of quality returns from your customer
- ▶ Ships from regional locations for faster delivery

Talk to your representative today and discover the exceptional speed, value and convenience of 3M Performance Labels Fast Track Service Programs. Call 1-800-328-1681 or visit 3M.com/converter.

You save time, money and effort while meeting your customers' needs more efficiently and effectively.

▶ Minimum order for 2-Day Precision Roll Program of 2.5" x 1668'.

▶ Minimum order for Mini-Master Program starts at 400' rolls.

▶ Minimum order for 2-Day Pre-Slit Program of 4.5" or 6" pre-slit rolls.

3M.com/converter

1-800-328-1681

Type of Product	Print Method	Product #	Agency Approvals	Facestock	Adhesive (mils)	Liners (mils)	Web Width	2-Day Pre-Slit Program	Mini-Master Program*	2-Day Precision Roll Program
Two-Day**										
Polyester	Flexo, Thermal Transfer	7871	UL/CSA	.002 White Polyester Gloss TC	350 (1.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7868	UL/CSA	.002 White Polyester Gloss TC	350 (1.1)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7816	UL/CSA	.002 White Polyester Gloss TC	310 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7815	UL/CSA	.002 White Polyester Matte TC	310 (0.8)	55# DK (3.2)	54"	4.5", 6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7872	UL/CSA	.002 Matte Platinum Polyester Gloss TC	350 (1.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7818	UL/CSA	.0033 Matte Silver Polyester TC	310 (0.8)	55# DK (3.2)	54"	4.5", 6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7350/7861	UL/CSA	.002 Clear Polyester Gloss TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Dot Matrix	7880	UL	.0023 Matte White Polyester DMI TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Polyester	Flexo, Thermal Transfer	7875	UL/CSA	.002 Matte Platinum Polyester Gloss TC	310 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Vinyl	Flexo, Thermal Transfer	OFV0202	UL	.0032 Soft White Vinyl TC6	P1400 (0.9)	50# SC (3.2)	54"	6" x 1668'	✓	✓
Polypropylene	Flexo, Thermal Transfer	7776	UL	.0026 White Polypropylene T2S	310 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Overlaminates	Not applicable	FM01N	UL	.001 Clear Polyester NTC	P1212 (0.8)	.001 Clear PET	54"	6" x 1668'	✓	✓
Overlaminates	Not applicable	7730FL	UL/CSA	.001 Clear Polyester NTC	400 (0.8)	.0015 Clear PET	54"	6" x 1668'	✓	✓
Overlaminates	Not applicable	7735FL	UL/CSA	.003 Gloss Clear Acylar™	400 (0.8)	.0015 Clear PET	48"	6" x 1668'	✓	✓
Tamper-Indicate	Flexo, Thermal Transfer	7381/7866	UL	.002 White Void Polyester Gloss TC	300 (1.0)	55# DK (3.2)	54"	4.5", 6" x 1668'	✓	✓
Tamper-Indicate	Flexo, Dot Matrix	7380	UL	.0023 Matte White Void Polyester DMI TC	300 (1.0)	55# DK (3.2)	54"	6" x 1668'	✓	✓
Removable	Flexo, Thermal Transfer	FP016902	—	.0023 White Polypropylene TC2S	R3500 (0.8)	50# SC (3.2)	54"	6" x 1668'	✓	✓
Removable	Flexo, Thermal Transfer	FP0862	—	.002 Clear Polypropylene TC2S	R3500 (0.8)	50# SC (3.2)	54"	6" x 1668'	✓	✓
Sheet	Screen	7045	UL	3.2 Soft White Vinyl NTC	P1400 (0.9)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓	✓
Sheet	Screen	7908	UL/CSA	2.0 White Polyester TC	350 (1.8)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓	✓
Sheet	Screen, Flexo	7214SA	Rohs	2.0 Brushed Silver TC	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓	✓

Type of Product	Print Method	Product #	Agency Approvals	Facestock	Adhesive (mils)	Liners (mils)	Web Width	2-Day Pre-Slit Program	Mini-Master Program*
Seven-Day + Two-Day Pre-slit**									
Polyester	Flexo, Thermal Transfer	7331/7860	UL/CSA	.002 White Polyester Gloss TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	7810	UL/CSA	.0023 Matte White Polyester TC	300 (0.8)	50# SC (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	7222/7865	UL/CSA	.002 Matte Silver Polyester Gloss TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	7813	UL/CSA	.0033 Matte Silver Polyester TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	7323/7863	UL/CSA	.002 Bright Silver Polyester Gloss TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	7876	UL/CSA	.002 Clear Polyester Gloss TC	350 (1.8)	55# DK (3.2)	54"	4.5", 6" x 1668'	✓
Polyester	Flexo, Thermal Transfer	OFM2902	UL	.002 Brushed Silver Polyester TC	P1400 (0.9)	50# SC (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Dot Matrix	7883	UL/CSA	.0033 Matte Silver Polyester DMI TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Dot Matrix	7881	UL/CSA	.0023 Matte Clear Polyester DMI TC	300 (0.8)	55# DK (3.2)	54"	6" x 1668'	✓
Polyester	Flexo, Laser	7840HL	UL/CSA	.002 White Polyester Matte TC	310 (0.8)	78# CCK (4.6)	54"	6" x 1668'	✓
Polyester	Flexo, Laser	FM01961K	—	.002 White Polyester MC	F2201 (0.8)	78# CCK (4.6)	54"	9" x 1668'	✓
Polyester	Thermal Transfer	7246	UL	.0022 Matte White Polyester TT3 TC	350 (1.8)	40# DG (2.2 glassine)	54"	4.5", 6" x 1668'	✓
Polyester	Thermal Transfer	7247	UL	.0022 Matte Silver Polyester TT3 TC	350 (1.8)	40# DG (2.2 glassine)	54"	4.5", 6" x 1668'	✓
Vinyl	Flexo	FV032	UL	.0032 Soft White Vinyl TC3	P1212 (0.9)	50# SC (3.2)	54"	6" x 1668'	✓
Polypropylene	Flexo, Thermal Transfer	FP022102	—	.003 Matte White Polypropylene EDP	P1480 (1.2)	50# SC (3.2)	54"	6" x 1668'	✓
Foil	Flexo, Dot Matrix	7800	UL/CSA	.002 Silver Foil Matte TC	320 (1.7)	60# DK (3.6)	40"	6.5" x 1668'	✓
Overlaminates	Not applicable	FM011	UL	.001 Clear Polyester NTC	P1212 (0.8)	40# SC (2.5)	54"	6" x 1668'	✓
Overlaminates	Not applicable	7733FL	UL	.001 Clear UV Resistant Polyester	400 (0.8)	.0015 Clear PET	54"	6", 12.25" x 1668'	✓
Overlaminates	Flexo, Dot Matrix	7745FL	UL/CSA	.0013 Matte Clear Polyester DMI TC	400 (0.8)	.0015 Clear PET	54"	6" x 1668'	✓
Overlaminates	Not applicable	FL02N	UL	.003 Velvet Lexan® NTC	P1212 (1.0)	.001 Clear PET	54"	6" x 1668'	✓
Overlaminates	Not applicable	FV02490N	—	.005 Clear Textured Vinyl NTC	P1212 (1.0)	.001 Clear PET	54"	6" x 1668'	✓
Tamper-Indicate	Flexo, Thermal Transfer	7613T	UL/CSA	.002 Cast White Destructible Vinyl	350 (0.8)	55# DK (3.2)	48"	4.5", 6" x 1668'	✓
Tamper-Indicate	Flexo, Thermal Transfer	3812	UL/CSA	.0016 White Destructible Polyurethane	35 (1.0)	90# DK (3.5 glassine)	48"	6" x 1668'	✓
Tamper-Indicate	Flexo, Thermal Transfer	FMV02	—	.002 Bright Silver Void Polyester TC	P1410 (0.9)	50# SC (3.2)	54"	6" x 1668'	✓
Tamper-Indicate	Flexo, Thermal Transfer	FMV22	—	.002 White Void Polyester	P1410 (0.9)	50# SC (3.2)	54"	6" x 1668'	✓
Removable	Flexo	7600	UL	.0035 Soft White Vinyl Gloss TC	500 (1.0)	43# DK (2.5)	54"	6" x 1668'	✓
Removable	Flexo	FV1222	—	.0035 Soft White Vinyl TC3	R3500 (0.8)	50# SC (3.2)	54"	6" x 1668'	✓
Paper	Flexo	7000	—	60# High Gloss Paper	320 (0.9)	43# DK (2.5)	60"	6" x 1668'	✓
High Temp	Thermal Transfer	3921	UL/CSA	.002 Matte White Acrylate	150 (1.0)	55# DK (3.2)	48"	6" x 1668'	✓
Reflective	Flexo, Thermal Transfer	3929	—	.0048 Bright Silver Retro Reflective	200 (1.0)	78# CCK (4.6)	24"	6" x 150 yards	✓
Sheets	Screen	7053	—	4.0 Soft Clear Vinyl NTC	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓
Sheets	Screen	7051SA	CSA	3.8 Extend Life Vinyl NTC	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓
Sheets	Screen	7930T	UL/CSA	2.0 White Destructible TC	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓
Sheets	Screen	7037	UL	2.0 White Polyester MC	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓
Sheets	Screen	7903	UL/CSA	2.0 Bright Silver PET PT	350 (1.1)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓
Sheets	Screen	7025	UL	2.0 Bright Silver PET TC	P1400 (0.9)	90# PCK (6.7)	54"	20" x 27"/100 sheets	✓

* 2-Day service items, minimum order quantity is 250 msi (full web width required). Maximum quantity of 3 rolls 54" x 5000'.
** Two-Day and Seven-Day refer to processing time and do not include shipping time. Orders must be received by noon CST to qualify for listed processing times. Processing times start the following day on orders received after noon.



The programs to help you keep pace with customer demands.

2-Day Pre-Slit Program

- ▶ Pre-slit stocked 4.5" or 6" rolls
- ▶ Shipped within 48 hours

Mini-Master Program

- ▶ Custom-slit, full web width master rolls
- ▶ Additional up-charge
- ▶ Roll length short as 400 ft.

2-Day Precision Roll Program

- ▶ Custom-slit widths
- ▶ No up-charge
- ▶ Roll length of 1,668 ft.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Converter Markets
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000

Phone 800-422-8116
Web 3M.com/converter



Please recycle. Printed in USA © 3M 2016. All rights reserved. 3M is a trademark of 3M. Acylar is a 3M trademark for acrylic. Lexan is a registered trademark of General Electric Company. 70-0711-1360-2