

Product Description

3M™ Easy Trap Duster - sweep & dust sheets (the “Product”) is a unique floor dusting material that captures and holds debris (dirt, dust, hair, sand, glitter, etc.). The Product can be adapted to any flat mop system.

Special Features

- The dusting sheets can be used on both sides to increase your effective floor dusting area.
- The open construction of the sheet provides space for dirt and debris to be captured.
- The proprietary coating of the fibers helps capture and hold debris.
- The open construction helps reduce drag when floor dusting.
- The proprietary fibers pick up even when wet.
- Perforated rolls allow you to customize the sheet size in increments of 6 in. (152 mm).

General Use Directions

Preparation

1. Tear off the needed amount of dust sheets to cover the width of the holder.
2. Place the sheet on the floor and place the holder directly on it, or apply the sheet on the holder and then put the system on the floor. You are now ready to dust the floor.

NOTE: When the sheet no longer picks up debris, remove the cloth from the holder, flip the cloth over and reapply it to the holder. When both sides of the cloth are completely soiled, replace the cloth.



Clean-up & Disposal

Remove used dust sheet from the holder and place in an appropriate container for disposal.

Product Specifications and Packaging

3M™ Easy Trap Duster - sweep & dust sheets

5 in. wide roll	
60 sheet box	5 in. x 30 ft. (12.1 cm x 9.14 m)
250 sheets/roll (2 rolls/box)	5 in. x 125 ft. (12.1 cm x 38.1 m)
8 in. wide roll	
60 sheet box	8 in. x 30 ft. (20.32 cm x 9.14 m)
250 sheets/roll (2 rolls/box)	8 in. x 125 ft. (20.32 cm x 38.1 m)

Commercial Solutions

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-0033
3M.com/Facility

© 3M 2017. All rights reserved.

3M is a trademark of 3M. Used under license in Canada.
All other trademarks are property of their respective owners.
TD 135, April 2017 (Supercedes March 2010)
Please recycle.

