


3M™ Screen Printing UV Ink Series 9800



Designed for multi-station printing, 3M™ Screen Printing UV Ink Series 9800 provides superior image quality, consistency of color and excellent processing capability. Backed by the 3M™ MCS™ Warranty, these flexible, color-fast, ultraviolet-curable inks offer up to seven years of durability and are ideal for transportation graphics, OEM applications and non-regulated signage.

Ink Series 9800 has a gloss finish. Inks from this series are press-ready and include blending colors and four-color process, and can be used on a wide variety of 3M graphic films. The transparent inks are suitable for printing on selected 3M™ Scotchlite™ Reflective Graphic films.



3M™ Screen Printing UV Ink Series 9800

Features	Advantages	Benefits
Designed for multi-station and single-station screen printing	<ul style="list-style-type: none"> • Excellent processing capability • Ease of use 	<ul style="list-style-type: none"> • Flexibility in scheduling and managing workflow • Saves time • Reduces cost
Excellent intercoat adhesion of inks	<ul style="list-style-type: none"> • No tie coat required • No need for solvent drying equipment 	<ul style="list-style-type: none"> • Improves workflow • Reduces cost
3M™ MCS™ Warranty	<ul style="list-style-type: none"> • Most comprehensive warranty in graphics market 	<ul style="list-style-type: none"> • Total component compatibility • Superior performance • Peace of mind
Wide palette of press-ready colors	<ul style="list-style-type: none"> • Quick startup • Easily blended to obtain custom and industry standard colors 	<ul style="list-style-type: none"> • Faster workflow • Consistent colors • Meets customer needs
Fade-resistant pigments	<ul style="list-style-type: none"> • Durable graphics maintain appeal throughout service life 	<ul style="list-style-type: none"> • Confidence throughout use
Compatible with: <ul style="list-style-type: none"> • Wide variety of 3M graphic films, including our reflective films • 3M's Screenprint clears 9720UV and 9730UV • Recommended 3M application tapes 	<ul style="list-style-type: none"> • Works with existing line of 3M products • One-stop shopping • No need to stock additional inventory 	<ul style="list-style-type: none"> • Expands use of existing inventory • Simplifies purchasing process • Reduces costs • Shortens learning curve
Compatible with established color-matching software	<ul style="list-style-type: none"> • Ease of color matching 	<ul style="list-style-type: none"> • No need for additional equipment • Reduces costs • Saves time

FAB Table

Application	<ul style="list-style-type: none"> • Short-, medium- and long-term graphics
Typical uses	<ul style="list-style-type: none"> • Fleet graphics, vehicle graphics, OEM graphics, railway applications, vending and dispensing equipment, non-regulated signage
Suitable application surfaces	<ul style="list-style-type: none"> • Flat, flat with rivets, simple curves, corrugated
Graphic imaging process	<ul style="list-style-type: none"> • Multi-station or single-station screen printing
Recommended cutting methods	<ul style="list-style-type: none"> • Hot kiss, electronic (drum or flatbed), cold or hot steel-ruled die cutting, guillotine
Warranted durability	<ul style="list-style-type: none"> • Up to 7 years

Film & Application Characteristics

See Product Bulletin 9800 for complete details.



Graphics Market Center

3M Center, Building 0220-12-E-04
St. Paul, MN 55144 USA
www.3M.com/graphics
Product Info. 1-800-328-3908

3M Canada

PO Box 5757
London, Ontario
Canada N6A 4T1
1-800-265-1840

3M México S.A. de C.V.

Av. Santa Fe No. 55
Col. Santa Fe, Del. Alvaro Obregón
México D.F. 01210
52-55-52-70-04-00

3M Puerto Rico, Inc.

Puerto Rico Industrial Park
PO Box 100
Carolina, PR 00986-0100
787-620-3000