



Adapter Kit Modular Splicing System

600 A

5, 8, 15 and 25 kV Class

5815-B Series


Instructions

The 3M™ 5815-B Series Adapter Kit is designed for use with the following 3M 5815 Series Modular Splicing System kits:


- 5815-S Splicing Kit (2 adapter kits required)
- 5815-T Tap Splicing Kit
- 5815-E Equipment Kit
- 5815-D Dead End Kit

1.0 General


The 5815-B Series Adapter Kits are designed to adapt the Modular Splicing System kits to the following common industrial shielded power cables:




Tape Shield Cable



Wire Shield Cable




UniShield® Cable



Jacketed Concentric Neutral (JCN) Cable

2.0 Installation

Install Adapter Kit components according to the instructions packaged with the appropriate Modular Splicing System Kit.




5815 Tee Module with Adapter Kit Installed

3.0 Kit Contents

- Cable Adapter
- Aluminum Compressed Connector
- Cold Shrink Jacketing Tube
- Ground Braid Assembly
- Constant Force Spring
- Mastic Sealing Strips (2)
- Silicone Lubricant (2)
- CC-3 Cable Cleaning Pad Kit
- Product Information Sheet

3M is a registered trademark of 3M. UniShield® is a registered trademark of BICC Cables.

Note: The core material being removed from the Cold Shrink Tube is mixed polymers and can be recycled with other waste. 

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.

3M

Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
800/245-3573
www.3M.com/elpd



Printed on 50% recycled paper
with 10% post-consumer

Litho in USA
©3M 1999 78-8124-5358-3-B