


3M™ Stamark™ Pavement Marking Tape
Series 270



The Intersection of Safety and Durability

High-visibility glass beads, built-in reinforced netting and ease of installation capabilities make 3M™ Stamark™ Pavement Marking Tape Series 270 the durable solution for improving intersection safety.

3M

Safety. Durability. Value.

3M™ Stamark™ Pavement Marking Tape Series 270

According to the FHWA, "... half of all highway crashes and injury crashes occur at, or are related to, intersections."¹ 3M™ Stamark™ Pavement Marking Tape Series 270 can help improve intersection safety by clearly marking stop bars, crosswalks, symbols, legends and channelizing lines—for both day and night visibility.

A durable solution for intersection safety


Intersections are not only tough places for vehicles, but also a challenging application for pavement marking products. Stamark Series 270 tape is designed to resist the destructive forces at intersections with high performance materials and strong, reinforced netting embedded into the tape. It's available in both white (270) and yellow (271).

- **Superior daytime visibility.** An exceptionally white or yellow base material is protected by a tough, polyurethane topcoat to resist dirt and ensure long-lasting daytime road presence.
- **High reflectivity at night.** Stamark Series 270 tape is embedded with glass beads on a raised diamond pattern, ensuring high visibility to drivers during nighttime hours.
- **Reinforced toughness.** A durable net material is embedded deep into the tape to minimize shear and tearing.

¹FHWA Safety Program, March 2009



- **Easy application.** During the normal marking season, there's no need for surface preparation adhesives with Stamark Series 270 tape. Adhesion to properly prepared pavement surfaces above 40°F is almost as easy as unwind, apply and tamp.
- **Extended season productivity.** When applying tapes outside the normal marking season, an easy-to-use surface preparation adhesive allows you to apply Stamark Series 270 tape when temperatures are above 40°F, increasing productivity and boosting application flexibility for both agencies and contractors.
- **3M technical assistance.** As a global company with local resources, 3M is much more than just a supplier of pavement markings. Our experienced representatives and technicians can show you how to improve roadway visibility and safety, reduce long-term costs, properly apply pavement marking materials, and maintain your roadway marking projects.



This cross-section of 3M™ Stamark™ Tape Series 270 shows how 3M's advanced technologies make this tape a durable value for intersection safety.

To learn more about 3M™ Stamark™ Pavement Marking Tapes or 3M's full line of traffic safety products and services, go to 3M.com/roadwaysafety or contact your local 3M representative at 1-800-553-1380.



Traffic Safety and Security Division
3M Center, Bldg 0235-03-A-09
St. Paul, MN 55144-1000
USA
1-800-553-1380
www.3M.com/roadwaysafety

3M Canada Company
P.O. Box 5757
London, Ontario N6A 4T1
1-800-3MHELPS

3M México, S.A. de C.V.
Av. Santa Fe No. 55
Col. Santa Fe,
Del. Alvaro Obregón
México, D.F. 01210

3M and Stamark are trademarks of 3M.
Used under license in Canada.
Please recycle. Printed in U.S.A.
© 2013, 3M. All rights reserved.
75-0301-9798-4