


# Accessories for 3M™ PPS™ Paint Preparation System



Mixing Sticks - regular and mini

Lid and Liner Dispensers

Spray Gun Holder

6 Cup Carrier

Wash Bottle

## 3M™ PPS™ Product Range

Part No.	Item	items/box
<b>Standard size</b>		
16000	PPS Standard Kit, 200 micron filter (lids, liners, 24 sealing caps)	50
16026	PPS Standard Kit, 125 micron filter (lids, liners, 24 sealing caps)	50
16001	PPS Standard mixing cups and locking collars	2
<b>Large size</b>		
16024	PPS Large Kit, 200 micron filter (lids, liners, 24 sealing caps)	25
16740	PPS Large Kit, 125 micron filter (lids, liners, 24 sealing caps)	25
16023	PPS Large mixing cup and locking collar	1
<b>Mini</b>		
16114	PPS Mini Kit, 200 micron filter (lids, liners, filters, 20 sealing caps)	50
16752	PPS Mini Kit, 125 micron filter (lids, liners, filters, 20 sealing caps)	50
16113	PPS Mini Introduction Kit 200 micron filter (50 lid/liners, 2 mixing cups, lid/liner dispenser, 20 sealing caps, 2 inserts)	1
16750	PPS Mini Introduction Kit 125 micron filter (50 lid/liners, 2 mixing cups, lid/liner dispenser, 20 sealing caps, 2 inserts)	1
16115	PPS Mini Mixing Cups and locking collars	2
16066	PPS Mini Kit scale film inserts	10
<b>Refillable</b>		
16743	rPPS Kit, 200 micron filter (lids,liners)	25
16746	rPPS Introduction Kit, 200 micron filter (50 lid/liners, 2 mixing cups and collars, lid dispenser, jug)	1
16744	rPPS 125 micron Drop-in Filter	25
<b>Accessories</b>		
16019	Liner Dispenser	1
16099	Lid Dispenser	1
16010	PPS 6 Cup Carrier	1
16012	PPS Wash Bottle	5
16022	PPS Mixing Sticks - regular	25
16755	mPPS Mixing Sticks - mini	25
16025	PPS Spray Gun Holder	1

**PPS adaptors**  
a full range of PPS adaptors for most spray guns, including suction-fed and mini is available from 3M, please contact your local representative.

# 3M™ PPS™ Paint Preparation System



- Well established and trusted system for the mixing and preparation of refinish paint prior to spraying
- Innovative, award-winning design used by leading paint shops throughout the world
- Industry needs are fully met through continuous development and improvement



Automotive Aftermarket,  
3M United Kingdom PLC,  
Tel: 016 1237 6391  
Fax: 016 1237 5911  
aadenquiries.uk@mmm.com

Automotive Aftermarket,  
3M Ireland,  
Tel: (01) 280 3555  
Fax: (01) 280 3509

[www.3mbodyshop.co.uk](http://www.3mbodyshop.co.uk)

AB 616  
EL63

Printed in UK 2/06

3M, PPS and PPS logo are trademarks of 3M company © 3M 2006

**3M Innovation**



# 3M™ PPS™ Paint Preparation System

3M originated the concept of a disposable paint mixing system to eliminate the need for separate traditional spray gun mixing pots and paper filters, resulting in dramatically increased paintshop efficiency.

Today, the 3M Paint Preparation System has the ability to meet all of the painter's requirements in the preparation and application of:

- **Primer**
- **Basecoat**
- **Clearcoat**

- for both large and small repairs

## • Only one cup for mixing and spraying

## • Closed system with built-in filter

- No contamination from outside

## • Up to 70% saving in solvent

## • Quick and easy gun cleaning

- No cup cleaning
- Neck of gun is simply flushed through with cleaning fluid

## • Spray gun functions at any angle

- Paint can be sprayed at any angle for application in awkward areas such as wheel arches and engine bays
- Spray gun can also be conveniently put down should the operator need to attend to another task e.g. masking adjustment in booth

## • Lids and liners are stored in a wall-mounted dispenser

- Instant accessibility.
- Keeps components dirt-free

## • Large, flat, securely built-in filters\*

- No manual fitting of filters
- Efficient filtration
- Optimal paint flow
- Ideal for water-based products



## • Unused paint easily stored for future use\*\*



## • Full range of PPS Adapters

- PPS can be used on virtually all spray guns
- Conversion of the gun takes seconds and is a one-time requirement

# Whatever the paint preparation requirements – 3M™ has a solution

## Applicaton

## Solution

- **Small or SMART repairs**
- **Preparation of blending solvents**
- **Primer spraying**
- **Spray-out cards**

- Mini PPS** - ideal whenever a small quantity of paint (less than 170 ml) is needed
- fits to any mini or standard gun
  - smaller cup enables access to hard-to-reach areas

## Large-area priming:

**Standard PPS** - up to 650 ml of material

**Large PPS** - up to 850 ml of material

**Refillable PPS** - when mixing large volumes of primer

- a premixed jug of primer can be used to top-up rPPS, so retaining all the advantages of PPS
- economical to use

## Basecoat:

**Mini, Standard or Large PPS**

for any quantity of material up to 850 ml

**rPPS** - is the most economic option for full car resprays and PDI or fleet work, where several vehicles of the same colour are painted

## Clearcoat:

**Standard and Large PPS** - suits most applications

**Refillable PPS** - offers the efficient and economic solution for large quantities

## 3M™ PPS™ Paint Preparation System family



### Mini PPS (mPPS)

- for spraying up to 170 ml of material
- Ideal for all small and SMART repairs
- Ideal for accessing awkward areas



### Standard PPS

- for up to 650 ml
- The original size PPS
- Suits most applications



### Large PPS

- for 650 to 850 ml
- For the larger job
- Saves refilling the pot



### Refillable PPS (rPPS)

- the most economical way of handling bulk mixes

\* rPPS utilises an alternative efficient filtering system

\*\* store paint in accordance with local laws & paint manufacturer recommendations