



3M Application Profile

Market: Converters, Flexo Printing, Printers & Web Handling

Application Description: Wrapping Rollers to provide traction while also providing a non-stick surface.



Application Method

The tape is often applied to rollers in printing, converting, and other web processing by hand in various wrap patterns to give traction to the roller while also providing a non-stick surface.

Key Application Requirements

Provide traction to material passing over the roller yet also give a non-stick surface for adhesives passing over the same surface as well. Tape is conformable and can be applied to rollers in spiral wrap or other formations. Product should remove cleanly after use with a minimal amount of clean up.

Benefits/Advantages To Customer

Versatile function: Backing provides a great traction surface while also providing non-stick properties.

Durable pliable structure: Fiberglass reinforcing provides a durable and conformable product for wrapping applications.

Strong adhesion: Silicone adhesive adheres well to most surfaces and removes cleanly.

PRODUCTS

3M™ Traction Tape 5401

Process

3M™ Traction Tape 5401 is used to cover drive rollers or rollers where tension is desired in the web. Traction Tape 5401 is applied by hand to the roller in various wrapping formations to achieve the desired result.

SIC Code

2671, 2673, 2674, 2679, 2759, 2796, 3069, 3081, 3555, 2656, 2657, 2752, 2754, 2672, 2653 and others

Key Decision Makers

Shop Foreman
Plant Manager
Press Foreman
Shift Supervisor
Machine Operators

For Additional Information

To request additional product information or to arrange for sales assistance, call 1-800-362-3550. Address correspondence to: 3M Industrial Business Customer Response Center, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55106. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. **3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence, or strict liability.



Industrial and Transportation Business
Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55106

Printed in USA
FpConvWrapRoll.pdf
© 3M 2006