



3M Commercial Graphics
3M™ Controltac™ Graphic Film 180



Product range includes: 180, 180C, 180Cv2,
IJ180, IJ180C, RG180, RG180C, 8620, 8620C

- Providing premium graphics for vehicles, interior and exterior signs and displays
- Positionable adhesive for ease of use
- Available in a variety of colours, and can be custom colour matched to your requirements

3M



Faster, easier applications

3M™ Controltac™ Graphic Marking Films are a range of high quality removable, cast films, providing long term durability for all your fleet and signage.

The application of large format graphics is made easier by the combination of 3M's Controltac, positionable adhesive and Comply performance to aid fast, bubble-free applications.

- High gloss, 2 mil cast film for high quality graphics
- Pigmented adhesive provides excellent hiding power*
- Can be used on irregular surfaces such as rivets and corrugations
- Provides dimensional stability – no shrinkage
- No adhesive curing time necessary – minimising vehicle off-road time
- Excellent finish, no edge lifting or cracking
- Removable with heat and/or chemicals
- Performs under a wide range of temperatures



* Please refer to product bulletin for further information on adhesive colour and Comply performance availability.



3M Europe S.A./N.V.
Commercial Graphics
 Hermeslaan 7
 1831 Diegem, Belgium
www.3M.eu/graphicsolutions

Please recycle. Printed in Germany
 © 3M 2010. All rights reserved.

3M™ Controltac™ Adhesive

- Repositionability if you don't get it right the first time
- Excellent initial adhesion assists in compound curves

3M™ Comply™ Performance Adhesive

- Air release channels eliminate bubbles and reduce wrinkling
- No visible channel pattern with 3M's second generation Comply performance adhesive



Applications and uses include:

- Car wrapping
- Vehicle livery and graphics for HGVs and LCVs
- Exterior and interior signs and displays

For more details please see our product information at www.3M.eu/graphicsolutions or contact your 3M distributor.

