


# Get More Of What You Want

## Products

### **3M™ Automix™ Heavy-Bodied Seam Sealer, PN 08308**

- Two-part epoxy, heavy-body seam sealer for use in vertical or horizontal seams to match OEM sealers.
- Excellent tooling properties.
- No shrinkage.
- Beads will remain in the same size and shape as extruded.
- Fast paint over times.
- Will cure to a smooth and hard finish in less than one hour.



**Heavy-Bodied** PN 08308

### **NEW!** 3M™ Duramix™ Factory Match Seam Sealer, PN 08323


- Use to duplicate factory doorskin seams.
- Flows slightly and softens on the edges, without tooling, giving a rounded appearance as if applied at the factory



**Factory Match** PN 08323

### **NEW!** 3M™ Duramix™ Controlled Flow Seam Sealer, PN 08329


- Excellent for sloping areas
- Will run approximately 1 1/2 to 2 inches when applied at a 45 degree angle.



**Controlled Flow** PN 08329

### **3M™ Automix™ Self-Leveling Seam Sealer, PN 08307**

- Fast cure-through
- Self-leveling for fast, effortless, smooth seams
- Paintable in 30 minutes to increase productivity
- Apply directly over primed metal - matches OEM seams
- Flexible over a wide range of temperatures
- No shrinkage, cracking or outgassing
- Work time = Approximately 15 minutes
- Paintable = 30 minutes



**Self-Leveling** PN 08307



## 3M™ 200 mL Line of Body Repair Products

### Metal Repair

#### Bonding

- 08115 3M™ Automix™ Panel Bonding Adhesive
- 08116 3M™ Automix™ Panel Bonding Adhesive
- 08229 3M™ Automix™ Door Skin Bonding Adhesive

### SMC/FRP Repair

#### Bonding

- 08219 3M™ Automix™ SMC/Fiberglass Panel Adhesive
- 08227 3M™ Automix™ SMC/Fiberglass Repair Adhesive
- 08243 3M™ Automix™ SMC/Fiberglass Repair Adhesive

#### Cosmetic

- 05885 3M™ Automix™ EZ Sand Rigid Parts Repair

### Plastic Repair

#### Bonding

- 04240 3M™ Duramix™ Plastic Repair Semi-Rigid
- 04247 3M™ Duramix™ Super Fast Plastic Repair Adhesive

#### Cosmetic

- 05887 3M™ Automix™ EZ Sand Flexible Parts Repair
- 08235 3M™ Automix™ Semi-Rigid Parts Repair
- 08237 3M™ Automix™ Semi-Rigid Parts Repair
- 08239 3M™ Automix™ TPO Plastic Parts Repair

### Sealers

#### Two Part

- 08307 3M™ Automix™ Self-Leveling Seam Sealer
- 08308 3M™ Automix™ Heavy-Bodied Seam Sealer
- 08323 3M™ Duramix™ Factory Match Seam Sealer
- 08329 3M™ Duramix™ Controlled-Flow Seam Sealer

### Foams

#### Flexible

- 04274 3M™ Duramix™ NVH Damping Material
- 08463 3M™ Automix™ Flexible Foam

#### Rigid

- 08458 3M™ Automix™ Pillar Foam

### Adhesive

#### General Purpose

- 08214 3M™ Duramix™ Universal Adhesive
- 08217 3M™ Automix™ Universal Adhesive Clear
- 08223 3M™ Automix™ Universal Adhesive Black

### Accessories

#### Applicators

- 08571 3M™ Manual Applicator Gun
- 08117 MixPac® Manual Applicator Gun
- 09930 MixPac® Pneumatic Applicator Gun

#### Nozzles

- 08193 3M™ Automix™ Mixing Nozzle - 3/8 in
- 08200 3M™ Automix™ OEM Seam Sealer Tip Kit
- 08201 3M™ Automix™ OEM Seam Sealer Tip 1/4" Rounded
- 08202 3M™ Automix™ OEM Seam Sealer Tip 3/8" Rounded
- 08203 3M™ Automix™ OEM Seam Sealer Tip 1/2" Rounded
- 08204 3M™ Automix™ OEM Seam Sealer Tip 3/8" Flat
- 08205 3M™ Automix™ OEM Seam Sealer Tip 3/8" Double Rounded

#### Organization

- 02530 3M™ Automix™ Shop Rack