


3M Automotive
3M™ Acrylic *Plus* Tape Series EX4000



Unique Solutions

Exterior Attachment Tape

Designed to meet the unique challenges of automotive manufacturers and their suppliers, 3M™ Acrylic *Plus* Tape Series EX4000 represents the latest advancement in exterior attachment tapes. Utilizing advanced technology, 3M Series EX4000 tape is designed to adhere to a wide variety of paint systems, including low surface energy and improved scratch- and mar-resistant paints. It incorporates a unique core that allows for stress relaxation when high stress loads are encountered and maintains bondline aesthetics under normal stress loads.

3M Series EX4000 tape is like no other exterior attachment currently on the market, offering a much-needed solution for the automotive industry.




Partnering to Solve Your Exterior Attachment Needs

3M™ Acrylic *Plus* Tape Series EX4000

offers an exterior attachment solution that is:

- **Compatible** - Engineered by 3M's expert scientists, 3M Series EX4000 tape meets the demands of new automotive paint systems used by many automotive manufacturers.
- **Versatile** - 3M Series EX4000 tape provides robust adhesion to a wide variety of paint systems and withstands a significant amount of stress.
- **Flexible** - 3M Series EX4000 tape is less sensitive to cold temperatures, making it suitable for a "just-in-time" delivery model at OEM assembly plants.
- **Aesthetically pleasing** - The black color of 3M Series EX4000 tape is inconspicuous, ensuring higher levels of satisfaction among consumers.



3M™ Acrylic *Plus* Tape Series EX4000 is like no other exterior attachment currently on the market, offering a much-needed solution for the automotive industry.

Key Questions

In addition to distinct product features, customers also benefit from 3M's unparalleled customer service and technical support. Superior service, combined with more than 90 years of expertise in the automotive industry, gives OEMs and automotive suppliers confidence in purchasing from 3M.

How can I purchase 3M Series EX4000 tape?

It can be purchased by contacting your 3M sales representative or by calling 3M Automotive customer service at 1-800-328-3081.

Are product samples available?

Product samples are available through 3M Automotive customer service.

Which liners are available for 3M Series EX4000 tape?

Two liners are available: standard KL2 red liner and special tabbable T version liner.

Contact Us

For more information, please contact your 3M sales representative or 3M Automotive customer service at 1-800-328-3081. You can also visit our website at www.3M.com/autosolutions.



Automotive Division

3M Center, Bldg. 223-1S-02
St. Paul, MN 55144-1000
www.3M.com/autosolutions

Please recycle. Printed in U.S.A.
© 3M 2007. All rights reserved.
75-3470-8833-0

3M is a trademark of 3M Company.