

Seam Sealer Tip Kit PN 08200

Reproduces Many OEM Seam Sealer Beads

- A versatile assortment of five different tips that reproduce many OEM seam sealer beads used on today's automobiles
- Saves time, labor and costly redos while trying to reproduce the factory OEM seams
- For use with 3M™ Automix™ Mixer Tip (PN 08193)
- Kit Contains: 1 Box of PN 08201, 08202, 08203, 08204, 08205 (each box contains six tips)
- Use 3M™ Automix™ OEM Seam Sealer Appearance Tips with Heavy-Bodied Seam Sealers from 3M to match factory applied beads. (3M™ Automix™ Heavy-Bodied Seam Sealers, PN08308 and PN08310 sold separately).



| PN | Description | Kit Includes | Kits/Case |
|-------|--------------------------------------|-----------------------------------|-----------|
| 08200 | 3M™ Automix™ OEM Seam Sealer Tip Kit | 08201, 08202, 08203, 08204, 08205 | 6 |

| PN | Description | Tips/Bag | Bags/Case |
|-------|--|----------|-----------|
| 08201 | 3M™ Automix™ 1/4" Rounded OEM Seam Sealer Tip | 6 | 6 |
| 08202 | 3M™ Automix™ 3/8" Rounded OEM Seam Sealer Tip | 6 | 6 |
| 08203 | 3M™ Automix™ 1/2" Rounded OEM Seam Sealer Tip | 6 | 6 |
| 08204 | 3M™ Automix™ 3/8" Flat OEM Seam Sealer Tip | 6 | 6 |
| 08205 | 3M™ Automix™ 3/8" Double-Rounded OEM Seam Sealer Tip | 6 | 6 |

| PN | Description | Size | Items/Case |
|--------|---|-------|------------|
| 08308 | 3M™ Automix™ Heavy-Bodied Seam Sealer | 200mL | 6 |
| 08310* | 3M™ Automix™ Heavy-Bodied Seam Sealer - Beige | 200mL | 6 |



* Available in 2008





3M™ Ultrapro™ OEM Seam Sealer Appearance Tip Adapter, PN08206

- Allows the use of the PN08200 3M™ Automix™ OEM Seam Sealer Tip Kit with single component Flex Pack style seam sealers.
- For use with 3M™ Ultrapro™ Urethane Seam Sealers (PN08360, PN08361, PN08364*) and 3M™ Ultrapro™ MSP Seam Sealers (PN08369, PN08370).



3M™ Automix™ OEM Seam Sealer Tip Kit, PN 08200

- A versatile assortment of five different tips that reproduce many OEM seam sealer beads used on today's automobiles
- Helps save time, labor and costly redos while trying to reproduce the factory OEM seams

* Available in 2008



**Automotive
Aftermarket Division**
3M Center
Building 223-6N-01
St. Paul, MN 55144-1000
U.S.A.
www.3M.com/automotive

Please recycle. Printed in U.S.A.
3M and Automix are trademarks of 3M.
© 3M 2007. All rights reserved.
60-4401-0235-2