

# 3M

# Scotch-Weld™

## High Temperature Instant Adhesives

### HT40 • HT700

**Technical Data**

**March, 2010**

---

**Product Description**

3M™ Scotch-Weld™ High Temperature Instant Adhesives provide superior performance for demanding applications where high temperatures, thermal cycling, or shock resistance is required.

---

**Specific Features**

- 3M™ Scotch-Weld™ High Temperature Instant Adhesive HT40 is a low viscosity high temperature resistant toughened cyanoacrylate that works well with close-fitting parts.
- 3M™ Scotch-Weld™ High Temperature Instant Adhesive HT700 is a medium viscosity high temperature resistant toughened cyanoacrylate that has some gap-filling capabilities.

# 3M™ Scotch-Weld™ High Temperature Instant Adhesives HT40 • HT700

## Typical Uncured Physical Properties

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	3M™ Scotch-Weld™ High Temperature Instant Adhesives	
	HT40	HT700
<b>Color</b>	Clear	Clear
<b>Base</b>	Ethyl Hybrid	Ethyl Hybrid
<b>Appearance</b>	Liquid	Liquid
<b>Specific Gravity (g/ml)</b>	1.05	1.05
<b>Viscosity (cps)</b>	30 - 50 <sup>1</sup>	700 - 900 <sup>2</sup>
<b>Time to Handling Strength (sec)</b>	5 - 20	15 - 40
<b>Full Cure Time (hr)</b>	24	24

<sup>1</sup> U-Tube E40 - E43.

<sup>2</sup> Brookfield LVF Spindle #2 @ 30 rpm.

## Typical Cured Properties

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	3M™ Scotch-Weld™ High Temperature Instant Adhesives	
	HT40	HT700
<b>Constant Temperature Range (°F)</b>	-65 to 223	-65 to 223
<b>Intermittent Temperature Range (°F)</b>	-65 to 250	-65 to 250
<b>Gap Fill (in)</b>	0.004	0.007

# 3M™ Scotch-Weld™ High Temperature Instant Adhesives HT40 • HT700

---

## Handling Information

### Surface Preparation

For optimum strength structural bonds, paint, oxide films, oils, dust, mold release agents, and all other surface contaminants must be completely removed. However, the amount of surface preparation depends on the required bond strength and the environmental aging resistance desired by the user. Typical quick surface preparation would include wiping with a clean solvent (such as isopropyl alcohol\*), abrading the surface with a clean fine abrasive, and then wiping again with a clean solvent to remove loose particles.

### Directions for Use

1. Ensure that parts are clean, dry, and free from oil and grease.
2. An instant adhesive activator may be required if there are bonding gaps or porous substrate surfaces, if substrates are low surface energy plastics (e.g., polyethylene, polypropylene) or if substrates have acidic surfaces (e.g., paper, leather).
3. Bond speed is typically very fast so ensure that parts are properly aligned before dispensing.
4. Product is normally hand applied from the bottle. Apply sparingly to one surface and press parts firmly together until handling strength is achieved. As a general rule, as little cyanoacrylate as possible should be used. Over application will result in slower cure speed and lower bond strength.

### Cured Bond Characteristics

1. Full bond strength will typically be achieved within a 24 hour cure time.
2. Low humidity or low temperature conditions will slow down the cure rate.
3. After curing, 3M™ Scotch-Weld™ High Temperature Instant Adhesive bonds are suitable for use at about 220°F (104°C) continuously, intermittently up to 250°F (121°C). At 220°F (104°C) the bond will be approximately 40% of the strength at room temperature.
4. Cyanoacrylate bond resistance to most oils and solvents is excellent. Long term humidity, moisture, or water immersion may affect the strength of a cured cyanoacrylate bond depending on the substrates and the bond gap. Testing is recommended to evaluate the effect.

**\*Note:** When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

---

## Storage

For short term storage (<30 days), keep adhesive in a cool (60°F to 80°F [16°C to 27°C]), dry place out of direct sunlight. Keep containers tightly covered and free of moisture. Refrigeration (40°F [4°C]) gives optimum long term storage stability.

---

## Shelf Life

3M™ Scotch-Weld™ High Temperature Instant Adhesives can be expected to have a shelf life of one year from the date of shipment from 3M when stored under refrigerated conditions.

# 3M™ Scotch-Weld™ High Temperature Instant Adhesives HT40 • HT700

---

## Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

---

## Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

## Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

## Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

## Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

**ISO 9001:2000**

This product was manufactured under a quality system registered to ISO 9001:2000 standards.



### Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/industrial



*Recycled Paper*  
40% pre-consumer  
10% post-consumer

3M and Scotch-Weld are trademarks of 3M Company.  
Printed in U.S.A.  
©3M 2010 78-9236-7150-3 (3/10)